

3M™ Polyurethane Protective Tape 8663HS

Technical Data Sheet

Product Description

3M™ Polyurethane Protective Tape 8663HS is made from a polyurethane elastomer that resists punctures, tearing, abrasion erosion and ultraviolet light. 3M 8663HS Tape provides a simple, easy method of protecting a surface from corrosion, abrasion and minor impact damage. It can be installed in a minimum amount of time with simple tools. It can be painted or applied over painted surfaces. 3M 8663HS Tape is constricted with a long aging, solvent-resistant, pressure sensitive acrylic adhesive that is protected with an easy-to-release poly liner. 3M 8663HS Tape is available in transparent or matte black color.

3M 8663HS Tape is available in two liner configurations:

1. Single poly line on the adhesive side
2. Single skip-slit poly liner on the adhesive side. Skip-slit liners are cut into narrow strips to enable easy installation.

Typical Physical Properties and Performance Characteristics

1. The following technical information and data should be considered repetitive of typical only and should not be used for specification purposes.
2. ASTM = American Society of Testing and Materials.
3. Metric values are listed in parenthesis.

Dimensions

Approximate applied Thickness*	0.016 inch (0.40 mm) Film 0.002 inch (0.05 mm) Adhesive Total Thickness 0.018 inch (0.45 mm)
Standard Roll Length	36 yd (32.9 m)
Available Widths	Minimum ½ inch Maximum 24 inches (1.25 cm to 61 cm)
Approximate Weight*	1.04 lb/yd ² (517 g/m ²)

* Excludes the polyethylene liner that is removed from the tape prior to application.

Typical Physical Properties and Performance Characteristics:

Property	Test Method	Units U.S. (SI)	Typical Value
Tensile Strength @ Break	ASTM D412	lb/in (N/100 mm)	117 (2,049)
Hardness	ASTM D2240	Shore A	80
Elongation % @ Break	ASTM D882	%	400
Peel Adhesion @ 70°F (21°C) to: Anodized, Alclad Aluminum Glossy Polyurethane Paint Mil-P-27733 Epoxy Primer 304 Brite #7 Stainless Steel	ASTM D-3330, 24 hr dwell	oz/in (N/100 mm)	110 (120) 45 (49) 110 (120) 60 (66)
Max. Service Temperature		°F (°C)	180°F (82°C)

General Information

- 3M™ Polyurethane Protective Tape has weather resistance properties and has been used to isolate and protect substrates from environmental damage and corrosive elements.
- Polyurethane Protective Tape may be painted per 3M Technical Bulletin, Polyurethane Protective Tape, Painting instructions

Shipping and Storage

No special/hazardous labeling or packaging required and no regulations for air, ground or water shipment for this product.

Keep film in clean area, away from excessive moisture and out of direct sunlight. Store rolls in the shipping carton. Return partially used rolls to shipping carton.

Shelf Life: Two (2) years from date of manufacture or as expressly certified by 3M.

Additional Information

In the U.S. call toll free 1-800-235-2376, or fax 1-800-435-3082 or 651-737-2171. For U.S. Military, call 1-866-556-5714. If you are outside of the U.S., please contact your nearest 3M representative.

These products were manufactured under a 3M Quality Management System registered to the AS9100 standard

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information. **Product Selection and Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. **Warranty, Limited Remedy, and Disclaimer:** Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Automotive & Aerospace Solutions Division
3M Center
St. Paul, MN 55144-1000
Phone 1-800-328-1684
Web www.3M.com/aerospace

8663HS
Issue date: 3/2025

3M is a trademark of 3M Company
© 3M 2025. All rights reserved.