## **Product Description**

3M<sup>™</sup> Low Outgassing Removable Label Material 5771 and 5771NF with 3M<sup>™</sup> Adhesive 550 provides stable adhesion that builds moderately without degrading over time and provides excellent adhesion for attachment to a wide variety of surfaces.

### **Product Construction**

(Calipers are nominal values.)

Product	Facestock	Adhesive	Liner
3M Label Material 5771	2.0 mils (51 microns) Gloss white polyster	0.8 mil (20 microns) 550 High Stability Acrylic	3.2 mils (81 microns) 55# Super calendared kraft – Easy-release
3M Label Material 5771NF	2.0 mils (51 microns) Gloss white polyster	0.8 mil (20 microns) 550 High Stability Acrylic	1.9 mils (48 microns) PET Non-silicone

### **Features**

- Labels remove cleanly and in one piece from most metal and high energy plastics.
- Facestock is topcoated for thermal transfer printing, and is also suitable for press printing.
- UL recognized (File MH16411) and CSA accepted (File 99316).

## **Application Ideas\***

- Identification of hard disk drive and its components.
- Bar Code labels and rating plates.
- Property identification and asset labeling.
- Warning, instruction, and service labels for durable goods.
- Nameplates for durable goods.



<sup>\*</sup>Before using this product for a specific application, you must evaluate it and determine if it is suitable for your application.

## **Typical Physical Properties**

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

**Adhesion:** 180° peel, test procedure is ASTM D 3330: 12 in./min.

Product	3M <sup>™</sup> Adhesive	Surface	Initial (20 Minute Dwell/RT) 180° peel	72 Hours at RT 72°F (22°C) 180° peel	72 Hours at 90°F (32°C) and 90% RH 180° peel
3M <sup>™</sup> Low Outgassing Removable Label Material			Oz./In.	Oz./In.	Oz./In.
3M Label Material 5771	550	Stainless Steel	27	35	36
3M Label Material 5771NF	550	Stainless Steel	18	34	39

Removability: Visual Inspection

All of the samples used to generate the adhesion values above showed no evidence of adhesive transfer to the test surface.

Liner Release: 180° Removal of Liner from Facestock.

Rate of removal 90 inches/minute.

ASTM D 3330 / TM-2033

Product	Initial 72 Hours @ Room Temperature g/in width	72 Hours @ 90°F (32°C) and 90% RH g/in width
3M™ Low Outgassing Removable Label Material		
3M Label Material 5771	4.1	6.9
3M Label Material 5771NF	6.1	7.4

#### **Shear Adhesion:**

ASTM D-3657 / TM-107

1/2" x 1" overlap, minutes to failure.

	3M™ Low Outgassing Removable Label Material 5771	3M™ Low Outgassing Removable Label Material 5771NF
Room Temperature 1000 grams, stainless steel	>10,000	>10,000

#### **Environmental Performance**

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

The properties defined are based on four hour immersions at room temperature (72°F/22°C) unless otherwise noted. Samples were applied to stainless steel panels 24 hours prior to immersion and were evaluated one hour after removal from the solution for peel adhesion.

#### **Chemical Resistance:**

Chemical	Appearance
Isopropyl Alcohol*	No change
Detergent (1% ALCONOX®*)	No change
Engine Oil (10W30) @ 250°F (121°C)	No change
Water for 48 hours	Slightly cloudy

#### **Temperature Resistance:**

250°F (121°C) for 72 hours:	No change

<sup>\*</sup>Note: When using solvents, read and follow the manufacturer's precautions and directions for use.

## **Processing**

#### **Printing:**

Facestock is topcoated for improved ink receptivity and is designed for thermal transfer printing. It is printable by all standard roll processing methods including flexography, hot stamp, letterpress, and screen printing. Refer to the Graphic Ink Selection Guide or call 3M Customer Service at 1-800-223-7427 for additional information.

#### **Die Cutting:**

Rotary die cutting is recommended.

#### Packaging:

Finished labels should be stored in plastic bags.

## **Application Techniques**

For maximum bond strength, the surface should be clean and dry. Typical cleaning solvents are heptane and isopropyl alcohol.\*

\*Note: When using solvents, read and follow the manufacturer's precautions and directions for use.

For best bonding conditions, application surface should be at room temperature or higher. Low temperature surfaces, below 50°F (10°C), can cause the adhesive to become so firm that it will not develop maximum contact with the substrate. Higher initial bonds can be achieved through increased rubdown pressure.

## Storage

Store at room temperature conditions of 72°F (22°C) and 50% relative humidity.

### Shelf Life

If stored under proper conditions, product retains its performance and properties for two years from date of manufacture.

## Certification/Recognition

MSDS: 3M has not prepared a MSDS for this product which is not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the product should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards.

**TSCA:** This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements.

**RoHs Complaint/REACH Compliant:** This product complies with the European Union's "Restriction of Hazardous Substances" (RoHs) initiative and with European REACH regulations 2002/95/EC and 2005/618/EC.

#### For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-251-8634. Address correspondence to: 3M, Electronics Markets Materials Division, 3M Center, Building 225-3S-06, St. Paul, MN 55144-1000. Our fax number is 651-778-4244 or 1-877-369-2923. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

## Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

## Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER** WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.







