

Particulate Respirator 8200, N95

Issue Date 11/27/07

An Economical Solution for Particulate Exposure.

The basic features and lightweight construction of the 8200 make it an economical choice for a variety of applications where exposure to particles may be a concern.


Product Features

- **Two-strap design** with dual point attachment helps provide a secure fit.
- **Adjustable noseclip** reduces eyewear fogging and helps ensure a better seal and fit.
- **Lightweight construction** enhances worker comfort and wear time.
- **Proprietary filter media** with advanced electrostatically charged microfibers help make breathing easier for enhanced user comfort.
- Meets NIOSH 42 CFR 84 N95 requirements. TC-84A-4271.



3M™ Particulate Respirator 8200, N95

3M Value vs. Competitors*



Question: Considering the quality of 3M's/Competitor's products, the services provided by 3M/Competitor and 3M's/Competitor's prices, how would you rate the overall value of 3M's/Competitor's products and services?

Suggested Applications

- Bagging
- Grinding
- Sanding
- Sawing
- Sweeping
- Woodworking
- Other dusty applications



For additional information on 3M use recommendations for this class of respirators, please consult the 3M™ Respirator Selection Guide found at www.3M.com/OccSafety.

* Based on a research study done for 3M by Burke Inc. August 2004 of safety officers and users from 89 companies that use both 3M and competitive disposable respirators.

Ordering Information

Product #/UPC/Stock #	Description/Packaging
8200 5 00 51131 919131 70-0712-8805-7	Particulate Respirator N95 20 Respirators/Box 8 Boxes/Case = 160 Each

3M facilitates convenient products and services that can help you achieve regulatory compliance. Our services are based on certain OSHA regulatory compliance requirements, including on-site fit testing and customized Respiratory Protection e-Tools to help optimize your compliance testing.

• Respirator Medical Evaluation:

- On-line
- Mail-In

• Respirator Fit Testing:

- Qualitative
- Quantitative

www.respexam.com

⚠ WARNING	
	<p>These respirators help reduce exposure to certain airborne contaminants. Misuse may result in sickness or death. Before use, the wearer must read and understand <i>User Instructions</i> provided as a part of product packaging. Time use limitations may apply. For proper use, see supervisor, packaging or call 3M OH&ESD Technical Service, call 1-800-243-4630. In Canada, call 1-800-267-4414 or 1-800-265-1840, ext. 6137.</p> <p>Each respirator must be properly selected based on the contaminant and concentration levels to which the worker is exposed. Particulate respirator 8200 may be used for exposures below 10X the PEL or applicable government occupational exposure limits, whichever is lower.</p> <p>Failure to follow the use and fitting instructions and warnings for proper use contained on the respirator packaging and/or failure to wear the respirator during all times of exposure can reduce respirator effectiveness and may result in sickness or death.</p>

<p>For more information, please contact:</p> <p>3M Occupational Health and Environmental Safety Division (OH&ESD)</p> <p>In the U.S., contact:</p> <p>Sales Assistance 1-800-896-4223</p> <p>Technical Assistance 1-800-243-4630</p> <p>Fax On Demand 1-800-646-1655</p> <p>Website http://www.3M.com/OccSafety</p> <p>For other 3M products 1-800-3M HELPS</p> <p>In Canada, contact: 3M Canada Company, OH&ESD P.O. Box 5757 London, Ontario N6A 4T1</p> <p>Sales Assistance 1-800-265-1840, ext. 6137</p> <p>Technical Assistance (Canada only) 1-800-267-4414</p> <p>Fax On Demand 1-800-646-1655</p> <p>Website http://www.3M.com/CA/OccSafety</p> <p>Technical Assistance In Mexico 01-800-712-0646 5270-2255, 5270-2119 (Mexico City only)</p> <p>Technical Assistance In Brazil 0800-132333</p> <p>Fax On Demand O.U.S. Locations 1-651-732-6530</p>

3M Occupational Health and Environmental Safety Division
3M Center, Building 235-2W-70
St. Paul, MN 55144-1000