



Science.
Applied to Life.™

Nothing but the best.

Reliable 3M building supplies in one catalog.

3M Building and Construction Market


Whether construction, renovation, demolition or clean-up, take 3M's proven performers with you.

This catalog is a combination of our top-sellers, new products, and proven performers for construction applications, including:

- ▶ Below-grade waterproofing
- ▶ Electrical insulating, sealing, padding, bundling, repair, and shaping
- ▶ Firestopping through-penetrations, wrap systems, and construction joints
- ▶ Protecting mechanical duct and pipe
- ▶ Sanding, grinding, and blending jobsite materials
- ▶ Sealing expansion joints and moisture barriers
- ▶ Seaming metal and flexible ducts
- ▶ Tilt-up concrete construction

For Customer Service, call:

1-866-513-4026



Reliable products that help you get the job done faster.



Abrasives

Cloth Belts.....	3
Cloth Roll.....	4
Cut & Grind Wheels	4
Cut-off Wheels	5
Depressed Center Grinding Wheels	6
Fibre Discs	7–8
Film Discs	8–9
Flap Discs	10
Paper Discs	11
Hand Pads	12
Sanding & Surface Restoration/Repair... 12	
Surface Conditioning Belts.....	13
Surface Conditioning Discs	14–15
Utility Cloth Rolls	16
Utility Cloth Sheets	17



Adhesives

Aerosol Adhesives	19
Cylinder Adhesives	20
Cylinder Accessories.....	20
Adhesive Removers	21
Polyurethane Sealants.....	21



Air Filtration

Air Filters.....	23
------------------	----



Electrical

Electrical Tapes	25–26
Direct Bury Kits	26
Standard Cable Ties	26
Wire Connectors	27



Fire Protection

Fire Barrier Foams	29
Fire Barrier Hard Goods	29–32
Fire Barrier Tapes.....	33
Sealants & Sprays.....	33–35
Wraps	35



Safety

Disposable Respirators	37
Reuseable Respirators	37–38
Cartridges and Filters.....	38
Eye Protection.....	39–40
Head Protection	41–42
Hearing Protection.....	42–43
Powered & Supplied Air	44
Protective Coveralls	44
Work Gloves.....	45
Safety Warnings.....	45



Tapes

Aluminum Foil Tapes	47
Box Sealing Tapes & Accessories	47
Duct Tapes	48–49
Filament Tapes	50
Flashing & Seaming Tapes	50
Flatback Tape	51
Flexible Duct Closure Tapes.....	51
HVAC Foil Tapes	51
HVAC Tapes	52
Insulation Jacketing Tapes.....	52
Insulation Seaming Tapes.....	53
Masking Films	54
Masking Film Accessories	54
Masking Tapes	55–56
Metal Building Tapes	57



Water Filtration

Under-Sink Filters & Cartridges.....	59
Whole House Systems.....	60
Commercial Filtration	61



Abrasives



Cloth Belts

3M™ Cubitron™ II Cloth Belt 784F

Features 3M Precision Shaped Grain for longer life and a faster, more consistent cut than conventional ceramic aluminum oxide belts. A precise mix of shaped ceramic and premium aluminum oxide delivers optimal cut in medium-pressure grinding and blending applications. The belt also features a waterproof backing and grinding aid.



Material ID	UPC	Grade/ Backing		W x L	Belt/ Case
7010512394	N/A	50+	YF	3" x 132"	25
7100119295	N/A	60+	YF	¾" x 18"	200
7100122769	5-00-76308- 45556 -4			½" x 24"	
7010299100	5-00-76308- 45557 -1			2" x 72"	50
7010512518	N/A			2" x 132"	
7100128758	5-00-76308- 45562 -5	80+	YF	¾" x 18"	200
7100119302	5-00-76308- 45563 -2			½" x 18"	
7100128757	5-00-76308- 45565 -6			½" x 24"	50
7010512285	N/A			2" x 132"	
7100122889	5-00-76308- 45566 -3	120+	YF	6" x 48"	20
7010308701	5-00-76308- 45568 -7			½" x 24"	200
7010362614	5-00-76308- 45572 -4			¾" x 18"	



3M™ Cubitron™ II Cloth Belt 984F

A revolutionary performance with 3M Precision Shaped Grain on a YF-weight polyester cloth backing. This high-performing belt contains a grinding aid, making it ideal for medium to high pressure applications on stainless steel and other exotic alloys, along with carbon steel, cobalt chrome, and nickel alloys.



Material ID	UPC	Grade/ Backing		W x L	Belt/ Case
7000045139	5-00-51141- 27511 -1	36+	YF	½" x 18"	200
7100020236	5-00-51141- 55064 -5			¾" x 18"	
7000119525	5-00-51141- 55068 -3			2" x 60"	50
7000119191	5-00-51141- 27516 -6			2" x 72"	
7100010397	5-00-51141- 27461 -9			3" x 132"	25
7000119181	5-00-51141- 27462 -6			4" x 132"	
7100076951	5-00-51141- 55071 -3	60+	YF	6" x 48"	20
7000144125	5-00-51141- 55032 -4			¼" x 24"	200
7000119511	5-00-51141- 55041 -6			½" x 18"	
7000119507	5-00-51141- 55031 -7			½" x 24"	
7100020234	5-00-51141- 55030 -0			¾" x 18"	
7000119514	5-00-51141- 55044 -7			2" x 132"	50
7010361639	5-00-51141- 55036 -2			2" x 60"	
7000119509	5-00-51141- 55034 -8			2" x 72"	
7100010398	5-00-51141- 55043 -0			3" x 132"	25
7010308910	5-00-51141- 55037 -9			6" x 48"	20
7010512180	N/A	80+	YF	⅛" x 18"	200
7000119515	5-00-51141- 55048 -5			½" x 18"	
7000144126	5-00-51141- 55047 -8			¾" x 18"	20
7010513564	N/A			2" x 48"	
7000119522	5-00-51141- 55057 -7			2" x 72"	50
7010327353	5-00-51141- 55058 -4			2-½" x 60"	
7100010402	5-00-51141- 55051 -5			3" x 132"	25
7000119516	5-00-51141- 55049 -2			3-½" x 15-½"	50
7000119523	5-00-51141- 55059 -1			6" x 48"	20
7010536326	N/A			19" x 48"	
7000148168	5-00-51141- 55063 -8			37" x 60"	2
7010327354	5-00-51141- 55062 -1			37" x 75"	
7010512979	N/A	120+	YF	⅛" x 18"	200
7100101153	5-00-76308- 64309 -1			½" x 18"	
7100095559	5-00-76308- 64310 -7			½" x 24"	

3M™ Cubitron™ II Cloth Belt 990FZ

A revolutionary performance with 3M Precision Shaped Grain on a tough polyester cloth backing. This high-performing belt is constructed with an open coat and an additional antistatic treatment to further prevent loading during use on wood. It can also be used in either wet or dry applications.

Material ID	UPC	Grade/ Backing		W x L	Belt/ Case
7010517915	N/A	36+	YF	52" x 75"	1



Cloth Roll

3M™ Cubitron™ II Cloth Roll 784F

A revolutionary performance with 3M Precision Shaped Grain on a polyester cloth backing. This high-performing roll contains a grinding aid, making it ideal for low to medium pressure applications on stainless steel and other exotic alloys, along with carbon steel, cobalt chrome and nickel alloys.



Material ID	UPC	Grade/ Backing	W x L	Roll/ Case
7100094192	5-00-76308- 65742 -5	36+	52" x 50 yd	1
7100094194	5-00-76308- 65744 -9	50+		
7100094196	5-00-76308- 65746 -3	60+		
7100094198	5-00-76308- 65748 -7	80+		
7100094186	5-00-76308- 65750 -0	120+	52" x 50 yd	1
7100094188	5-00-76308- 65752 -4	150+		
7100094190	5-00-76308- 65754 -8	180+		

Cut & Grind Wheels

3M™ Cubitron™ II Cut & Grind Wheel

Features 3M Precision Shaped Ceramic Grain to bring you an exceptionally fast-cutting and long-lasting wheel for use on both stainless steel and mild steel. These versatile wheels are designed to be used both as a grinding wheel and as a cut-off wheel — making them ideal for cutting, grinding, gouging and more.



DO NOT USE ON TOOLS WITHOUT GUARDS.

Material ID	UPC	Dia x Thk x AH	Wheel/Case
T27			
7100019056	0-40-46719- 82646 -9	4" x 1⁄8" x 3⁄8"	20
7100019244	0-40-46719- 82654 -4	4-½" x 1⁄8" x 7⁄8"	
7100019243	0-40-46719- 82657 -5	5" x 1⁄8" x 7⁄8"	
7100019067	5-00-51141- 28758 -9	6" x 1⁄8" x 7⁄8"	
7100019072	5-00-51141- 28760 -2	7" x 1⁄8" x 7⁄8"	
7100019075	5-00-51141- 28761 -9	9" x 1⁄8" x 7⁄8"	
T27 Quick Change			
7100018882	5-00-51141- 28762 -6	4-½" x 1⁄8" x 5⁄8-11"	20
7100018883	5-00-51141- 28763 -3	5" x 1⁄8" x 5⁄8-11"	
7100019069	5-00-51141- 28764 -0	6" x 1⁄8" x 5⁄8-11"	
7100019074	5-00-51141- 28765 -7	7" x 1⁄8" x 5⁄8-11"	
7100019076	5-00-51141- 28766 -4	9" x 1⁄8" x 5⁄8-11"	




For full Abrasives portfolio, please visit [3M.com/abrasives](https://www.3M.com/abrasives)



Cut-off Wheels

3M™ Cubitron™ II Cut-Off Wheels


Features 3M Precision Shaped Ceramic Grain to bring you an exceptionally fast-cutting and long-lasting wheel for use on almost all materials, including stainless steel, mild steel, and aerospace alloys. This cut-off wheel surpasses 3M™ High Performance wheels in both cut and life to deliver significant gains in productivity.



Material ID	UPC	Dia x Thk x AH	Wheel/Case
T1			
7100094770	5-00-51115- 66513 -9	3" x .035" x ¼"	50
7100094771	5-00-51115- 66514 -6	3" x .035" x ⅜"	
7000119639	5-00-51115- 66516 -0	3" x .06" x ⅜"	
7100094773	5-00-51115- 66518 -4	4" x .035" x ⅜"	
7000119643	5-00-51115- 66520 -7	4" x .06" x ⅜"	
7100036620	5-00-51115- 66524 -5	4" x .125" x ⅜"	
7100024773	5-00-51115- 66525 -2	4-½" x .045" x ⅞"	
7100094781	5-00-51125- 86929 -9	4-½" x .040" x ⅞"	
7100024774	5-00-51115- 66526 -9	5" x .045" x ⅞"	
7100098146	5-00-51115- 66527 -6	6" x .045" x ⅞"	
7100098145	5-00-51115- 66528 -3	7" x .045" x ⅞"	
T27			
7100094440	5-00-48011- 64999 -8	4-½" x .045" x ⅞" Single Pack	10
7100094783	5-00-51125- 86946 -6	4-½" x .040" x ⅞"	50
7100024953	5-00-51115- 66531 -3	4-½" x .045" x ⅞"	
7000119648	5-00-51115- 66535 -1	4-½" x .125" x ⅞"	
7100023745	5-00-51115- 66537 -5	5" x .045" x ⅞"	
7000119651	5-00-51115- 66539 -9	5" x .09" x ⅞"	
7100098316	5-00-51115- 66541 -2	6" x .045" x ⅞"	
7000119653	5-00-51115- 66543 -6	7" x .09" x ⅞"	
T27 Quick Change			
7100034773	5-00-51115- 66530 -6	4-½" x .045" x ⅝-11"	50
7100106098	5-00-51115- 66532 -0	4-½" x .09" x ⅝-11"	
7000144134	5-00-51115- 66534 -4	4-½" x .125" x ⅝-11"	
7100098355	5-00-51115- 66540 -5	6" x .045" x ⅝-11"	
7000119652	5-00-51115- 66542 -9	7" x .09" x ⅝-11"	

3M™ Silver Cut-Off Wheel

Designed to deliver an unbeatable combination of performance and value in metal cutting applications. This long-lasting wheel uses 3M Precision Shaped Grains to deliver a fast and consistent cut through pipes, tubes or flat sheets of stainless steel, mild steel, aerospace alloys and more.



Material ID	UPC	Dia x Thk x AH	Wheel/Case
T1			
7100138406	5-00-51125- 87457 -6	3" x .035" x ¼"	50
7100139208	5-00-51125- 87458 -3	3" x .035" x ⅜"	
7100139210	5-00-51125- 87459 -0	3" x .060" x ⅜"	
7100139212	5-00-51125- 87460 -6	4" x .035" x ¼"	
7100139214	5-00-51125- 87461 -3	4" x .035" x ⅜"	
7100139215	5-00-51125- 87462 -0	4" x .060" x ⅜"	
7100139226	5-00-51125- 87464 -4	4-½" x .40" x ⅞"	
7100139228	5-00-51125- 87465 -1	4-½" x .045" x ⅞"	
7100139236	5-00-51125- 87467 -5	5" x .045" x ⅞"	
7010412152	5-00-51125- 87469 -9	6" x .045" x ⅞"	
7010414998	5-00-51125- 87471 -2	7" x .045" x ⅞"	
T27			
7100147388	5-00-51125- 87660 -0	4-½" x .045" x ⅞" Single Pack	10
7100139230	5-00-51125- 87466 -8	4-½" x .045" x ⅞"	50
7100141055	5-00-51125- 87659 -4	4-½" x .045" x ⅞"	
7100139237	5-00-51125- 87468 -2	5" x .045" x ⅞"	
7010409304	5-00-51125- 87470 -5	6" x .045" x ⅞"	



Depressed Center Grinding Wheels

3M™ Cubitron™ II Depressed Center Grinding Wheel

Constructed of 3M Precision Shaped Ceramic Grain to bring you an exceptionally fast-cutting and long-lasting rigid bonded wheel for heavy weld removal and other heavy-duty grinding applications. This grinding wheel works well on almost all materials and is specially formulated for use on stainless steel, mild steel, and aerospace alloys. **DO NOT USE ON TOOLS WITHOUT GUARDS.**



Type 27

Material ID	UPC	Dia x Thk x AH	Each/Case
T27			
7010299049	5-00-51125- 87209 -1	4-½" x ¼" x ⅞" Single Pack	10
7100086894	5-00-51115- 78466 -3	4-½" x ¼" x ⅞"	20
7000118418	N/A	5" x ¼" x ⅞"	
7100095557	5-00-51115- 78467 -0	5" x ¼" x ⅞"	
7100094061	5-00-76308- 64314 -5	6" x ¼" x ⅞"	
7000118419	5-00-51115- 66589 -4	6" x ¼" x ⅞"	
7000118420	5-00-51115- 66590 -0	7" x ¼" x ⅞"	
7100094062	5-00-76308- 64315 -2	7" x ¼" x ⅞"	
7100094063	5-0-076308- 64316 -9	9" x ¼" x ⅞"	
7100119216	5-00-51125- 87206 -0	7" x ¼" x ⅞" Trial Pack	10
T27 Quick Change			
7010327592	5-00-51125- 87208 -4	4-½" x ¼" x ⅝-11" Single Pack	10
7100103334	5-00-76308- 64320 -6	4-½" x ¼" x ⅝-11"	20
7100103025	5-00-76308- 64317 -6	5" x ¼" x ⅝-11"	
7100103318	5-00-76308- 64318 -3	6" x ¼" x ⅝-11"	
7100103317	5-00-76308- 64319 -0	7" x ¼" x ⅝-11"	
7100103313	5-00-51125- 87153 -7	9" x ¼" x ⅝-11"	



3M™ Silver Depressed Center Grinding Wheel

A wheel designed to deliver an unbeatable combination of performance and value. This long-lasting wheel uses 3M Precision Shaped Grains to deliver a fast and consistent cut during grinding and heavy stock removal on stainless steel, mild steel, aerospace alloys and more. **DO NOT USE ON TOOLS WITHOUT GUARDS.**



Type 27

Material ID	UPC	Dia x Thk x AH	Each/Case
T27			
7100141076	5-00-51125- 87456 -9	4" x ¼" x ⅝"	20
7100141079	5-00-51125- 87453 -8	4-½" x ¼" x ⅞"	
7100141078	5-00-51125- 87454 -5	5" x ¼" x ⅞"	
7010414997	5-00-51125- 87450 -7	6" x ¼" x ⅞"	
7010412151	5-00-51125- 87451 -4	7" x ¼" x ⅞"	
T27 Quick Change			
7010362237	5-00-51125- 87397 -5	4-½" x ¼" x ⅝-11"	20
7010412149	5-00-51125- 87446 -0	5 x ¼ x ⅝-11"	
7010412150	5-00-51125- 87448 -4	7" x ¼" x ⅝-11"	
7010409732	5-00-51125- 87449 -1	9" x ¼" x ⅝-11"	






Fibre Discs

3M™ Cubitron™ II Fibre Disc 982C

Slices through carbon steel with 3M Precision Shaped Grain and generates up to twice the cut-rate, durability, and life of other fiber discs — all with less grinding pressure. That means less operator fatigue, faster throughput, and more parts per disc when tackling high pressure grinding applications such as medium to heavy-duty stock removal.



Material ID	UPC	Grade	Size	Disc/Case
7100094359	5-00-51125- 86942 -8	36+	4-½" x ⅞" Trial Pack	10
7000028205	5-00-51141- 27763 -4		4" x ⅝"	100
7000148153	5-00-51141- 27400 -8		4-½" x ⅞"	
7000000392	5-00-51141- 27401 -5		5" x ⅞"	
7000000393	5-00-51141- 27402 -2		7" x ⅞"	
7000045132	5-00-51141- 27403 -9		9-⅞" x ⅞"	
7000119196	5-00-51141- 27631 -6	60+	4-½" x ⅞"	100
7000119197	5-00-51141- 27632 -3		5" x ⅞"	
7000028198	5-00-51141- 27633 -0		7" x ⅞"	
7000119199	5-00-51141- 27635 -4	80+	4-½" x ⅞"	100
7000119200	5-00-51141- 27636 -1		5" x ⅞"	
7000119201	5-00-51141- 27637 -8		7" x ⅞"	

GL Quick Change


7000148154	5-00-51141- 27406 -0	36+	5"	100
7000119163	5-00-51141- 27407 -7		7"	
7000119206	5-00-51141- 27644 -6	60+	5"	100

TN Quick Change

7010326612	5-00-51141- 28107 -5	36+	4"	100
7000119173	5-00-51141- 27425 -1		4-½"	
7000119161	5-00-51141- 27404 -6		5"	
7000119162	5-00-51141- 27405 -3		7"	
7000119203	5-00-51141- 27639 -2	60+	4-½"	100
7000119205	5-00-51141- 27641 -5		7"	
7010326768	5-00-51141- 27642 -2	80+	4-½"	100
7000119206	5-00-51141- 27644 -6		7"	

3M™ Cubitron™ II Roloc™ Fibre Disc 982C

Outstanding performance and productivity for medium to high pressure grinding applications on carbon steel when a smaller sized disc is needed.



Material ID	UPC	Grade	Size	Disc/Case
TR				
7000118429	5-00-51115- 66778 -2	36+	2"	200
7000118430	5-00-51115- 66779 -9		3"	
7100006575	5-00-51115- 66780 -5		4"	100
7000118431	5-00-51115- 66783 -6	60+	2"	200
7100006574	5-00-51115- 66785 -0		4"	100
7000118432	5-00-51115- 66788 -1	80+	2"	200
7000044904	5-00-51115- 66789 -8		3"	
7100006573	5-00-51115- 66790 -4		4"	100






Fibre Discs

3M™ Cubitron™ II Fibre Disc 987C

Offers significant gains in productivity on medium to heavy-duty operations thanks to the exceptionally high-performing 3M Precision Shaped Grain combined with a stiff fiber backing. This disc achieves a higher cut-rate, greater durability, and longer life than other fiber discs — all with less grinding pressure.



Material ID	UPC	Grade	Size	Disc/Case
7000119175	5-00-51141- 27447 -3	36+	4-½" x ⅞"	100
7100011522	5-00-51141- 27448 -0		5" x ⅞"	
7000119177	5-00-51141- 27449 -7		7" x ⅞"	
7000119207	5-00-51141- 27653 -8	60+	4-½" x ⅞"	100
7000119208	5-00-51141- 27654 -5		5" x ⅞"	
7000148158	5-00-51141- 27655 -2		7" x ⅞"	
7010308171	5-00-51141- 27953 -9		7" x ⅞"	
7000045163	5-00-51141- 27656 -9	80+	9-⅛" x ⅞"	100
7000119209	5-00-51141- 27657 -6		4-½" x ⅞"	
7000119210	5-00-51141- 27658 -3		5" x ⅞"	
7000119211	5-00-51141- 27659 -0		7" x ⅞"	

GL Quick Change

7010326433	5-00-51141- 27728 -3	36+	5"	100
------------	-----------------------------	-----	----	-----

TN Quick Change

7000144096	5-00-51141- 27469 -5	36+	4-½"	100
7000119182	5-00-51141- 27467 -1		5"	
7100068024	5-00-51141- 27661 -3	60+	4-½"	100
7000119212	5-00-51141- 27662 -0		5"	
7010362281	5-00-51141- 27664 -4	80+	4-½"	100

3M™ Cubitron™ II Roloc™ Fibre Disc 987C

Designed for heavy duty metalworking applications such as weld grinding, beveling and flame-cut edge clean-up. This product uses 3M Precision Shaped Grain on a fiber backing for fast grinding and blending.



Material ID	UPC	Grade	Size	Disc/Case
TR				
7100063613	5-00-51125- 94952 -6	36+	2"	200
7100050304	5-00-51125- 94953 -3		3"	
7100063614	5-00-51125- 94957 -1	60+	2"	200
7100063615	5-00-51125- 94962 -5	80+	2"	200
TSM				
7010360663	5-00-51125- 94955 -7	36+	2"	200
7010325841	5-00-51125- 94956 -4		3"	

Film Discs

3M™ Cubitron™ II Hookit™ Clean Sanding Film Disc 775L Multi-Pack

3M Precision Shaped Ceramic Grain, a revolutionary advancement in abrasive technology. The triangular shaped ceramic mineral is designed to slice through the substrate, rather than gouging or "plowing" like conventional abrasives, resulting in a disc that cuts up to 2x as fast and lasts up to 6x as long as conventional abrasives.



Material ID	UPC	Grade	Size	Pack/Case
7010327612	5-00-51125- 87338 -8	80+ to 220+	5" x NH	20

3M™ Cubitron™ II Stikit™ Film Disc 775L Multi-Pack

Features 3M Precision Shaped Ceramic Grain, a revolutionary advancement in abrasive technology. The triangular shaped ceramic mineral is designed to slice through the substrate, rather than gouging or "plowing" like conventional abrasives, resulting in a disc that cuts up to 2x as fast and lasts up to 6x as long as conventional abrasives.




Material ID	UPC	Grade	Size	Pack/Case
7010363665	5-00-51125- 87337 -1	80+ to 220+	5" x NH	20



Film Discs

3M™ Cubitron™ II Hookit™ Film Disc 775L

Features 3M Precision Shaped Ceramic Grain, a revolutionary advancement in abrasive technology. The triangular shaped ceramic mineral is designed to slice through the substrate, rather than gouging or “plowing” like conventional abrasives, resulting in a disc that cuts up to 2x as fast and lasts up to 6x as long as conventional abrasives.



Material ID	UPC	Grade	Size	Disc/Case
7100106742	5-00-51125- 87266 -4	80+	3" x NH	250
7100106764	5-00-51125- 87267 -1	120+		
7100106768	5-00-51125- 87274 -9	180+		
7100046325	5-00-51125- 86818 -6	80+	5" x NH	250
7100046326	5-00-51125- 86819 -3	120+		
7100064174	5-00-51125- 87026 -4	150+		
7100064176	5-00-76308- 64263 -6	180+		
7100064179	5-00-76308- 64269 -8	220+		
7100145403	5-00-76308- 47095 -6	240+		
7100145405	5-00-76308- 47080 -2	320+	6" x NH	250
7100145436	5-06-38060- 05055 -7	400+		
7100046327	5-00-51125- 86820 -9	80+		
7100046328	5-00-51125- 86821 -6	120+		
7100075202	5-00-51125- 87045 -5	150+		
7100064272	5-00-51125- 87040 -0	180+		
7100064274	5-00-51125- 87089 -9	220+		
7100145462	5-00-76308- 47099 -4	320+		
7100145469	5-06-38060- 05056 -4	400+		
Dust-Free				
7100106678	5-00-51125- 87270 -1	80+	3" x D/F	250
7100106717	5-00-51125- 87272 -5	150+		
7100106716	5-00-51125- 87273 -2	220+		
7100046323	5-00-51125- 86816 -2	80+	6" x D/F	250
7100046324	5-00-51125- 86817 -9	120+		
7100075202	5-00-51125- 87045 -5	150+		
7100067092	5-00-51125- 87096 -7	220+		
Clean Sanding				
7100045070	5-00-51125- 86822 -3	80+	5"	250
7100045071	5-00-51125- 86823 -0	120+		
7100064175	5-00-76308- 64258 -2	150+		
7100064177	5-00-76308- 64264 -3	180+		
7100064270	5-00-76308- 64270 -4	220+		
7100145362	5-00-76308- 47097 -0	240+		
7100145363	5-00-76308- 47081 -9	320+		
7100145404	5-06-38060- 05058 -8	400+	6"	250
7100045072	5-00-51125- 86824 -7	80+		
7100045073	5-00-51125- 86825 -4	120+		
7100065918	5-00-76308- 64259 -9	150+		
7100064178	5-00-76308- 64265 -0	180+		
7100064271	5-00-76308- 64271 -1	220+		
7100145316	5-00-76308- 47098 -7	240+		
7100141692	5-00-76308- 47082 -6	320+		
7100145455	5-06-38060- 05059 -5	400+		

3M™ Cubitron™ II Stikit™ Film Disc 775L

Features 3M Precision Shaped Ceramic Grain, a revolutionary advancement in abrasive technology. The triangular shaped ceramic mineral is designed to slice through the substrate, rather than gouging or “plowing” like conventional abrasives, resulting in a disc that cuts up to 2x as fast and lasts up to 6x as long as conventional abrasives.




Material ID	UPC	Grade	Size	Disc/Case
Linered with Tab				
7100048736	5-00-51125- 86802 -5	80+	5" x NH	250
7100045865	5-00-51125- 86803 -2	120+		
7100075678	5-00-76308- 64275 -9	150+		
7100075690	5-00-76308- 64279 -7	180+		
7100075692	5-00-76308- 64283 -4	220+		
7100145365	5-00-76308- 47083 -3	320+	6" x NH	250
7100045866	5-00-51125- 86804 -9	80+		
7100045867	5-00-51125- 86805 -6	120+		
7100075206	5-00-51125- 87052 -3	180+		
7100075221	5-00-51125- 87105 -6	220+		
7100145432	5-00-76308- 47105 -2	320+		
Disc Rolls (100/roll, 4 rolls/case)				
7100045901	5-00-51125- 86810 -0	80+	5" x NH	400
7100045902	5-00-51125- 86811 -7	120+		
7100075693	5-00-76308- 64284 -1	220+		
7100145429	5-00-76308- 47091 -8	240+		
7100145417	5-00-76308- 47084 -0	320+		
7100046309	5-00-51125- 86812 -4	80+	6" x NH	400
7100046320	5-00-51125- 86813 -1	120+		
7100067212	5-00-51125- 87049 -3	150+		
7100067211	5-00-51125- 87048 -6	180+		
7100145467	5-00-76308- 47103 -8	320+		
Dust-Free				
7100145468	5-00-76308- 47102 -1	320+	5" x D/F	400
7100045900	5-00-51125- 86809 -4	120+	6" x D/F	500
7100075205	5-00-51125- 87050 -9	180+		400
7100145449	5-00-76308- 47090 -1	240+		
7100145456	5-06-38060- 05066 -3	400+		
Dust-Free Linered with Tab				
7100145448	5-06-38060- 05070 -0	400+	5" x D/F	250



Flap Discs

3M™ Cubitron™ II Flap Disc 967A


Ideal for medium-pressure applications on flat and contoured surfaces, especially in light deburring or weld leveling to prep for paint in mild steel. It's also great for stainless steel fabrication where finish and gouge resistance are important. Powered by 3M Precision Shaped Grain, this disc cuts fast and lasts long.



Material ID	UPC	Grade	Dia x Thk x AH	Max RPM	Disc/Case
T27					
7100094358	5-00-51125- 86855 -1	40+	4-½" x ⅞" Single Pack	13,300	10
7000148181	5-00-51141- 55605 -0		4-½" x ⅞"		
7100085781	5-00-51141- 55635 -7		4-½" x ⅞" Giant		
7000148196	5-00-51125- 86715 -8		5" x ⅞"	12,000	
7000148184	5-00-51141- 55611 -1		7" x ⅞"	8,600	
7000148182	5-00-51141- 55606 -7	60+	4-½" x ⅞"	13,300	10
7010327062	5-00-51141- 55636 -4		4-½" x ⅞" Giant		
7000148200	5-00-51125- 86719 -6		5" x ⅞"		
7000148183	5-00-51141- 55607 -4	80+	4-½" x ⅞"	13,300	10
7000148186	5-00-51141- 55613 -5		7" x ⅞"		
T27 Quick Change					
7100058067	5-00-51141- 55602 -9	40+	4-½" x ⅝-11"	13,300	10
7010363301	5-00-51141- 55632 -6		4-½" x ⅝-11" Giant		
7100058060	5-00-51141- 55603 -6	60+	4-½" x ⅝-11"	13,300	10
7010327061	5-00-51141- 55633 -3		4-½" x ⅝-11" Giant		
7100032505	5-00-51141- 55604 -3	80+	4-½" x ⅝-11"	13,300	10
7010294535	5-00-51141- 55634 -0		4-½" x ⅝-11" Giant		

Material ID	UPC	Grade	Dia x Thk x AH	Max RPM	Disc/ Case
T29					
7100097661	5-00-51141- 55617 -3	40+	4" x 5/8"	13,300	10
7000148187	5-00-51141- 55623 -4		4-1/2" x 7/8"		
7000148197	5-00-51125- 86716 -5		5" x 7/8"		
7100097650	5-00-51141- 55618 -0	60+	4" x 5/8"	13,300	10
7000148188	5-00-51141- 55624 -1		4-1/2" x 7/8"		
7000148198	5-00-51125- 86717 -2		5" x 7/8"		
7000148189	5-00-51141- 55625 -8	80+	4-1/2" x 7/8"	13,300	10
7000148201	5-00-51125- 86720 -2		5" x 7/8"		
7000148192	5-00-51141- 55631 -9		7" x 7/8"		
T29 Quick Change					
7010327056	5-00-51141- 55614 -2	40+	4-1/2" x 3/8"-24"	13,000	10
7100049935	5-00-51141- 55620 -3		4-1/2" x 5/8"-11"		
7100032359	5-00-51141- 55621 -0	60+	4-1/2" x 5/8"-11"	13,000	10
7010308943	5-00-51141- 55616 -6	80+	4-1/2" x 3/8"-24"	13,000	10
7100031307	5-00-51141- 55622 -7		4-1/2" x 5/8"-11"		

**More material.
Longer life.**



Need more cutting power? Go GIANT!

Our Giant flap discs are 25% thicker, for an aggressive cut with added durability and longer life.



Paper Discs

3M™ Stikit™ Paper Disc Roll 236U

A versatile gold disc with a convenient adhesive backing ready for quick and easy attachment to a 3M™ Stikit™ backup pad (sold separately). The roll offers quick access to a disc and eliminates disc liners. The disc features a strong, paper backing that resists wear during aggressive sanding.



Material ID	UPC	Grade	Size	Discs/ Roll	Roll/ Case
7000119535	5-00-51141- 55540 -4	P80	5 in x NH	100	4
7000028098	5-00-51141- 55541 -1	P100			
7100031875	5-00-51141- 55542 -8	P120			
7000119538	5-00-51141- 55543 -5	P150			
7000028228	5-00-51141- 55544 -2	P180			
7000119539	5-00-51141- 55545 -9	P220			
7000028229	5-00-51141- 55546 -6	P240			
7000028230	5-00-51141- 55547 -3	P320			
7000028231	5-00-51141- 55548 -0	P400			
7000119540	5-00-51141- 55549 -7	P500			
7000119551	5-00-51141- 55560 -2	P80	6 in x NH	100	4
7000119552	5-00-51141- 55561 -9	P100			
7000119553	5-00-51141- 55562 -6	P120			
7000119554	5-00-51141- 55563 -3	P150			
7000119555	5-00-51141- 55564 -0	P180			
7000119556	5-00-51141- 55565 -7	P220			
7000119557	5-00-51141- 55566 -4	P240			
7000119558	5-00-51141- 55567 -1	P320			
7000119559	5-00-51141- 55568 -8	P400			


Material ID	UPC	Grade	Size	Discs/ Roll	Roll/ Case
Dust-Free					
7000119541	5-00-51141- 55550 -3	P80	5 in x D/F	100	4
7000119542	5-00-51141- 55551 -0	P100			
7000119545	5-00-51141- 55554 -1	P180			
7000119546	5-00-51141- 55555 -8	P220			
7000119548	5-00-51141- 55557 -2	P320			
7000119549	5-00-51141- 55558 -9	P400			
7000119550	5-00-51141- 55559 -6	P500			
7000119561	5-00-51141- 55570 -1	P80			
7000119562	5-00-51141- 55571 -8	P100			
7000119563	5-00-51141- 55572 -5	P120			
7000119564	5-00-51141- 55573 -2	P150	6 in x D/F	100	4
7000119565	5-00-51141- 55574 -9	P180			
7000119566	5-00-51141- 55575 -6	P220			
7000119568	5-00-51141- 55577 -0	P320			
7000119569	5-00-51141- 55578 -7	P400			



Hand Pads

Scotch-Brite™ General Purpose Hand Pads 7447 and 7448

Combines flexibility with effective cutting action and precise hand control to accomplish tough cleaning jobs or produce fine finishing results, use after use. Very fine grade aluminum oxide abrasives cut fast and fine, leaving a smooth, finished surface. Suitable for use on a wide variety of materials and for many different tasks.



Material ID	UPC	Prod ID	Size	Color/Grade	Pad/Case
7000027560	5-00-48011- 04229 -4	7447	6" x 9"	Maroon A VFN	60 Bulk
7100089226	5-00-048011- 04028 -8	7448	6" x 9"	Gray S ULF	

Scotch-Brite™ Hand Pads 7447 PRO and 7448 PRO

High performance pad takes less time to prep surface and lasts longer. Tightly graded abrasive particles for consistent, uniform scratch throughout life of the hand pad. Long lasting pad made with durable non-woven nylon web is flexible enough to get into hard-to-sand places. Specially coated to minimize loading. Ideal for everyday uses like prepping surfaces for color coat; general scuffing, cleaning and hand blending. Center perforated for convenience.



Material ID	UPC	Prod ID	Size	Color/ Grade	Pad/ Case
7100023339	5-00-048011- 64926 -9	7447 PRO	6" x 9"	Maroon A VFN	60
7100023340	5-00-048011- 64935 -1	7448 PRO	6" x 9"	Gray S ULF	
7100033494	5-00-048011- 64933 -7	Trial Pack	Includes one each: 7447 PRO and 7448 PRO		

Sanding & Surface Restoration/Repair

3M™ Pro-Pak™ Drywall Sanding Screens and Sheets

Fits most drywall sanding tools. Made with a sharp synthetic mineral for long-lasting performance. Waterproof and can be rinsed for reuse.



Material ID	UPC	Size	Grade	Each/Case
Screens				
7000047624	5-00-51111- 11656 -7	4-3/16" x 11-1/4"	100	10/PK
7010331884	5-00-51144- 99438 -5		120	
7000047623	5-00-51144- 99436 -1		220	
Sheets				
7100138085	0-00-51144- 99433 -5	4-3/16" x 11-1/4"	30	10
7100138095	0-00-51144- 99432 -8		100	
7100138588	0-00-51144- 99431 -1		150	

3M™ Sanding Sponge

For either dry or wet sanding. Ideal for sanding wood, paint, metal, plastic and drywall. Two sanding grades on one sponge in a combination of extra fine/fine or fine/medium. Rinse and reuse.



Material ID	UPC	Size	Grade	Each/Case
7100176010	0-00-51111- 10628 -0	3-3/4" x 2 5/8" x 1"	Extra Fine/Fine	24
7100175118	0-00-51131- 50038 -9		Fine/Medium	
7100176775	0-00-51115- 00409 -4		Fine	
7100172569	0-00-51115- 00408 -7		Medium	

3M™ Angled Sanding Sponge

Ideal for sanding in tight corners or next to textured ceilings. When finished, simply rinse and reuse. Available in fine, medium and coarse grades.



Material ID	UPC	Size	Grade	Each/Case
7100101550	5-00-51115- 09174 -7	2-7/8" x 4-7/8" x 1"	Fine	24
7100101548	5-00-51115- 09166 -2		Medium	



Surface Conditioning Belts

Scotch-Brite™ Surface Conditioning Belt

A durable belt engineered to perform detail work such as blending, blending corners, cleaning, contour finishing, deburring, deburring edges, fine finishing, flat finishing, setting the grain, stainless steel finishing, and attaining straightline-brushed finishes on a variety of metals.



Material ID	UPC	Grade/Color	W x L	Belt/Case
7000120665	5-00-48011- 13230 -8	A VFN Blue	¼" x 18"	20
7000120694	5-00-48011- 14501 -8		⅜" x 13"	
7010291316	5-00-48011- 18302 -7		⅝" x 18"	
7000120687	5-00-48011- 14276 -5	A MED Maroon	¼" x 18"	20
7000120661	5-00-48011- 13131 -8		¼" x 24"	
7100103026	5-00-48011- 14502 -5		⅜" x 13"	
7010329658	5-00-48011- 93543 -5	A MED Maroon	⅜" x 24"	20
7000120669	5-00-48011- 13290 -2		¼" x 18"	
7000120662	5-00-48011- 13132 -5		¼" x 24"	
7000120901	5-00-48011- 19687 -4	A MED Maroon	½" x 12"	20
7000028455	5-00-48011- 08858 -2		½" x 18"	
7000120716	5-00-48011- 05741 -0		½" x 24"	
7000120674	5-00-48011- 13639 -9	A CRS Brown	¾" x 18"	10
7000120601	5-00-48011- 08886 -5		2" x 34"	
7000120603	5-00-48011- 08890 -2		2" x 48"	
7000045881	5-00-48011- 05820 -2	A CRS Brown	3" x 10-⅞"	10
7000120722	5-00-48011- 05023 -7		3" x 21"	
7010329076	5-00-48011- 08879 -7		3" x 132"	
7000028433	5-00-48011- 05016 -9	A CRS Brown	3-½" x 15-½"	10
7000120727	5-00-48011- 05019 -0		6" x 48"	
7010365617	5-00-48011- 05235 -4		½" x 18"	
7000120714	5-00-48011- 08855 -1	SiC SFN Gray	1" x 42"	10
7000120589	5-00-48011- 05644 -4		3-½" x 15-½"	
7000120902	5-00-48011- 19688 -1		½" x 12"	
7000120715	5-00-48011- 08856 -8	A MED Maroon	½" x 18"	20
7000045944	5-00-48011- 04299 -7		½" x 24"	
7000120700	5-00-48011- 14543 -8		¾" x 18"	
7100068000	5-00-48011- 17517 -6	A/O VFN Blue	1" x 18"	10
7000120609	5-00-48011- 08920 -6		1" x 30"	
7100017820	5-00-48011- 04190 -7		1" x 42"	
7000120717	5-00-48011- 04295 -9	A/O VFN Blue	2" x 48"	10
7000120610	5-00-48011- 08922 -0		2" x 60"	
7000120576	5-00-48011- 00579 -4		2" x 72"	
7100032503	5-00-48011- 04298 -0	A/O VFN Blue	3" x 24"	5
7000120721	5-00-48011- 04289 -8		3" x 132"	
7000028436	5-00-48011- 05643 -7		3-½" x 15-½"	

Material ID	UPC	Grade/Color	W x L	Belt/Case
7100029205	5-00-48011- 05406 -8	A/O VFN Blue	4" x 60"	10
7010328716	5-00-48011- 14291 -8		4" x 90"	
7010292398	5-00-48011- 04281 -2		4" x 132"	
7000120726	5-00-48011- 04283 -6	A/O VFN Blue	6" x 48"	5
7000121041	5-00-48011- 93524 -4		37" x 60"	
7000120795	5-00-48011- 17515 -2		½" x 12"	
7000028454	5-00-48011- 08857 -5	A/O MED Maroon	½" x 18"	20
7000045943	5-00-48011- 03998 -0		½" x 24"	
7000028461	5-00-48011- 15899 -5		¾" x 18"	
7000120754	5-00-48011- 15897 -1	A/O MED Maroon	¾" x 20-½"	10
7010366213	5-00-48011- 19628 -7		1" x 12"	
7000120693	5-00-48011- 14398 -4		1" x 18"	
7000120605	5-00-48011- 08898 -8	A/O MED Maroon	1" x 30"	20
7000120565	5-0-048011- 04189 -1		1" x 42"	
7100024611	5-00-48011- 09498 -9		1-⅞" x 21"	
7000120607	5-00-48011- 08905 -3	A/O MED Maroon	2" x 34"	10
7000120736	5-00-48011- 08915 -2		2" x 48"	
7010309628	5-00-48011- 08916 -9		2" x 60"	
7000120578	5-00-48011- 00580 -0	A/O MED Maroon	2" x 72"	5
7010309300	5-00-48011- 03999 -7		2" x 132"	
7010329181	5-00-48011- 08906 -0		3" x 21"	
7000120719	5-00-48011- 00583 -1	A/O MED Maroon	3" x 24"	10
7100018917	5-00-48011- 93540 -4		3" x 79"	
7000120720	5-00-48011- 00568 -8		3" x 132"	
7000028435	5-00-48011- 05228 -6	A/O MED Maroon	3-½" x 15-½"	10
7000120606	5-00-48011- 08900 -8		4" x 36"	
7100083550	5-00-48011- 14401 -1		4" x 60"	
7010309610	5-00-48011- 05407 -5	A/O MED Maroon	4" x 90"	5
7000120725	5-00-48011- 00590 -9		6" x 48"	
7010364958	5-00-48011- 18900 -5		6" x 79"	
7010365833	5-00-48011- 14544 -5	A/O MED Maroon	9" x 48"	1
7010365610	5-00-48011- 05229 -3		25" x 48"	
7100019079	5-00-48011- 05231 -6		36" x 75"	
7000121043	5-00-48011- 93536 -7	A/O MED Maroon	37" x 60"	1
7000121034	5-00-48011- 93090 -4		37" x 75"	



Surface Conditioning Discs

Scotch-Brite™ Roloc™ Surface Conditioning Disc

Combines our durable, non-woven disc with the 3M™ Roloc™ quick-change attachment system for an effective disc that cleans, finishes, blends, and deburrs. Non-woven fiber construction conforms well to help preserve irregular or contoured surfaces and the Roloc™ backing supports the disc for aggressive cutting.



Material ID	UPC	Grade/Color	Size	Disc/Case
TP				
7010328577	5-00-48011- 13237 -7	A/O CRS Brown	2"	200
7000120666	5-00-48011- 13238 -4	A/O MED Maroon	2"	200
7010300794	5-00-48011- 13242 -1		3"	100
TR				
7000021280	5-00-48011- 15392 -1	A/O MED Maroon	1"	200
7000045888	5-00-48011- 08765 -3		1-½"	
7000000751	5-00-48011- 05527 -0		2"	
7000000755	5-00-48011- 05531 -7		3"	100
7100007035	5-00-48011- 12953 -7		4"	
7000021279	5-00-48011- 15391 -4	A/O VFN Blue	1"	200
7000120595	5-00-48011- 08766 -0		1-½"	
7000000750	5-00-48011- 05523 -2		2"	
7100007032	5-00-48011- 12952 -0		4"	100
7000000753	5-00-48011- 05522 -5	SiC SFN Gray	2"	200
7000028501	5-00-48011- 05529 -4		3"	100
7100007040	5-00-48011- 12951 -3		4"	
7010366420	5-00-48011- 25706 -3	A CRS Brown	¾"	200
7000000704	5-00-48011- 15393 -8		1"	
7000045887	5-00-48011- 08764 -6		1-½"	
7000028507	5-00-51131- 07480 -9		2"	
7000000752	5-00-48011- 05528 -7		2"	100
7000046114	5-00-51131- 07485 -4		3"	
7000000756	5-00-48011- 05532 -4		3"	
7000120800	5-00-51131- 07482 -3		4"	
7100007009	5-00-48011- 12954 -4		4"	
7000028506	5-00-51131- 07481 -6	A MED Maroon	2"	100
7000046113	5-00-51131- 07486 -1		3"	
7000028508	5-00-51131- 07515 -8	A VFN Blue	2"	100
7000046108	5-00-51131- 07513 -4		3"	
7000000754	5-00-48011- 05530 -0		3"	
7000000753	5-00-48011- 05522 -5	S SFN Gray	2"	100
7000028509	5-00-51131- 07516 -5		2"	
7000120974	5-00-51131- 07514 -1		3"	
7000028501	5-00-48011- 05529 -4		3"	

Material ID	UPC	Grade/Color	Size	Disc/Case
TS				
7000035850	5-00-48011- 19562 -4	A/O CRS Brown	¾"	200
7010364510	5-00-48011- 13253 -7		2"	
7010328681	5-00-48011- 13257 -5		3"	100
7000035846	5-00-48011- 18433 -8	A/O MED Maroon	¾"	200
7010365996	5-00-48011- 16507 -8		1"	
7000120667	5-00-48011- 13254 -4		2"	
7100035317	5-00-48011- 13258 -2		3"	100
7000035847	5-00-48011- 18434 -5	A/O VFN Blue	¾"	200
7010292394	5-00-48011- 13255 -1		2"	
7100035125	5-00-48011- 13259 -9		3"	100
7010294756	5-00-48011- 16509 -2	SiC SFN Gray	1"	100
7000035851	5-00-48011- 19698 -0	A CRS Brown	¾"	200
7000035849	5-00-48011- 18436 -9	A MED Maroon	¾"	200
7000035848	5-00-48011- 18435 -2	A VFN Blue	¾"	200
TSM				
7000120992	5-00-48011- 25765 -0	A CRS Brown	2"	200
7000120991	5-00-48011- 25764 -3	A MED Maroon	2"	200
7000120993	5-00-48011- 25766 -7		3"	100
7000120996	5-00-48011- 25770 -4	A VFN Blue	2"	200
7000120998	5-00-48011- 25780 -3		3"	100

TP (Plastic Button)	
TR (Plastic Button)	
TSM (Metal Button)	
TS (Plastic Button)	



Surface Conditioning Discs

Scotch-Brite™ Surface Conditioning Disc

Comes in a wide variety of grades and sizes and is an ideal first-step for cleaning, blending, deburring, and finishing. Durable, non-woven fiber construction conforms well on irregular or contoured surfaces without undercutting or damaging the base material.



Material ID	UPC	Grade/Color	Size	Disc/Case
7010292386	5-00-48011- 04118 -1	A/O CRS Brown	1-½"	200
7000120557	5-00-48011- 07458 -5		2"	
7000120558	5-00-48011- 04120 -4		3"	100
7000000661	5-00-48011- 07450 -9		4"	
7000046019	5-00-48011- 14101 -0		4-½"	50
7000000717	5-00-48011- 00750 -7		5"	
7000046016	5-00-48011- 03927 -0		6"	25
7000000653	5-00-48011- 00751 -4		7"	
7100141688	5-00-48011- 00752 -1		8"	200
7010364310	5-00-48011- 04122 -8	A/O MED Maroon	1-½"	
7100141893	5-00-48011- 07459 -2		2"	100
7000136520	5-00-48011- 04124 -2		3"	
7000000652	5-00-48011- 07451 -6		4"	50
7000046018	5-00-48011- 14100 -3		4-½"	
7000000719	5-00-48011- 00643 -2		5"	25
7010328918	5-00-48011- 03928 -7		6"	
7000000716	5-00-48011- 00645 -6		7"	200
7000120859	5-00-48011- 00670 -8		8"	
7010365581	5-00-48011- 04275 -1	A/O VFN Blue	1-½"	200
7000120572	5-00-48011- 04276 -8		2"	
7000136521	5-00-48011- 04277 -5		3"	100
7000000658	5-00-48011- 04278 -2		4"	
7000046017	5-00-48011- 14099 -0		4-½"	50
7000000718	5-00-48011- 04303 -1		5"	
7100134242	5-00-48011- 04304 -8		6"	25
7100094539	5-00-48011- 04305 -5		7"	
7000120657	5-00-48011- 13099 -1		48"	2

Material ID	UPC	Grade/Color	Size	Disc/Case
7000136522	5-00-48011- 27671 -2	A CRS Brown	4-½"	10
7100141913	5-00-48011- 27674 -3		5"	
7100141921	5-00-48011- 27677 -4		7"	
7000136523	5-00-48011- 27672 -9	A MED Maroon	4-½"	10
7000136525	5-00-48011- 27675 -0		5"	
7000136528	5-00-48011- 27678 -1		7"	
7000121008	5-00-48011- 27673 -6	A VFN Blue	4-½"	10
7000136526	5-00-48011- 27676 -7		5"	
7000136529	5-00-48011- 27679 -8		7"	
7010364312	5-00-48011- 04127 -3	SiC SFN Gray	2"	200
7000028428	5-00-48011- 04129 -7		4"	100
7010364893	5-00-48011- 14102 -7		4-½"	50
7000046015	5-00-48011- 00647 -0		5"	
7100101185	5-00-48011- 00648 -7		7"	25
Center Hole				
7010329310	5-00-48011- 60215 -3	A/O CRS Brown	4-½" x ⅞"	50
7000120760	5-00-48011- 16047 -9		5" x ⅞"	
7100141917	5-00-48011- 00644 -9	A/O MED Maroon	5" x ⅞"	50
7100028390	5-00-48011- 18618 -9	A/O VFN Blue	5" x ⅞"	50
7100054378	5-00-48011- 18624 -0		7" x ⅞"	25



Utility Cloth Rolls

3M™ Portable Utility Cloth Roll 314D

Provides light-weight cloth sanding strips used for hand sanding in many different applications. Constructed with aluminum oxide abrasive, our utility rolls come in a range of grades for common applications such as deburring, blending and repairing metal finishes, rust or other contaminant removal, and surface preparation for paints and coatings.



Material ID	UPC	Size	Grade/ Backing	Roll/Case
7010308203	5-00-51141- 20964 -2	1" x 12'	P80 J	5

3M™ Utility Cloth Roll 211K

A light J-weight cloth abrasive for general maintenance work. This closed coat aluminum oxide abrasive comes in a range of grades for common applications like repairing metal finishes, removing rust, deburring, blending and surface preparation for paints and coatings.



Material ID	UPC	Size	Grade/ Backing	Roll/Case
7000118330	5-00-51144- 05010 -4	1" x 50 yd	80	J 5
7100016843	5-00-51144- 05009 -8		100	
7000118335	5-00-51144- 05008 -1		120	
7000118338	5-00-51144- 05007 -4		150	
7000118340	5-00-51144- 05006 -7		180	
7000118357	5-00-51144- 05040 -1		220	
7000118350	5-00-51144- 05002 -9		320	
7000118331	5-00-51144- 05030 -2	1-½" x 50 yd	80	J 5
7000118333	5-00-51144- 05029 -6		100	
7000118336	5-00-51144- 05028 -9		120	
7100031693	5-00-51144- 05027 -2		150	
7000118341	5-00-51144- 05026 -5		180	
7000118347	5-00-51144- 05024 -1		240	
7000118351	5-00-51144- 05022 -7		320	
7010308048	5-00-51144- 05020 -3	2" x 50 yd	500	J 5
7000118332	5-00-51144- 05050 -0		80	
7000118334	5-00-51144- 05049 -4		100	
7000118337	5-00-51144- 05048 -7		120	
7000118339	5-00-51144- 05047 -0		150	
7000118342	5-00-51144- 05046 -3		180	
7000118345	5-00-51144- 05045 -6		220	
7000118348	5-00-51144- 05044 -9		240	
7000118352	5-00-51144- 05042 -5		320	
7000118355	5-00-51144- 05041 -8		400	
7000118357	5-00-51144- 05040 -1		500	

3M™ Utility Cloth Roll 314D

Provides light-weight cloth sanding strips used for hand sanding in many different applications. Constructed with aluminum oxide abrasive, our utility rolls come in a range of grades for common applications such as deburring, blending and repairing metal finishes, rust or other contaminant removal, and surface preparation for paints and coatings.



Material ID	UPC	Size	Grade/ Backing	Roll/Case
7000118515	5-00-51115- 19793 -7	1" x 50 yd	P60	J 5
7000118514	5-00-51115- 19792 -0		P80	
7000118513	5-00-51115- 19791 -3		P100	
7000118512	5-00-51115- 19790 -6		P120	
7000118510	5-00-51115- 19788 -3		P180	
7000118508	5-00-51115- 19786 -9		P240	
7000118506	5-00-51115- 19784 -5		P320	
7000118505	5-00-51115- 19783 -8		P400	
7000118520	5-00-51115- 19800 -2	1-½" x 20 yd	P120	J 5
7000118519	5-00-51115- 19799 -9		P150	
7000118533	5-00-51115- 19813 -2	1-½" x 50 yd	P50	J 5
7000118532	5-00-51115- 19812 -5		P60	
7000118531	5-00-51115- 19811 -8		P80	
7000118530	5-00-51115- 19810 -1		P100	
7000118529	5-00-51115- 19809 -5		P120	
7000118528	5-00-51115- 19808 -8		P150	
7000118527	5-00-51115- 19807 -1		P180	
7000118526	5-00-51115- 19806 -4		P220	
7000118525	5-00-51115- 19805 -7	2" x 50 yd	P240	J 5
7000118523	5-00-51115- 19803 -3		P320	
7000118522	5-00-51115- 19802 -6		P400	
7000118546	5-00-51115- 19826 -2		P40	
7000118545	5-00-51115- 19825 -5		P50	
7000118544	5-00-51115- 19824 -8		P60	
7000118543	5-00-51115- 19823 -1		P80	
7000118542	5-00-51115- 19822 -4		P100	
7000118541	5-00-51115- 19821 -7		P120	
7000118540	5-00-51115- 19820 -0		P150	
7000118539	5-00-51115- 19819 -4		P180	
7000118538	5-00-51115- 19818 -7		P220	
7000118537	5-00-51115- 19817 -0		P240	
7000118536	5-00-51115- 19816 -3		P280	
7000118535	5-00-51115- 19815 -6		P320	
7000118534	5-00-51115- 19814 -9		P400	



Utility Cloth Sheets

3M™ Utility Cloth Sheet 011K

A lightweight pliable abrasive cloth sheet made with aluminum oxide mineral and used for hand polishing soft metals.



Material ID	UPC	Size	Grade	Sheet/Case
7000118250	5-00-51144- 02433 -4	9" x 11"	Coarse	250
7000118252	5-00-51144- 02432 -7		Medium	
7000118251	5-00-51144- 02431 -0		Fine	

3M™ Utility Cloth Sheet 211K

Provides a light-weight cloth sandpaper used for hand sanding. This closed coat product uses aluminum oxide mineral in its construction. Rolls come in a range of grades for common applications such as repairing (metal finishes, rust or other contaminant removal), deburring, blending and surface preparation for paints and coatings.



Material ID	UPC	Size	Grade/ Backing	Sheet/ Case
7000118253	5-00-51144- 02410 -5	9" x 11"	80	J 250
7000118255	5-00-51144- 02408 -2		120	
7010360277	5-00-51144- 02407 -5		150	
7000118256	5-00-51144- 02406 -8		180	
7010299775	5-00-51144- 02405 -1		220	
7000148116	5-00-51144- 02404 -4		240	
7000118257	5-00-51144- 02402 -0		320	

3M™ Utility Cloth Sheet 314D

Features a closed coat aluminum oxide abrasive bonded to a durable cloth backing suitable for blending, cleaning, contour finishing, deburring and rust removal on all metals and paints.



Material ID	UPC	Size	Grade/ Backing	Sheet/ Case
7000000359	5-00-51115- 19772 -2	9" x 11"	P80	J 250
7000021272	5-00-51115- 19771 -5		P100	
7000000358	5-00-51115- 19770 -8		P120	
7000000357	5-00-51115- 19769 -2		P150	
7000000356	5-00-51115- 19768 -5		P180	
7000118495	5-00-51115- 19767 -8		P220	
7000000354	5-00-51115- 19766 -1		P240	
7000000353	5-00-51115- 19765 -4		P280	
7000000352	5-00-51115- 19764 -7		P320	
7000118494	5-00-51115- 19763 -0		P400	
7000000360	5-00-51115- 19773 -9	9" x 11"	P40	X 250
7000118496	5-00-51115- 19774 -6		P50	
7000118497	5-00-51115- 19775 -3		P60	



Adhesives



Aerosol Adhesives

3M™ Pressure Sensitive Spray Adhesive 72

A permanently tacky industrial grade spray adhesive. This unique adhesive features an added blue color and, combined with a variable spray pattern, allows for a precise application. The very long open bond time provides ample time for positioning of substrates even hours after spraying in order to ensure an ideal fit.



Material ID	UPC	Net Weight	Color	Can/Case
7000046588	5-00-48011- 62837 -5	17.3 oz.	Blue	12

3M™ Foam Fast 74 Spray Adhesive

A fast-drying spray adhesive that bonds foam and fabric to a wide range of substrates. Its permanent bond provides fast results to keep projects moving ahead. The non-yellowing formula dispenses easily in a lace-spray pattern and applies directly onto surfaces and materials where needed.



Material ID	UPC	Net Weight	Color	Can/Case
7000023925	5-00-48011- 62838 -2*	16.9 oz.	Orange	12

*Not for sale or use CA and other states. Consult local air quality rules before use.

3M™ Super 77™ Multipurpose Spray Adhesive

An extremely versatile, fast-drying spray adhesive that bonds a wide range of lightweight materials. Our permanent bond provides fast results to keep projects moving ahead. The photo-safe spray formula is easy to dispense and apply directly onto surfaces and materials where needed, with no soak-in or yellowing over time.



Material ID	UPC	Net Weight	Color	Can/Case
7000000931	5-00-21200- 49868 -3	16.75 oz.	Clear	12

3M™ Super 77™ CA Multi-Purpose Spray Adhesive — Low VOC <25%*

An extremely versatile, fast-drying adhesive that bonds a wide range of lightweight materials quickly, without soaking through. Its fast, aggressive tack makes it ideal for a wide variety of projects.



Material ID	UPC	Net Weight	Color	Can/Case
7100014109	5-00-51111- 97956 -8	18 oz.	Clear	12

*Meets CARB/OTC VOC requirements and helps contribute to LEED® credits. Review applicable VOC requirements to ensure local compliance GREENGUARD Gold Certified.

3M™ Polystyrene Insulation 78 Spray Adhesive

A high strength, industrial grade spray adhesive. It is effective for bonding most types of insulation such as fiberglass and expanded polystyrene foam (EPS) onto numerous kinds of materials.



Material ID	UPC	Net Weight	Color	Can/Case
7000046590	5-00-48011- 62843 -6*	17.9 oz.	Clear	12
7000046591	5-00-51111- 07279 -5		Inverted	

*Not for sale or use CA and other states. Consult local air quality rules before use.

3M™ Rubber & Vinyl 80 Spray Adhesive

A high-performance, neoprene-based contact aerosol adhesive. Formulated for high strength, this adhesive is fast-setting, quickly producing strong bonds ideal for bonding rubber and vinyl sheets, including weather stripping. This spray adhesive also features exceptional heat resistance for bond durability and long-lasting results.



Material ID	UPC	Net Weight	Color	Can/Case
7000028604	5-00-21200- 82618 -9	19 oz.	Yellow	6

*Not for sale or use CA and other states. Consult local air quality rules before use.

3M™ Hi-Strength 90 Spray Adhesive

An extremely versatile, fast-drying spray adhesive that bonds strongly to a wide range of materials. Our permanent bond provides fast results to keep projects moving ahead. The spray formula is easy to dispense, offering a variable-width spray pattern, and applies directly onto surfaces and materials where needed.



Material ID	UPC	Net Weight	Color	Can/Case
7000023924	5-00-48011- 62839 -9	17.6 oz.	Clear	12
7000121418	5-00-76308- 86235 -5	12.23 oz.		
7010292719	5-00-51111- 07278 -8	17.6 oz.	Inverted	

Not for sale or use CA and other states. Consult local air quality rules before use.

3M™ Hi-Strength 90 CA Spray Adhesive — Low VOC <25%*

An extremely versatile, fast-drying spray adhesive that bonds strongly to a wide range of materials. Our permanent bond provides fast results to keep projects moving ahead. The spray formula is easy to dispense, offering a variable-width spray pattern, and applies directly onto surfaces and materials where needed.



Material ID	UPC	Net Weight	Color	Can/Case
7010366483	5-00-51111- 97957 -5	19 oz.	Clear	12

Not for sale or use CA and other states. Consult local air quality rules before use.

*Meets CARB/OTC VOC requirements and helps contribute to LEED® credits. Review applicable VOC requirements to ensure local compliance GREENGUARD Gold Certified.



Cylinder Adhesives

3M™ HoldFast 70 Cylinder Spray Adhesive

An extremely versatile, fast-tacking industrial grade spray adhesive with a unique wide-web spray pattern well suited for bonding a variety of construction materials. It requires a short dry time yet provides long open time to perfectly position your materials. It is an effective adhesive for waterproofing and protecting from moisture.



Material ID	UPC	Size	Weight	Color	Each/Case
7100138479	5-00-48011- 61690 -7	Large	27.3 lbs.	Clear	1

Not for consumer/retail sale or use.

3M™ Hi-Strength 90 Cylinder Spray Adhesive

An extremely versatile, fast-drying spray adhesive that bonds strongly to a wide range of materials. Our permanent bond provides fast results to keep projects moving ahead. The spray formula is easy to dispense, offering a variable-width spray pattern, and applies directly onto surfaces and materials where needed.



Material ID	UPC	Size	Weight	Color	Each/Case
7000028603	5-00-48011- 62849 -8	Large	28.8 lbs.	Clear	1

Not for consumer/retail sale or use.

3M™ General Purpose 60 CA Cylinder Spray Adhesive

An economical low VOC, general purpose spray adhesive ideal for non-critical applications involving large surfaces. Formulated as an affordable option. Delivers fast results for immediate handling.



Material ID	UPC	Size	Weight	Color	Each/Case
7010330388	0-00-48011- 61687 -2	Large	27.3 lbs.	Clear	1

Not for consumer/retail sale or use.

3M™ Hi-Strength Laminating 92 Cylinder Spray Adhesives

A high-tack, industrial-grade spray adhesive that offers a strong hold. This high-performance laminating adhesive is resistant to high temperatures, providing durability and resilience for applications involving large surfaces. Formulated as a fast-tack adhesive, it delivers fast results for immediate handling.



Material ID	UPC	Size	Weight	Color	Each/Case
7100138900	5-00-48011- 61697 -6	Large	29.3 lbs.	Clear	1

Not for consumer/retail sale or use.

Cylinder Accessories

3M™ Cylinder Adhesive Applicator

Standard output device for use with most of our cylinder spray adhesive products and is recommended where normal output rates are desired. We combine durable, all metal construction, a balanced design and comfortable grip to provide effective control during operation.



Material ID	UPC	Type	Output	Includes Tip	Each/Case
7000028628	0-00-48011- 61706 -0	–	Standard	9501	1
7000028630	5-00-51111- 07329 -7	–	High	QSS	
7000046662	5-00-51115- 25779 -2	EX*	Standard	9501	
7000028629	5-00-51115- 25039 -7	H	Reduced	4001	

18" Extension included.

3M™ Cylinder Adhesive Hose

Provide convenient length and portability needed to accomplish small-, medium- and large-area coverage applications, such as flooring, dry wall and hard-to-reach areas. The convenience afforded by the various lengths allows the worker to cover areas with tank in hand or from a bulk tank and keeps the hose from interfering or tangling.



Material ID	UPC	Size	Color	Each/Case
7000046656	0-00-51115- 25036 -1	6'	Black	1
7000028624	0-00-48011- 61988 -0	12'		
7000046657	0-00-48011- 61989 -7	25'		
7000121609	0-00-51115- 25782 -7	50'		

3M™ Cylinder Adhesive Spray Tips

Control your adhesive output from 2 to 18". Proper spray patterns provide uniform coverage and consistent drying times to help keep projects moving forward.

Material ID	UPC	Spray Tip	Each/Case
7000046659	0-00-48011- 61993 -4	QSS	1
7000046661	0-00-48011- 61707 -7	9501	
7000046658	0-00-48011- 61991 -0	6501	
7000028626	0-00-48011- 61990 -3	4001	





Adhesive Removers

3M™ Adhesive Remover

3M™ Adhesive Removers are excellent for removing adhesive residue, or for cleaning surfaces prior to bonding. It cleans and removes heavy oils, grease, silicone, tar, paraffinic materials such as wax, labels, stickers, dirt, marker graffiti, gum and other soil and contaminants from a variety of substrates.



Material ID	UPC	Prod ID	Net Weight	Color	Can/Case
7000121409	5-00-21200- 49179 -0*	6040	5 oz.	Pale Yellow	6
7000121410	5-00-21200- 49048 -9*	6041	18.5 oz.		

*Not for sale or use CA and other states. Consult local air quality rules before use.

3M™ Cylinder Adhesive Removers

Excellent for removing adhesive residue, or for cleaning surfaces prior to bonding. It cleans and removes heavy oils, grease, silicone, tar, paraffinic materials such as wax, labels, stickers, dirt, marker graffiti, gum and other soil and contaminants from a variety of substrates.



Material ID	UPC	Size	Weight	Color	Cyl/Case
7100138124	5-00-51115- 25748 -8	Mini	8.5 lbs.	Pale Yellow	1

Not for consumer/retail sale or use.

3M™ Adhesive Remover — Low VOC <20%*

Ideal for helping dissolve and remove dirt, grease, tar, and many non-curing type adhesives. They clean without streaking and have proven to be excellent for surface preparation in adhesive applications. While these multipurpose cleaners are suitable for industrial use, they are also safe enough for everyday projects.



Material ID	UPC	Net Weight	Color	Can/Case
7000121420	5-00-51111- 97974 -2	18.7 oz.	Clear	12

Not for sale or use CA and other states. Consult local air quality rules before use.

*Meets CARB/OTC VOC requirements and helps contribute to LEED® credits. Review applicable VOC requirements to ensure local compliance GREENGUARD Gold Certified.



Polyurethane Sealants

3M™ Polyurethane Construction Sealant 525

A single-component, moisture-curing, gap-filling elastomeric sealant that creates permanently elastic seals and bonds well to concrete. Skin time in 90–150 minutes.




Material ID	UPC	Container	Weight	Color	Each/Case
7100200170	5-00-48011- 62823 -8	Cartridge	10.1 fl. oz.	Gray	12
7000028609	5-00-51111- 07535 -2	Sausage Pack	600mL		

3M™ Polyurethane Sealant 540

An all-purpose, single-component, moisture-curing, gap-filling polyurethane that creates permanently elastic seals and bonds in a wide variety of service environments.



Material ID	UPC	Container	Weight	Color	Each/Case
7000000941	5-00-21200- 49054 -0	Cartridge	10.1 fl. oz.	White	12
7000000942	5-00-21200- 41594 -9			Gray	
7100001804	5-00-21200- 41595 -6			Black	
7100198006	5-00-21200- 96277 -1	Sausage Pack	400mL	Gray	12
7100198004	5-00-21200- 96278 -8			White	
7100198008	5-00-21200- 96276 -4			Black	
7100198007	5-00-76308- 14303 -4		600mL	Gray	
7100198005	5-00-21200- 56561 -3			White	
7100198009	5-00-21200- 96272 -6			Black	



Air Filtration




Air Filters

3M™ MERV 8 Electrostatic Filters

3M™ MERV 8 Electrostatic Filters are designed for general air filtration in all types of residential cooling, heating and ventilation systems. They are a better-performing upgrade from fiberglass and non-electrostatic filters. The electrostatic filter media helps protect equipment from unwanted particles and is also easy on HVAC systems, with low initial pressure drop and good airflow.



Material ID	UPC	Size	Filter/Case
1"			
7100218182	5-06-38060- 65987 -3	12" x 12" x 1"	12
7100218188	5-06-38060- 65992 -7	12" x 20" x 1"	
7100218181	5-06-38060- 65988 -0	14" x 14" x 1"	12
7100218203	5-06-38060- 65986 -6	14" x 20" x 1"	
7100218193	5-06-38060- 65994 -1	14" x 24" x 1"	
7100218183	5-06-38060- 65985 -9	14" x 25" x 1"	
7100218192	5-06-38060- 65995 -8	14" x 30" x 1"	
7100218082	5-06-38060- 65977 -4	16" x 20" x 1"	12
7100218191	5-06-38060- 65996 -5	16" x 24" x 1"	
7100218195	5-06-38060- 65979 -8	16" x 25" x 1"	
7100218186	5-06-38060- 65991 -0	18" x 18" x 1"	12
7100218196	5-06-38060- 65999 -6	18" x 20" x 1"	
7100218159	5-06-38060- 65981 -1	20" x 20" x 1"	12
7100218197	5-06-38060- 66000 -8	20" x 22" x 1"	
7100218162	5-06-38060- 65983 -5	20" x 25" x 1"	
7100218180	5-06-38060- 65989 -7	24" x 24" x 1"	12
7100218198	5-06-38060- 66001 -5	25" x 30" x 1"	12
2"			
7100218194	5-06-38060- 65993 -4	12" x 24" x 2"	6
7100218083	5-06-38060- 65978 -1	16" x 20" x 2"	6
7100218199	5-06-38060- 65980 -4	16" x 25" x 2"	
7100218190	5-06-38060- 65997 -2	16" x 24" x 2"	
7100218179	5-06-38060- 65982 -8	20" x 20" x 2"	6
7100218189	5-06-38060- 65998 -9	20" x 24" x 2"	
7100218161	5-06-38060- 65984 -2	20" x 25" x 2"	
7100218187	5-06-38060- 65990 -3	24" x 24" x 2"	6





Electrical



Electrical Tapes

Scotch® Super 33+™ Vinyl Electrical Tape

7-mil thick, premium-grade, all-weather, vinyl electrical tape that is designed to provide electrical insulation for cable splices up to 600V. The flame-retardant tape withstands a temperature range of 0–221°F (-18–105°C).



Material ID	UPC	Size	Color	Roll/Case
7100002398	5-00-54007- 06130 -9	¾" x 20'	Black	100
7000057831	5-00-54007- 06132 -3	¾" x 66'		
7000058432	5-00-54007- 00053 -7	¾" x 36 yds		48

More colors available.

Scotch® Vinyl Electrical Tape Super 88

8.5-mil thick, premium-grade, all-weather, vinyl electrical tape that is designed to provide a protective jacket and primary electrical insulation for splices up to 600V. The flame-retardant tape withstands a temperature range of 0–221°F (-18–105°C).



Material ID	UPC	Size	Color	Roll/Case
7000006092	5-00-54007- 06143 -9	¾" x 66'	Black	100

Scotch® Vinyl Color Coding Electrical Tape 35

A 7-mil thick, premium-grade, color-coded electrical tape. This flame-retardant tape is suitable for use in phase identification, color coding of motor leads and piping systems and for marking safety areas. This tape is 600V-rated and withstands a temperature range of 32–221°F (0–105°C).




Material ID	UPC	Size	Color	Roll/Case
7000132637	5-00-54007- 10240 -8	½" x 20'	Blue	100
7000132638	5-00-54007- 10299 -6		Brown	
7000132640	5-00-54007- 10281 -1		Gray	
7000132639	5-00-54007- 10265 -1		Green	
7000058438	5-00-54007- 10273 -6		Orange	
7000132636	5-00-54007- 10224 -8		Red	
7100067890	5-00-54007- 49923 -2		Violet	
7000058436	5-00-54007- 10232 -3		White	
7000058435	5-00-54007- 10257 -6		Yellow	
7000006095	5-00-54007- 10836 -3	¾" x 66'	Blue	100
7000031580	5-00-54007- 10885 -1		Brown	
7000006099	5-00-54007- 00072 -8		Gray	
7000006098	5-00-54007- 10851 -6		Green	
7000031581	5-00-54007- 10869 -1		Orange	
7010411602	5-00-51128- 61333 -2		Pink	
7000006094	5-00-54007- 10810 -3		Red	
7000058437	5-00-54007- 11271 -1		Violet	
7000006097	5-00-54007- 10828 -8		White	
7000006096	5-00-54007- 10844 -8		Yellow	



3M™ Scotchrap™ Vinyl Corrosion Protection Tape 50

A premium-grade, 10-mil thick, all-weather, PVC backing tape. It withstands temperatures of -55–176 °F (-48–80°C). This high-tack adhesive tape offers resistance to corrosion, impact, abrasion and puncture, making it suitable for use on metal piping systems, conduits and fittings both above and below ground.



Material ID	UPC	Size	Color	Roll/Case
7000005812	5-00-54007- 10638 -3	2" x 100'	Black	24

3M™ Economy Vinyl Electrical Tape 1400

A 7-mil thick, economy, electrical tape with a rubber adhesive. This low-voltage, flame-retardant tape is designed to provide electrical insulation for all wires and cables and is rated up to 600V. It continuously performs in temperatures up to 176°F (80°C).



Material ID	UPC	Size	Color	Roll/Case
7010398051	5-00-51128- 58297 -3	¾" x 60'	Black	100
7010398062	5-00-51128- 58424 -3		Blue	
7010349674	5-00-51128- 58425 -0		Brown	
7010398063	5-00-51128- 58426 -7		Gray	
7010319708	5-00-51128- 58427 -4		Green	
7010297493	5-00-51128- 58430 -4		Orange	
7010398064	5-00-51128- 58428 -1		Red	
7010398065	5-00-51128- 58431 -1		Violet	
7010349675	5-00-51128- 58429 -8		White	
7010349676	5-00-51128- 58432 -8		Yellow	



Electrical Tapes

3M™ Temflex™ Vinyl Electrical Tape 1700

A 7-mil thick, general-purpose, vinyl electrical tape. This flame-retardant tape is designed for protective jacketing and harnessing. This tape is 600V-rated and withstands a temperature range of 32–176°F (0–80°C).



Material ID	UPC	Size	Color	Roll/Case
7000008400	5-00-51138- 94316 -0	¾" x 60'	Black	100
7000132902	5-00-54007- 43962 -7	1" x 66'		99

More colors available.

Scotch® Linerless Rubber Splicing Tape 130C

A linerless 30-mil thick, premium-grade, rubber splicing tape used for splicing and terminating cables and wires. It withstands temperatures up to 194°F (90°C) with emergency overload up to 266°F (130°C). The tape has excellent electrical and mechanical properties to provide moisture-seal protection.




Material ID	UPC	Size	Color	Roll/Case
7000006085	5-00-54007- 41717 -5	¾" x 30'	Black	24

Direct Bury Kits

3M™ Direct Bury Splice Kits

Combine the quick, reliable connection of a 3M™ Performance Plus™ Wire Connector with the moisture resistance of a high impact, UV resistant tube prefilled with moisture resistant grease. It is UL Listed for 600 volts in direct bury applications.




Material ID	UPC	Prod	AWG	Kit/Case
7000006238	5-00-51128- 59076 -3	DBO/B-6	18–10	100 Bulk
7000006235	5-00-51128- 58574 -5	DBR/Y-6		



Standard Cable Ties

3M™ Standard Nylon Cable Ties

Made with high-quality nylon 6/6 and designed to secure wire bundles and harness components quickly, without slipping. The curved tip allows for faster threading and installation, and they feature a self-locking head.



TENSILE KEY:

M = Miniature I = Intermediator S = Standard LHD = Light Heavy Duty

Material ID	UPC	Prod	Tensile	Color	Ea/Inner (Cs)
8"					
7010398268	5-00-51128- 59280 -4	CT8BK18-C	M	Black	100 (1,000)
7010349804	5-00-51128- 59281 -1	CT8BK18-M		Black	1,000 (10,000)
7000031852	5-00-51128- 59283 -5	CT8NT18-M		Beige	
7100027555	5-00-51128- 59288 -0	CT8BK40-C	I	Black	100 (1,000)
7010400105	5-00-51128- 59291 -0	CT8NT40-M		Beige	1,000 (10,000)
7000031853	5-00-51128- 59293 -4	CT8BK50-C	S	Black	100 (1,000)
7010400149	5-00-51128- 59559 -1	CT8RD50-C		Red	
7000133464	5-00-51128- 59310 -8	CT8BK120-L	LHD	Black	50 (500)
7000133460	5-00-51128- 59299 -6	CT8NT50-M	S	Beige	10,000
7000031851	5-00-51128- 59282 -8	CT8NT18-C	M	Beige	100 (1,000)
7000133456	5-00-51128- 59290 -3	CT8NT40-C	I	Beige	
7000031854	5-00-51128- 59294 -1	CT8BK50-M		Black	
11"					
7000133461	5-00-51128- 59301 -6	CT11BK50-D	I	Black	500 (2,500)
7000133462	5-00-51128- 59303 -0	CT11NT50-D		Beige	
7010349835	5-00-51128- 59560 -7	CT11RD50-C		Red	100 (1,000)
7000058850	5-00-51128- 59300 -9	CT11BK50-C		Black	
7000031856	5-00-51128- 59302 -3	CT11NT50-C		Beige	
15"					
7000031857	5-00-51128- 59304 -7	CT15BK50-C	I	Black	100 (1,000)
7000031859	5-00-51128- 59307 -8	CT15NT50-C		Beige	
7000133463	5-00-51128- 59309 -2	CT15NT50-D		Beige	500 (2,500)
7000133466	5-00-51128- 59313 -9	CT15BK120-D	LHD	Black	
7000031860	5-00-51128- 59312 -2	CT15BK120-C		Black	
7000031858	5-00-51128- 59305 -4	CT15BK50-D	I	Black	500 (2,500)
7000133469	5-00-51128- 59317 -7	CT15NT120-D	LHD	Beige	
7100038009	5-00-51128- 59315 -3	CT15NT120-C		Beige	100 (1,000)




Wire Connectors

3M™ Highland™ Wire Connectors

Make it quick and easy to match the right connector to the size of the wire. The shells are designed to withstand temperatures up to 221°F (105°C). Highland wire connectors are UL Listed and work equally well with either solid or stranded copper wire.



Material ID	UPC	Prod	AWG	Color	Ea/Inner (Cs)
7010290980	5-00-54007- 43134 -8	H-29	22-16	Gray	1,000
7010348890	5-00-76308- 92441 -1	H-29-POUCH			100 (1,000)
7010304019	5-00-54007- 43123 -2	H-30	22-14	Blue	1,000
7010397048	5-00-54007- 43124 -9	H-30-KEG			10,000
7010303651	5-00-76308- 92442 -8	H-30-POUCH			100 (1,000)
7010349040	5-00-54007- 43119 -5	H-31	18-14	Orange	1,000
7010396549	5-00-76308- 92443 -5	H-31-BAG			500 (10,000)
7010293621	5-00-54007- 43120 -1	H-31-KEG			10,000
7010348891	5-00-76308- 92444 -2	H-31-POUCH			100 (1,000)
7010349033	5-00-54007- 43137 -9	H-33	18-12	Yellow	1,000
7010320417	5-00-54007- 43139 -3	H-33-KEG			5,000
7010396550	5-00-76308- 92445 -9	H-33-BAG			500 (5,000)
7010318552	5-00-76308- 92446 -6	H-33-POUCH			100 (1,000)
7010349034	5-00-54007- 43141 -6	H-35	18-10	Red	1,000
7010396551	5-00-76308- 92447 -3	H-35-BAG			250 (2,500)
7010348892	5-00-76308- 92448 -0	H-35-POUCH			100 (1,000)

3M™ Performance Plus™ Wire Connectors

Designed with a uniquely flexible spring that has generous room for expansion and a strong bite for a secure connection. Because of their increased wire range, just three Performance Plus wire connectors handle the work of eight standard connectors. And the flexible skirt helps prevent copper exposure for enhanced safety.



Material ID	UPC	Prod	AWG	Color	Ea/Inner (Cs)
7000058825	5-00-54007- 43151 -5	B/G+JUG	14-16	Blue/Gray	250 (200)
7100127167	5-00-76308- 92464 -0	B/G+POUCH			50 (500)
7000133222	5-00-54007- 43153 -9	O/B+JUG	22-12	Orange/Blue	500 (10,000)
7100127195	5-00-76308- 92465 -7	O/B+POUCH			100 (1,000)
7000058824	5-00-54007- 43155 -3	R/Y+JUG	22-8	Red/Yellow	500 (4,000)
7100127164	5-00-76308- 92466 -4	R/Y+POUCH			100 (1,000)
7000133219	5-00-51128- 57943 -0	R/Y+KEG			17,000
7100019140	5-00-51128- 54455 -1	T/R+JUG		Tan/Red	750 (6,000)
7100127165	5-00-76308- 92467 -1	T/R+POUCH			100 (1,000)
7000132941	5-00-51128- 54456 -8	T/R+KEG	22-12	Tan/Yellow	25,000
7000133223	5-00-51128- 55219 -8	T/Y+JUG			500 (10,000)
7100127163	5-00-76308- 92468 -8	T/Y+POUCH			100 (1,000)
7000133268	5-00-51128- 58623 -0	T/Y+KEG			40,000



Fire Protection



Fire Barrier Foams

3M™ Fire Block Foam FB-Foam

A fireblock and draftstop used to help seal, fill, insulate and bond for non-rated residential and commercial construction. This foam-in-place fireblock is heat-resistant up to 240°F (115°C) and meets ASTM E 84 (mod) Class 1 for smoke spread and flame development. This fireblock foam is ready-to-use and tack-free in approximately 5 minutes.



Material ID	UPC	Net Weight	Color	Cans/Case
7100006734	5-00-51115- 54907 -1	12 fl. oz.	Orange	12

3M™ Fire Barrier Rated Foam, FIP 1-Step

A two-part urethane, smoke, sound and firestopping foam designed to expand up to 5 times in volume after dispensing. This intumescent foam can be used to fill the annular space created by pipes and cables penetrating through fire-rated construction. It's an alternative to mineral wool, bricks, pillows and runny, ineffective foams and is UL listed.




Material ID	UPC	Net Weight	Color	Each/Case
7100020738	5-00-51115- 54925 -5	12.85 fl. oz.	Maroon	6

Fire Barrier Hard Goods

3M™ Fire Barrier Block B258

A pre-formed foam block designed for easy installation to effectively seal larger openings against smoke, toxic gas and flame. It is simple to use and helps reduce sound transmission.



Material ID	UPC	Size	Color	Block/Case
7010305974	5-00-76308- 97939 -8	2-2 ³ / ₄ " x 5- ¹ / ₈ " x 8"	Maroon	12

3M™ Fire Barrier Plank PK39

A pre-formed foam plank designed for easy installation to effectively seal larger openings against smoke, toxic gas and flame. It is simple to use and helps reduce sound transmission.



Material ID	UPC	Size	Color	Plank/Case
7010401344	5-00-76308- 98231 -2	39 ³ / ₈ " x 5- ¹ / ₈ " x 2-2 ³ / ₄ "	Maroon	3

Albion® Manual Dispenser

Manually operated dispenser (gun) for use with 3M™ Fire Barrier Rated Foam FIP 1-Step.

Material ID	UPC	Description	Each/Case
7100169332	0-00-76308- 14612 -2	HandyMax Dispenser HMS-G4C2	1

Albion® Battery Operated Power Dispenser

Battery operated dispenser (gun) for use with 3M™ Fire Barrier Rated Foam FIP 1-Step. Battery delivers fade-free power until end of discharge.

Material ID	UPC	Description	Each/Case
7100170625	0-00-76308- 14610 -8	Dispenser	1
7100169439	0-00-76308- 14614 -6	18V Li-ion Battery	

3M™ Fire Barrier Plug

A replacement foam plug for 2" round 3M™ Fire Barrier Pass-Through Device. This product works together with the device to help prevent the spread of smoke and fire. These foam plugs enhance the cold and hot smoke seal and help the system achieve UL classified L-Rating.



Material ID	UPC	Prod ID	Size	Color	Plug/Case
7010353409	5-00-76308- 98126 -1	PL62	2"	Maroon	4
7010401345	5-00-76308- 98203 -9	PL64	4"		



Fire Barrier Hard Goods

3M™ Fire Barrier Cast-In Devices

Provide one-step firestopping for penetrations through fire-rated concrete floor assemblies. Instead of drilling holes, installers simply attach the devices directly to floor decking, pour slabs around them and route penetrants after curing. Heights are easily adjustable, and these intumescent devices are rated for up to 3-hour fire protection.



Material ID	UPC	Prod ID	Size	Color	Each/Case
For Metal Pipe					
7100138825	5-00-51115- 16540 -0	2MCID	2"	Red	12
7100138824	5-00-51115- 16541 -7	3MCID	3"		
7100138823	5-00-51115- 16542 -4	4MCID	4"		6
7100138822	5-00-51115- 16543 -1	6MCID	6"		2
For Plastic Pipes					
7100138821	5-00-51115- 16536 -3	2PCID	2"	Red	12
7100138820	5-00-51115- 16537 -0	3PCID	3"		
7100138819	5-00-51115- 16538 -7	4PCID	4"		6
7100138818	5-00-51115- 16539 -4	6PCID	6"		2

3M™ Fire Barrier Cast-In Device Height Adaptors

1-piece extensions that provide up to 4" of additional height to 3M™ Fire Barrier Cast-In Devices. No fasteners are required and installers simply snap the adaptor onto a metallic or non-metallic Cast-In Device. Adaptors adjust to accommodate concrete slab pour depths up to 12" thick. Adaptor/device assemblies are firestop tested up to 3 hours.



Material ID	UPC	Prod ID	Size	Color	Each/Case
7000133836	5-00-51115- 16548 -6	2HA	2"	Red	12
7000133837	5-00-51115- 16549 -3	3HA	3"		
7000133838	5-00-51115- 16550 -9	4HA	4"		
7000133839	5-00-51115- 16551 -6	6HA	6"		

3M™ Fire Barrier Cast-In Device Metal Deck Adaptors

Are one-piece plastic body adaptors for one-step firestopping on fluted metal decks. Installers simply snap a metallic or non-metallic 3M™ Fire Barrier Cast-In Device into the adaptor — no fasteners are required — and attach it to the metal decking before concrete slabs are poured. Adaptor/device assemblies are firestop tested up to 3 hours.



Material ID	UPC	Prod ID	Size	Color	Each/Case
7000133834	5-00-51115- 16544 -8	2MDA	2"	Red	12
7000148879	5-00-51115- 16545 -5	3MDA	3"		
7000133835	5-00-51115- 16546 -2	4MDA	4"		
7000148880	5-00-51115- 16547 -9	6MDA	6"		

3M™ Fire Barrier Cast-In Tub Box Assembly, Foam

Create a void on the top surface of a concrete slab to allow for plumbing. Simply remove the foam insert after the slab is cured to access the void. This provides a secure and permanent firestop solution. Firestop tested for up to 3 hours, when used in conjunction with a 2" (50.8 mm) 3M™ Fire Barrier Cast-In Device for metallic and non-metallic penetrations, in accordance with ASTM E 814 (UL 1479).



Material ID	UPC	Prod ID	Size	Color	Each/Case
7000148881	5-00-51115- 16586 -8	3TB	8" x 12" x 3"	Red	6

3M™ Fire Barrier RC-1 Restricting Collar


Works with our 3M™ Fire Barrier Wrap Strip FS-195+ or Ultra GS firestops for through penetrations in wall, floor and floor/ceiling assemblies. Durable 28-gauge steel collar is easily cut to fit the pipe diameter. The collar secures the firestop and provides tabs for anchoring to walls or floor slabs, helping ensure stability for effective firestops.



Material ID	UPC	Size	Color	Each/Case
7100009600	5-00-54007- 08324 -0	2" x 25'	Silver	1

3M™ Fire Barrier Composite Sheet CS-195+

A lightweight intumescent firestop that combines four components into a single system to help slow the spread of fire, smoke and noxious gases. Sheets combine 28-gauge steel, intumescent material, wire mesh and aluminum foil and are easy to handle and install with common trade tools. They are firestop tested for up to 4 hours of fire protection.



Material ID	UPC	Size	Color	Each/Case
7100139139	0-00-51115- 07437 -0	16" x 28"	Silver	1
7100006140	0-00-51115- 08260 -3	28" x 52"		
7100011414	0-00-51115- 07220 -8	36" x 24"		
7100011415	0-00-51115- 07222 -2	36" x 36"		
7000006372	0-00-51115- 07224 -6	36" x 41"		

3M™ Fire Barrier Mortar

A lightweight, gypsum-based powder that mixes with water to form a heat-absorbing firestop for through penetrations in fire-rated floor or wall assemblies. Versatile mortar can be mixed self-leveling or non-sag, and adheres to a range of construction substrates and penetrants. It also acts as a heat sink, reducing the chance of fire on unexposed sides of the assembly.



Material ID	UPC	Size	Color	Each/Case
7000031968	0-00-51115- 54901 -4	5 Gallon Pail	Off-White	1
7000031967	0-00-51115- 54900 -7	44 lb. Bag		



Fire Barrier Hard Goods

3M™ Fire Barrier Moldable Putty Pads MPP+

A one-part firestop material used in various fire-rated assemblies, such as electrical box protection. Designed to prevent spread of fire, smoke and noxious gasses, this intumescent material comes ready to use in convenient 1/10" (2.54mm) thick pads that are conformable by hand with no mixing or tools. Pads are firestop tested up to 4 hours.



Material ID	UPC	Size	Color	Each/Case
7000059410	5-00-51115-16508-0	4" x 8"	Red	100
7100134123	5-00-51115-16509-7	7" x 7"		20
7000031965	5-00-51115-16510-3	9-½" x 9-½"		

3M™ Fire Barrier Moldable Putty Stix MP+

A one-part, re-enterable, intumescent putty that can be easily formed to firestop through penetrations and blank openings in fire-rated assemblies. We formulated this dark red, easily moldable putty stick to provide up to 4 hours of fire protection. These putty stix produce a draft and cold smoke seal and reduce noise transfer.



Material ID	UPC	Size	Color	Each/Case
7000006381	5-00-51115-16526-4	1.4" x 11"	Red	10

3M™ Fire Barrier Putty Sleeve Kits

Designed to help prevent the passage of fire and smoke in new or existing cable penetrations through walls or floors. Kits are tested up to 4 hours for fire-rated through penetration systems (in accordance with ASTM E814). No gasket is required with this product and it allows for both new and retrofit data and telecom cable firestop installations.



Material ID	UPC	Size	Color	Kit/Case
7000145572	0-00-51115-18809-1	1"	Silver	1
7000145571	0-00-51115-18808-4	2"		
7000145570	0-00-51115-18806-0	4"		

3M™ Fire Barrier Pass-Through Devices

One-piece hinged metal enclosures designed to prevent the passage of fire, smoke and toxic gas. This easily-installed device is ideal for firestopping penetrations in high traffic areas where telecom, data or electrical cables are frequently added or removed. Intumescent material and foam smoke seals achieve a 3 hour fire protection rating.



Material ID	UPC	Prod	Size	Type	Each/Case
7000059412	5-00-51115-18773-0	PTRD2	2"	Round	6
7000059406	5-00-51115-16598-1	PTRD4	4"		
7100004181	5-00-51115-16597-4	PT4SD	4"	Square	

3M™ Fire Barrier Pass-Through Device Foam Plugs


Designed for closing 3M™ Fire Barrier Pass-Through Devices which are used in wall and floor through-penetrations. They are simple to use and help reduce sound and smoke transmission. During a fire, this product, used in conjunction with a 3M™ Fire Barrier Pass-Through Device, helps maintain a tight seal against smoke.



Material ID	UPC	Size	Type	Each/Case
7010304637	0-00-51115-18793-3	2"	Round	24
7100035288	0-00-51115-18791-9	4"		
7100084021	0-00-51115-18794-0	4"	Square	

3M™ Fire Barrier Pass-Through Device Mounting Brackets

Designed for use in conjunction with our 3M™ Fire Barrier Pass-Through Devices to support and strengthen firestop through penetration installations. Metal brackets come in pairs for securing the device on each side of the floor or wall assembly.



Material ID	UPC	Size	Mounting	Type	Color	Each/Case
7000133842	5-00-51115- 18774 -7	2"	Single	Round	Silver	24
7000059409	5-00-51115- 18754 -9	4"	Single			24
7000059407	5-00-51115- 18752 -5	4"	Single	Square		24
7000133843	5-00-51115- 18777 -8	8" x 12"	Sixplex			6
7000059408	5-00-51115- 18753 -2	4" x 12"	Triple			48



Fire Barrier Hard Goods

3M™ Fire Barrier Pillows

Self-contained, intumescent products designed for use in through-penetration firestops, providing up to 3 hours of protection. This fire barrier pillow expands to form a hard char that tightly seals against flame spread, smoke and toxic gases. We also engineered this product to be re-enterable and re-useable for new or retrofit installations. Self-locking pillows also available — featuring interlacing strips to easily lock multiple pillows together to achieve precise fill and compression with no additional support required.



Material ID	UPC	Size	Type	Each/Case
7100138835	5-00-51115- 16530 -1	2" x 4" x 9"	Small	24
7100016178	5-00-51115- 16531 -8	2" x 6" x 9"	Medium	16
7100138834	5-00-51115- 16532 -5	3" x 6" x 9"	Large	20
Self-Locking				
7100138833	5-00-51115- 16578 -3	2" x 4" x 9"	Small	24
7100138832	5-00-51115- 16579 -0	2" x 6" x 9"	Medium	16
7100138831	5-00-51115- 16580 -6	3" x 6" x 9"	Large	20

3M™ Fire Barrier Plastic Pipe Device

Designed for 6" non-metallic pipe in new and retrofit through penetration installations. This one-piece metal collar assembly is designed to fit smoothly around the pipe with no assembly required, and provides anchor tabs for stability. It is firestop tested up to 2 hours in tested and listed systems.



Material ID	UPC	Product	Size	Color	Each/Case
7100139136	5-00-51115- 08253 -0	PPD6	6"	Silver	5
7100139138	5-00-51115- 08378 -0	ULTRA PPD1.5	1-½"		10
7000006374	5-00-51115- 08379 -7	ULTRA-PPD2	2"		
7000006375	5-00-51115- 08380 -3	ULTRA-PPD3	3"		
7000006376	5-00-51115- 08381 -0	ULTRA-PPD4	4"		

3M™ Fire Barrier Packing Material PM4

An alternative packing material to mineral wool, fiberglass and backer rod in UL-listed through-penetration 3M firestop systems. Strong, flexible and non-combustible per ASTM E 136, this non-asbestos mold-resistant material is fully portable and can be installed without tools.



Material ID	UPC	Size	Thick	Color	Roll/Case
7000059411	5-00-51115- 1876 -8	4" x 20'-½"	½"	Off-White	5

3M™ Fire Barrier Tuck-In Wrap Strips


Intumescent wrap strips that are primarily used in top-side firestop installations. Engineered to help eliminate the need for retaining collars, concrete screws, ladders etc., saving time and labor. They are flexible around pipe, fill tough areas and gaps, and come with an adhesive-backed label for quick installation.



Material ID	UPC	Prod ID	Size	Color	Each/Case
7000006387	5-00-51115- 18814 -0	WS 200	2"	Red	24
7000006388	5-00-51115- 18815 -7	WS 300	3"		
7000006389	5-00-51115- 18817 -1	WS 400	4"		
7000006390	5-00-51115- 18821 -8	WS ROLL	8.2'		6

3M™ Fire Barrier Wrap Strips FS-195+

Convenient and cost-effective, firestop for plastic pipes insulated pipe and cable, blank and other penetrations in fire-rated wall, floor and floor/ceiling assemblies. This intumescent firestop with aluminum foil exterior blocks flame, heat and toxic by-products of combustion. Installers simply wrap the strips around the penetration, secure and seal.



Material ID	UPC	Size	Color	Each/Case
7000006371	5-00-51115- 07115 -2	2" x 24" Roll	Red	10

3M™ Fire Barrier Ultra GS Wrap Strip

A quick, cost-effective firestop for non-metallic pipe, insulated pipe and combo penetrations in fire-rated wall, floor and floor/ceiling assemblies. This graphite-based intumescent firestop blocks flame, heat and toxic by-products of combustion. Rolled strip is easily cut to size and the flexible material conforms even to irregular-shaped penetrations.



Material ID	UPC	Size	Color	Each/Case
7000006380	5-00-51115- 16507 -3	2" x 40' Roll	Black	5



Fire Barrier Tapes

3M™ Fire and Water Barrier Tape

An elastomeric fire, water, smoke and sound tape. When installed properly it can act as a barrier to water leakage and airborne sound transmission, while helping to control the transmission of fire, heat and smoke.



Material ID	UPC	Prod ID	Size	Color	Roll/Case
7100139307	5-00-76308- 86899 -9	FWBT2	2" x 75'	Translucent	24
7100166471	5-00-76308- 14453 -6	FWBT3	3" x 75'		24
7100139303	5-00-76308- 86900 -2	FWBT4	4" x 75'		12
7100166467	5-06-38060- 13899 -6	FWBT6	6" x 75'		8
7100139309	5-00-76308- 86901 -9	FWBT8	8" x 75'		4
7100139304	5-00-76308- 86902 -6	FWBT12	12" x 75'		4

3M™ Smoke and Sound Tapes

An elastomeric tape that can act as a barrier to smoke and airborne sound in non-fire-rated wall and floor assemblies.



Material ID	UPC	Prod ID	Size	Color	Roll/Case
7100138393	5-00-76308- 86903 -3	SST2	2" x 75'	Translucent	24
7100152602	5-00-76308- 14452 -9	SST3	3" x 75'		16
7100139305	5-00-76308- 86936 -1	SST4	4" x 75'		12
7100138394	5-00-76308- 86937 -8	SST8	8" x 75'	Gray	4
7100138395	5-00-76308- 86938 -5	SST12	12" x 75'		

Sealants & Sprays

3M™ FireDam™ Spray 200

A sprayable material that dries to form a tough, elastomeric coating. It will firestop building joints, curtain wall perimeter joints and through penetration seals to control the transmission of fire, heat, smoke and noxious gas. This water-based firestop sealer is applied with conventional airless sprayers, dries quickly and cleans up easily.



Material ID	UPC	Size	Color	Each/Case
7000026567	0-00-51115- 18798 -8	5 Gallon Pail	Red	1
7100006336	0-00-51115- 18797 -1		Gray	

3M™ Fire Barrier Water Tight Sealant 1003 SL

A self-leveling silicone sealant firestop that creates a flexible seal and resists moisture across floors and other horizontal surfaces. This ready-to-use, single component neutral cure firestop is tested to ASTM and UL standards to help control the spread of fire, smoke and noxious gasses.



Material ID	UPC	Size	Color	Each/Case
7000059388	5-00-51115- 11538 -2	10.1 fl. oz. Cartridge	Light Gray	12
7000059414	5-00-51115- 18789 -1	20 fl. oz. Sausage		
7000059389	5-00-51115- 11540 -5	4.5 Gallon Pail		1

3M™ Fire Barrier Water Tight Sealant 1000 NS

A ready-to-use, single component, neutral cure, silicone sealant that cures upon exposure to atmospheric humidity to form a flexible firestop seal. Our water tight sealants help control the spread of fire, smoke and noxious gases before, during and after exposure to fire.



Material ID	UPC	Size	Color	Each/Case
7000006377	5-00-51115- 11535 -1	10.1 fl. oz. Cartridge	Light Gray	12
7010353044	5-00-51115- 18790 -7	20 fl. oz. Sausage		
7000006378	5-00-51115- 11537 -5	4.5 Gallon Pail		1

3M™ Fire Barrier Silicone Sealant 2000+

An elastomeric, ready-to-use, single-component, neutral-cure silicone sealant that cures upon exposure to atmospheric humidity. We designed this sealant to form a flexible firestop seal that also acts as a barrier to airborne sound transmission. This product is firestop tested up to 3 hours in accordance with ASTM E 814 (UL 1479) and CAN/ULC S115.



Material ID	UPC	Size	Color	Each/Case
7100139278	5-00-51115- 11558 -0	10.3 fl. oz. Cartridge	Light Gray	12
7100139277	5-00-51115- 11559 -7	4.5 Gallon Pail		1



Sealants & Sprays

3M™ Fire Barrier Water Tight Sealant 3000 WT

A gun-grade, intumescent, silicone, elastomeric sealant that cures upon exposure to the atmosphere to form a monolithic flexible firestop seal. Properly installed, this sealant helps control the spread of fire, smoke and noxious gasses before, during and after exposure to fire and exhibits good adhesion to a full range of construction substrates.



Material ID	UPC	Size	Color	Each/Case
7000006386	5-00-51115- 16593 -6	10.1 fl. oz. Cartridge	Gray	12
7000059413	5-00-51115- 18788 -4	20 fl. oz Sausage		12
7100006306	5-00-51115- 16594 -3	4.5 Gallon Pail		1

3M™ Fire Barrier Sealant CP 25WB+

A fire sealant to dry and form a monolithic firestop seal that also acts as a barrier to airborne sound transmission. A red, one-component, gun-grade, latex-based, intumescent firestop sealant. This fire barrier sealant helps control the spread of fire, smoke and noxious gases before, during and after exposure to a fire.



Material ID	UPC	Size	Color	Each/Case
7000006383	5-00-51115- 11638 -9	10.1 fl. oz. Cartridge	Red	12
7000059394	5-00-51115- 11641 -9	27 fl. oz. Cartridge		6
7000145569	5-00-51115- 11642 -6	20 fl. oz. Sausage		10
7100006311	0-00-51115- 11639 -1	2 Gallon Pail		1
7000006379	0-00-51115- 11640 -7	5 Gallon Pail		

3M™ Fire Block Sealant FB 136

A one component, non-combustible draft, smoke and fireblocking sealant, designed to resist high temperatures and smoke passage in nonrated construction. Use to seal interior construction voids around wires, pipes, HVAC ducts and vents, in wood or steel framed non-rated construction.



Material ID	UPC	Size	Color	Each/Case
7100155919	5-00-51115- 16591 -2	10.1 fl. oz. Cartridge	Blue	12

3M™ Fire Barrier Sealant FD 150+

A gun-grade, latex-based, elastomeric sealant that cures upon exposure to the atmosphere to form a monolithic flexible firestop seal. This sealant helps control the spread of fire, smoke and noxious gasses before, during and after exposure to a fire. Excellent adhesion to substrates.



Material ID	UPC	Size	Color	Each/Case
7000059420	5-00-51115- 11574 -0	10.1 fl. oz. Cartridge	Blue	12
7010400774	5-00-51115- 18812 -6		Red	
7000133848	5-00-51115- 11602 -0	28 fl. oz. Cartridge	Blue	6
7010320536	5-00-51115- 18811 -9		Red	
7100009734	5-00-51115- 16567 -7	20 fl. oz. Sausage	Limestone	12
7100044834	5-00-51115- 11634 -1		Blue	
7100040146	5-00-51115- 18810 -2		Red	
7100027887	5-00-51115- 16565 -3	4.5 Gallon Pail	Limestone	1
7000059421	5-00-51115- 11575 -7		Blue	
7000140773	0-00-51115- 18813 -8		Red	

3M™ Fire Barrier Sealant IC 15WB+

Engineered to form a monolithic seal after drying. One-part, gun-grade, intumescent firestop sealant that provides up to 3-hour fire protection in tested and listed systems. Helps prevent the spread of fire, smoke and noxious gas, while acting as an acoustic barrier to help minimize noise transfer.



Material ID	UPC	Size	Color	Each/Case
7100011413	5-00-51115- 16557 -8	10.1 fl. oz. Cartridge	Yellow	12
7000059405	5-00-51115- 16560 -8	20 fl. oz. Sausage		10
7000059404	0-00-51115- 16558 -0	4.5 Gallon Pail		1

3M™ Smoke and Sound Sealant SS100

A designed to seal construction joints and through penetrations in non-fire-rated wall and floor assemblies. In addition, this latex sealant acts as a draftstop to prevent unwanted air movement while providing a barrier against dust and other airborne particulates.



Material ID	UPC	Size	Color	Each/Case
7100038650	5-00-51115- 54923 -1	20 fl. oz. Sausage	White	12



Sealants & Sprays

3M™ Fire Barrier Watertight Spray

A sprayable, moisture-curing hybrid siliconized polymer that forms a tough, elastomeric coating. This material is used to firestop perimeter joints (curtain wall joints) and other construction joints that need to prevent fire and water from moving floor to floor.



Material ID	UPC	Size	Color	Each/Case
7100139274	0-00-76308- 98232 -4	5 Gallon Pail	Red	1
7100138396	0-00-76308- 86113 -1		White	



Wraps

3M™ Fire Barrier Plenum Wrap 5A+

A fire-resistant wrap that consists of an inorganic fiber blanket encapsulated with a scrim-reinforced foil. We designed this plenum wrap as a strong, lightweight and flexible material for easy installation. This product is engineered to create a fire-resistive enclosure that can reduce flame and smoke spread ratings to acceptable levels in return air plenums.



Material ID	UPC	Size	Thick	Color	Roll/Case
7000133846	0-00-51115- 18802 -2	½" x 24" x 50'	½"	Silver	1
7000059415	5-00-51115- 18805 -8	½" x 48" x 25'			2

3M™ Dryer Ventilation Wrap

A fire-resistant wrap that consists of an inorganic fiber blanket encapsulated with a scrim-reinforced foil. We designed this dryer ventilation wrap as a strong, lightweight and flexible material for easy installation. This product is engineered to create a fire-resistive enclosure capable of 1-hour ratings to acceptable levels for dryer and kitchen ventilation ducts in wood frame fire rated construction.



Material ID	UPC	Size	Color	Roll/Case
7100216418	5-06-38060- 40469 -5	16" x 25' x 0.5"	Silver	1
7100216834	5-06-38060- 40495 -4	20" x 25' x 0.5"		
7100216417	5-06-38060- 40496 -1	32" x 25' x 0.5"		

3M™ Fire Barrier Duct Wrap 615+


Thin, lightweight and flexible. Provides excellent insulating capabilities and offers a space-saving alternative to traditional bulky fire protection methods obtained through a gypsum wall shaft or enclosure. This wrap is commonly used in commercial kitchen grease ducts, as well as ventilation ducts.



Material ID	UPC	Size	Color	Roll/Case
7000059419	0-00-51115- 54905 -2	24" x 25'	Silver	1
7100004463	0-00-51115- 54906 -9	48" x 25'		2

3M™ Interam™ Endothermic Mat E-5A-4

Easy-to-install heat-absorbing wrap system that provides excellent fire resistance for structural steel components, critical electrical components and wall opening membranes. When exposed to intense heat, the mat releases chemically-bound water to cool its outer surfaces. Installers can easily cut the material to fit even complex installations.



Material ID	UPC	Size	Color	Roll/Case
7000031969	0-00-51115- 54913 -7	24.5" x 20'	Silver	1



Safety



Disposable Respirators

3M™ Particulate Respirator 8200, N95

Economical disposable N95 particulate respirator designed to help provide reliable worker respiratory protection against certain non-oil based particles.



Material ID	UPC	Size	Color	Each/Case
7000052787	5-00-51131- 07023 -8	Standard	White	160

3M™ Particulate Respirator 8210, N95

Classic disposable N95 particulate respirator designed to help provide comfortable, reliable worker respiratory protection against certain non-oil based particles.



Material ID	UPC	Size	Color	Each/Case
7100132742	5-00-51138- 46457 -3	Standard	White	160

3M™ Particulate Respirator 8210Plus, N95

This disposable N95 particulate respirator offers braided headbands and staple free attachment points. It is designed to help provide comfortable, reliable worker respiratory protection against certain non-oil based particles.



Material ID	UPC	Size	Color	Each/Case
7000002176	5-00-51131- 52924 -8	Standard	White	160

3M™ Particulate Respirator 8210V, N95

This disposable N95 particulate respirator featuring 3M™ Cool Flow™ Valve helps provide comfortable, reliable worker respiratory protection against certain non-oil based particles. Ideally suited for hot/dusty work settings or long periods of wear.



Material ID	UPC	Size	Color	Each/Case
7000002462	5-00-51131- 49711 -0	Standard	White	80

3M™ Particulate Respirator 8511, N95

This disposable N95 particulate respirator features the proprietary 3M™ Cool Flow™ Valve and helps provide comfortable, reliable worker respiratory protection. It is ideally suited for hot/dusty work settings that require long periods of wear.



Material ID	UPC	Size	Color	Each/Case
7000002056	5-00-51138- 54343 -8	Standard	White	80

3M™ Aura™ Particulate Respirator 9211+, N95

Three panel disposable flat fold respirator features soft inner material and 3M™ Cool Flow™ Valve to help provide comfortable, reliable worker respiratory protection. Ideally suited for hot/dusty work settings that require long periods of wear.



Material ID	UPC	Size	Color	Each/Case
7100110432	5-88-87719- 99716 -9	Standard	White	120

Reusable Respirators

3M™ Half Facepiece Reusable Respirators

This half facepiece reusable respirator offers reliable and convenient respiratory protection and is suitable for many situations, helping provide protection against particulates and a wide variety of gases and vapors according to NIOSH approvals.



Material ID	UPC	Prod ID	Size	Each/Case
7000001933	5-00-51131- 07025 -2	6200	Medium	24
7000001934	5-00-51131- 07026 -9	6300	Large	

3M™ Full Facepiece Reusable Respirators

This full facepiece reusable respirator offers lightweight comfort and ease of use. Combine with appropriate 3M™ particulate filters or cartridges to help provide respiratory protection against particulates and/or a variety of gases and vapors.



Material ID	UPC	Prod ID	Size	Each/Case
7000002030	5-00-51138- 54146 -5	6800	Medium	4
7000002037	5-00-51138- 54159 -5	6900	Large	



Reusable Respirators

3M™ Half Facepiece Reusable Respirator 7500 Series

This half facepiece reusable respirator uses advanced silicone material to help provide comfortable and durable respiratory protection. The 3M™ Cool Flow™ Valve helps make breathing easier and can reduce heat and moisture build-up for cool, dry comfort.



Material ID	UPC	Prod ID	Size	Each/Case
7000002162	5-00-51131- 37082 -6	7502	Medium	10
7100134949	5-00-51131- 37083 -3	7503	Large	

3M™ Rugged Comfort Quick Latch Half Facepiece Reusable Respirator

This facepiece combines comfort, durability, and stability. The proprietary quick latch design offers an easy, one-hand touch drop-down mechanism for putting the facepiece on and/or off while moving in and out of contaminated areas.



Material ID	UPC	Prod ID	Size	Each/Case
7000128239	5-00-51131- 49490 -4	6502QL	Medium	10
7000128241	5-00-51131- 49492 -8	6503QL	Large	10

Reusable Respirator Cartridges & Filters

3M™ Particulate Filters 2000 Series

99.97% filter efficiency meets NIOSH P100-series test criteria. Protection against oil and non-oil based particulate contaminants. Bayonet compatibility allows use with many 3M half and full facepiece designs.



Material ID	UPC	Product ID	Each/Case
7000002058	5-00-51138- 54356 -8	2071 Particulate Filter, P95	100
7000051991	5-00-51131- 07000 -9	2091 Particulate Filter, P100	
7000029657	5-00-51131- 07184 -6	2097 Particulate Filter, P100 with Nuisance Level Organic Vapor Relief*	

*3M recommended for relief against nuisance levels of organic vapors. Nuisance level organic vapor refers to concentrations not exceeding OSHA PEL or applicable government occupational exposure limits, whichever is lower. Do not use for respiratory protection against organic vapors.

3M™ Combination Cartridges/ P100 Particulate Filters 6000 Series

P100 Particulate filter is permanently attached to cartridge for easy, one-step assembly. Full range of cartridges. Swept-back design allows an enhanced field of view and comfort. Bayonet compatibility allows use with many 3M half and full facepiece designs.



Material ID	UPC	Product ID	Each/Case
7000029639	5-00-51138- 46465 -8	60921 Cartridge/Filter, Organic Vapor/P100	60
7000029640	5-00-51138- 46467 -2	60923 Cartridge/Filter, Organic Vapor/Acid Gas/P100	
7000002041	5-00-51138- 54187 -8	60926 Cartridge/Filter, Multi-Gas/Vapor/P100	

3M™ Gas/Vapor Cartridges 6000 Series

NIOSH approved against certain organic vapors. Swept-back design allows an enhanced field of view and comfort. Bayonet compatibility allows use with many 3M half and full facepiece designs.



Material ID	UPC	Product ID	Each/Case
7000051851	5-00-51138- 21674 -5	6001 Cartridge, Organic Vapor	60
7000051849	5-00-51131- 07047 -4	6003 Cartridge, Organic Vapor/Acid Gas	
7000002040	5-00-51138- 54186 -1	6006 Cartridge, Multi Gas/Vapor	

3M™ Particulate Filter 7093, P100

NIOSH approved for environments containing certain oil and non-oil based particles. Bayonet compatibility allows use with many 3M half and full facepiece designs.



Material ID	UPC	Prod ID	Type	Each/Case
7000002154	5-00-51131- 52705 -3	7093	P100	60
7000002155	5-00-51131- 52706 -0	7093B		144















Eye Protection

	Material ID	UPC	Prod ID	Color	Pair/Case	Features
3M™ SecureFit™ Protective Eyewear – 200 Series						
	7100090435	1-00-78371- 65717 -5	SF201AF	Clear Anti-Fog Lens	20	<ul style="list-style-type: none">Secure, comfortable fit with 3M™ Pressure Diffusion Temple (PDT) TechnologyPolycarbonate lens absorbs 99.9% UVA & UVB; meets the requirements of ANSI Z87.1-2015Contemporary and lightweight, weighs less than 1 oz.Molded nose bridge
	7000128262	1-00-78371- 65720 -5	SF201AS	Clear Anti-Scratch Lens		
	7100180044	5-00-51131- 27843 -6	SF201SGAF-BLU	Blue Temple, Scotchgard™ Anti-Fog Coating		
	7100022210	1-00-78371- 65718 -2	SF202AF	Gray Anti-Fog Lens		
	7100022211	1-00-78371- 65721 -2	SF202AS	Gray Anti-Scratch Lens		
	7100021793	1-00-78371- 65719 -9	SF203AF	Amber Anti-Fog Lens		
	7010293198	1-00-78371- 65722 -9	SF203AS	Amber Anti-Scratch Lens		
3M™ SecureFit™ Protective Eyewear – 400 Series						
	7100112435	1-00-78371- 66211 -7	SF401AF	Clear Anti-Fog Coating	20	<ul style="list-style-type: none">Motion-inspired, contoured piping in bold, modern colorsProprietary 3M™ Pressure Diffusion Temple (PDT) Technology minimizes pressure over the ear without compromising securityAvailable in a variety of lens colors for a range of applications; polycarbonate lenses absorb 99.9% of UVA and UVB raysAll options meet the requirements of ANSI Z87.1 Standard as an Impact Rated spectacleEffective for at least 25 washes with water,* Scotchgard™ Anti-fog Lens Coating provides abrasion and fog resistance <p>*When tested using EN168 Resistance to Fogging of Oculars and Resistance to Surface Damage by Fine Particles test methods.</p>
	7100112131	5-00-51131- 27475 -9	SF401AF-FM	Clear Anti-Fog Coating, Foam Gasket		
	7100158218	5-00-51131- 27715 -6	SF401SGAF-RED	Red/Gray, Scotchgard™ Anti-Fog Coating		
	7100150838	5-00-51131- 27728 -6	SF401SGAF-BLU	Blue/Gray, Scotchgard™ Anti-Fog Coating		
	7100156104	5-00-51131- 27731 -6	SF401SGAF-BLU-F	Blue/Gray, Scotchgard™ Anti-Fog Coating, Foam Gasket		
	7100112433	1-00-78371- 66212 -4	SF402AF	Gray Anti-fog Coating		
	7100112244	5-00-51131- 27565 -7	SF402AF-FM	Gray Anti-Fog Coating, Foam Gasket		
	7100156101	5-00-51131- 27734 -7	SF402SGAF-BLU	Blue/Gray, Scotchgard™ Anti-Fog Coating		
	7100156137	5-00-51131- 27732 -3	SF402SGAF-BLU-F	Blue/Gray, Scotchgard™ Anti-Fog Coating, Foam Gasket		
	7100158219	5-00-51131- 27735 -4	SF403SGAF-YEL	Yellow/Black, Amber Scotchgard™ Anti-fog Coating.		
	7100155940	5-00-51131- 27736 -1	SF405SGAF-BLA	Black/Brown, Brown Scotchgard™ Anti-fog Coating.		
	7100156103	5-00-51131- 27729 -3	SF407SGAF-BLU	Blue/Gray, Gray Scotchgard™ Anti-fog Coating.		
	7100112436	1-00-78371- 66213 -1	SF410AS	Indoor/Outdoor Mirror Anti-Scratch Lens		
	7100112223	5-00-51131- 27545 -9	SF410AS-FM	Indoor/Outdoor Mirror AntiScratch Lens, Foam Gasket		
	7100115326	1-00-78371- 66512 -5	SF415AF	Clear Anti-Fog Coating, +1.5 Diopter		
	7100115325	1-00-78371- 166513 -2	SF420AF	Clear Anti-Fog Coating, +2.0 Diopter		
3M™ SecureFit™ Protective Eyewear – 400X Series						
	7100180045	5-00-51131- 27845 -0	SF401XAF-GRN	Hi-Vis Green/Black, Clear Anti-Fog Coating	20	<ul style="list-style-type: none">Contoured brow guard rests comfortably against forehead3M™ Pressure Diffusion Temple TechnologySoft nosepiece to help reduce slippage
	7100180048	5-00-51131- 27848 -1	SF401XSGAF-GRN	Hi-Vis Green/Clear, Clear Scotchgard™ Anti-Fog Coating		

See Warnings on Page 45



Eye Protection

Material ID	UPC	Prod ID	Color	Pair/Case	Features
3M™ SecureFit™ Protective Eyewear – 600 Series					
	7100128689	5-00-51131- 27337 -0	SF601SGAF	Clear Scotchgard™ Anti-Fog Coating	<div>20</div> <ul style="list-style-type: none">Secure, comfortable fit with 3M™ Pressure Diffusion Temple (PDT) TechnologyLong lasting clarity with 3M™ Scotchgard™ Anti-fog Coating which retains its effectiveness for at least 25 washings with water*Stylish, sturdy frame that nearly anyone can wearOptional removable foam-lined gasket helps keep debris out of your eyes while providing comfort and cushioningAdditional personal protective equipment may be required for SF617AS, SF630AS and SF650AS <p>*When tested using EN168 Resistance to Fogging of Oculars and Resistance to Surface Damage by Fine Particles test methods.</p>
	7100133322	5-00-51131- 27340 -0	SF601SGAF-FM	Clear Scotchgard™ Anti-fog Coating, Foam Gasket	
	7100128690	5-00-51131- 27338 -7	SF602SGAF	Gray Scotchgard™ Anti-Fog Lens	
	7100132350	5-00-51131- 27341 -7	SF602SGAF-FM	Clear Scotchgard™ Anti-Fog Lens, Foam Gasket	
	7100132351	5-00-51131- 27342 -4	SF607SGAF	Indoor/Outdoor, Grey Scotchgard™ Anti-fog Coating	
	7100132359	5-00-51131- 27348 -6	SF620SGAF	Clear Scotchgard™ Anti-fog Coating	
	7100132361	5-00-51131- 27351 -6	SF620GSGAF	Grey Scotchgard™ Anti-fog Coating	
3M™ SecureFit™ Protective Eyewear – 3700 Series					
	7100203179	5-00-51131- 27896 -2	SF3701SGAF-BLU	Blue Temple, Scotchgard™ Anti-Fog Coating	<div>10</div> <ul style="list-style-type: none">Over-the-glass protectionAll day wearabilityAngle adjustment points on the temple
3M™ Virtua™ Protective Eyewear					
	7100112434	1-00-78371- 62105 -3	11329-00000-20	Clear Anti-Fog Coating, Clear Temple	<div>20</div> <ul style="list-style-type: none">Holds the cord of the earplug to keep it securely in place and untangled while in useAllows the corded earplugs to dual as a lanyardWraparound design provides extended eye protection and unobstructed viewingFoam gasket helps limit eye exposure to nuisance dust while providing additional cushioning.Contoured temples fit comfortably and snugly
	7100114636	1-00-78371- 62102 -2	11327-00000-20	Gray Hard Coat Lens, Gray Temple	
	7000128259	1-00-78371- 11872 -0	11872-00000-20	Clear Anti-Fog Coating, Foam Gasket	
	7000029998	1-00-78371- 62036 -0	11672-00000-20	Clear Anti-fog Coating, Black/Gray Temple	
3M™ GoggleGear™ — Protective Eyewear Safety Goggles					
	7100112956	5-00-51131- 27561 -9	GG501NS-GAF	Clear Scotchgard™ Anti-fog Coating, Neoprene Strap	<div>10</div> <ul style="list-style-type: none">Modern designIndirect ventingAnti-scratch and 3M™ Scotchgard™ Anti-fog coating which retains its effectiveness for at least 25 washings with water*Clear polycarbonate lensD3 (droplet and splash) rated4 (dust) rated <p>*When tested using EN168 Resistance to Fogging of Oculars and Resistance to Surface Damage by Fine Particles test methods.</p>
	7100079187	5-00-51131- 27455 -1	GG501SGAF	Clear Scotchgard™ Anti-fog Coating	
	7100168468	5-00-51131- 27711 -8	GG502SGAF	Grey Clear Scotchgard™ Anti-fog Coating	
	7010386529	5-00-51131- 27437 -7	GG2891-SGAF	Clear Scotchgard™ Anti-fog Coating	
	7010386491	5-00-51131- 27439 -1	GG2892-SGAF	Grey, Scotchgard™ Anti-fog Coating	
	7100191924	5-00-51131- 27898 -6	GG6001SGAF-BLK	Black Shroud, Clear Scotchgard™ Anti-fog Coating	
	7100191926	5-00-51131- 27899 -3	GG6001SGAF-RED	Red Shroud, Clear Scotchgard™ Anti-fog Coating	

See Warnings on Page 45



Head Protection

3M™ Hard Hats — 700 Series

A comfortable, tough and lightweight protective headgear that helps protect the top of the head due to the potential hazard of small falling objects or exposed fixed objects that may be bumped into. Protective hard hat with vents and comfortable 4 point ratchet suspension and standard brow pad. Available in several colors. Meets requirements of ANSI/ISEA Z89.1 2014 Type I.



Material ID	UPC	Color	Each/Case	Vented	UVicator™
7000002416	1-00-78371-64199-0	Blue	20		
7000128174	1-00-78371-65552-2		20		•
7000002420	1-00-78371-64209-6		20	•	
7000128178	1-00-78371-65557-7		20	•	•
7000030065	1-00-78371-64204-1	Gray	20		
7010384834	1-00-78371-65697-0		20		•
7010385059	1-00-78371-66541-5		20	•	
7010316601	1-00-78371-66552-1	Green	20	•	•
7000030062	1-00-78371-64200-3		20		
7000128175	1-00-78371-65553-9		20		•
7000052942	1-00-78371-64210-2		20	•	
7000128179	1-00-78371-65558-4	Orange	20	•	•
7000030063	1-00-78371-64202-7		20		
7010341147	1-00-78371-65654-3		20		•
7100084762	1-00-78371-66539-2	Red	20	•	
7010342429	1-00-78371-66550-7		20	•	•
7000002417	1-00-78371-64201-0		20		
7100081972	1-00-78371-65695-6	White	20		•
7100065187	1-00-78371-66538-5		20	•	
7100081973	1-00-78371-66549-1		20	•	•
7000002414	1-00-78371-64197-6	Yellow	20		
7000053152	1-00-78371-65550-8		20		•
7000002418	1-00-78371-64207-2		20	•	
7000053153	1-00-78371-65555-3		20	•	•
7000002415	1-00-78371-64198-3	Hi-Vis Orange	20		
7000128173	1-00-78371-65551-5		20		•
7000002419	1-00-78371-64208-9		20	•	
7000128177	1-00-78371-65556-0	Hi-Vis Yellow	20	•	•
7000030064	1-00-78371-64203-4		20		
7100046566	1-00-78371-66291-9		20		•
7010342428	1-00-78371-66540-8		20	•	
7010385061	1-00-78371-66551-4		20	•	•
7000030066	1-00-78371-64205-8		20		
7000128176	1-00-78371-65554-6		20		•
7010384679	1-00-78371-65590-4		20	•	
7010385062	1-00-78371-66553-8		20	•	•

3M™ Hard Hats Full Brim — 800 Series

Protective full brim hard hat with vents, comfortable 4 point ratchet suspension, standard brow pad and UVicator™ Sensor. Available in several colors. Meets requirements of ANSI/ISEA Z89.1 2014 Type I.



Material ID	UPC	Color	Each/Case	Vented	UVicator™
7000053176	1-00-78371-65777-9	Blue	20		
7000144977	1-00-78371-65799-1		20		•
7000144967	1-00-78371-65788-5		20	•	
7000144988	1-00-78371-65810-3		20	•	•
7000144961	1-00-78371-65782-3	Gray	20		
7000144982	1-00-78371-65804-2		20		•
7000144972	1-00-78371-65793-9		20	•	
7000144993	1-00-78371-65815-8		20	•	•
7000053177	1-00-78371-65778-6	Green	20		
7000144978	1-00-78371-65800-4		20		•
7000144968	1-00-78371-65789-2		20	•	
7000144989	1-00-78371-65811-0		20	•	•
7000144959	1-00-78371-65780-9	Orange	20		
7000144980	1-00-78371-65802-8		20		•
7000144970	1-00-78371-65791-5		20	•	
7000144991	1-00-78371-65813-4		20	•	•
7000053178	1-00-78371-65779-3	Red	20		
7000144979	1-00-78371-65801-1		20		•
7000144969	1-00-78371-65790-8		20	•	
7000144990	1-00-78371-65812-7		20	•	•
7000144957	1-00-78371-65775-5	White	20		
7000053179	1-00-78371-65797-7		20		•
7000144965	1-00-78371-65786-1		20	•	
7000144986	1-00-78371-65808-0		20	•	•
7000144958	1-00-78371-65776-2	Yellow	20		
7000144976	1-00-78371-65798-4		20		•
7000144966	1-00-78371-65787-8		20	•	
7000144987	1-00-78371-65809-7		20	•	•
7000144960	1-00-78371-65781-6	Hi-Vis Orange	20		
7000144981	1-00-78371-65803-5		20		•
7000144971	1-00-78371-65792-2		20	•	
7000144992	1-00-78371-65814-1		20	•	•
7000144962	1-00-78371-65783-0	Hi-Vis Yellow	20		
7000144983	1-00-78371-65805-9		20		•
7000144973	1-00-78371-65794-6		20	•	
7000144994	1-00-78371-65816-5		20	•	•



Head Protection

3M™ SecureFit™ Safety Helmet X5000

Provides comfort and security for workers in a variety of situations because it features climbing helmet-inspired design that meets occupational safety requirements, works with a variety of 3M faceshields, earmuffs and other accessories, and the suspension incorporates exclusive 3M patented Pressure Diffusion technology.



Material ID	UPC	Color	Each/Case	Vented
7100175576	5-00-76308- 94305 -4	Black	10	
7100175584	5-00-76308- 94313 -9			•
7100175568	5-00-76308- 94297 -2		4	•
7100175560	5-00-76308- 94289 -7			
7100175572	5-00-76308- 94301 -6	Blue	10	•
7100175580	5-00-76308- 94309 -2			•
7100175564	5-00-76308- 94293 -4		4	
7100175556	5-00-76308- 94285 -9			
7100175573	5-00-76308- 94302 -3	Green	10	•
7100175581	5-00-76308- 94310 -8			•
7100175565	5-00-76308- 94294 -1		4	
7100175557	5-00-76308- 94286 -6			
7100175575	5-00-76308- 94304 -7	Orange	10	•
7100175583	5-00-76308- 94312 -2			•
7100175567	5-00-76308- 94296 -5		4	
7100175559	5-00-76308- 94288 -0			
7100175574	5-00-76308- 94303 -0	Red	10	•
7100175582	5-00-76308- 94311 -5			•
7100175566	5-00-76308- 94295 -8		4	
7100175558	5-00-76308- 94287 -3			
7100175570	5-00-76308- 94299 -6	White	10	•
7100175578	5-00-76308- 94307 -8			•
7100175562	5-00-76308- 94291 -0		4	
7100175554	5-00-76308- 94283 -5			
7100175571	5-00-76308- 94300 -9	Yellow	10	•
7100175579	5-00-76308- 94308 -5			•
7100175563	5-00-76308- 94292 -7		4	
7100175555	5-00-76308- 94284 -2			
7100175577	5-00-76308- 94306 -1	Hi-Viz Green	10	•
7100175569	5-00-76308- 94298 -9			•
7100175561	5-00-76308- 94290 -3		4	
7100175585	5-00-76308- 94314 -6			•

Hearing Protection

3M™ Foam Earplugs 1100

Foam earplugs feature soft, hypoallergenic foam and a tapered design to fit comfortably in the ear canal. One size fits most.



Material ID	UPC	Description	Color	Pair/Case
7100099847	5-00-51138- 29009 -7	Corded	Orange	500
7100099848	5-00-51138- 29008 -0	Uncorded		1,000

3M™ E-A-R™ Classic™ Earplugs

Uncorded earplugs set the standard in hearing protection as the world's first foam earplugs. Constructed from slow-recovery foam, the disposable earplug comes in a clean, convenient pillow pack.



Material ID	UPC	Prod	Color	Pair/Case
7000002299	1-00-80529- 10000 -6	310-1001	Yellow	2,000

3M™ E-A-Rsoft™ FX™ Earplugs

Earplugs feature a bell shape and super-soft, slow-recovery foam to effectively seal the ear canal and provide reliable hearing protection.



Material ID	UPC	Prod ID	Desc.	Color	Pair/Case
7000127177	1-00-80529- 12085 -1	312-1260	Corded	Yellow	2,000
7000029951	1-00-80529- 12086 -8	312-1261	Uncorded		

3M™ E-A-Rsoft™ Yellow Neon Blasts™

Corded earplugs seal the ear canal with soft, slow-recovery foam for excellent noise reduction and comfort.



Material ID	UPC	Prod	Color	Pair/Case
7000052721	1-00-80529- 11035 -7	311-1252	Yellow/Red	2,000

3M™ E-A-Rsoft™ Yellow Neons™ Earplugs

Earplugs seal the ear canal with soft, slow-recovery foam for excellent noise reduction and comfort.



Material ID	UPC	Prod ID	Desc.	Color	Pair/Case
7000002306	1-00-80529- 11033 -3	311-1250	Corded	Yellow	2,000
7000002303	1-00-80529- 12063 -9	312-1250	Uncorded		



Hearing Protection

3M™ E-A-R™ Push-Ins™ Earplugs

All-day hearing comfort, convenience and protection. Constructed of 3M™ E-A-Rform™ foam, these earplugs feature a no roll-down design and a blue stem for a quick and easy fit. One size fits most.



Material ID	UPC	Prod ID	Desc.	Color	Pair/Case
7000127213	1-00-80529- 18001 -5	318-1001	Corded	Blue	400
7000052745	1-00-80529- 18000 -8	318-1000	Uncorded		

3M™ Skull Screws™ Earplugs

Push-to fit uncorded foam earplugs sport the tough look of threaded metal, but feel of soft foam, while offering push-to-fit convenience and noise attenuation with attitude. Effective hearing protection and compliance with a clean, easy twist.



Material ID	UPC	Prod ID	Desc.	Color	Pair/Case
7000127182	1-00-93045- 92952 -5	P1301	Corded	Silver	480
7000127181	1-00-93045- 92951 -8	P1300	Uncorded		

3M™ E-A-R™ UltraFit™ Earplugs

Features a proprietary, premolded, triple-flange design that fits comfortably in most earcanals.



Material ID	UPC	Prod ID	Color	Pair/Case
7000002320	1-00-80529- 40003 -8	340-4004	Yellow	400

The 3M™ PELTOR™ EEP-100 Electronic Earplugs

Helps protect your hearing, and can help improve situational awareness and communications in challenging environments. This kit includes a protective charging case and an assortment of eartips.



Material ID	UPC	Prod ID	Pair/Case
7100193144	0-00-51131- 27743 -4	EEP-100	10

3M™ Peltor™ X Series Over the Head Earmuffs

This lightweight earmuff is designed for protection against high-level industrial noise and other loud sounds. It features an electrically insulated wire headband, often referred to as "dielectric". One size fits most. The X3A features a newly designed spacer to help improve attenuation without the need for a much larger cup or double cup design. One size fits most.



Material ID	UPC	Prod ID	Color	Each/Case
Hard Hat Attached				
7000104075	1-00-93045- 93728 -5	X1P3E	Black/ Green	10
7100135816	1-00-78371- 67135 -5	X1P51E	Black	
7100135827	1-00-78371- 67136 -2	X4P51E	Black	
Cap-Attached				
7000104077	1-00-93045- 93730 -8	X3P3E	Black/ Red	10
7000104078	1-00-93045- 93731 -5	X4P3E	Black/ Chartreuse	
7000104076	1-00-93045- 93729 -2	X2P3E	Black/ Yellow	
7000104079	1-00-93045- 93732 -2	X5P3E	Black/ Grey	
Over-the-Head				
7000104070	1-00-93045- 93723 -0	X1A	Black/ Green	10
7000104072	1-00-93045- 93725 -4	X3A	Black/ Red	
7000104073	1-00-93045- 93726 -1	X4A	Black/ Chartreuse	
7100135827	1-00-93045- 93727 -8	X5A	Black	

The 3M™ PELTOR™ Wireless Communication Accessory

The X Series Earmuffs can help keep you protected while allowing you to communicate in noisy environments. Take that important call without stepping away your work. The Wireless Communication Accessory easily attaches to your existing 3M™ PELTOR™ X Series earmuffs. Bluetooth® Technology.



Material ID	UPC	Prod ID	Each/Case
7100143063	1-00-78371- 67137 -9	WS-CUSH	10



Powered & Supplied Air

3M™ Versaflo™ Heavy Industry PAPR Kit TR-300N+ HIK

A complete, ready to use HE PAPR system for industrial applications. Provides protection against particulates.



Material ID	UPC	Prod ID	Kit/Case
7100153815	0-00-76308- 94269 -4	TR-300N+ HIK	1

3M™ Versaflo™ PAPR Assembly

Workers can customize their respiratory protection system by choosing the headtop. With the option to customize, workers can design a respiratory system that meets their specific needs. Suggested industries include: Pharmaceutical and Healthcare.



Material ID	UPC	Prod ID	Color	Kit/Case
7100098537	0-00-51131- 27502 -7	TR-614-HK	Gray	1



3M™ Versaflo™ Heavy Industry PAPR Kit TR-600-HIK

This ready-to-use kit provides a simple way to purchase a complete PAPR system for use in rugged environments such as industrial, demolition, grinding, metal finishing and casting operations.



Material ID	UPC	Prod ID	Color	Kit/Case
7100035755	0-00-51131- 37374 -7	TR-600-HIK	Gray	1

3M™ Versaflo™ Respiratory Hard Hat Assembly M-307, with Premium Visor and Faceseal

Used with an approved air source, M-300 Series hard hats provide respiratory (OSHA APF=25) and limited head (ANSI Z89.1-2003 Type 1 Class G) and eye (ANSI Z87.1-2010) protection. The M-307 assembly includes a premium visor and premium faceseal.



Material ID	UPC	Prod ID	Size	Color	Each/Case
7000052874	0-00-51131- 17317 -0	M-307	M	White	25

Protective Coveralls

3M™ Protective Coverall 4510

A disposable safety work wear made of a high quality microporous laminated material. It helps provide basic barrier protection against light liquid splashes and hazardous dusts.

Material ID	UPC	Size	Color	Each/Case
7000109028	0-00-51131- 49788 -7	M	White	25
7000109029	0-00-51131- 49789 -4	L		
7000109030	0-00-51131- 49790 -0	XL		
7000109031	0-00-51131- 49791 -7	XXL		
7000109032	0-00-51131- 49792 -4	3XL		



See Warnings on Page 45



Work Gloves

3M™ Comfort Grip Gloves


A nitrile palm coating that makes these gloves a light, flexible, abrasion-resistant and long lasting alternative to many cotton and latex palm-coated gloves. They provide excellent grip, even in wet or oily conditions. Elastic knit wrist cuff is easy to pull on and off quickly and keeps out debris.


	Material ID	UPC	Prod ID	Size	Pairs/Bag	ANSI* Cut Level	EN388**
General Use							
	7100034912	5-00-54007- 98954 -2	CGM-GU	8M	6	N/A	3122A
	7100034911	5-00-54007- 98955 -9	CGL-GU	9L			
	7100034910	5-00-54007- 98956 -6	CGXL-GU	10XL			
Winter							
	7010352930	5-00-54007- 99150 -7	CGM-W	8M	6	N/A	2121A
	7010305066	5-00-54007- 99151 -4	CGL-W	9L			
	7010352931	5-00-54007- 99152 -1	CGXL-W	10XL			
Cut Resistant							
	7100023132	5-00-54007- 98957 -3	CGM-CR	8M	6	A3	4444D
	7100023421	5-00-54007- 98958 -0	CGL-CR	9L			
	7100023131	5-00-54007- 98959 -7	CGXL-CR	10XL			
	7100097229	5-00-51128- 61032 -4	CGM-CRE	8M	6	A1	4342B
	7100097230	5-00-51128- 61033 -1	CGL-CRE	9L			
	7100023131	5-00-51128- 61034 -8	CGXL-CRE	10XL			

*ANSI 105-2016 Cut Level (A1 – A9). Previous ANSI ratings based on ANSI 105-2011 Cut Level (0-5). For more information on ratings changes, please reach out to your 3M sales representative.

**EN 388:2016: Abrasion Level (1-4), Coupe Cut Level (1-5), Tear (1-4), Puncture (1-4), TDM Cut Test (A-F). Please note that the TDM cut resistance test is the reference performance result, and the Coupe test results are only indicative where both cut resistance test results are shown for EN388:2016. Previous EN 388 levels based on EN 388 2003: Abrasion (1-4), Coupe cut test (1-5), Tear (1-4), Puncture (1-4). For more information on ratings changes, please reach out to your 3M sales representative.

Safety Warnings

	<p>⚠ WARNING: RESPIRATORS</p> <p>These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 29 CFR 1910.134 including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. Misuse may result in sickness or death. For correct use, consult supervisor and User Instructions or call 3M Technical Service in the U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414.</p>
---	---

	<p>⚠ WARNING: HEARING PROTECTION</p> <p>These hearing protectors help reduce exposure to hazardous noise and other loud sounds. Misuse or failure to wear hearing protectors at all times that you are exposed to noise may result in hearing loss or injury. For correct use, consult supervisor and User Instruction, or call 3M Technical Service in the U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414. If there is any drainage from your ear or you have an ear infection, consult with your physician before wearing earplugs. Failure to do so may result in hearing loss or injury.</p>
---	--

	<p>⚠ WARNING: PROTECTIVE EYEWEAR</p> <p>These eye and face protection products help provide limited eye and face protection. Misuse or failure to follow warnings and instructions may result in serious potential injury, including blindness or death. For proper use, selection, and applications against flying particles, optical radiation and/or splash, consult supervisor and User Instructions and warnings on package, or call 3M Technical Service in the U.S.A. at 1-800-243-4630. In Canada, call 1-800-267-4414.</p>
---	---



Tapes



Aluminum Foil Tapes

3M™ Aluminum Foil Tape 425

The go-to foil tape for numerous applications across a broad range of industries. Comprised of a dead soft aluminum foil backing and coated with a highly engineered pressure sensitive acrylic adhesive, it is ideal for heat shielding, heat reflecting, chemical masking, light enhancement, chemical milling, seaming, sealing and de-paint operations.



Material ID	UPC	Size	Thick	Color	Roll/Case
7100053644	5-00-51125- 885312 -0	3" x 60'	4.6 mils	Silver	12

Box Sealing Tapes & Accessories

Tartan™ Box Sealing Tape 302

A light-duty packing tape that is suitable for manual applications specifically internally in warehouse and for recuperage. The polypropylene film backing is easy to handle and resists abrasion, moisture and scuffing. The consistent and reliable backing easily conforms around edges and on rough surfaces for a tight seal.



Material ID	UPC	Size	Color	Roll/Case
7100053644	5-00-51115- 25657 -3	48mm x 100m	Clear	36

Scotch® Box Sealing Tape 371

An industrial grade packing tape that securely closes a wide variety of medium weight Box materials, including recycled fiberboard. The polypropylene film backing is easy to unwind and resists abrasion, moisture and scuffing. The backing easily conforms around edges and on rough surfaces for a tight seal.



Material ID	UPC	Size	Color	Roll/Case
7100053644	5-00-21200- 61823 -4	48mm x 100m	Clear	6

Scotch® High Tack Box Sealing Tape 371+

An industrial grade packing tape that securely closes a wide variety of medium weight box materials, including recycled fiberboard. The polypropylene film backing is easy to unwind and resists abrasion, moisture and scuffing. The backing easily conforms around edges and on rough surfaces for a tight seal.



Material ID	UPC	Size	Color	Roll/Case
7100166312	5-06-38060- 12195 -0	48mm x 100m	Clear	36

Scotch® High Tack Box Sealing Tape 311+

A high performance industrial packaging tape for box sealing, splicing, recuperage and other demanding packaging applications. It boasts excellent performance in damp and cold shipping and storage environments, even in below freezing temperatures.



Material ID	UPC	Size	Color	Roll/Case
7010306820	5-00-51128- 00024 -8	48mm x 100m	Clear	36

Scotch® Box Sealing Tape 375

A superior performance packing tape that securely closes a wide variety of heavy weight Box materials, including recycled fiberboard. The polypropylene film backing is easy to unwind and resists abrasion, moisture and scuffing. The backing easily conforms around edges and on rough surfaces for a tight seal.



Material ID	UPC	Size	Color	Roll/Case
7000028907	5-00-21200- 72406 -5	48mm x 50m	Clear	36

Scotch® Box Sealing Tape Dispenser

A pistol-grip design that allows you to apply, cut, and buff tape in an easy, one-hand motion. It dispenses up to a 109' of Box Sealing tape with a maximum width of 3". The hub mounted adjustable brake controls tension to help you dispense the tape along the Box seam and prevent waste. Tape sold separately.



Material ID	UPC	Prod ID	Size	Each/Case
7000042997	5-00-21200- 45834 -2	H180	2"	6
7000031099	5-00-21200- 61850 -0	H183	3"	5



Duct Tapes

3M™ All Purpose Duct Tape DT8

Constructed of polyethylene film laminated to cloth with a natural rubber adhesive, this aggressive tape resists curling and tears off the roll cleanly even when used in challenging jobs. Designed to provide a versatile, conformable, quick stick solution for demanding applications.

Material ID	UPC	Size	Thick	Color	Roll/Case
7100158345	5-00-76308- 98118 -6	48mm x 54.8m	8 mils	Silver	24
7100174104	5-06-89330- 17809 -9			Black	16



3M™ Heavy Duty Duct Tape DT11

Constructed of polyethylene film laminated to cloth with a natural rubber adhesive, this tough tape resists curling and tears off the roll cleanly for a variety of applications. Designed to provide a formidable, reliable solution for everyday challenges and adheres to numerous substrates, including plastic.

Material ID	UPC	Size	Thick	Color	Roll/Case
7100158377	5-00-76308- 98120 -9	48mm x 54.8m	11 mils	Silver	24
7100158346	5-00-76308- 98119 -3			Black	16



3M™ Super Duty Duct Tape DT17

Constructed of polyethylene film laminated to cloth with a natural rubber adhesive, this very thick and strong tape resists curling and tears off the roll cleanly even when used in the most demanding jobs. Designed to provide a maximum-strength, long-lasting solution for the ultimate applications.

Material ID	UPC	Size	Thick	Color	Roll/Case
7100158390	5-00-76308- 98121 -6	48mm x 54.8m	17 mils	Black	24



3M™ Venture Tape™ Cloth Duct Tape 1500

Constructed of polyethylene film laminated to cloth with a rubber adhesive, which resists curling and tears off the roll cleanly for easy application in MRO/construction. Unique construction that allows for permanent and temporary applications.



Material ID	UPC	Size	Thick	Color	Roll/Case
7100043778	5-00-51115- 78488 -5	48mm x 54.8m	10 mils	Black	24
7100043836	5-07-50351- 50004 -3			Silver	16

3M™ Value Duct Tape 1900

Constructed of polyethylene film laminated to cloth with a synthetic rubber adhesive, this value tape resists curling and tears off the roll cleanly for simple applications in MRO/construction. Economically priced to best provide a quick solution for simple tasks.



Material ID	UPC	Size	Thick	Color	Roll/Case
7010375734	5-00-51111- 97841 -7	48mm x 55m	5.8 mil	Silver	24



Duct Tapes

3M™ General Use Duct Tape 2929

Constructed of polyethylene film laminated to cloth with a rubber adhesive, this thin tape resists curling and tears off the roll cleanly for wiring applications in MRO/construction. Especially helpful when it comes to wire pulling. Removable with little or no adhesive residue up to three months after application.



Material ID	UPC	Size	Thick	Color	Roll/Case
7000029030	5-00-51115- 24883 -7	1.88" x 50 yd	5.5 mils	Silver	24

3M™ Heavy Duty Duct Tape 3939

Constructed of polyethylene film laminated to cloth with a rubber adhesive, this durable tape resists curling and tears off the roll cleanly for easy application in MRO/construction. A unique construction that allows for permanent and temporary applications. It is removable with little or no adhesive residue up to three months.



Material ID	UPC	Size	Thick	Color	Roll/Case
7100146009	5-00-51131- 06975 -1	48mm x 54.8m	9 mils	Silver	24

3M™ Contractor Grade Multi-Use Duct Tape 2979

Constructed of polyethylene film laminated to cloth with a rubber adhesive, this economical tape resists curling and tears off the roll cleanly for applications in MRO/construction. Economically priced to best provide a temporary solution for light duties. Removable with little or no adhesive residue up to three months after application.



Material ID	UPC	Size	Thick	Color	Roll/Case
7010335692	5-00-51115- 63738 -9	48mm x 54.8m	7 mils	Silver	24

3M™ Contractor Grade Pro Strength Duct Tape 3979

Constructed of polyethylene film laminated to cloth with a rubber adhesive, this economical tape resists curling and tears off the roll cleanly for use in MRO/construction. Economically priced to provide a medium-strength, temporary solution. It is removable with little or no adhesive residue up to three months after application.



Material ID	UPC	Size	Thick	Color	Roll/Case
7010375912	5-00-51115- 64070 -9	1.88" x 60 yd	8.0 mils	Silver	24

3M™ Multi-Purpose Duct Tape 3900

Constructed of polyethylene film laminated to cloth with a rubber adhesive, this durable tape resists curling and tears off the roll cleanly for easy application in MRO/construction. Our Multi-Purpose Duct Tape 3900 has a unique construction that allows for permanent and temporary applications. It is removable with little or no adhesive residue up to three months after application.



Material ID	UPC	Size	Thick	Color	Roll/Case
7000144749	5-00-21200- 49830 -0	48mm x 54.8m	8.1 mils	Red	24

Also available in Black, Blue, Olive, Silver, White, and Yellow.

3M™ Extra Heavy Duty Duct Tape 6969

Constructed of polyethylene film laminated to cloth with a rubber adhesive, this economical tape resists curling and tears off the roll cleanly for easy application in MRO/construction. A unique construction that allows for permanent and temporary indoor applications. It is removable with little or no adhesive residue up to three months after application.



Material ID	UPC	Size	Thick	Color	Roll/Case
7010375912	5-00-51131- 06969 -0	48mm x 54.8m	10.7 mils	Silver	24

3M™ Vinyl Duct Tape 3903

A hand-tearable general purpose tape with a rubber adhesive and embossed vinyl backing. This tape is ideal for a variety of purposes including temporary repairs, identification, contrast, decoration, securing wiring, bundling, sealing, holding, protecting, and other jobs including applications requiring moisture resistance.




Material ID	UPC	Size	Thick	Color	Roll/Case
7100146009	5-00-51131- 06982 -9	2" x 50 yd	6.5 mils	Yellow	24

Also available in Black, Blue, Gray, Green, Red and White.

3M™ Performance Plus Duct Tape 8979

Constructed of polyethylene film laminated to cloth with a rubber adhesive, this tape resists curling and tears off the roll cleanly for easy application on rough surfaces. 3M™ Performance Plus Duct Tape 8979 has a unique construction that allows for applications indoors and outdoors. It is removable with little or no adhesive residue up to six months after application.



Material ID	UPC	Size	Thick	Color	Roll/Case
7000001330	5-00-21200- 56468 -5	48mm x 54.8m	12.1 mils	Blue	24



Filament Tapes

Tartan™ Filament Tape 8934

General purpose clear fiberglass-reinforced tape with a synthetic rubber resin adhesive, ideal for light duty strapping, bundling and reinforcing. Our synthetic rubber resin adhesive provides good adhesion to most fiberboard surfaces, and a variety of plastics and metal surfaces.

Material ID	UPC	Size	Thick	Color	Roll/Case
7000028886	5-00-21200- 86519 -5	18mm x 55m	4 mils	Clear	48
7000028887	5-00-21200- 86520 -1	24mm x 55m			36



Flashing & Seaming Tapes

3M™ All Weather Flashing Tape 8067

Self-adhered, waterproof flashing membrane designed for sealing around openings and penetrations in exterior walls. This product has a unique acrylic pressure sensitive adhesive that aggressively sticks and stays stuck both at lower and higher application temperatures than traditional flashing tapes. It even adheres to damp surfaces. Slit liner.

Material ID	UPC	Size	Thick	Color	Roll/Case
7000001346	5-00-51115- 31620 -8	4" x 75'	9.9 mils	Tan	12
7000049772	5-00-51115- 31621 -5	6" x 75'			8
7000124877	5-00-51115- 31622 -2	9" x 75'			4



3M™ Through Wall Flashing Tape 8071TWF

Specially designed for use as a through wall flashing and dampproof course. Features exceptional puncture and abrasion resistance. It is an impermeable polyethylene membrane with an aggressive, high-tack acrylic pressure sensitive adhesive that does not require the use of a primer on most construction surfaces. Provides both cold and hot temperature adhesion to most surfaces.



Material ID	UPC	Size	Liner	Color	Roll/Case
7100210602	5-06-38060- 40383 -4	12" x 75'	Slit	Black	4
7100210600	5-06-38060- 40386 -5	18" x 75'			1

3M™ Construction Seaming Tape 8087CW

Cold weather sheathing tape designed to seal seams on housewrap and exterior sheathing materials. This tape features an aggressive pressure sensitive acrylic adhesive mounted on a biaxially oriented polypropylene film. It performs exceptionally well in cold temperature applications.



Material ID	UPC	Size	Color	Roll/Case
7010379550	5-00-76308- 14234 -1	48mm x 50m	White	24
7010314187	5-00-76308- 14235 -8	48mm x 50m	Red	
7010379551	5-00-76308- 14236 -5	60mm x 50m		
7010337895	5-00-76308- 14237 -2	72mm x 50m		
7010291680	5-00-76308- 14238 -9	99mm x 50m		



Flatback Tapes

3M™ High Performance Flatback Tape 2519

A high-performance, general purpose tape ideal for splicing liner boards, as well as bundling and packaging applications where adhesion to paper products is necessary. This thick, 7.1 mil tape features a strong kraft paper backing capable of resisting moisture and high temperatures, and can be torn by hand for fast application. It is brown in color.



Material ID	UPC	Size	Thick	Color	Roll/Case
7100097927	5-00-51128- 98283 -4	24mm x 55m	7.1 mils	Tan	36
7010405983	5-00-51128- 98284 -1	36mm x 55m			24
7100087901	5-00-51128- 99446 -2	48mm x 55m			12
7100087902	5-00-51128- 99447 -9	72mm x 55m			

Flexible Duct Closure Tape

3M™ Venture Tape™ UL181B-FX Polypropylene Duct Tape 1599B

A UL181B-FX Listed, UV resistant flexible duct closure tape featuring a cold weather acrylic adhesive system. It is designed to perform well in a broad range of temperatures and is primarily used for sealing flexible air ducts and air connectors, and for securing flex ducts to duct wrap facing.



Material ID	UPC	Size	Thick	Color	Roll/Case
7100043760	5-07-50351- 15996 -8	48mm x 109.7m	3 mils	Silver	24
7100043816	5-07-50351- 15998 -2	72mm x 109.7m		Black	
7100043909	5-07-50351- 50017 -3	72mm x 109.7m		Silver	16
7100043898	5-07-50351- 50016 -6	72mm x 109.7m		Black	

HVAC Foil Tapes

3M™ Venture Tape™ Mastik Foil Tape 1580-P

A 2 mil aluminum foil coated with a heavy application of mastic adhesive that is UL181B-FX Listed.



Material ID	UPC	Size	Thick	Color	Roll/Case
7010337393	5-07-50351- 50023 -4	2" x 100'	2 mils	Silver	24
7100043954	5-07-50351- 50011 -1	3" x 100'			16

3M™ Venture Tape™ Aluminum Foil Tape 3520CW

A dead soft aluminum foil tape coated with a pressure sensitive acrylic adhesive designed to perform in a broad range of temperatures. This malleable foil tape applies easily to fibrous and sheet metal ducts and conforms to irregular surfaces, excellent for HVAC. It excels in a variety of temperatures and environmental conditions.



Material ID	UPC	Size	Thick	Color	Roll/Case
7100043750	5-00-51115- 78311 -6	72mm x 45.7m	2 mils	Silver	16
7100043755	5-07-50351- 35202 -4	48mm x 45.7m			24
7100166385	5-06-38060- 13992 -4	63.5mm x 45.7m			20

3M™ Venture Tape™ UL181A-P Aluminum Foil Tape 1581A

A high temperature, high strength UL printed aluminum foil tape coated with an acrylic pressure sensitive adhesive that meets UL181A-P, UL181B-FX and ULC S102 specifications. Conformable foil is excellent for rigid duct board applications. The tape excels in a variety of temperatures and environmental conditions, including high temperatures.



Material ID	UPC	Size	Thick	Color	Roll/Case
7100043830	5-07-50351- 15817 -6	2-1/2" x 60 yd	2 mils	Silver	20
7100043929	5-07-50351- 15813 -8	72mm x 55m			16
7010302857	5-00-76308- 14187 -0	99mm x 55m			12



HVAC Tapes

3M™ Venture Tape™ Reflective BOPP Tape 1507

Bright, super shiny silver polypropylene film tape coated with a cold weather, mold inhibiting, solvent acrylic adhesive. This tape is primarily used for seaming reflective bubble insulation.



Material ID	UPC	Size	Color	Roll/Case
7100043965	5-07-50351- 50008 -1	72mm x 55m	Silver	16
7100043964	5-07-50351- 15071 -2	48mm x 55m	Black	24
7100043958	5-07-50351- 50024 -1	48mm x 55m	White	
7010378681	5-07-50351- 10571 -2	48mm x 55m	Black Printed "UV Resistant"	



Insulation Jacketing Tapes

3M™ VentureClad™ Insulation Jacketing Tape — 1577 Series

All-weather option for various jacketing applications. It offers superior resistance to weathering, mold, UV and extreme environmental conditions. Aluminum multi-layered laminate tape is designed to provide zero permeability and act as a vapor barrier for insulation cladding and jacketing applications.



Material ID	UPC	Size	Color	Roll/Case
7100043719	0-00-51128- 95759 -2	23" x 50 yd	Silver Embossed	1
7100043742	0-00-51128- 95757 -8	35-½" x 50 yd		
7100043718	0-00-51128- 95768 -4	23" x 50 yd	Silver Flat	
7100043761	0-00-51128- 95779 -0	35-½" x 50 yd		

Meets the FDA Compositional Requirements for Indirect Food Contact

7100043844	0-00-51128- 96529 -0	23" x 50 yd	White Embossed	1
7100043813	0-00-51128- 96530 -6	35-½" x 50 yd		
7100043741	0-00-51128- 95782 -0	23" x 50 yd	White Flat	
7100043716	0-00-51128- 95781 -3	35-½" x 50 yd		

3M™ VentureClad™ Heavy Duty Insulation Jacketing Tape — 1579 Series

A heavy duty, multilayered, self adhesive embossed jacketing system.



Material ID	UPC	Size	Color	Roll/Case
7100214292	5-06-38060- 40466 -4	30" x 25 yd	Silver Embossed	1
7100209735	5-06-38060- 40465 -7		Silver Flat	
7100197873	0-06-38060- 40143 -9		White Flat	



Insulation Seaming Tapes

3M™ Venture Tape™ Film Faced ASJ Tape 106FXP

Flexible, white polypropylene/core/scrim/foil laminate facing coated with one of our 3M™ proprietary adhesives specifically formulated to adhere to polypropylene facings in both cold and hot humid temperatures. Contains mold inhibiting agents to help prevent corrosion under the insulation.



Material ID	UPC	Size	Color	Roll/Case
7100043807	5-00-51128- 95199 -1	72mm x 45.7m	White	16
7100087900	5-00-51128- 95200 -4	72mm x 45.7m		12
7010376447	5-00-76308- 98455 -2	5" x 50 yd Buttstrip		8

3M™ Venture Tape™ ASJ Facing Tape 1540CW

A white kraft paper, scrim and foil laminated tape coated with a pressure sensitive, cold weather, solvent acrylic adhesive. This tape combines quick stick at normal temperatures with superior low temperature performance. It applies easily and excels in demanding temperature and humidity conditions.



Material ID	UPC	Size	Color	Roll/Case
7100043768	5-07-50351- 15403 -1	72mm x 45.7m	White	16
7100043969	5-00-51128- 95658 -3	99mm x 45.7m		12
7100087495	5-00-51128- 95657 -6	123.75mm x 45.7m		8

3M™ Venture Tape™ Aluminum Foil Tape 1520CW


Features a nominal aluminum foil coated with pressure sensitive, cold weather acrylic adhesive. This tape combines flexible foil for irregularly-shaped applications and excellent low temperature performance. It conforms to fibrous ductboard and sheet metal ducts and works well in general-purpose heat shielding and light reflecting applications.



Material ID	UPC	Size	Color	Roll/Case
7100043715	5-07-50351- 15202 -0	48mm x 45.7m	Silver	24
7100169857	5-06-38060- 13991 -7	63.5mm x 45.7m		20
7100043713	5-07-50351- 15203 -7	72mm x 45.7m		16
7100043875	5-00-51128- 95520 -3	99mm x 45.7m		12

3M™ Venture Tape™ Cryogenic Vapor Barrier Tape 1555CW


All-weather conformable, multi-layered self-adhesive tape designed for low temperature vapor barrier joint closure applications. This tape features a durable aluminum foil backing between two layers of .5 mil polyester film. Xero permeable laminate is coated with an aggressive, pressure sensitive cold weather acrylic adhesive.



Material ID	UPC	Size	Color	Roll/Case
7000049898	5-00-51128- 95731 -3	72mm x 45.7m	Silver	16
7100104081	5-00-51128- 95727 -6		White	

3M™ Venture Tape™ FSK Facing Tape 1525CW

Matches FSK faced insulation board and duct. A foil/scrim/kraft (FSK) laminated tape coated with pressure sensitive, cold weather solvent acrylic adhesive. Quick stick at normal temperatures with superior low temperature performance. It conforms well to fibrous ductboard and blankets.



Material ID	UPC	Size	Color	Roll/Case
7100043764	5-07-50351- 15253 -2	72mm x 45.7m	Silver	16
7100043850	5-07-50351- 50015 -9	99mm x 45.7m		12

3M™ Venture Tape™ White Aluminum Foil Tape 1558HT

A high strength white aluminum foil coated with an aggressive cold weather acrylic pressure sensitive adhesive. It is designed for low temperature vapor barrier joint closure applications such as lap joints and vapor seals. It is ideal for use on white foil faced ductboard for a traditional crisp, white appearance.



Material ID	UPC	Size	Color	Roll/Case
7010335933	5-00-51115- 81356 -1	72mm x 45.7m	White	16



Masking Films

3M™ Hand-Masker™ Advanced Masking Film

Now with paint bond technology. 3M's most flake resistant film for multi-coat paint applications. Use for paint masking and overspray protection (12" product folds out to 24".)



Material ID	UPC	Size	Roll/Case
7100155261	0-06-38060- 08076 -4	24" x 360'	12
7100155263	5-00-51141- 90038 -9	48" x 180'	
7100155262	5-00-51141- 90039 -6	72" x 90'	
7100155264	5-00-51141- 90040 -2	99" x 90'	

3M™ Hand-Masker™ Contractor's Plastic

Non-treated high-density plastic dispenses from M3000/M2000 Tools and unfolds for draping and covering large areas, dust containment and overspray protection with latex paints.



Material ID	UPC	Size	Roll/Case
7100083470	5-00-51131- 79683 -1	6' x 90'	12
7100066366	5-00-51131- 79684 -8	9' x 90'	

3M™ Hand-Masker™ Painter's Plastic Plus

A specially treated film alternative to Boxed plastic or film. This product offers several advantages over current Boxed plastic or film. Flake Resistant: Paint anchorage to reduce flaking and clean up time. Static cling making the film easy to work with Lacquer and Solvent Resistant.



Material ID	UPC	Size	Roll/Case
7100091364	0-00-51141- 90366 -8	9' x 400'	1
7010336209	0-00-51141- 90387 -3	12' x 400'	

Masking Film Accessories

3M™ Hand-Masker™ Film Blades

Made from durable stainless steel with a protective plastic blade guard.



Material ID	UPC	Size	Roll/Case
7100091214	5-00-51131- 06802 -0	12"	6

3M™ Hand-Masker™ Straight Cut Film Blades

Made from durable stainless steel and have an assembly that attaches to the end of the roll and helps provide a straight cut. Also contains a protective plastic blade guard.



Material ID	UPC	Size	Roll/Case
7100110918	0-00-51141- 59803 -1	12"	6



The 3M™ Hand-Masker™ M3000 Dispenser

Applies masking tape to masking film measuring up to 144" or to paper measuring up to 18" in one continuous application. Compact, lightweight, saves time. For professional heavy-duty use.



Material ID	UPC	Use with	Each/Case
7100054147	5-00-51131- 77385 -6	18" to 144" paper widths	4



Masking Tapes



ScotchBlue™ Original Painter's Tape 2090



Features Edge-Lock™ Technology that seals out paint to deliver sharp paint lines. Provides multi-surface performance, 21 day clean removal, and medium adhesive.


Material ID	UPC	Size	Color	Roll/Case
7100185226	0-00-51115- 03680 -4	18mm x 54,8m	Blue	48
7100185227	5-00-51115- 03681 -6	24mm x 54,8m		36
7100186419	5-00-51115- 03682 -3	36mm x 54,8m		24
7100185142	0-00-21200- 46985 -5	72mm x 54,8m		12
7100185189	5-00-51115- 09171 -6	24mm x 54,8m Contractors Pack	Blue	4 PK
7100185196	5-00-51115- 09221 -8	36mm x 54,8m Contractors Pack		
7100185190	5-00-51115- 09168 -6	48mm x 54,8m Contractors Pack		

ScotchBlue™ Sharp Lines Painter's Tape 2093



Features Edge-Lock™ Technology that seals out paint to deliver sharp paint lines. Provides multi-surface performance, 21 day clean removal, and medium adhesive.

Material ID	UPC	Size	Color	Roll/Case
7100185011	0-00-51141- 32030 -4	24mm x 55m	Blue	24
7100185012	0-00-51141- 32032 -8	36mm x 55m		16
7100185013	0-00-51141- 32034 -2	48mm x 55m		12





Masking Tapes

Scotch® Rough Surface Painter's Tape 2060

Very strong adhesive designed for performance on rough, non-damageable surfaces. Provides 5 day clean removal.



Material ID	UPC	Size	Color	Roll/Case
7100185556	0-00-21200- 71131 -2	18mm x 55m	Green	48
7100185563	0-00-21200- 71132 -9	24mm x 55m		36
7100185332	5-00-21200- 71133 -1	36mm x 55m		24
7100185557	0-00-21200- 71134 -3	48mm x 55m		

Scotch® Exterior Surface Painter's Tape 2097

Developed for outdoor painting projects for when you need a tape that can handle wind, rain, humidity and direct sunlight. Provides 10 day clean removal, very strong adhesive, and tear-free removal.



Material ID	UPC	Size	Color	Roll/Case
7100185554	0-00-51141- 36200 -7	1.41" x 45 yd	Yellow	16
7100185564	0-00-51141- 36197 -0	1.88" x 45 yd	Yellow	12

Scotch® Delicate Surface Painter's Tape 2080

Great for surfaces that require a little extra care. Provides 60 day clean removal, gentle adhesive and Edge-Lock™ Technology that seals out paint to deliver sharp paint lines.



Material ID	UPC	Size	Color	Roll/Case
7100184838	0-00-51131- 80988 -8	18mm x 55m	Purple	32
7100185006	0-00-51131- 79748 -2	24mm x 55m		24
7100185010	0-00-51131- 79749 -9	36mm x 55m		16
7100185009	0-00-51141- 92578 -3	48mm x 55m		12

3M™ Outdoor Masking and Stucco Tape 5959

Constructed of polyethylene film laminated to cloth with a rubber adhesive. Resists curling and tears off the roll cleanly for easy application on stucco and other challenging surfaces. Permanent and temporary applications. Removable up to three months after application.



Material ID	UPC	Size	Color	Roll/Case
7000124742	5-00-51115- 15491 -3	1.41" x 45 yd	Red	12

3M™ Value Masking Tape 101+

Cost-effective crepe paper tape that holds, bundles, seals and performs other non-critical taping jobs where a pressure sensitive tape is needed. This tape offers controlled unwind to prevent shredding or splintering and tears easily from the roll by hand.



Material ID	UPC	Size	Thick	Color	Roll/Case
7100021274	5-00-51115- 68709 -4	36mm x 55m	5.1 mils	Tan	24
7000147264	5-00-51115- 68310 -0	48mm x 55m			

More sizes and individually wrapped options available.

3M™ General Use Masking Tape 201+

A go-to tape that holds strongly in settings where surface temperatures can reach up to 200°F (93°C). This light tan crepe paper tape has a low unwind and sticks to many surfaces, making it an ideal everyday-use tape.



Material ID	UPC	Size	Thick	Color	Roll/Case
7000124882	5-00-51115- 64741 -8	36mm x 55m	4.4 mils	Tan	24
7000144752	5-00-51115- 64742 -5	48mm x 55m			

More sizes and individually wrapped options available.

3M™ Performance Yellow Masking Tape 301+

Deliver good paint lines where surface temperatures can reach up to 225°F (107°C). This yellow crepe paper tape is ideal for paint masking applications where strong holding performance is required.



Material ID	UPC	Size	Thick	Color	Roll/Case
7000124890	5-00-51115- 64752 -4	36mm x 55m	6.3 mils	Yellow	24
7000124891	5-00-51115- 64753 -1	48mm x 55m			

More sizes and individually wrapped options available.

3M™ High Performance Green Masking Tape 401+

Deliver sharp paint lines where surface temperatures can reach up to 250°F/121°C for 30 minutes. This green crepe paper tape is ideal for critical paint masking applications where strong holding and high temp performance is required.



Material ID	UPC	Size	Thick	Color	Roll/Case
7000124897	5-00-51115- 64762 -3	36mm x 55m	6.7 mils	Green	16
7000124898	5-00-51115- 64763 -0	48mm x 55m			12

More sizes and individually wrapped options available.



Metal Building Tapes

3M™ Venture Tape™ Woven Patch Tape 442

Designed to match black woven insulation facings. It is capable of bonding quickly and strongly to a variety of hard-to-bond substrates. It is an acrylic tape composed of a high tack adhesive and a woven composition that has high elongation.



Material ID	UPC	Prod ID	Size	Color	Roll/Case
7100043941	5-00-51128- 96125 -9	442B	99mm x 50m	Black	15
7100043788	5-00-51128- 96128 -0	442W		White	

3M™ Venture Tape™ Vinyl Seaming Tape 460V

Embossed vinyl seaming tape coated with a high tack cold weather acrylic adhesive. Delivers excellent resistance to weathering and environmental conditions, and is ideal for seaming on vinyl faced fiberglass insulation and water heater blanket insulation systems.



Material ID	UPC	Prod ID	Size	Color	Roll/Case
7100043935	5-07-50351- 04607 -7	460V	72mm x 45.7m	White	16
7100043948	5-00-51128- 96144 -0			Black	

3M™ Venture Tape™ Metal Building Facing Tape

Tri-directionally reinforced, black metalized polypropylene film/scrim/kraft facing tape coated with a cold weather acrylic pressure sensitive adhesive.



Material ID	UPC	Prod ID	Size	Color	Roll/Case
7100043747	5-00-51128- 95615 -6	1531CW	72mm x 45.7m	White	16
7100043858	5-00-51128- 95613 -2			Black	
7100043751	5-07-50351- 15373 -7	1537CW		White	
7100052071	5-00-51128- 95621 -7			Black	
7100043931	5-00-51128- 95720 -7	1547CW		White	
7100043851	5-00-51128- 95739 -9	1568CW		White	

3M™ Venture Tape™ Vinyl Foam Tape

Designed to provide both a quick fix and long-lasting solution in applications that require vapor sealing and gap covering. It is composed of a closed-cell vinyl foam coated with a pressure-sensitive acrylic adhesive.








Material ID	UPC	Prod ID	Size	Color	Roll/Case
7010379940	5-00-51128- 95941 -6	1714	3/8" x 50'	Gray	32
7010313519	5-00-51128- 95940 -9		3/4" x 50'		16
7010378908	5-00-51128- 96543 -1		1-1/2" x 50'		8
7100051412	5-00-51128- 95942 -3		2" x 50'		6
7100043822	5-00-51128- 95943 -0		3" x 50'		4
7010379941	5-00-51128- 95946 -1	1718	3/8" x 75'	Gray	32
7010379942	5-00-51128- 95948 -5		1" x 75'		12
7100043818	5-00-51128- 95949 -2		2" x 75'		6
7100043826	5-00-51128- 95947 -8		3" x 75'		4



Water Filtration






Under-Sink Filters & Cartridges

	Material ID	UPC	Prod ID	Capacity (gallon)	Flow Rate (gpm/lpm)	Micron Rating	Life (months)	Each/ Case	Comments
3M™ Under Sink Full Flow Water Filter System 3MFF100									
	7000125866	0-00-16145- 23311 -1	5616318	6,000	2.5/9.5	.2	12	6	<ul style="list-style-type: none">• NSF listed to reduce particulate, chlorine taste and select VOCs such as benzene, p-Dichlorobenzene and toxaphene.• This system connects to the primary kitchen or bath water faucet.
	Replacement Cartridge 3MFF101								
	7000125865	0-00-16145- 23310 -4	5613432	6,000	2.5/9.5	.2	12	6	
3M™ Aqua-Pure™ Under Sink Dedicated Water Filter System AP Easy Complete									
	7010410047	3-00-76308- 87938 -0	04-99535	750	.75/2.8	.5	6	6	<ul style="list-style-type: none">• NSF listed to reduce particulate, chlorine taste and odor, asbestos, parasitic protozoan cysts, lead, mercury, select VOCs and more.• This compact AP Easy Complete system connects to a dedicated drinking water faucet (included).
	Replacement Cartridge								
	7010413733	3-00-76308- 87937 -3	04-99534	750	.75/2.8	.5	6	6	
3M™ Aqua-Pure™ Under Sink Dedicated Faucet Replacement Water Filter Cartridge AP Easy C-Complete									
	7100049876	0-00-51128- 88912 -1	5618044	750	0.75/2.8	.5	6	6	<ul style="list-style-type: none">• For use with the AP Easy Complete system.• NSF listed to reduce particulate, chlorine taste and odor, asbestos, parasitic protozoan cysts, lead, mercury, select VOCs such as atrazine, benzene, lindane, toxaphene, p-dichlorobenzene and carbofuran.
3M™ Aqua-Pure™ AP-DWS1000 Under Sink Dedicated Faucet Water Filter System									
	7000050280	0-00-16145- 10001 -7	558310	625	0.6/2.3	.5	6	1	<ul style="list-style-type: none">• Helps reduce particulate, chlorine taste and odor, as well as lead and cysts that may be in your drinking water.• This system connects easily under the kitchen sink and includes an attractive dedicated drinking water faucet.
	Replacement Cartridge AP-OW90/90								
	7100000550	0-00-16145- 08090 -6	5585102	625	0.6/2.3	.5	6	4	
3M™ Under Sink Reverse Osmosis Water Filter System 3MRO401									
	7100086836	0-00-51128- 89397 -5	3MRO401-01A	2,500	23.922/90.55	5	12	1	<ul style="list-style-type: none">• Multi-stage reverse osmosis water filter system.• NSF listed to reduce particulate, chlorine taste and odor, arsenic, barium, cadmium, chromium (both Hexavalent & Trivalent), copper, parasitic protozoan cysts, fluoride, lead, radium, selenium, p-Dichlorobenzene & toxaphene (both VOCs), TDS and turbidity.
	Replacement Cartridge								
	7100086838	0-00-51128- 89525 -2	3MROP411-20A	–	23.922/90.55	5	12	20	
	7100086680	0-00-51128- 89526 -9	3MROP412-20A	–	37.38/141.5	N/A	12	20	
	7100086842	0-00-51128- 89576 -4	3MROP416-20A	–	23.92/90.55	N/A	12	20	






Whole House Systems

	Material ID	UPC	Prod ID	Capacity (gallon)	Flow Rate (gpm/lpm)	Micron Rating	Life (months)	Each/ Case	Comments
3M™ Aqua-Pure™ Whole House Sanitary Quick Change Water Filter System AP904									
	7100008212	0-00-16145- 26699 -7	5621104	10,0000	10/37.9	5	12	1	<ul style="list-style-type: none">Activated carbon filter system with a nominal heavy duty particulate reduction rating of 5 microns and 100,000 gallon capacity.Reduces sediment, and chlorine taste and odor.We also combine scale inhibition media to help prevent scale build-up and corrosion in hot water-using appliances and pipes.
	Replacement Cartridge AP917HD-S								
	7000029542	0-00-16145- 25654 -7	5621008	10,0000	10/37.9	5	12	1	
3M™ Whole House Scale Inhibition Water Treatment System AP430SS									
	7100051446	0-00-51128- 88987 -9	AP43011	–	10/37.9	N/A	6	6	<ul style="list-style-type: none">Reduce scale build-up on hot water-using appliances such as water heaters (standard and tank-less), clothes washers and dishwashing machines, and on plumbing fixtures like faucets, pipes, and shower heads.The AP430SS provides unrestricted flow of up to 10 gpm with ¾" NPT inlet/outlet connections.The AP431 replacement cartridge is as easy to change-out as a lightbulb.
	Replacement Cartridge AP431								
	7100051432	0-00-51128- 88988 -6	AP43111	–	10/37.9	N/A	6	6	
3M™ Aqua-Pure™ Whole House Standard Diameter Water Filter Transparent Plastic Housing System — AP100 Series									
	7000001617	0-00-16145- 00111 -6	5529902	Housing AP11T				4	<ul style="list-style-type: none">Together with various cartridges, filters all incoming water throughout the home.Universal 2-high housing design allows for use on both chlorinated (municipal) and non-chlorinated (well water) systems.Cartridge options exist to reduce sediment, chlorine taste and odor, as well as scale.
	7100008195	0-00-16145- 01011 -8	5530002	Housing AP101T				2	
	7000001639	0-00-16145- 00102 -4	5530008	Housing AP102T				4	
	Replacement Cartridge AP110								
	7000029441	0-00-16145- 15734 -9	5620404	–	8/30.8	5	6	5	
	Replacement Cartridge AP124								
	7000051058	0-00-16145- 15742 -4	5620601	–	8/30.8	50	6	5	
	Replacement Cartridge AP117								
7100057796	0-00-51128- 89175 -9	5541731	–	3/11.4	5	6	5		



Commercial Filtration

	Material ID	UPC	Prod ID	Capacity (gallon)	Flow Rate (gpm/lpm)	Micron Rating	Each/ Case	Comments
3M™ High Flow Series System for Brewed Coffee & Hot Tea Applications featuring Valve-in-Head Design — Model BREW120-MS								
	7000125417	0-00-16145- 80116 -7	5616001	10,000	1.5/5.7	1	6	<ul style="list-style-type: none">Provides consistent high quality water by reducing particulate, chlorine taste and odor, cyst, and scale.The Sanitary Quick Change (SQC) design allows for easy cartridge change-outs.
	Replacement Cartridge HF20-MS							
	7000001674	0-00-16145- 80199 -0	5615109	9,000	1.5/5.7	.5	6	
3M™ High Flow Series System for Ice Applications ICE120-S featuring Valve-in-Head Design								
	7000144833	0-00-16145- 80118 -1	5616003	9,000	1.5/5.7	.5	6	<ul style="list-style-type: none">Designed for commercial ice machines.Helps to reduce sediment, chlorine taste and odor, cyst and scale.The Sanitary Quick Change (SQC) design allows for no contact with the filter media during cartridge change-out.
	Replacement Cartridge HF20-S							
	7000125416	0-00-16145- 80141 -9	5615103	9,000	1.5/5.8	.6	6	
3M™ High Flow Series System for Cold Beverage Applications BEV140								
	7000029269	0-00-16145- 80103 -7	5616201	25,000	2.5/9.5	.2	2	<ul style="list-style-type: none">Provides consistent high quality water by reducing particulate, chlorine taste and odor, cyst, and bacteria.The Sanitary Quick Change (SQC) design allows for easy cartridge change-outs.
	Replacement Cartridge HF40							
	7000001665	0-00-16145- 80148 -8	5613303,	25,000	2.5/9.5	.2	2	

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



3M Building and Construction Markets

Building 225-3S-06
St. Paul, MN 55144-1000
1-866-513-4026
3M.com/construction

Please Recycle. Printed in U.S.A.
© 3M 2020 All rights reserved.
70-0709-4163-1 Feb 2020

3M, Albion, Aquar-Pure, Aura, Blasts, Classic, Cool Flow, Cubitron, E-A-R, E-A-Rsoft, FX, GoggleGear, Hand-Masker, Highland, Hookit, Interam, Peltor, Performance Plus, Pro-Pak, Push-Ins, Roloc, Scotch-Blue, Scotch-Brite, Scotchgard, SecureFit, Skull Screws, Stikit, Super 33+, Super 77, Tartan, Temflex, Ultrafit, Uvicator, Venture Tape, VentureClad, Versaflo and Virtua are trademarks of 3M Company.

Scotch is a registered trademark of 3M Company.