




1. Position 3M™ Cold Shrink Insulator QSLV-M assembly on cable or wire prior to connecting.




2. Make connection. Place a tape marker 7" (180 mm) from the center of the crimped connector on both Cable A and Cable B sides.



3. Clean cable insulation between tape markers.



4. Center 3M™ Cold Shrink Insulator QSLV-M between the 2 tape markers.



5. Pull one of the loose pull tabs while unwinding (counter-clockwise) to lock 3M™ Cold Shrink Insulator QSLV-M into place. Pull the other loose pull tab while unwinding (counter-clockwise). Installation is now complete.



Note: The ends of the 3M Cold Shrink QSLV-M Insulator may be squeezed to assist the tube in shrinking to its final diameter.

3M and the 3M logo are trademarks of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

3M

Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800-245-3573
Fax 800-245-0329
www.3M.com/electrical

Please Recycle. Printed in USA.
© 3M 2008. All Rights Reserved.
78-8127-6785-9-B

3M

Cold Shrink Connector Insulator QSLV-M

For 1000 volts or less

Product Name	Cable Size Range (AWG or kcmil)*	Cable Insulation O.D. Range Inches (mm)	Max Connector O.D. Inches (mm)	Max Connector Length Inches (mm)
QSLV-M 8-2/0	8-2/0	0.20-0.75 (5-19)	0.687 (17)	2.5 (63)
QSLV-M 2-500	2-500	0.40-1.60 (10-41)	1.500 (38)	4.25 (108)

*Insulator may be used on cable sizes outside of the recommended range, provided both cables are within the insulation O.D. range and the connector meets the dimensional requirements shown above.

QTY: 1 Each

78-8127-6785-9-B

⚠ CAUTION

Working around energized electrical systems may cause serious injury or death. Installation should be performed by personnel familiar with good safety practice in handling electrical equipment. De-energize and ground all electrical systems before installing product.