

Particulate Filters P100

Issue Date 9/1/09

3M™ Particulate Filters P100:
NIOSH's highest filtration efficiency class that is simple to understand and easy to use.

This is how 3M P100 filters can help you:

Convenience

P100 filters are well suited for a wide range of oil and non-oil based particulate contaminants. As a result, filter selection is greatly simplified and use is made easier.

Choice


3M provides a variety of P100 filters to address the different requirements of a broad range of applications. 3M P100 filter construction is a self supporting system.

Versatility

3M P100 filters can be used with a variety of half face and full facepieces. This makes compliance with the regulations easy while allowing for individual facepiece preferences.

Comfort

3M P100 filter design helps provide workers with an improved field of vision. The construction is lightweight for enhanced comfort, longer wear time and better acceptance.



3M™ Particulate Filters P100 help provide protection which is easy to understand, to use and to implement.

Highest filter efficiency

3M P100 filters pass NIOSH's 42 CFR 84 most rigorous filter test criteria by providing a minimum 99.97% filter efficiency.

Suggested Applications




- OSHA substance specific particle exposures:
 - Lead
 - Asbestos
 - Cadmium
 - Arsenic
 - 4,4'-Methylenedianiline (MDA)




WARNING

These filters help protect against certain particles. **Misuse may result in sickness or death.** Before use, the wearer must read and understand *User Instructions* provided as a part of product packaging. Time use limitations may apply. For proper use, see package instructions, supervisor or call 3M OH&ESD Technical Service in U.S.A., 1-800-243-4630. In Canada, call 1-800-267-4414.


Additional use instructions, product limitations, approval labels, and warnings are included with each facepiece and filter package.




6000 half facepiece with 2091 P100 filters




6000 full facepiece with stacked cartridge P100 filters



7500 half facepiece with 7093 cartridge P100 filters



7800 full facepiece with 7093 P100 filters



FF-400 full facepiece with 2297 P100 filters



Occupational Health and Environmental Safety Division
3M Center, Building 235-2E-91
St. Paul, MN 55144-1000

For more information, please contact:

3M Occupational Health and Environmental Safety Division (OH&ESD)

In the U.S., contact:

Customer Service

1-800-328-1667

Technical Assistance

1-800-243-4630

Website

www.3M.com/OccSafety

For other 3M products

1-800-3M HELPS

In Canada, contact:

3M Canada Company, OH&ESD

P.O. Box 5757

London, Ontario N6A 4T1

Customer Care

1-800-364-3577

Technical Assistance (Canada only)

1-800-267-4414

Website

www.3M.ca/safety

Technical Assistance In Mexico

01-800-712-0646

5270-2255, 5270-2119 (Mexico City only)

Technical Assistance In Brazil

0800-132333