



## Profile Selector

[select printer OEM]

Epson

Gandinnovations

HP

Mimaki

Mutoh

OCÉ

Roland

Seiko

Vutek

### 3M Graphics Warranties

3M offers you a choice of warranties that give you everything you want. Including the peace of mind. Click [here](#) for more details.

Not sure you have the latest version of this profile selector?

Check [here](#) for most actual version.

This selector is linked to an online database. To get the profiles an internet connection is needed.

In the online database select the desired profiles and follow the 'high Res Download' link at the left navigation menu. Follow the instructions to download a ZIP-archieve, containing all selected items. If needed, WinZip can be downloaded for unzipping the packed profiles.



# Media Profiles for Epson Printers

[select RIP @ appropriate printer model]

## **Stylus Pro GS6000**

- 8 color -- UltraChrome Inks

ColorGate Productionserver 6 / IGEPA MasterRIP

Ergosoft PosterPrint 12 / 2008

Onyx PosterShop 7.2

## **SureColor SC-S30600**

- 4 color -- UltraChrome GSX Inks

efi Fiery XF

Ergosoft PosterPrint 14

GMG ColorProof

ColorGate Productionserver 7/IGEPA MasterRIP



# Media Profiles for Gandinnovations Printers

[select RIP @ appropriate printer model]

**Jeti 3324 Silvent RTR** (80pl dropsize version)

- 6 color -- HLv2 Inks

Gandinnovations GandiSoft



# Media Profiles for HP Printers

page 1 of 3

[select RIP @ appropriate printer model]

## Designjet 8000

- 6 color -- HP780 Inks

Amiable FlexiSign 8 / PhotoPrint 5

Onyx PosterShop 7.1

## Designjet 9000

- 6 color -- HP790 Inks

Amiable FlexiSign 8 / PhotoPrint 5

Caldera VisualRIP 7.5

Ergosoft PosterPrint 12

Onyx PosterShop 6.5

## Designjet 10000

- 6 color -- HP790 Inks

Amiable FlexiSign 8 / PhotoPrint 5

Ergosoft PosterPrint 12

Onyx PosterShop 6.5



# Media Profiles for HP Printers

page 2 of 3

[select RIP @ appropriate printer model]

## Designjet L25500

- 6 color -- HP789 Inks

Caldera VisualRIP 7.5

ColorGate Productionserver 6 / IGEPa MasterRIP

Onyx PosterShop 7.3

HP Guide for finding best temperature settings with L25500

## Designjet L26500

- 6 color -- HP792Inks

Onyx PosterShop 10

Caldera VisualRIP 9.1

## Designjet L28500

- 6 color -- HP792Inks

ColorGate ProductionServer 7 / IGEPa MasterRIP

Caldera VisualRIP 9.1

## Designjet L65500

- 6 color -- 3M LX600 Inks

Caldera VisualRIP 7.5

Onyx PosterShop 7.2



# Media Profiles for HP Printers page 3 of 3

[select RIP @ appropriate printer model]

## **Designjet L65500**

- 6 color -- HP786 Inks

Caldera VisualRIP 7.5

Onyx PosterShop 7.2

## **HP Scitex LX600/800**

- 6 color -- 3M LX600 Inks

Caldera VisualRIP 7.5

Onyx PosterShop 7.2

## **HP Scitex LX600/800**

- 6 color -- HP786 Inks

Caldera VisualRIP 7.5

Onyx PosterShop 7.2

## **HP Scitex LX800/820/850**

- 6 color -- LX610 (3M) Inks

Caldera VisualRIP 9.1

Onyx PosterShop 10.2



# Media Profiles for Mimaki Printers

[select RIP @ appropriate printer model]

## **CJV30**

ColorGate ProductionServer

Caldera VisualRIP 7.5

Mimaki RasterLink 5

- 4 color -- SS21 Inks

## **JV3-SP**

Wasatch SoftRIP 4.5/5.1

Onyx PosterShop 6.0

- 4 color -- SS2 Inks

## **JV33**

ColorGate ProductionServer

Caldera VisualRIP 7.5

Ergosoft PosterPrint 12

Onyx PosterShop 7.1

Mimaki RasterLink 5

- 4 color -- SS21 Inks



# Media Profiles for Mimaki Printers

[select RIP @ appropriate printer model]

## **JV5-SP**

- 4 color -- HS2 Inks

Caldera VisualRIP 7.5

Onyx PosterShop 7.1

## **UJV-160**

- 4 color -- LF200 Inks

Mimaki RasterLink 5





# Media Profiles for Mutoh Printers

page 1 of 3

[select RIP @ appropriate printer model]

## **Blizzard 65/90**

-4 color -- 3M 600 Inks

Caldera VisualRIP 7.5

65 - Onyx PosterShop 7.1

90 - Onyx PosterShop 7.1

Ergosoft PosterPrint 12 / 2008

## **Blizzard 65/90**

- 4 color -- Mutoh mild-solvent Inks

Caldera VisualRIP 7.5

65 - Onyx PosterShop 7.2

90 - Onyx PosterShop 7.2

Ergosoft PosterPrint 12 / 2008



# Media Profiles for Mutoh Printers

page 2 of 3

[select RIP @ appropriate printer model]

## Rockhopper 2 + 3

- 6 color -- Eco-Ultra Inks

Ergosoft PosterPrint 12

## Rockhopper 3

- 4 color -- Eco-Ultra Inks

65 - Onyx PosterShop 7.2

90 - Onyx PosterShop 7.2

## Spitfire 65

- 4 color -- RJ80MS Inks

Onyx PosterShop 6.5

## Spitfire 65/90 Extreme

- 4 color -- 3M 600 Inks

Caldera VisualRIP 7.2

Colorgate ProductionServer 5 / IGEPA MasterRIP

Ergosoft PosterPrint 12

65 - Onyx PosterShop 7.1

90 - Onyx PosterShop 7.1



# Media Profiles for Mutoh Printers

page 3 of 3

[select RIP @ appropriate printer model]

## Spitfire 65/90 Extreme

- 4 color -- RJ80MS Inks

Caldera VisualRIP 7.2

Colorgate ProductionServer 5 / IGEPA MasterRIP

Ergosoft PosterPrint 12

65 - Onyx PosterShop 7.1

90 - Onyx PosterShop 7.1

## ValueJet

- 4 color -- Eco-Ultra Inks

1304 - Onyx PosterShop 7.1

1604 - Onyx PosterShop 7.1

1608 - Onyx PosterShop 7.1

1614 - Onyx PosterShop 7.1



# Media Profiles for Océ Printers

[select RIP @ appropriate printer model]

**CS 6060**

- 6 color -- IJC610 Inks

AIT Shiraz 6

Ergosoft PosterPrint 11

Onyx PosterShop 6.5



# Media Profiles for Roland Printers

page 1 of 3

[select RIP @ appropriate printer model]

**SolJet Pro II - SC-545EX, SJ-645/745/1045** - 6 color -- Eco-Max Inks

Caldera VisualRIP 7.2

Onyx PosterShop 7.1

Roland VersaWorks 3.1

**SolJet Pro III - XC-540** (without use of RIPC) - 6 color -- Eco-Max Inks

Caldera VisualRIP 7.2

Ergosoft PosterPrint 12

Onyx PosterShop 7.1

Roland VersaWorks 3.1

**SolJet Pro III - XC-540, XJ-640/740** - 6 color -- Eco-Max Inks

Roland VersaWorks 3.1



# Media Profiles for Roland Printers page 2 of 3

[select RIP @ appropriate printer model]

## **VersaArt RS-540/640** - 4 color -- Eco-Max Inks

ColorGate Productionserver 6 / IGEPA MasterRIP

Onyx PosterShop 7.3

Roland VersaWorks 3.1

## **VersaCamm SP-300V/540V** - 4 color -- Eco-Max Inks

Onyx PosterShop 6.5

Roland VersaWorks 2.6

Caldera VisualRIP 7.56

## **VersaCamm VP-300/540** (without use of RIP) - 4 color -- Eco-Max Inks

Onyx PosterShop 6.5

Roland VersaWorks 2.0

Caldera VisualRIP 7.56

## **VersaCamm VP-300i/540i** - 4 color -- Eco-Max Inks

ColorGate Productionserver 6 / IGEPA MasterRIP

Roland VersaWorks 3.2



# Media Profiles for Roland Printers page 3 of 3

[select RIP @ appropriate printer model]

## **VersaCamm VS-540/640**

- 4 color

-- Eco-Max Inks

Onyx PosterShop 10

Roland VersaWorks 4.2

## **VersaCamm VS-540/640**

- 6 color; wh; mt -- Eco-Max Inks

Onyx PosterShop 10

Roland VersaWorks 4.2



# Media Profiles for Seiko Printers

[select RIP @ appropriate printer model]

## Colorpainter S

- 6 color -- IP6 Inks

AIT Shiraz 6

Caldera VisualRIP 7.5

Ergosoft PosterPrint 11

Onyx PosterShop 6.5

## Colorpainter HS-74s / -104s

- 8 color -- EGO Inks

Caldera VisualRIP 7.2

Onyx PosterShop 7.3





# Media Profiles for Vutek Printers

[select RIP @ appropriate printer model]

**Vutek 150, Vutek 2330, Vutek 3360**

- 6 color -- 3M 1500v2 Inks

Onyx PosterShop 7.3



# 3M Graphics Warranties

## Basic Product Warranty

This gives you a solid foundation with the assurance that you are getting what you pay for. By itself, it's just enough protection for many short-term promotional graphics where warranted finished graphics aren't specified.

## 3M Performance Guarantee

Step up to this when you need media, printers and inks guaranteed to work together with optimized performance, guaranteed durability and good adhesive and application characteristics. This comprehensive guarantee is given by using the original manufacturer's ink of your printer.

## 3M™ MCS™ Warranty

This is the first and still the strongest finished graphics warranty in the industry - gives peace of mind to discriminating users that require optimum performance for the intended life of the graphic.

| At a Glance  |  | 3M Basic Product Warranty | 3M Performance Guarantee | 3M™ MCS™ Warranty |
|--|--|---------------------------|--------------------------|-------------------|
| <b>3M Components and Remedies for Each Warranty</b>  |  |                           |                          |                   |
| <b>3M Graphic Materials</b>  | Remedy: credit or replacement of defect materials  | ✓                         |                          |                   |
| <b>3M Graphic Materials and Qualified Inks</b>   | Remedy: credit or replacement of defective 3M products for the stated warranted durability period. In case a 3M manufactured ink is used ink performance related issue (see * in the overview) are covered as well |                           | ✓                        |                   |
| <b>3M Graphic Film or Substrates, 3M Inks, 3M Graphic Protection on approved printers</b>                    | Remedy: credit or replacement of all 3M materials used in the graphic. Certain fleet and vehicle graphics may also have a labor reimbursement component.   |                           |                          | ✓                 |
| <b>Coverage</b>  |  |                           |                          |                   |
| <b>Finished Graphic</b>  | As defined in Product Bulletin for 3M products only  | ✓                         | ✓                        | ✓                 |
| <b>Warranted Durability</b>  | As defined in Product Bulletin   |                           | ✓                        | ✓                 |
| <b>Physical Defects</b>  | Obvious damage for any reason  | ✓                         | ✓                        | ✓                 |
|  | Visual defects   | ✓                         | ✓                        | ✓                 |
| <b>Manufacturing Defects</b>   | Adhesive defects   | ✓                         | ✓                        | ✓                 |
|  | Adhesion failure on recommended substrates   |                           | ✓                        | ✓                 |
|  | Image defects when printing  |                           | ✓                        | ✓                 |
|  | Excessive image fading *   |                           | ✓                        | ✓                 |
|  | Image cracking or crazing *  |                           | ✓                        | ✓                 |
| <b>Printing Defects and Ink Performance</b>  | Image peeling *  |                           | ✓                        | ✓                 |
|  | Gloss changes *  |                           | ✓                        | ✓                 |
|  | Blistering   |                           | ✓                        | ✓                 |
|  | Excessive dimensional change   |                           | ✓                        | ✓                 |
| <b>Cutting Defects</b>   | Clean cutting and weeding  |                           | ✓                        | ✓                 |
| <b>Removal</b>   | Removable or changeable films do not remove as stated  |                           | ✓                        | ✓                 |
| <b>Additional Coverage for 3M™ Panaflex™ Awning and Sign Facing and 3M™ Panagraphics Flexible Substrates</b> | Seam or splice failure when made as recommended  |                           |                          | ✓                 |
|  | Blowout when used as recommended   |                           |                          | ✓                 |
|  | Milddewing   |                           |                          | ✓                 |
|  | Wicking  |                           |                          | ✓                 |

Discover details about 3M Performance Guarantee and 3M™ MCS™ Warranty and visit the [web pages of your local 3M subsidiary](#) or step direct to our [European web site](#).

