

IJ63-20

Quick Links

[3M Graphics Warranties](#)
[Technical Information Selector](#)
[Safety Data Sheets \(SDS\)](#)
[Flammability \(ASTM E84 Reports\)](#)
[Videos](#)

Product Description

- For Solvent, UV and Latex Inkjet Printing and Screen Printing
- 3.2-mil matte white vinyl film

Product Features

- Pressure-sensitive adhesive
- Changeable
- Expected Performance Life of 1 year (unwarranted period for unprinted film with no graphic protection, applied to a flat, vertical, outdoor surface)

Recommended Types of Graphics and End Uses

The user is responsible for determining the product's suitability for the intended application. This product should be used on a test-and-approve basis.

- Short to medium-term, indoor and outdoor, backlit promotional graphics
- Signs, trade show and point-of-purchase displays, windows and taxi tops

Characteristics

These are typical values for unprocessed product. Processing may change the values.

Physical Characteristics

Characteristic	Value
Material	Calendered Vinyl
Film Color	White translucent
Thickness	Without adhesive: 3.2 mil (0.081 mm) With adhesive: 4.0 mil (0.102 mm)
Adhesive	Pressure-sensitive
Adhesive Color	Clear
Liner	Polycoated paper
Flammability	Call 1-800-328-3908 for information

Application Characteristics

Characteristic	Value
Finished Graphic Application Recommendation	Surface type: Smooth, flat and simple curved surfaces Substrate type: Metal, rigid plastic, windows and fiberglass Application temperature: 40° – 100°F (4° – 38°C) air and substrate Application method: wet or dry
Temperature Range After Application	-59 to +192 °F (-50 to +90 °C) (not for extended periods of time at the extremes)
Graphic Removal	Changeable



Warranty Information

3M Basic Product Warranty

3M Graphics Products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in its applicable 3M Graphics Product Bulletin and as further set forth in the [3M Graphics Warranties Bulletin](#).

Limited Remedy

The limited remedy applicable to each warranty is addressed in the 3M Graphics Warranties Bulletin found at 3MGraphics.com/warranties.

Limitation of Liability

Except where prohibited by law, 3M SHALL NOT UNDER ANY CIRCUMSTANCES BE LIABLE TO PURCHASER OR USER FOR ANY DIRECT (EXCEPT FOR THE LIMITED REMEDY PROVIDED IN THE 3M GRAPHICS WARRANTIES BULLETIN), INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES (INCLUDING, BUT NOT LIMITED TO, LABOR, NON-3M MATERIAL CHARGES, LOSS OF PROFITS, REVENUE, BUSINESS, OPPORTUNITY, OR GOODWILL) RESULTING FROM OR IN ANY WAY RELATED TO 3M'S GRAPHICS PRODUCTS, SERVICES, or THIS BULLETIN. This limitation of liability applies regardless of the legal or equitable theory under which such losses or damages are sought.

Additional Limitations

See the 3M Graphics Warranties Bulletin at 3MGraphics.com/warranties, for terms, additional limitations of your warranty, if any, information on reduced warranties for different exposures, and limitations of liability.

Factors that Affect Graphic Performance Life

The actual performance life of a graphic is affected by:

- the combinations of graphics materials used.
- complete ink drying or curing.
- selection, condition and preparation of the substrate.
- surface texture.
- application methods.
- angle and direction of sun exposure.
- environmental conditions.
- cleaning or maintenance methods.

Graphics Manufacturing



Before using any equipment, always read the manufacturer's instructions for safe operation.

Fabrication

All Printing Methods

This film has been optimized to perform well with a variety of inkjet printers and inks as well as screen printing inks and processes. It is the graphic manufacturer's responsibility to determine the film's suitability for use with their printers and inks.

To maximize the film performance:

- Use graphic protection. [3M™ Scotchcal™ Luster Overlamine 8509](#) has been specifically designed for use with 3M's promotional graphic films.
- Thoroughly dry the ink and film or properly cure the ink before applying graphic protection, and before storing or installing a graphic.

Inkjet Printing

Always read and follow the ink manufacturer's written instructions on usage.

- **Sheeted film:** When used on a flat-bed inkjet printer, sheeted film may produce printing defects.
- **Ink limiting:** The recommended maximum ink limit is 250%.
- **If sheeted or stacked graphics will be stored:** If you plan to store sheeted and stacked finished graphics for an extended period of times, leave an unprinted margin (about 1/4 inch) to allow for possible shrinkage before trimming the graphic.

Do not exceed the recommended total ink coverage for the ink series used on this film. Having too high a total physical ink amount on the film results in media characteristic changes, incomplete drying, overlamine lifting, and/or poor graphic performance.

Cutting

See [3M Instruction Bulletin 4.1](#) for Sheeting, Scoring and Film Cutting details.

Application and Installation

A wet application method is recommended. The film may exhibit some hazing, but this should disappear within 24 to 48 hours.

A dry application method can be used if necessary.

In addition to other 3M Bulletins specified in this document, the following Bulletins provide details that you may need to successfully apply a graphic.

- [3M Instruction Bulletin 5.7](#) Application, Wet Method for Translucent, Inkjet, Screen Printed and Cut Graphics
- [3M Instruction Bulletin 5.1](#) Select and Prepare Substrates for Graphic Application
- [3M Instruction Bulletin 5.5](#) Application, General Procedures for Interior and Exterior Dry Application

Pressure-sensitive Adhesive

This film has a pressure-sensitive adhesive. It bonds to the surface even with light pressure and cannot be repositioned.

Maintenance and Cleaning

Use a cleaner designed for high-quality painted surfaces. The cleaner must be wet, non-abrasive, without solvents, and have a pH value between 3 and 11 (neither strongly acidic nor strongly alkaline). See [3M Instruction Bulletin 6.5](#) for details.

Removal

This film can be easily removed without heat or chemicals. Most graphics can be removed and leave little or no adhesive residue on the substrate. The ease and rate of removal depends on a number of factors. See [3M Instruction Bulletin 6.5](#) for details.

Shelf Life, Storage and Shipping

Shelf Life

The shelf life is **never more than 2 years** from the date of manufacture on the original box.

If you process the film, the shelf life is changed to **1 year** from the processing date, but not later than the 2 year maximum from the manufacturing date.

Storage Conditions

- 90 °F (32 °C) maximum
- Out of sunlight
- Clean, dry area
- Original container
- Bring the film to print room temperature before using

Shipping Finished Graphics

Flat, or rolled printed side out on 6 inch (15 cm) or larger core. This helps prevent the liner, if used, from popping off.

Health and Safety



CAUTION

When handling any chemical products, read the manufacturer's container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to 3M.com/SDS, or by mail or in case of an emergency, call 1-800-364-3577 or 1-651-737-6501.

When using any equipment, always follow the manufacturer's instructions for safe operation.

Bulletin Change Summary

For the most current 3M Technical Information available to successfully use this product, please view this Bulletin electronically and click on the blue underlined links to view the relevant documents. Please read the entire Bulletin thoroughly.

Release E MAY-2016

- Updated Product Bulletin to new format. Please read the entire Bulletin thoroughly.

3M Commercial Solutions

3M Center
Building 220-12E-04
St. Paul, MN 55144-1000
1-800-328-3908
Fax 651-736-4233
3M.com/GRAPHICS

3M Canada

PO Box 5757
London, ON N6A 4T1
1-800-265-1840
Fax 519-452-6245

3M México S.A. de C.V.

Av. Santa Fe No. 55
Col. Santa Fe, Del. Alvaro Obregón
México D.F. 01210
General 5255-5270-0400
Fax 5255-5270-2277

3M Puerto Rico, Inc.

350 Chardon Avenue
Suite 1100
San Juan, PR 00918
General 787-620-3000
Fax 787-620-3018