


OGA DIAGONAL: 22.93 [582.46]
 VA DIAGONAL: 22.22 [564.34]
 PA DIAGONAL: 20.94 [531.80]

THIS PRODUCT IS MANUFACTURED IN ACCORDANCE WITH THE CURRENT CLEARTEK II CAPACITIVE TOUCH SCREEN SPECIFICATION (DOCUMENT 23655).



TOP LEVEL NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH
17-9331-206	NOV	SEE DWG	AG500

NOTES:

- WEIGHT OF GLASS IN GRAMS: 1221.14±10%
- 5 PIN AMP CONNECTOR
 LATCH STYLE HOUSING P/N: 487526-4
 TIN CONTACTS P/N: 2-487406-4
 HOUSING ORIENTED WITH LATCH DOWN

UNITS INCHES [MM]		3M TOUCH SYSTEMS METHUEN, MA USA <small>© COPYRIGHT 2008 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.</small>	01 INITIAL RELEASE PER CO 029159	6/08	SB
TOLERANCES UNLESS OTHERWISE SPECIFIED			CHANGE NOTICE		
.X ± .XX ±.03 [.76] .XXX ±.015 [.38] ANGLES ±1°		TITLE MARKETING DRAWING 17-9331-2XX			
THIRD ANGLE PROJECTION		DRAWN SB 6/08		CAD FORMAT AUTOCAD SHEET 1 OF 1	
DO NOT SCALE DRAWING		SCALE 1 = 1		SIZE C DOCUMENT NO. 35861-MKT REV 01	