3M Screen Printable Polyester Performance Label Products with Structured Adhesive 7214SA • 7215SA • 7218SA • 7220SA

Technical Data				October, 2009	
Product Description	3M TM Screen Printable Polyester Performance Label Products with Structured Adhesive are durable, high performance materials that offer excellent thermal stability and moisture resistance. These topcoated polyester label stocks utilize 3M TM Adhesive 350, which is designed to permanently bond to high and low surface energy plastics, textured and contoured surfaces, powder coatings, and slightly oily metals.				
	With unique microchannels throughout the structured adhesive, air flows freely from between the adhesive and substrate. Hand applied labels go on smoothly and stay that way. Even when labels are used on injection-molded plastic parts, bubbles that form from plastic outgassing can be smoothed to regain a neat appearance for the graphic.				
Construction	Product Number	Facestock	Adhesive	Liner	
	3M™ Screen Printable Polyester Performance Label Product 7214SA	.002 in. Brushed Silver Polyester TC	350 1.1 mils	90# Embossed Polycoated 7.8 mil bleached kraft sheet polyethylene coated on two sides	
	3M™ Screen Printable Polyester Performance Label Product 7215SA	.002 in. Bright Silver Polyester Gloss TC	350 1.1 mils	90# Embossed Polycoated 7.8 mil bleached kraft sheet polyethylene coated on two sides	
	3M™ Screen Printable Polyester Performance Label Product 7218SA	.002 in. Clear Polyester Gloss TC	350 1.1 mils	90# Embossed Polycoated 7.8 mil bleached kraft sheet Polyethylene coated on two sides	
	3M™ Screen Printable Polyester Performance Label Product 7220SA	.002 in. White Polyester Gloss TC	350 1.1 mils	90# Embossed Polycoated 7.8 mil bleached kraft sheet Polyethylene coated on two sides	
	(Calipers are nominal values)				
	 Most universal adhesive for label materials. Adhesive offers excellent chemical resistance and holding strength, even at high temperatures. Liner provides easy sheet processing and is designed for the ultimate in layflat. The hold is high in the processing and is designed for the ultimate in layflat. 				
	 Structured adhesive designed to allow air to flow from between adhesive and substrates so that hand applied labels go on smoothly and stay that way. 3MTM Screen Printable Polyester Performance Label Product 7220SA is UL recognized (File MH16411). See the UL listings for details 				

3M[™] Screen Printable Polyester Performance Label Products with Structured Adhesive

7214SA • 7215SA • 7218SA • 7220SA

Application Ideas	• Nameplates and product ID labels.					
	 Rating plates. Property identification and asset labeling. Warning, instruction, and service labels for durable goods, equipment/machinery and outdoor power equipment for lawn and garden. 					
Typical Physical Properties	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes. Adhesion properties determined per TLMI Method using 2.0 mil polyester with 1.1 mil of					
	autestve on a ponsileu staniess steel parei on the substrates risted in the table below.					
	Peel Adhesion to					
	Stainless Steel	3.8 lbs./in. (665 N/m)	TLMI Method, 180° Peel, 12"/min., 1" wide sample			
	HDPE	2.4 lbs./in. (420 N/m)	TLMI Method, 180° Peel, 12"/min., 1" wide sample			
	Polypropylene	3.1 lbs./in. (542 N/m)	TLMI Method, 180° Peel, 12"/min., 1" wide sample			
	Polycarbonate	3.1 lbs./in. (542 N/m)	TLMI Method, 180° Peel, 12"/min., 1" wide sample			
	Shear	> 100 hours	TLMI Method, 0.25 in ² x 500g			
	Adhesive Coat Weight	1.70 to 2.00 g/100 in.2	TM-2279			
	Release Range	10 to 110 g/2 in.	TLMI Method, 180° removal, 300 in./min.			
	Service 3M [™] Label Products Temperature 7214SA, 7220SA	-20°F to 302°F (-29°C to 150°C)				
	Minimum Application Temperature	50°F (10°C)				
	Convertability	In order to capture the superior performance properties of 3M [™] High Holding Acrylic Adhesive 350, thicker calipers are utilized for LSE or textured substrates. Its higher caliper, while desirable for the end use applications, may require extra care during processing. Please refer to the die cutting/converting section of this data page or the "Guide to Converting and Handling Label Products" technical bulletin for additional information.				

ApplicationFor maximum bond strength, the surface should be clean and dry. Typical cleaning
solvents are heptane and isopropyl alcohol.*TechniquesFor best bonding conditions, application surface should be at room temperature or
higher L ow temperature surfaces, helow 40°E (5°C) can acuse the adhesive to

higher. Low temperature surfaces, below $40^{\circ}F(5^{\circ}C)$ can cause the adhesive to become so firm that it will not develop maximum contact with the substrate. Higher initial bonds can be achieved through increased rubdown pressure.

*When using solvents, read and follow the manufacturer's precautions and directions for use.

3M[™] Screen Printable Polyester Performance Label Products with Structured Adhesive

7214SA • 7215SA • 7218SA • 7220SA

Printing	• High gloss general purpose topcoating is designed for use with UV, solvent and water-based screen inks. Topcoating will also accept flexo, ion deposition, off set, letter press, hot stamp, and thermal transfer printing. The converter should verify that their ink systems are compatible with the topcoating on the polyester film by testing beforehand. Ink systems recommended for testing are listed below.			
	UV Screen Inks: ANI Printing Inks (formerly Akzo Nobel) Uvoscreen II Environmental UV III Screen Pro Nazdar 1600 Sericol's Uviflex, 021 UV, UV and Pl	Solvent Screen Inks: Nazdar's 7700 and System 2 Sericol's Polyplast PY, GVYL, VYL, TMI and Techmark EL		
	Water-based Screen Inks: Nazdar 2700	Water-based Flexo Inks: ANI Printing Inks Hydro Film 4000 Series Arcar Ultra Film Series 5 Inks		
Die Cutting / Converting	Die cut with steel rule or flatbed dies. The 90# lay-flat liner also allows kiss cutting and back splitting. The converter can cut through the polyester facestock without cutting through the liner. Care should be taken to process this liner through rotary die cutting and stripping operations. If finished labels are applied to substrate by use of application machinery, thorough testing should be completed for compatibility with equipment.			
Packaging	Finished labels should be stored in plastic bags.			
Storage	Store at room temperature conditions of 72°F (22°C) and 50% relative humidity.			
Shelf Life	If stored under proper conditions, product retains its performance and properties for one year from date of manufacture.			

3M[™] Screen Printable Polyester Performance Label Products with Structured Adhesive

7214SA • 7215SA • 7218SA • 7220SA

Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.		
Product Use	Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.		
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.		
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.		
	This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.		

3M

Industrial Adhesives and Tapes Division Converter Markets

1030 Lake Road Medina, OH 44256-0428 800-422-8116 • 877-722-5072 (fax) www.3M.com/converter



3M is a trademark of 3M Company. Printed in U.S.A. ©3M 2009 70-0713-4528-7 (10/09)