

3M™ DI-NOC™ Architectural Finishes



Wood & Application
Information



3M™ DI-NOCT™ Abrasion Resistant Family

The superior abrasive resistance of this material is best for refurbishing or upgrading high traffic areas, counter and table tops. Designs for indoor usage only.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Abrasion Resistant	AR-1115	Indoor					
Abrasion Resistant	AR-1116	Indoor					
Abrasion Resistant	AR-1117	Indoor					
Abrasion Resistant	AR-1118	Indoor					
Abrasion Resistant	AR-1119	Indoor		Oak	Straight Grain	980	560
Abrasion Resistant	AR-1120	Indoor		Oak	Straight Grain	980	310

3M™ DI-NOCT™ Abstract Hard Family

Abstract Hard groups three families: LZ, PG and RT (rusty patterns), for indoor applications only.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Abstract Hard	LZ-461	Indoor					
Abstract Hard	LZ-462	Indoor					
Abstract Hard	LZ-480	Indoor					
Abstract Hard	LZ-587	Indoor					
Abstract Hard	PG-188	Indoor					
Abstract Hard	PG-189	Indoor					
Abstract Hard	PG-190	Indoor					
Abstract Hard	PG-193	Indoor					
Abstract Hard	PG-194	Indoor					
Abstract Hard	PG-195	Indoor					
Abstract Hard	PG-197	Indoor					
Abstract Hard	RT-1111	Indoor					
Abstract Hard	RT-1112	Indoor					

3M™ DI-NOCTM Abstract Soft Family

Available in different designs, all of them in soft tints, compassing the FA, PT, PX, and SE series. Mainly for indoor applications.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces












Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Abstract Soft	FA-1093	Indoor					
Abstract Soft	FA-1094	Indoor					
Abstract Soft	FA-1095	Indoor					
Abstract Soft	FA-1096	Indoor					
Abstract Soft	FA-1097	Indoor					
Abstract Soft	FA-1098	Indoor					
Abstract Soft	FA-1099	Indoor					
Abstract Soft	FA-1102	Indoor					
Abstract Soft	FA-1103	Indoor					
Abstract Soft	FA-591	Indoor					
Abstract Soft	FA-592	Indoor					
Abstract Soft	FA-601	Indoor					
Abstract Soft	FA-602	Indoor					
Abstract Soft	FA-688	Indoor					
Abstract Soft	FA-690	Indoor/Outdoor	*				
Abstract Soft	FA-7036	Indoor					
Abstract Soft	FA-7037	Indoor					
Abstract Soft	FA-7038	Indoor					
Abstract Soft	FA-7039	Indoor					
Abstract Soft	FA-7040	Indoor					
Abstract Soft	PT-344	Indoor					
Abstract Soft	PT-345	Indoor					
Abstract Soft	PT-346	Indoor					
Abstract Soft	PT-347	Indoor					
Abstract Soft	PT-735	Indoor					
Abstract Soft	PX-1088	Indoor					
Abstract Soft	PX-1089	Indoor					
Abstract Soft	PX-1090	Indoor					
Abstract Soft	SE-567	Indoor					
Abstract Soft	SE-568	Indoor					
Abstract Soft	SE-570	Indoor					
Abstract Soft	SE-684	Indoor					
Abstract Soft	SE-685	Indoor					

3M™ DI-NOCT™ Carbon Family





Very trendy family. Designs for indoor and outdoor usage.





















-  Can be used outdoor. Can be applied on PVC coated substrates
-  Can be used outdoor. Can not be applied on PVC coated substrates
-  Not meant for 3D application - Do not used on compound curved surfaces
-  Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Carbon	CA-418	Indoor					
Carbon	CA-419	Indoor					
Carbon	CA-420	Indoor/Outdoor					
Carbon	CA-421	Indoor/Outdoor					
Carbon	CA-422	Indoor					
Carbon	CA-423	Indoor/Outdoor					
Carbon	CA-424	Indoor/Outdoor					
Carbon	VM-425	Indoor					

3M™ DI-NOCTM Chic Family

Created through aluminium flake and pigment. Most of these patterns can be used outdoors as well.

-  Can be used outdoor. Can be applied on PVC coated substrates
-  Can be used outdoor. Can not be applied on PVC coated substrates
-  Not meant for 3D application - Do not used on compound curved surfaces
-  Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Chic	PA-036	Indoor/Outdoor					
Chic	PA-038	Indoor/Outdoor					
Chic	PA-039	Indoor/Outdoor					
Chic	PA-041	Indoor/Outdoor					
Chic	PA-045	Indoor/Outdoor					
Chic	PA-046	Indoor/Outdoor					
Chic	PA-175	Indoor/Outdoor					
Chic	PA-176	Indoor/Outdoor					
Chic	PA-177	Indoor/Outdoor					
Chic	PA-178	Indoor/Outdoor					
Chic	PA-179	Indoor/Outdoor					
Chic	PA-180	Indoor/Outdoor					
Chic	PA-181	Indoor/Outdoor					
Chic	PA-183	Indoor/Outdoor					
Chic	PA-184	Indoor					
Chic	PA-185	Indoor/Outdoor					
Chic	PA-187	Indoor/Outdoor					
Chic	PA-320	Indoor/Outdoor					
Chic	PA-389	Indoor/Outdoor					
Chic	PA-390	Indoor/Outdoor					
Chic	PA-683	Indoor/Outdoor					

3M™ DI-NOCT™ Fine Wood Family

A combination of unique processing steps results in a woodgrain appearance and texture that closely resemble authentic wood. Available in different patterns, varying from traditional wood to modern architectural designs. New designs within the Fine Wood series with horizontal grains (H), giving an even more natural look to your interior.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Fine Wood	FW-1016	Indoor		Ovangkol	Straight Cathedral Grain	1290	510
Fine Wood	FW-1017	Indoor		Ovangkol	Straight Cathedral Grain	1290	510
Fine Wood	FW-1018	Indoor		Ovangkol	Straight Cathedral Grain	1290	510
Fine Wood	FW-1019	Indoor		Ovangkol	Straight Cathedral Grain	1290	510
Fine Wood	FW-1020	Indoor		Walnut	Cathedral Grain	990	410
Fine Wood	FW-1021	Indoor		Walnut	Cathedral Grain	990	410
Fine Wood	FW-1022	Indoor		Walnut	Straight Cathedral Grain	1280	590
Fine Wood	FW-1023	Indoor		Walnut	Straight Cathedral Grain	1280	590
Fine Wood	FW-1024	Indoor		Camphor	Straight Grain	990	395
Fine Wood	FW-1025	Indoor		Persimmon	Straight Grain	1290	540
Fine Wood	FW-1026	Indoor		Persimmon	Straight Grain	1290	540
Fine Wood	FW-1027	Indoor		Persimmon	Straight Grain	1290	540
Fine Wood	FW-1028	Indoor		Persimmon	Straight Cathedral Grain	990	590
Fine Wood	FW-1029	Indoor		Zelkova	Straight Grain	830	295
Fine Wood	FW-1030	Indoor		Sucupira	Straight Grain	1280	590
Fine Wood	FW-1031	Indoor		Sucupira	Straight Grain	1280	590
Fine Wood	FW-1032	Indoor		Tiger Wood	Straight Grain	1280	440
Fine Wood	FW-1033	Indoor		Pine/Larch	Straight Grain	970	400
Fine Wood	FW-1034	Indoor		Pine/Larch	Straight Grain	1280	395
Fine Wood	FW-1035	Indoor		Pine/Larch	Straight Grain	1280	395
Fine Wood	FW-1036	Indoor		Pine/Larch	Straight Cathedral Grain	970	605
Fine Wood	FW-1037	Indoor		Mahogany	Cathedral Grain	1280	660
Fine Wood	FW-1038	Indoor		Mahogany	Straight Grain	970	460
Fine Wood	FW-1039H	Indoor		Teak	Straight Grain	660	1220
Fine Wood	FW-1040H	Indoor		Mahogany	Straight Grain	990	935
Fine Wood	FW-1113	Indoor		Walnut	Straight Grain	1280	530
Fine Wood	FW-1114	Indoor		Wenge	Straight Grain	640	295
Fine Wood	FW-231	Indoor		Anigre	Straight Grain	970	410
Fine Wood	FW-232	Indoor		Anigre	Straight Grain	970	410

3M™ DI-NOCT™ Fine Wood Family

A combination of unique processing steps results in a woodgrain appearance and texture that closely resemble authentic wood. Available in different patterns, varying from traditional wood to modern architectural designs. New designs within the Fine Wood series with horizontal grains (H), giving an even more natural look to your interior.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Fine Wood	FW-233	Indoor		Walnut	Straight Grain	970	490
Fine Wood	FW-234	Indoor		Cherry	Straight Grain	990	360
Fine Wood	FW-235	Indoor		Cherry	Straight Grain	970	315
Fine Wood	FW-236	Indoor		Oak	Straight Grain	980	560
Fine Wood	FW-237	Indoor		Oak	Straight Grain	980	560
Fine Wood	FW-238	Indoor		Wenge	Straight Grain	970	300
Fine Wood	FW-239	Indoor		Wenge	Straight Grain	970	300
Fine Wood	FW-240	Indoor		Padauk	Straight Cathedral Grain	980	570
Fine Wood	FW-322	Indoor/Outdoor	*	Parudao	Straight Grain	980	575
Fine Wood	FW-324	Indoor		Parudao	Straight Grain	1290	740
Fine Wood	FW-326	Indoor/Outdoor	*	Teak	Straight Grain	980	460
Fine Wood	FW-327	Indoor		Beech	Straight Cathedral Grain	1290	615
Fine Wood	FW-328	Indoor/Outdoor	*	Anigre	Straight Grain	1290	460
Fine Wood	FW-329	Indoor/Outdoor	*	Anigre	Straight Grain	1290	460
Fine Wood	FW-330	Indoor/Outdoor	*	Walnut	Cathedral Grain	1280	580
Fine Wood	FW-331	Indoor/Outdoor	*	Walnut	Cathedral Grain	1280	385
Fine Wood	FW-332	Indoor/Outdoor	*	Walnut	Cathedral Grain	1280	385
Fine Wood	FW-333	Indoor/Outdoor	*	Maple	Cathedral Grain	1280	550
Fine Wood	FW-334	Indoor/Outdoor	*	Maple	Cathedral Grain	1280	550
Fine Wood	FW-335	Indoor		Wenge	Straight Grain	970	300
Fine Wood	FW-336	Indoor		Tamo	Straight Cathedral Grain	1290	470
Fine Wood	FW-337	Indoor/Outdoor	*	Tamo	Straight Cathedral Grain	1290	470
Fine Wood	FW-338	Indoor/Outdoor	*	Walnut	Straight Grain	1290	580
Fine Wood	FW-339	Indoor/Outdoor	*	Nezuko	Straight Grain	830	465
Fine Wood	FW-340	Indoor/Outdoor	*	Sycamore	Straight Grain	970	620
Fine Wood	FW-341	Indoor		Anigre	Straight Grain	990	215
Fine Wood	FW-342	Indoor		Anigre	Straight Grain	990	215
Fine Wood	FW-501	Indoor		Walnut	Straight Grain	990	300
Fine Wood	FW-502	Indoor		Walnut	Straight Grain	990	300

3M™ DI-NOCT™ Fine Wood Family

A combination of unique processing steps results in a woodgrain appearance and texture that closely resemble authentic wood. Available in different patterns, varying from traditional wood to modern architectural designs. New designs within the Fine Wood series with horizontal grains (H), giving an even more natural look to your interior.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Fine Wood	FW-510	Indoor		Walnut	Straight Grain	990	300
Fine Wood	FW-521	Indoor		Slimline	Straight Grain	970	530
Fine Wood	FW-522	Indoor		Slimline	Straight Grain	970	530
Fine Wood	FW-575	Indoor		Persimmon	Straight Grain	1290	540
Fine Wood	FW-576	Indoor		Walnut	Straight Cathedral Grain	1290	570
Fine Wood	FW-577	Indoor		Camphor	Straight Grain	1280	780
Fine Wood	FW-606H	Indoor		Zebra Wood	Straight Grain	790	935
Fine Wood	FW-607H	Indoor		Zebra Wood	Straight Grain	790	935
Fine Wood	FW-608H	Indoor		Walnut	Straight Grain	970	1220
Fine Wood	FW-609H	Indoor		Walnut	Straight Grain	970	1220
Fine Wood	FW-612	Indoor/Outdoor	✳	Cherry	Straight Grain	990	340
Fine Wood	FW-613	Indoor/Outdoor	✳	Walnut	Straight Cathedral Grain	990	515
Fine Wood	FW-614	Indoor/Outdoor	✳	Walnut	Straight Cathedral Grain	990	515
Fine Wood	FW-616	Indoor		Beech	Straight Grain	990	300
Fine Wood	FW-617	Indoor		Beech	Straight Grain	990	300
Fine Wood	FW-618	Indoor/Outdoor	✳	Wenge	Straight Grain	970	300
Fine Wood	FW-619	Indoor/Outdoor	✳	Padauk	Straight Cathedral Grain	980	570
Fine Wood	FW-625	Indoor/Outdoor	✳	Oak	Straight Grain	980	310
Fine Wood	FW-627	Indoor/Outdoor	✳	Oak	Straight Grain	1280	580
Fine Wood	FW-638H	Indoor		Wenge	Straight Grain	990	935
Fine Wood	FW-639H	Indoor		Wenge	Straight Grain	990	935
Fine Wood	FW-640	Indoor		Paulownia	Straight Grain	980	335
Fine Wood	FW-641	Indoor/Outdoor	✳	Pine/Larch	Straight Grain	830	315
Fine Wood	FW-642	Indoor/Outdoor	✳	Pine/Larch	Straight Grain	830	315
Fine Wood	FW-643	Indoor/Outdoor	✳	Ebony	Straight Grain	830	400
Fine Wood	FW-644	Indoor/Outdoor	✳	Ebony	Straight Grain	830	400
Fine Wood	FW-645	Indoor		Zebra Wood	Straight Grain	980	470
Fine Wood	FW-646	Indoor/Outdoor	✳	Zebra Wood	Straight Grain	980	470
Fine Wood	FW-647	Indoor/Outdoor	✳	Mahogany	Straight Grain	830	485

3M™ DI-NOCT™ Fine Wood Family

A combination of unique processing steps results in a woodgrain appearance and texture that closely resemble authentic wood. Available in different patterns, varying from traditional wood to modern architectural designs. New designs within the Fine Wood series with horizontal grains (H), giving an even more natural look to your interior.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Fine Wood	FW-648	Indoor/Outdoor	✳	Mahogany	Straight Grain	830	485
Fine Wood	FW-649	Indoor/Outdoor	✳	Bubinga	Straight Grain	1290	590
Fine Wood	FW-650	Indoor/Outdoor	✳	Walnut	Straight Grain	1290	580
Fine Wood	FW-651	Indoor/Outdoor	✳	Walnut	Cathedral Grain	1290	590
Fine Wood	FW-652	Indoor		Cherry	Straight Grain	790	395
Fine Wood	FW-653	Indoor/Outdoor	✳	Ebony	Straight Grain	990	200
Fine Wood	FW-654	Indoor/Outdoor	✳	Ebony	Straight Grain	990	200
Fine Wood	FW-655	Indoor/Outdoor	✳	Cherry	Cathedral Grain	990	600
Fine Wood	FW-656	Indoor/Outdoor	✳	Zebra Wood	Straight Grain	970	350
Fine Wood	FW-677	Indoor/Outdoor	✳	Mahogany	Straight Grain	830	295
Fine Wood	FW-7001	Indoor		Elm	Straight Cathedral Grain	980	710
Fine Wood	FW-7002	Indoor		Redwood	Straight Cathedral Grain	1290	600
Fine Wood	FW-7003	Indoor		Redwood	Straight Cathedral Grain	1290	600
Fine Wood	FW-7004	Indoor		Redwood	Straight Cathedral Grain	1290	600
Fine Wood	FW-7005	Indoor		Redwood	Straight Cathedral Grain	1290	600
Fine Wood	FW-7006	Indoor		Walnut	Straight Cathedral Grain	830	425
Fine Wood	FW-7007	Indoor		Teak	Straight Grain	980	460
Fine Wood	FW-7008	Indoor		Walnut	Cathedral Grain	1290	1220
Fine Wood	FW-7009	Indoor		Walnut	Cathedral Grain	1290	1220
Fine Wood	FW-7010	Indoor		Camphor	Straight Grain	1280	780
Fine Wood	FW-7011	Indoor		Camphor	Straight Grain	1280	780
Fine Wood	FW-7012	Indoor		Camphor	Straight Grain	1280	780
Fine Wood	FW-7013	Indoor		Rosewood	Straight Grain	1280	455
Fine Wood	FW-7014	Indoor		Rosewood	Straight Grain	1280	455
Fine Wood	FW-7015	Indoor		Teak	Cathedral Grain	1280	495
Fine Wood	FW-7016	Indoor		Mahogany	Straight Grain	970	315
Fine Wood	FW-7017	Indoor		Oak	Straight Grain	1280	315
Fine Wood	FW-7018	Indoor		Pine/Larch	Straight Grain	1280	395
Fine Wood	FW-788	Indoor		Oak	Straight Grain	990	300
Fine Wood	FW-789	Indoor		Oak	Straight Grain	990	300

3M™ DI-NOCT™ Fine Wood Family

A combination of unique processing steps results in a woodgrain appearance and texture that closely resemble authentic wood. Available in different patterns, varying from traditional wood to modern architectural designs. New designs within the Fine Wood series with horizontal grains (H), giving an even more natural look to your interior.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces









Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Fine Wood	FW-791	Indoor/Outdoor	✳	Persimmon	Straight Cathedral Grain	990	590
Fine Wood	FW-795	Indoor/Outdoor	✳	Walnut	Straight Grain	990	300
Fine Wood	FW-796	Indoor/Outdoor	✳	Walnut	Straight Grain	990	300
Fine Wood	FW-799	Indoor/Outdoor	✳	Cherry	Straight Grain	830	455
Fine Wood	FW-886	Indoor/Outdoor	✳	Mahogany	Straight Grain	970	460
Fine Wood	FW-887	Indoor/Outdoor	✳	Mahogany	Straight Grain	970	460
Fine Wood	FW-888	Indoor/Outdoor	✳	Anigre	Straight Grain	990	235
Fine Wood	FW-889	Indoor/Outdoor	✳	Anigre	Straight Grain	990	235

3M™ DI-NOCTM G-Emboss Family





Recently developed series, with an unique design feature because of their geometric patterns. Available in both plain and metallic colours, of which the colourful appearance will be further enhanced by indirect ambient lighting. Most references are suited for outdoor use.




-  Can be used outdoor. Can be applied on PVC coated substrates
-  Can be used outdoor. Can not be applied on PVC coated substrates
-  Not meant for 3D application - Do not used on compound curved surfaces
-  Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
G-Emboss	GE-822	Indoor					
G-Emboss	GE-923	Indoor/Outdoor					
G-Emboss	GE-924	Indoor/Outdoor					

3M™ DI-NOCTM Hyper Metallic Family





Patterns contain real gold leaf, making the product suitable for high class environments.














-  Can be used outdoor. Can be applied on PVC coated substrates
-  Can be used outdoor. Can not be applied on PVC coated substrates
-  Not meant for 3D application - Do not used on compound curved surfaces
-  Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Hyper Metallic	HM-35D	Indoor					
Hyper Metallic	HM-35F	Indoor					
Hyper Metallic	HM-37F	Indoor					

3M™ DI-NOCT™ Leather Family

This film feels like authentic leather because of the special production process. All patterns are suited for 3D applications. Some of them can be used outdoors as well. New design: Metallic Leather (LE-1108, LE-1109 and LE-1110).

-  Can be used outdoor. Can be applied on PVC coated substrates
-  Can be used outdoor. Can not be applied on PVC coated substrates
-  Not meant for 3D application - Do not used on compound curved surfaces
-  Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Leather	LE-010	Indoor					
Leather	LE-015	Indoor					
Leather	LE-017	Indoor					
Leather	LE-018	Indoor					
Leather	LE-1104	Indoor					
Leather	LE-1105	Indoor					
Leather	LE-1106	Indoor					
Leather	LE-1107	Indoor					
Leather	LE-1108	Indoor					
Leather	LE-1109	Indoor					
Leather	LE-1110	Indoor					
Leather	LE-126	Indoor/Outdoor					
Leather	LE-128	Indoor/Outdoor					
Leather	LE-129	Indoor					
Leather	LE-137	Indoor/Outdoor					
Leather	LE-367	Indoor/Outdoor					
Leather	LE-516	Indoor/Outdoor					
Leather	LE-517	Indoor/Outdoor					
Leather	LE-593	Indoor					
Leather	LE-700	Indoor/Outdoor					
Leather	LE-701	Indoor					
Leather	LE-702	Indoor					
Leather	LE-703	Indoor/Outdoor					
Leather	LE-741	Indoor/Outdoor					
Leather	LE-742	Indoor/Outdoor					
Leather	LE-778	Indoor/Outdoor					
Leather	LE-779	Indoor					
Leather	LE-782	Indoor/Outdoor					
Leather	LE-783	Indoor/Outdoor					

3M™ DI-NOCT™ Little Wave Family

New emboss featuring straight line and wavy pattern. Some colors show three dimensionality.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Little Wave	LW-1080	Indoor					
Little Wave	LW-1081	Indoor					
Little Wave	LW-1082	Indoor					
Little Wave	LW-1083	Indoor					
Little Wave	LW-1084	Indoor					
Little Wave	LW-1085	Indoor					

3M™ DI-NOCT™ Metallic Wood Family

Black Persimmon and Ebony - 3 kinds of brightness



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Metallic Wood	MW-1073	Indoor		Persimmon	Straight Grain	1290	540
Metallic Wood	MW-1074	Indoor		Persimmon	Straight Grain	1290	540
Metallic Wood	MW-1075	Indoor		Persimmon	Straight Grain	1290	540
Metallic Wood	MW-776	Indoor/Outdoor		Ebony	Straight Grain	830	395
Metallic Wood	MW-777	Indoor/Outdoor		Ebony	Straight Grain	830	395

3M™ DI-NOCT™ Metallic Family

This colourful product range is varying from anodized to embossed appearance.
ME Metallics have a satin finish, whilst the VM Metallics are glossy.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces











Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Metallic	ME-1434	Indoor					
Metallic	ME-1435	Indoor					
Metallic	ME-147	Indoor/Outdoor	☀				
Metallic	ME-148	Indoor/Outdoor	☀				
Metallic	ME-377	Indoor/Outdoor	☀				
Metallic	ME-379	Indoor					
Metallic	ME-380	Indoor					
Metallic	ME-388	Indoor/Outdoor	☀				
Metallic	ME-391	Indoor/Outdoor	☀				
Metallic	ME-396	Indoor/Outdoor	☀				
Metallic	ME-431	Indoor					
Metallic	ME-432	Indoor					
Metallic	ME-433	Indoor					
Metallic	ME-486	Indoor/Outdoor	☀				
Metallic	ME-531	Indoor					
Metallic	ME-536	Indoor					
Metallic	ME-904	Indoor/Outdoor	☀				
Metallic	VM-1076	Indoor	✍				
Metallic	VM-1077	Indoor	✍				
Metallic	VM-167	Indoor	✍				
Metallic	VM-168	Indoor	✍				
Metallic	VM-169	Indoor	✍				
Metallic	VM-305	Indoor	✍				
Metallic	VM-306	Indoor	✍				
Metallic	VM-307	Indoor	✍				
Metallic	VM-368	Indoor	✍				
Metallic	VM-381	Indoor	✍				
Metallic	VM-383	Indoor	✍				
Metallic	VM-451	Indoor	✍				
Metallic	VM-452	Indoor	✍				
Metallic	VM-800	Indoor	✍				

3M™ DI-NOCTM Random Squares Family


The patchwork of small vertical, horizontal and diagonally grooved squares allows the most attractive space design, in line with the latest trends. White and black are recommended for office, whilst champagne gold and light green have been specially developed for retail environments.

-  Can be used outdoor. Can be applied on PVC coated substrates
-  Can be used outdoor. Can not be applied on PVC coated substrates
-  Not meant for 3D application - Do not used on compound curved surfaces
-  Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Random Squares	RS-487	Indoor					
Random Squares	RS-488	Indoor					
Random Squares	VM-482	Indoor					
Random Squares	VM-483	Indoor					
Random Squares	VM-484	Indoor					
Random Squares	VM-485	Indoor					

3M™ DI-NOCTM Sand Family

These modern colours and patterns achieve an authentic sandstone appearance, which makes these designs attractive for usage in plenty of different applications and environments.

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Sand	PC-224	Indoor					
Sand	PC-226	Indoor					
Sand	PC-491	Indoor					
Sand	PC-672	Indoor					
Sand	PC-673	Indoor					
Sand	PC-750	Indoor/Outdoor					
Sand	PC-751	Indoor					
Sand	PC-754	Indoor					
Sand	PC-756	Indoor					
Sand	PC-758	Indoor					
Sand	PC-760	Indoor					
Sand	PC-762	Indoor					
Sand	PC-785	Indoor					

3M™ DI-NOCT™ Single Color Family

Family consisting of soft and vivid colour groups. PS 959SR white is smoke resistant.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Single Color	PS-022	Indoor/Outdoor	*				
Single Color	PS-027	Indoor/Outdoor	*				
Single Color	PS-031	Indoor/Outdoor	*				
Single Color	PS-034	Indoor/Outdoor	*				
Single Color	PS-042	Indoor/Outdoor	*				
Single Color	PS-048	Indoor/Outdoor	*				
Single Color	PS-073	Indoor/Outdoor	*				
Single Color	PS-074	Indoor/Outdoor	*				
Single Color	PS-075	Indoor/Outdoor	*				
Single Color	PS-090	Indoor/Outdoor	*				
Single Color	PS-091	Indoor/Outdoor	*				
Single Color	PS-093	Indoor/Outdoor	*				
Single Color	PS-096	Indoor/Outdoor	*				
Single Color	PS-1001	Indoor					
Single Color	PS-1002	Indoor					
Single Color	PS-1003	Indoor					
Single Color	PS-1004	Indoor					
Single Color	PS-1005	Indoor					
Single Color	PS-1006	Indoor					
Single Color	PS-1007	Indoor					
Single Color	PS-1008	Indoor					
Single Color	PS-1009	Indoor					
Single Color	PS-1010	Indoor					
Single Color	PS-1011	Indoor					
Single Color	PS-1012	Indoor					
Single Color	PS-1013	Indoor					
Single Color	PS-106	Indoor/Outdoor	*				
Single Color	PS-107	Indoor/Outdoor	*				
Single Color	PS-110	Indoor/Outdoor	*				
Single Color	PS-112	Indoor/Outdoor	*				
Single Color	PS-113	Indoor/Outdoor	*				
Single Color	PS-116	Indoor/Outdoor	*				
Single Color	PS-121	Indoor/Outdoor	*				
Single Color	PS-132	Indoor/Outdoor	*				

3M™ DI-NOCT™ Single Color Family

Family consisting of soft and vivid colour groups. PS 959SR white is smoke resistant.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Single Color	PS-134	Indoor/Outdoor	*				
Single Color	PS-135	Indoor/Outdoor	*				
Single Color	PS-138	Indoor/Outdoor	*				
Single Color	PS-139	Indoor/Outdoor	*				
Single Color	PS-140	Indoor/Outdoor	*				
Single Color	PS-141	Indoor/Outdoor	*				
Single Color	PS-151	Indoor/Outdoor	*				
Single Color	PS-152	Indoor/Outdoor	*				
Single Color	PS-279	Indoor/Outdoor	*				
Single Color	PS-280	Indoor/Outdoor	*				
Single Color	PS-281	Indoor/Outdoor	*				
Single Color	PS-292	Indoor/Outdoor	*				
Single Color	PS-293	Indoor/Outdoor	*				
Single Color	PS-294	Indoor/Outdoor	*				
Single Color	PS-316	Indoor/Outdoor	*				
Single Color	PS-503	Indoor/Outdoor	*				
Single Color	PS-504	Indoor/Outdoor	*				
Single Color	PS-505	Indoor/Outdoor	*				
Single Color	PS-506	Indoor/Outdoor	*				
Single Color	PS-538	Indoor/Outdoor	*				
Single Color	PS-539	Indoor/Outdoor	*				
Single Color	PS-546	Indoor/Outdoor	*				
Single Color	PS-665	Indoor/Outdoor	*				
Single Color	PS-668	Indoor/Outdoor	*				
Single Color	PS-713	Indoor/Outdoor	*				
Single Color	PS-718	Indoor/Outdoor	*				
Single Color	PS-719	Indoor/Outdoor	*				
Single Color	PS-720	Indoor/Outdoor	*				
Single Color	PS-721	Indoor/Outdoor	*				
Single Color	PS-885	Indoor/Outdoor	*				
Single Color	PS-900	Indoor/Outdoor	*				
Single Color	PS-902	Indoor/Outdoor	*				
Single Color	PS-910	Indoor/Outdoor	*				

3M™ DI-NOCT™ Single Color Family

Family consisting of soft and vivid colour groups. PS 959SR white is smoke resistant.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces







Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Single Color	PS-912	Indoor/Outdoor	*				
Single Color	PS-914	Indoor/Outdoor	*				
Single Color	PS-917	Indoor/Outdoor	*				
Single Color	PS-920	Indoor/Outdoor	*				
Single Color	PS-948	Indoor/Outdoor	*				
Single Color	PS-949	Indoor/Outdoor	*				
Single Color	PS-950	Indoor/Outdoor	*				
Single Color	PS-952	Indoor/Outdoor	*				
Single Color	PS-954	Indoor/Outdoor	*				
Single Color	PS-955	Indoor/Outdoor	*				
Single Color	PS-957	Indoor/Outdoor	*				
Single Color	PS-959	Indoor/Outdoor	*				
Single Color	PS-959 SR	Indoor					
Single Color	PS-971	Indoor/Outdoor	*				
Single Color	PS-975	Indoor/Outdoor	*				
Single Color	PS-976	Indoor/Outdoor	*				
Single Color	PS-980	Indoor/Outdoor	*				
Single Color	PS-982	Indoor/Outdoor	*				
Single Color	PS-983	Indoor/Outdoor	*				
Single Color	PS-992	Indoor/Outdoor	*				
Single Color	PS-998	Indoor/Outdoor	*				
Single Color	PS-999	Indoor/Outdoor	*				

3M™ DI-NOCTM Stone Family








All designs with a similar look to authentic stone. For interior usage only.

-  Can be used outdoor. Can be applied on PVC coated substrates
-  Can be used outdoor. Can not be applied on PVC coated substrates
-  Not meant for 3D application - Do not used on compound curved surfaces
-  Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Stone	ST-440	Indoor					
Stone	ST-442	Indoor					
Stone	ST-523	Indoor					
Stone	ST-526	Indoor					
Stone	ST-553	Indoor					
Stone	ST-555	Indoor					
Stone	ST-556	Indoor					
Stone	ST-557	Indoor					
Stone	ST-736	Indoor					
Stone	ST-737	Indoor					

3M™ DI-NOCTM Stucco Family

This film simulates the appearance of Italian plaster. Available in two product variations: muted and vibrant shades.

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Stucco	SE-1086	Indoor					
Stucco	SE-1087	Indoor					
Stucco	SE-824	Indoor/Outdoor					
Stucco	SE-825	Indoor/Outdoor					
Stucco	SE-826	Indoor/Outdoor					
Stucco	SE-827	Indoor/Outdoor					
Stucco	SE-828	Indoor/Outdoor					
Stucco	SE-829	Indoor					
Stucco	SE-893	Indoor/Outdoor					
Stucco	SE-896	Indoor/Outdoor					





3M™ DI-NOCTM Terracotta Family








Available in 2 attractive patterns. Suitable for 3D applications. Interior use only.

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Terracotta	FA-565	Indoor					
Terracotta	FA-671	Indoor					

3M™ DI-NOCTM Weave Family

This film has a woven, embossed surface texture. It is soft to the touch, yet it resists dirt and abrasion. Suitable only for interior usage and for both flat and curved surfaces.

-  Can be used outdoor. Can be applied on PVC coated substrates
-  Can be used outdoor. Can not be applied on PVC coated substrates
-  Not meant for 3D application - Do not used on compound curved surfaces
-  Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Weave	FE-1014	Indoor					
Weave	FE-1015	Indoor					
Weave	FE-1091	Indoor					
Weave	FE-1092	Indoor					
Weave	FE-1100	Indoor					
Weave	FE-1101	Indoor					
Weave	FE-299	Indoor					
Weave	FE-301	Indoor/Outdoor	 				
Weave	FE-801	Indoor					
Weave	FE-802	Indoor					
Weave	FE-804	Indoor					
Weave	FE-805	Indoor					
Weave	FE-813	Indoor					

3M™ DI-NOCT™ Wood Grain Family

The natural appearance of the different patterns, varying from light to dark, and all popular timber types create an atmosphere of warmth and prestige. Because of their natural repeat and grain pattern they have a similar look to authentic wood. Some references have a glossy visual effect.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Wood Grain	WG-101	Indoor		Ebony	Straight Grain	980	460
Wood Grain	WG-102	Indoor		Ebony	Straight Grain	980	460
Wood Grain	WG-103	Indoor		Ebony	Straight Grain	980	460
Wood Grain	WG-1041	Indoor		Walnut	Straight Cathedral Grain	1280	610
Wood Grain	WG-1042	Indoor		Walnut	Straight Cathedral Grain	1280	610
Wood Grain	WG-1043	Indoor		Walnut	Straight Cathedral Grain	1280	610
Wood Grain	WG-1044	Indoor		Elm	Straight Cathedral Grain	980	710
Wood Grain	WG-1045	Indoor		Elm	Straight Cathedral Grain	980	710
Wood Grain	WG-1046	Indoor		Elm	Straight Grain	980	710
Wood Grain	WG-1047	Indoor		Oak	Straight Grain	1280	635
Wood Grain	WG-1048	Indoor		Oak	Straight Grain	1280	635
Wood Grain	WG-1049	Indoor		Oak	Straight Grain	1280	635
Wood Grain	WG-1050	Indoor		Oak	Straight Grain	1280	590
Wood Grain	WG-1051	Indoor		Kaya	Straight Grain	980	560
Wood Grain	WG-1052	Indoor		Kaya	Straight Grain	980	560
Wood Grain	WG-1053	Indoor		Ebony	Straight Cathedral Grain	1280	395
Wood Grain	WG-1054	Indoor		Sycamore	Straight Grain	980	590
Wood Grain	WG-1055	Indoor		Sycamore	Straight Grain	980	590
Wood Grain	WG-1056	Indoor		Sycamore	Straight Grain	980	590
Wood Grain	WG-1057	Indoor		Cherry	Cathedral Grain	1290	710
Wood Grain	WG-1058	Indoor		Cherry	Cathedral Grain	1290	710
Wood Grain	WG-1059	Indoor		Cherry	Straight Grain	1290	540
Wood Grain	WG-1060	Indoor		Cherry	Straight Grain	1290	540
Wood Grain	WG-1061	Indoor		Cherry	Straight Grain	1290	540
Wood Grain	WG-1062	Indoor		Cherry	Straight Grain	1290	540
Wood Grain	WG-1063	Indoor		Hickory	Straight Cathedral Grain	990	395
Wood Grain	WG-1064	Indoor		Hickory	Straight Cathedral Grain	990	395
Wood Grain	WG-1065	Indoor		Hickory	Straight Cathedral Grain	990	395
Wood Grain	WG-1066	Indoor		Plum	Straight Cathedral Grain	970	605
Wood Grain	WG-1067	Indoor		Plum	Straight Cathedral Grain	970	605
Wood Grain	WG-1068	Indoor		Yew	Straight Grain	830	395
Wood Grain	WG-1069	Indoor		Yew	Straight Grain	830	395

3M™ DI-NOCT™ Wood Grain Family

The natural appearance of the different patterns, varying from light to dark, and all popular timber types create an atmosphere of warmth and prestige. Because of their natural repeat and grain pattern they have a similar look to authentic wood. Some references have a glossy visual effect.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Wood Grain	WG-1070	Indoor		Ebony	Straight Grain	640	60
Wood Grain	WG-1071	Indoor		Ebony	Straight Grain	640	60
Wood Grain	WG-1072	Indoor		Design Wood	Design	640	465
Wood Grain	WG-108	Indoor		Slimline	Straight Grain	970	530
Wood Grain	WG-109	Indoor		Slimline	Straight Grain	970	530
Wood Grain	WG-115	Indoor/Outdoor	☀	Oak	Straight Cathedral Grain	650	295
Wood Grain	WG-143	Indoor		Oak	Straight Grain	970	300
Wood Grain	WG-144	Indoor		Oak	Straight Cathedral Grain	990	290
Wood Grain	WG-145	Indoor		Zebra Wood	Straight Grain	1290	975
Wood Grain	WG-156	Indoor/Outdoor	☀ ☒	Tamo	Straight Cathedral Grain	1300	595
Wood Grain	WG-157	Indoor/Outdoor	☀ ☒	Teak	Straight Cathedral Grain	980	345
Wood Grain	WG-159	Indoor/Outdoor	☀ ☒	Rosewood	Straight Cathedral Grain	1300	625
Wood Grain	WG-166	Indoor	☒	Oak	Straight Cathedral Grain	1300	600
Wood Grain	WG-222	Indoor		Aged Wood	Design	970	610
Wood Grain	WG-242	Indoor		Hard Maple	Cathedral Grain	990	300
Wood Grain	WG-243	Indoor		Hard Maple	Cathedral Grain	990	300
Wood Grain	WG-244	Indoor		Pear	Straight Grain	990	295
Wood Grain	WG-245	Indoor		Pear	Straight Grain	990	295
Wood Grain	WG-246	Indoor		Pear	Cathedral Grain	990	415
Wood Grain	WG-247	Indoor		Sycamore	Straight Grain	990	420
Wood Grain	WG-248	Indoor		Sycamore	Straight Grain	990	420
Wood Grain	WG-249	Indoor		Sycamore	Straight Grain	1300	415
Wood Grain	WG-250	Indoor		Silver Heart	Straight Cathedral Grain	1300	415
Wood Grain	WG-251	Indoor/Outdoor	☀	Silver Heart	Straight Cathedral Grain	1300	415
Wood Grain	WG-254	Indoor/Outdoor	☀	Teak	Straight Cathedral Grain	980	1200
Wood Grain	WG-256	Indoor/Outdoor	☀	Oak	Straight Grain	980	310
Wood Grain	WG-304	Indoor/Outdoor	☀	Rosewood	Straight Cathedral Grain	980	1220
Wood Grain	WG-364	Indoor		Bubinga	Burl	990	295
Wood Grain	WG-364GN	Indoor		Bubinga Gloss	Burl	990	295
Wood Grain	WG-372	Indoor/Outdoor	☀	Teak	Straight Grain	780	235

3M™ DI-NOCT™ Wood Grain Family

The natural appearance of the different patterns, varying from light to dark, and all popular timber types create an atmosphere of warmth and prestige. Because of their natural repeat and grain pattern they have a similar look to authentic wood. Some references have a glossy visual effect.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-joint method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Wood Grain	WG-373	Indoor/Outdoor	☀	Shioji	Straight Grain	650	295
Wood Grain	WG-376	Indoor		Oak	Straight Grain	1280	580
Wood Grain	WG-408	Indoor/Outdoor	☀	Primavera	Straight Grain	980	395
Wood Grain	WG-410	Indoor/Outdoor	☀	Pear	Straight Grain	990	295
Wood Grain	WG-411	Indoor/Outdoor	☀	Pear	Straight Grain	990	295
Wood Grain	WG-416	Indoor/Outdoor	☀	Design Wood	Burl	640	465
Wood Grain	WG-417	Indoor/Outdoor	☀	Design Wood	Burl	640	465
Wood Grain	WG-428	Indoor/Outdoor	☀	Design Wood	Burl	640	465
Wood Grain	WG-430	Indoor/Outdoor	☀	Teak	Straight Cathedral Grain	980	1200
Wood Grain	WG-453	Indoor		Hinoki	Straight Grain	970	265
Wood Grain	WG-467	Indoor		Ash	Straight Cathedral Grain	1300	555
Wood Grain	WG-477	Indoor		Sycamore	Straight Cathedral Grain	780	595
Wood Grain	WG-478	Indoor		Sycamore	Straight Cathedral Grain	780	595
Wood Grain	WG-624	Indoor/Outdoor	☀	Pear	Straight Grain	990	295
Wood Grain	WG-628	Indoor		Anigre	Straight Grain	970	395
Wood Grain	WG-629	Indoor/Outdoor	☀	Cherry	Straight Grain	970	315
Wood Grain	WG-657	Indoor		Design Wood	Burl	640	465
Wood Grain	WG-658	Indoor		Design Wood	Burl	640	465
Wood Grain	WG-659	Indoor		Design Wood	Burl	640	465
Wood Grain	WG-660	Indoor		Sycamore	Straight Grain	980	590
Wood Grain	WG-662	Indoor		Bubinga	Straight Grain	1290	590
Wood Grain	WG-663	Indoor/Outdoor	☀	Bubinga	Cathedral Grain	970	250
Wood Grain	WG-664	Indoor/Outdoor	☀	Ebony	Straight Grain	830	395
Wood Grain	WG-693	Indoor/Outdoor	☀	Primavera	Straight Grain	980	395
Wood Grain	WG-694	Indoor/Outdoor	☀	Primavera	Straight Grain	980	395
Wood Grain	WG-695	Indoor		Oak	Straight Cathedral Grain	980	610
Wood Grain	WG-696	Indoor		Oak	Straight Cathedral Grain	980	610
Wood Grain	WG-697	Indoor/Outdoor	☀	Oak	Straight Cathedral Grain	1300	600
Wood Grain	WG-698	Indoor		Oak	Straight Cathedral Grain	1300	600
Wood Grain	WG-699	Indoor		Pear	Straight Cathedral Grain	970	380

3M™ DI-NOCT™ Wood Grain Family

The natural appearance of the different patterns, varying from light to dark, and all popular timber types create an atmosphere of warmth and prestige. Because of their natural repeat and grain pattern they have a similar look to authentic wood. Some references have a glossy visual effect.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces



Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Wood Grain	WG-7019	Indoor		Walnut	Straight Cathedral Grain	830	425
Wood Grain	WG-7020	Indoor		Beech	Straight Cathedral Grain	1290	710
Wood Grain	WG-7021	Indoor		Beech	Straight Cathedral Grain	1290	710
Wood Grain	WG-7022	Indoor		Teak	Cathedral Grain	1280	495
Wood Grain	WG-7023	Indoor		Teak	Cathedral Grain	1280	495
Wood Grain	WG-7024	Indoor		Padauk	Cathedral Grain	1280	550
Wood Grain	WG-7025	Indoor		Cherry	Straight Grain	790	210
Wood Grain	WG-7026	Indoor		Cherry	Straight Grain	790	210
Wood Grain	WG-7027	Indoor		Cherry	Straight Grain	790	210
Wood Grain	WG-7028	Indoor		Zebra Wood	Straight Grain	990	375
Wood Grain	WG-7029	Indoor		Ebony	Straight Cathedral Grain	1280	395
Wood Grain	WG-7030	Indoor		Ebony	Straight Cathedral Grain	1280	395
Wood Grain	WG-7031	Indoor		Ebony	Straight Cathedral Grain	1280	395
Wood Grain	WG-7032	Indoor		Pine/Larch	Straight Grain	1280	395
Wood Grain	WG-7033	Indoor		Walnut	Straight Cathedral Grain	1280	590
Wood Grain	WG-7034	Indoor		Beech	Straight Cathedral Grain	1280	395
Wood Grain	WG-7035	Indoor		Beech	Straight Cathedral Grain	1280	395
Wood Grain	WG-705	Indoor		Zebra Wood	Straight Grain	990	295
Wood Grain	WG-706	Indoor		Zebra Wood	Straight Grain	990	295
Wood Grain	WG-707	Indoor		Zebra Wood	Straight Grain	990	295
Wood Grain	WG-709	Indoor		Sycamore	Straight Cathedral Grain	780	595
Wood Grain	WG-763	Indoor		Bird's Eye Maple	Burl	810	420
Wood Grain	WG-763GN	Indoor		Bird's Eye Maple Gloss	Burl	810	420
Wood Grain	WG-765	Indoor		Bird's Eye Maple	Burl	810	420
Wood Grain	WG-765GN	Indoor		Bird's Eye Maple Gloss	Burl	810	420
Wood Grain	WG-766	Indoor/Outdoor	★	Anigre	Straight Grain	970	395
Wood Grain	WG-767	Indoor		Bird's Eye Maple	Burl	810	420
Wood Grain	WG-821	Indoor		Sycamore	Straight Cathedral Grain	780	595
Wood Grain	WG-831	Indoor/Outdoor	★	Maple	Straight Grain	820	180
Wood Grain	WG-832	Indoor		Maple	Straight Grain	970	265
Wood Grain	WG-833	Indoor		Maple	Straight Grain	970	265

3M™ DI-NOCT™ Wood Grain Family

The natural appearance of the different patterns, varying from light to dark, and all popular timber types create an atmosphere of warmth and prestige. Because of their natural repeat and grain pattern they have a similar look to authentic wood. Some references have a glossy visual effect.



Can be used outdoor. Can be applied on PVC coated substrates



Can be used outdoor. Can not be applied on PVC coated substrates



Not meant for 3D application - Do not used on compound curved surfaces















Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Wood Grain	WG-835	Indoor		Maple	Straight Grain	990	445
Wood Grain	WG-836	Indoor		Maple	Straight Grain	990	445
Wood Grain	WG-837	Indoor		Maple	Straight Grain	990	445
Wood Grain	WG-839	Indoor		Ash	Straight Grain	970	445
Wood Grain	WG-840	Indoor		Alder	Straight Grain	1290	445
Wood Grain	WG-841	Indoor		Alder	Straight Grain	1290	445
Wood Grain	WG-845	Indoor		Hinoki	Straight Grain	980	275
Wood Grain	WG-846	Indoor		Sugi/Cedar	Straight Grain	1290	195
Wood Grain	WG-854	Indoor/Outdoor	✳	Oak	Straight Grain	980	560
Wood Grain	WG-855	Indoor		Cherry	Straight Grain	990	295
Wood Grain	WG-856	Indoor/Outdoor	✳	Beech	Straight Cathedral Grain	1300	645
Wood Grain	WG-857	Indoor/Outdoor	✳	Beech	Straight Cathedral Grain	1300	645
Wood Grain	WG-860	Indoor		Walnut	Straight Grain	970	365
Wood Grain	WG-862	Indoor		Walnut	Straight Grain	990	555
Wood Grain	WG-863	Indoor		Pine/Larch	Straight Grain	820	500
Wood Grain	WG-865	Indoor/Outdoor	✳	Cherry	Cathedral Grain	1300	600
Wood Grain	WG-866	Indoor/Outdoor	✳	Cherry	Cathedral Grain	1300	600
Wood Grain	WG-867	Indoor		Pine/Larch	Burl	980	610
Wood Grain	WG-871	Indoor		Birch	Cathedral Grain	990	455
Wood Grain	WG-872	Indoor		Birch	Cathedral Grain	990	455
Wood Grain	WG-877	Indoor/Outdoor	✳	Cherry	Straight Grain	970	385
Wood Grain	WG-878	Indoor/Outdoor	✳	Cherry	Straight Grain	970	385
Wood Grain	WG-879	Indoor/Outdoor	✳	Maple	Straight Grain	970	460
Wood Grain	WG-880	Indoor/Outdoor	✳	Maple	Straight Grain	970	460
Wood Grain	WG-881	Indoor/Outdoor	✳	Barr	Burl	810	590

3M™ DI-NOCTM Wood Grain Family

The natural appearance of the different patterns, varying from light to dark, and all popular timber types create an atmosphere of warmth and prestige. Because of their natural repeat and grain pattern they have a similar look to authentic wood. Some references have a glossy visual effect.

-  Can be used outdoor. Can be applied on PVC coated substrates
-  Can be used outdoor. Can not be applied on PVC coated substrates
-  Not meant for 3D application - Do not used on compound curved surfaces
-  Do not conduct butt-join method and apply with reveals or joint separations

Family	Reference Number	Indoor/Outdoor Application	Usage	Wood Type	Surface Pattern	Repeat Pattern Height	Repeat Pattern Width
Wood Grain	WG-940	Indoor/Outdoor		Plum	Straight Cathedral Grain	970	605
Wood Grain	WG-941	Indoor/Outdoor		Zebra Wood	Straight Grain	1280	590
Wood Grain	WG-942	Indoor		Maple	Straight Grain	1280	625
Wood Grain	WG-943	Indoor/Outdoor		Oak	Straight Cathedral Grain	1280	690
Wood Grain	WG-944	Indoor/Outdoor		Oak	Straight Grain	1280	635
Wood Grain	WG-946	Indoor/Outdoor		Pear	Straight Cathedral Grain	1290	640
Wood Grain	WG-947	Indoor/Outdoor		Tamo	Straight Cathedral Grain	1290	470
Wood Grain	WG-960	Indoor		Tamo	Straight Cathedral Grain	1290	470
Wood Grain	WG-962	Indoor/Outdoor		Design Wood	Burl	640	465
Wood Grain	WG-964	Indoor/Outdoor		Oak	Straight Cathedral Grain	990	590
Wood Grain	WG-965	Indoor		Oak	Straight Cathedral Grain	1280	590