

# 3M Industrial Adhesives and Tapes Division

## Custom Printed Box Sealing Tapes



# Make Your Message Stick



### Get the Message

Everyone will know exactly who the package came from when you put your company logo or message on every package you send with 3M Custom Printed Box Sealing Tapes. Every package becomes a communication center for free advertising, package handling instructions, or tamper evidence. Choose one or two color printing in your choice of eleven Pantone ink colors on white, tan or clear tape.



# Custom Tapes and Dispensers to Fit Your Needs



## Custom Printed Security Tape Designs

Select one of our Scotch® Box Sealing Tapes, then choose one of our existing tamper evident patterns, add your company colors and logo, or you can design your own security related graphic.



## Standard Message Tape

Available in 100 yd length rolls.



## Scotch® Box Sealing Tape Dispenser H-192

Combines features of our most popular roll-on and hand-held dispensers. It is easy to use in one-hand application, plus the operator can control the tape tension with the tape roll brake. Its unique design minimizes wrist movement for comfortable operation. It accommodates tape up to 2" wide.



## Scotch® M-900 Box Sealing Tape Definite Length Dispenser

Dispenses 1.5" to 3" wide "Scotch" Brand box sealing tape (maximum roll diameter - 9"). Tape lengths from 1.5" to 16" (40 to 400mm) maximum are delivered with one level stroke.



## 3M-Matic™ a20 Adjustable Case Sealer

When your packaging volume exceeds the limits of manual case sealing, the 3M-Matic™ Adjustable Case Sealer a20 is an affordable increase in productivity for top and bottom sealing of RSCs. With quick, easy adjustments you can seal up to 30 cases per minute.



## 700a

Productivity and performance - Four belts (two top and bottom) for positive traction and gear motor drive for high volume, heavy duty reliability shift-after-shift for up to 40 cases per minute.

3M and Scotch are trademarks of 3M Company.

**Product Use:** All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

**Warranty, Limited Remedy, and Disclaimer:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. **3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE.** If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



## Industrial Business Industrial Adhesives and Tapes Division

Customer Response Center  
900 Bush Avenue  
Building 21-1W-10  
St. Paul, MN 55144-1000  
1-800-362-3550  
[www.3M.com/industrial](http://www.3M.com/industrial)

Please recycle. Printed in USA.  
© 3M 2008. All rights reserved.  
70-0710-0385-2