

3M Science.
Applied to Life.™

Flex your work zone management muscle.

Help improve work zone safety with 3M™ Flexible Prismatic Reflective Sheeting Series 3300.





Super thin for a work zone win.

Stay on top of ever-changing work zone traffic guidance with Series 3300. This super-thin sheeting is quick and easy to apply and conforms to virtually any curved surface, giving your drums, barricades and channelizers outstanding visibility—even in less-than-optimal situations. Its impact-resistant coating gives this durable sheeting long-lasting reflectivity and visibility.

- ▶ Applies easily by hand or using a squeeze roller
- ▶ Pre-coated pressure-sensitive adhesive
- ▶ Maintains visibility at high entrance angles



Available in orange, white, orange/white or red/white stripes

3M

Transportation Safety Division
3M Center, Building 225-4N-14
St. Paul, MN 55144-1000
1.800.553.1380

Find work zone flexibility at [3M.com/RoadSafety](https://www.3m.com/RoadSafety).

Please recycle. Printed in USA.
3M is a trademark of 3M.
© 3M 2020. All rights reserved.