


OGA DIAGONAL: 18.25 [463.63]
 VA DIAGONAL: 17.54 [445.50]
 PA DIAGONAL: 16.54 [420.12]

US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PRODUCT SPEC
98-0003-3177-1	FFC	8.00" [203.20]	AG500	36235
98-0003-3178-9	SER	8.00" [203.20]	AG500	36235
98-0003-3179-7	USB R	8.00" [203.20]	AG500	36235



SECTION A-A
SCALE: NONE

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 1893±10%
2. NICOMATIC HOUSING P/N: OLO5
 NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
 HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LL
2	UL
3	SHLD
4	UR
5	LR

UNITS INCHES [MM]

TOLERANCES UNLESS OTHERWISE SPECIFIED
 .X ±
 .XX ±.03 [.76]
 .XXX ±.015 [.38]
 ANGLES ±1°

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

SCALE 1 = 1

3M 3M TOUCH SYSTEMS
 METHUEN, MA
 USA

© COPYRIGHT 2004
 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
 3M COMPANY AND MAY NOT BE REPRODUCED
 WITHOUT 3M WRITTEN PERMISSION OR USED OR
 DISCLOSED FOR OTHER THAN 3M AUTHORIZED
 PURPOSES.

DRAWN MTD 1/15/09

REV	CHANGE NOTICE	DATE	DRW
C	REVISED PER CO 033533	9/11	SB
O2	REVISED PER CO 030448	5/09	SB
O1	INITIAL RELEASE PER CO 029934	1/09	MTD

TITLE
MARKETING DRAWING
SCT76NN 17.54"

CAD FORMAT AUTOCAD SHEET 1 OF 1

SIZE C DOCUMENT NO. 36481-MKT REV C