

3M Advanced Materials Division

3M™ Glass Bubbles XLD3000

Introduction

3M™ Glass Bubbles XLD3000 are high-strength additives for polymers made from a water-resistant and chemically stable soda-lime-borosilicate glass. These glass bubbles are designed for numerous applications such as deep water syntactic foams and airless spray coatings. The bubbles produce strong, stable voids with low thermal conductivity, helping the coating achieve the necessary compressive strength.

3M™ Glass Bubbles help to reduce weight; reduce noise, vibration and harmonics; reduce thermal expansion; and contribute to cost savings. They are used in a variety of applications in diverse markets, including paints and coatings, thermoset rubber and plastic, insulation and buoyancy and wet pipe flowline insulation.

Flow properties: 3M glass bubbles XLD3000 will remain free flowing for at least two years from the date of manufacture when stored in the original, unopened container in accordance with the recommended storage conditions. (See storage recommendations at right).

Glass bubble breakage: Breakage may occur if the product is severely processed. To minimize breakage, minimize exposure to high shear processes and point contact shear such as gear pumps and 3-roll mills. When adding to an extrusion process, the material should be added downstream of the feed

Material Description (Not for specification purposes.)

| Property | 3M™ Glass Bubbles XLD3000 |
|--------------------|--------------------------------|
| Shape | Hollow spheres with thin walls |
| Composition | Soda-lime-borosilicate glass |
| Color, unaided eye | White, powdery |

Typical Physical Properties (Not for specification purposes.)

| Property | 3M™ Glass Bubbles XLD3000 |
|--|---------------------------|
| Crush strength, 90% survival by volume (psi) | 3,000 |
| True density (g/cc) | 0.23 |
| Packing factor (bulk density to true particle density) | 60% |
| pH (at 5 wt% loading in water) | 9.5 |
| Average diameter (microns) | 30 |
| Softening point (°C) | 600 |
| Flotation (density <1.0 g/cc) | 99% |
| Volatile content (by weight) | 0.5% |

3M Advanced Materials product realization process and manufacturing sites are aligned to ISO 9001 Quality Systems. Test data is generated by following documented procedures and test methods.

hopper via a side stuffer or top feeder (similar to adding glass fiber). Contact 3M technical service or your equipment vendor for assistance if breakage is suspected.

Packaging

3M glass bubbles XLD3000 are available in the following packaging sizes:

Gallon: 1 lb/0.4 kg

Small box: 50 lb/23 kg

Large box: 330 lb/50 kg

Bulk bag: 375 lb/170 kg

Bulk trailer: 15,000 lb/6,804 kg

Product Storage, Handling and Safety

Storage: Ideal storage conditions include unopened cartons in a dry and temperature-controlled warehouse. Extended exposure of 3M glass bubbles XLD3000 boxes to high humidity and/or conditions susceptible to condensation may result in some amount of “caking” of the glass bubbles.

To minimize the potential for caking and thereby maximize storage life, the following suggestions are offered:

1. Carefully re-tie opened bags immediately after use.

Continued on next page.

Product Storage, Handling and Safety (continued)

2. If the polyethylene bag is punctured during shipping or handling, seal the hole as soon as possible or insert the contents into an undamaged bag.
3. During hot and/or humid months, store boxes in the driest, coolest space available.

If controlled storage conditions are unavailable, carry a minimum inventory, and process on a first in/first out basis.

Handling: Due to the low weight and small particle size of 3M™ Glass Bubbles XLD3000, dusting may occur while handling and processing. To minimize the dusting potential during handling, consider the following:

- Do not open glass bubbles packages until ready to use.
- Upon opening, have local exhaust ventilation near the opening to pull away airborne particles. (Dust collection equipment may be required – check local OSHA and other applicable regulations.)

- Remove glass bubbles with a suction “wand” (with slight positive pressure aeration) and transfer to a closed mixing tank inside fully contained piping. If a closed mixing tank is not available, use dust collection equipment as close as practical to the point of entry. Pneumatic conveyor systems have been used successfully to transport glass bubbles without dusting from shipping containers to batch mixing equipment. Equipment vendors should be consulted for recommendations.

- Static eliminators should be used to prevent static buildup.

Safety: For worker protection, please consider the following:

- Use safety glasses with side shields for eye protection.
- An air-purifying respirator suitable for particulates may be selected for protection after an optional exposure assessment is performed for your specific application. (For additional information about personal protective equipment, refer to the product Safety Data Sheet.)

- Use with appropriate local exhaust ventilation/dust collection in the work area.
- Refer to the 3M™ Glass Bubbles Safety Data Sheet for additional safety information.

Additional Information

3M glass bubbles are supported by global sales, technical and customer service resources, with fully-staffed technical service laboratories in the U.S., Europe, Japan, Latin America and Southeast Asia. Users benefit from 3M’s broad technology base and continuing attention to product development, performance, safety and environmental issues.

For additional technical information on 3M glass bubbles in the United States, call 3M Advanced Materials Division, **800-367-8905**. For other 3M global offices, and information on additional 3M products, visit our web site at: www.3M.com/glassbubbles.

Warranty, Limited Remedy, and Disclaimer: Many factors beyond 3M’s control and uniquely within user’s knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user’s method of application. User is solely responsible for evaluating third party intellectual property rights and for ensuring that user’s use of 3M product does not violate any third party intellectual property rights. Unless a different warranty is specifically stated in the applicable product literature or packaging insert, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OF NON-INFRINGEMENT OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M’s option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damages arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

Technical Information: Technical information, recommendations, and other statements contained in this document or provided by 3M personnel are based on tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed. Such information is intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.



3M Advanced Materials Division
3M Center
St. Paul, MN 55144 USA

Phone 1-800-367-8905
Web www.3M.com/glassbubbles

3M is a trademark of 3M Company.
Used under license by 3M subsidiaries
and affiliates.

Please recycle. Printed in USA. © 3M 2017.
All rights reserved. Issued: 5/17 11188HB
98-0212-4138-9 Rev. B