

Transportation Safety Division

# 3M™ Stamark™ Wet Reflective Removable Tape Series 710

Product Bulletin Series 710  
April 2019

Replaces Product Bulletin Series 710 Dated January 2014

## 1 Description

3M Stamark Wet Reflective Removable Tape Series 710 (“Tape”) is highly reflective under both wet and dry conditions. Tape is a conformable marking tape intended for longitudinal line applications in highway work zones where removability is required. Tape is designed to perform for the duration of the normal construction season. A normal construction season is defined as the time after the last snow plowing in the spring and before the first snow plowing in the fall/winter. In locations where snow removal is not performed, Tape is intended for use for up to one year. Tape is a temporary removable product not intended for multi-year applications.

Under most conditions, once Tape pavement markings are no longer required, Tape can be manually removed largely intact or in large pieces, saving additional time, labor, and materials normally required to re-mark roadways.

**Note:** Tape installations that have been subjected to high traffic flows (ADT > 10 000), installed on marginal pavement surfaces, left on pavement for long periods (more than 6 months), or are being removed at low temperatures are more difficult to remove. Tape is most easily removed after short periods of use, at temperatures above 40 °F (4 °C), and from smooth pavement surfaces that have been subject to moderate traffic flows.

Tape is also supplied as pre-cut symbols and legends for work zone applications. Tape utilizes specially designed optics to provide dry and wet retroreflective performance. Tape is made up of a white or yellow film, supported by a flexible, conformable backing, reinforced with a structured medium, and pre-coated with a pressure sensitive adhesive that allows for easy, rapid application at temperatures above 50 °F (10 °C).

Tape is available in the following colors.

**Table 1.** Product codes by color.

Color	Product Code
White	710
Yellow	711

## 2 Tape Features and Advantages

- Highly reflective, under both wet and dry conditions.
- Durable for the duration of a normal work zone season, as defined above.
- Skid resistant.
- Coated with pressure sensitive adhesive.
- Available in white and yellow.
- Symbols and legends available in white only.
- Provides continuous delineation, day or night.
- Easy to apply by hand or by machine.
- Easy to remove largely intact or in large pieces under most conditions.
- Leaves no permanent marks.
- Roadway may be opened to traffic immediately following application.

## 3 Specifications

### 3.1 Reflectance

The photometric quality to be measured is coefficient of retroreflected luminance ( $R_L$ ). Dry values shall be obtained in accordance with the testing procedures of ASTM D4061. Wet & Rainy values shall be obtained in accordance with testing procedures of ASTM E2176 or ASTM E2177, using a portable reflectometer.

Wet retroreflectance values obtained under a “condition of continuous wetting” (simulated rain) shall be measured in accordance with the ASTM E2176 testing procedure. To reduce variability between measurements, ASTM E2176 tests shall to be performed in a controlled laboratory environment with Tape positioned on a 3-5° lateral slope. Use a wetting agent to improve wetting of Tape by water. A 0.1% by volume aqueous liquid soap solution is the recommended wetting agent. Take measurements at a minimum of three locations per roll and report average value for each roll tested.

Wet retroreflectance values obtained under a “condition of wetness” (simulated rain) shall be measured in accordance with the ASTM E2177 testing procedure. The test may be performed on Tape installed on the road. New markings shall be tested using a wetting agent, as previously described. Perform laboratory measurements on Tape positioned on a 3-5° lateral slope. Take measurements at a minimum of three locations per roll and report average value for each roll tested.

Tables 2 and 3 present initial minimum  $R_L$  values under wet and dry conditions for white and yellow Tape, respectively.

**Table 2.** Minimum retroreflectivity values for white Tape.

White, 710	Dry	Wet & Rainy
Entrance Angle	88.76°	88.76°
Observation Angle	1.05°	1.05°
Retroreflected Luminance, $R_L$ [(mcd • m <sup>-2</sup> ) • lx <sup>-1</sup> ]	500	250

**Table 3.** Minimum retroreflectivity values for yellow Tape.

Yellow, 711	Dry	Wet & Rainy
Entrance Angle	88.76°	88.76°
Observation Angle	1.05°	1.05°
Retroreflected Luminance, $R_L$ [(mcd • m <sup>-2</sup> ) • lx <sup>-1</sup> ]	300	200

**Note:** Wet  $R_L$  values are higher when measured under a “condition of wetness” than when measured under a “condition of continuous wetting.” Regardless, Tape shall meet stated minimum values using either test method.

**English  $R_L$ :** Millicandelas per square foot per foot-candle  $[(\text{mcd} \bullet \text{ft}^{-2}) \bullet \text{fc}^{-1}]$

**Metric  $R_L$ :** Millicandelas per square meter per lux  $[(\text{mcd} \bullet \text{m}^{-2}) \bullet \text{lx}^{-1}]$

**Note:** The entrance angle of 88.76° and observation angle of 1.05° represent a simulated driver viewing geometry at a 30 meter distance.

### 3.2 Skid Resistance

Tape surface provides a minimum initial average skid resistance value of 45 BPN when tested in accordance with ASTM E303.

## 4 Application

Tape should only be installed to surfaces conforming to the [3M Road Surface Guide](#) and according to the instructions presented in this product bulletin and the appropriate sections of [3M Information Folder 3.2](#). Areas that have been newly marked with Tape can be opened to traffic immediately following Tape application.

### 4.1 General Application Conditions:

- o Air and pavement temperature minimums are both 50 °F (10 °C) and rising.
- o Pavement surface must be clean and dry.
- o Butt splices must be used; do not overlap Tape ends.
- o Do not apply Tape on longitudinal seams or joints.
- o In areas of high traffic encroachment or rough, exposed aggregate surfaces, service life may be limited; for example, on tined Portland cement or open graded asphalt cement concrete. In such situations, it is recommended that Tape be inspected for replacement on a two-month cycle.

### 4.2 Surface Preparation Adhesive

Surface preparation adhesive is not needed when applying Tape under normal conditions, outlined in Section 4.1, General Application Conditions. Under marginal weather conditions, however, 3M surface preparation adhesive can be used to improve initial and long term adhesion. For long line applications, 3M surface preparation adhesive should be applied with a 3M PS-14 Adhesive Spray Applicator. For symbols and legends, the surface preparation adhesive should be applied using a 3/8" nap paint roller.

Marginal weather conditions can include circumstances where:

- o The air and pavement temperatures are not expected to exceed the minimum application temperature for 24 to 48 hours.
- o Prolonged or heavy rainfall following Tape application is predicted.
- o Application is planned for the early spring or late fall, beyond the typical road construction season.

## 5 Removability

Under most conditions, Tape can be removed, largely intact or in large pieces, from asphalt and smooth Portland cement concrete surfaces, at temperatures above 40 °F (4 °C), without the use of heat, solvents, grinding, or sandblasting. At temperatures below 40 °F (4 °C), Mask may be more difficult to remove in large pieces and leave faint but visible temporary traces on the pavement.

Use the following procedure to remove Tape:

- 1 Always wear gloves and eye protection when removing Tape.
- 2 Pry up the edge of the Tape using a chisel-like tool.
- 3 Pull Tape straight up (at an angle of approximately 90°, relative to the pavement).
- 4 At temperatures below 40 °F (0 °C), Tape may be brittle and difficult to remove in large pieces. In these situations, a small amount of heat may be used to help soften the adhesive.

**Note:** Neither burning nor grinding is recommended for Tape removal. In areas of high encroachment or where Tape has been installed on rough exposed aggregate surfaces, removal and replacement of Tape may be required during the normal construction season, defined in Section 1, Description. In such instances, mechanical methods, such as high pressure water blasting may be required to remove Tape. User is responsible for determining the

suitability of Tape for their specific application.

## 6 Durability

Tape has been designed to provide excellent reflectivity under both wet and dry conditions. Tape's actual performance will be dependent on pavement and atmospheric conditions present at the time of application, application method used, traffic exposure, and environmental conditions. Users should verify that Tape conforms to their requirements before applying it in any significant quantity.

3M makes no generalized effective performance claims or material replacement provisions. Abrasion or heavy wear may significantly reduce effective performance, however, 3M's experience has shown that properly installed Tape is a highly effective traffic control device.

## 7 Storage

Tapes should be stored in a cool, dry indoor area and used within one year of receipt.

## 8 Health and Safety Information

Read all health hazard, precautionary, and first aid statements found in the Safety Data Sheets (SDS), Article Information Sheets, and products labels of any materials for important health, safety, and environmental information prior to handling or use. When removing Tape, obey all best practices described in the FWHA and State DOT safety guidelines. When using a pavement preparation adhesive with this product, refer to the appropriate MSDS for information about the volatile organic compound (VOC) content of the adhesive. Consult local regulations and authorities for possible restrictions on product VOC content and/or VOC emissions. To obtain SDSs and Article Information Sheets for 3M products, go to [3M.com/SDS](http://3M.com/SDS), contact 3M by mail, or for urgent requests call 1-800-364-3577.

## 9 Warranty Information

### 9.1 3M Basic Product Warranty

3M warrants that Tape will be free of defects in materials and manufacture at the time of shipment and meet the specifications stated in this product bulletin ("Basic Warranty"). If Tape is proven not to have met the Basic Warranty on its shipment date, then a buyer's exclusive remedy, and 3M's sole obligation, at 3M's option, will be refund or replacement of the Tape.

### 9.2 Disclaimer

THE 3M WARRANTY IS MADE IN LIEU OF ALL OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE, OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING OR OF PERFORMANCE, CUSTOM, OR USAGE OF TRADE.

### 9.3 Limitation of Liability

Except for the limited remedy stated above, and except where prohibited by law, 3M will not be liable for any loss or damage arising from the Signs or any 3M product, whether direct, indirect, special, incidental, or consequential damages (including but not limited to lost profits, business, or revenue in any way), regardless of the legal theory asserted including warranty, contract, negligence, or strict liability.

## 10 Other Product Information

Always confirm that you have the most current version of the applicable product bulletin, information folder, or other product information from 3M's Website at <http://www.3M.com/roadsafety>.

## 11 Literature References

- [3M IF 3.2](#) 3M™ Stamark™ Removable Tapes Pavement Surface Preparation and Application Procedures
- [3M IF 5.2](#) 3M™ Highway Tape Applicator (HTA)
- [3M IF 5.17](#) 3M™ Stamark™ Surface Preparation Adhesive P-50 Instructions for use with 3M™ Stamark™ Pavement Marking Tapes
- [3M IF 5.21](#) 3M™ Stamark™ Low VOC Surface Preparation Adhesive SPA60 Spray Application Instructions for Bulk Liquid for Longitudinal Pavement Marking Tapes
- [3M Road Surface Guide](#)

ASTM Test Methods are available from ASTM International, West Conshohocken, PA.

## For Information or Assistance

Call: 1-800-553-1380

In Canada Call:

1-800-3M HELPS (1-800-364-3577)

## Internet:

<http://www.3M.com/roadsafety>

3M, Science. Applied to Life., and Stamark are trademarks of 3M. Used under license in Canada. All other trademarks are the property of their respective owners.

3M assumes no responsibility for any injury, loss, or damage arising out of the use of a product that is not of our manufacture. Where reference is made in literature to a commercially available product, made by another manufacturer, it shall be the user's responsibility to ascertain the precautionary measures for its use outlined by the manufacturer.

## Important Notice

All statements, technical information and recommendations contained herein are based on tests we believe to be reliable at the time of this publication, but the accuracy or completeness thereof is not guaranteed, and the following is made in lieu of all warranties, or conditions express or implied. Seller's and manufacturer's only obligation shall be to replace such quantity of the product proved to be defective. Neither seller nor manufacturer shall be liable for any injury, loss or damage, direct, special or consequential, arising out of the use of or the inability to use the product. Before using, user shall determine the suitability of the product for his/her intended use, and user assumes all risk and liability whatsoever in connection therewith. Statements or recommendations not contained herein shall have no force or effect unless in an agreement signed by officers of seller and manufacturer.



## Transportation Safety Division

3M Center, Building 0225-04-N-14  
St. Paul, MN 55144-1000 USA

Phone 1-800-553-1380

Web [3M.com/roadsafety](http://www.3M.com/roadsafety)

Please recycle. Printed in USA © 3M 2019.  
All rights reserved. Electronic Only