

3M[™] Acrylic *Plus* Tape Series PT1000

Technical Data Sheet



Description

3M[™] Acrylic Plus Tape Series PT1000 is a black, double-coated acrylic foam tape designed for the attachment of automotive exterior trim parts such as body side moldings and claddings.

3M Tape Series PT1000 offers the following key features:

- High conformability
- Black, high-strength core with low elongation properties
- Cold temperature impact resistance
- Easy liner release

The highly conformable core, which improves adhesive wet out, combines with high performance adhesive systems to provide robust part adhesion to many challenging surfaces. The black color and low elongation properties improve the bond-line appearance of the attached part. Some typical applications for 3M Tape Series PT1000 include body side moldings, claddings, roof ditch moldings and wheel flares.

Product Construction



Liner Options

See the technical update "<u>3M[™] Acrylic Foam and Acrylic Plus Tapes:</u> <u>Product Constructions</u>" for liner and tabbing information.

Physical Properties

	PT1100	PT1500	PT1100T
Thickness	1.14 mm (0.045 in)	1.52 mm (0.060 in)	1.14 mm (0.045 in)
Range	+/- 0.13 mm (0.005 in)	+/- 0.13 mm (0.005 in)	+/- 0.13 mm (0.005 in)
Density	545 kg/m³ (34 lb/ft³)	521 kg/m³ (32.5 lb/ft³)	545 kg/m³ (34 lb/ft³)
Range	+/- 80 kg/m³ (5 lb/ft³)	+/- 80 kg/m³ (5 lb/ft³)	+/- 80 kg/m³ (5 lb/ft³)

Performance Properties

Typical performance of 3M[™] Acrylic *Plus* Tape Series PT1000 is shown below. Peel and shear values depend on plastic substrate characteristics and/or paint composition. These values are for reference only.

Note: Care should be taken to make sure the surface is clean and dry prior to application of the tape. After adhesion build, the adhesive is durable to typical automotive environmental conditions and chemicals and provides a robust attachment solution. For more details and application guidance, please contact your 3M Technical Representative.

90° Peel Adhesion Testing





High Conformability (Angled Gap)



Static Break Away (Typical Results)



Technical Data Sheet 3M[™] Acrylic *Plus* Tape Series PT1000

Shelf Life

Two years from date of manufacture when stored at 4°C–38°C (40°F–100°F) and 0–95% relative humidity (RH). The optimum storage conditions are 22°C (72°F) and 50% relative humidity.

Regulatory Information

Please refer to the product label and Safety Data Sheet (SDS) for health and safety information before using. Observe proper handling precautions as outlined in the SDS, which is available on request or at <u>www.3M.com/msds</u>.

The product is published as a material entry and is available for access on <u>www.mdsystem.com</u>. For product IMDS I.D. number, email requests to <u>3M-IMDSrequest@mmm.com</u>.

Contact Information

The information provided in this technical document is intended as a guide for this product. For more information or help in selecting a 3M product for an application, please contact your 3M application engineer or call product application support at 1-800-328-1684.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information. Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property. Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Automotive and Aerospace Solutions Division 3M Center St. Paul, MN 55144-1000 1-800-328-1684 3M.com/autosolutions

3M is a trademark of 3M Company Please recycle. Printed in USA. © 3M 2020. All rights reserved.