

“WHY USE A TWO-PART COMPOUND?”

	Bondo® Home Solutions™ Two-Part	Most One-Part Products
Drying Time	30 Minutes*	24 Hours
Shrinking	No	Yes
Cracking	No	Yes
Adhesion	Stronger Than Existing Surface	Like Chewing Gum
Durability	Excellent	Poor to Fair
Storage	Will Not Dry in the Can	Better Use the Whole Can Now
Overall Performance	Designed for Specific Problems: Resistance to Water, Oil, Chemicals, Etc.	Limited Performance

*Epoxy compounds take longer. Marked clearly on packages.



Appliance & Porcelain Touch Up Paint
Scratches and other flaws on white or almond appliances can be removed quickly and easily with this convenient half-ounce touch-up bottle.



All-Purpose Putty
If it needs to stay put, these are the formulas for the job. Use the All-Purpose formulation for high strength repairs and the Extra-Strength where a superior bond is needed or where the repair will contact water, temperature extremes, chemicals or petroleum products. Permanently bonds almost anything to almost anything else: securing eye bolts or anchors, bonding loose hinge mountings, repairing broken parts, replacing missing pieces. Quarts and gallons.



All-Purpose Fiberglass Resin
Use for bridging large, gaping holes, breaks or cracks in fiberglass boats, tubs or pools. Can also be used to bridge large gaps in metal. Should be used with fiberglass cloth tape or matting (see Accessories, below).

ACCESSORIES

Green means go when you need accessories and tools to complete your **Bondo® Home Solutions™** projects. Spreaders, mixing boards, fiberglass cloth and matting let you get professional results in less time and for a fraction of the cost!



CONTRACTOR QUALITY – FOR EVERYONE!

Sometimes repairs need to stand up to years of abuse, harsh conditions and high stress. When you use **Bondo® Home Solutions™** products with the black border, you can make the repair and forget about it. Now in easier-to-measure and mix formulations, these contractor-grade products create super-strong bonds and patches that can be exposed to extremes of heat and cold, water, solvents, salt, oil, gas and chemicals. Extra-Strength products are epoxy-based, requiring longer curing times than other **Bondo® Home Solutions™** products.



Extra-Strength Epoxy Resin
Use to repair and seal boat hulls, join fiberglass panels, tub and shower surrounds, dock repairs, pools, tanks, fountains, ponds, outdoor planters, sealing cedar strips, canoes and birdbaths.



Extra-Strength Concrete Repair Epoxy
Creates a watertight repair or coating on garage floors, cracks in basement floors or walls and exterior chimneys.



Extra-Strength Wood Repair Epoxy
Repairs gouges, knotholes or cuts in wood beams, joists, fencing posts, rotted wood deck and play equipment supports. For all wood repairs requiring resistance to water, shrinkage, sagging and load.



Extra-Strength All-Purpose Epoxy
The best bet for broken bolts, hinges, seams, anchors; wherever permanent strong bonds need to be established or restored. Bonds and fills gaps. For many home repairs in most environment.



Deep Gloss Tabletop Finish
The best bet for broken bolts, hinges, seams, anchors; wherever permanent strong bonds need to be established or restored. Bonds and fills gaps. For many home repairs in most environment.



Fiberglass Resin Liquid Hardener
The best bet for broken bolts, hinges, seams, anchors; wherever permanent strong bonds need to be established or restored. Bonds and fills gaps. For many home repairs in most environment.



White Cream Hardener
The best bet for broken bolts, hinges, seams, anchors; wherever permanent strong bonds need to be established or restored. Bonds and fills gaps. For many home repairs in most environment.




3M Automotive Aftermarket Division
3M Center/Bldg. 223-6N-01
St. Paul, MN 55144-1000
1-877-MMM-CARS (666-2277)
www.3m.com/automotive
Made in U.S.A.
© 3M 2009
3M is a trademark of 3M.
Bondo is a trademark of 3M.
Home Solutions is a trademark of 3M.
60-4402-4607-6

“When I fix it, and it looks right, then I know I can try even more.”




Repair Guide

Turn the page if you need to make fast, easy, quality repairs to concrete, wood, metal, sheetrock, plaster, brick, fiberglass, gel-coat or clear glossy surfaces.



FIX IT RIGHT




“If you gave me great directions, I would try it!”

BONDO® HOME SOLUTIONS™

REPAIR KITS

Have you ever made three or four trips to the hardware store for one small repair? Most people have. Do you wind up spending more money and time, feeling frustrated and owning tools you'll never use again? **Bondo® Home Solutions™** Kits take the guesswork out of shopping for home repairs. They include everything you will need to make the repair. Everything. Mixing sticks, cups, mixing boards, spreaders, sandpaper, brushes, fiberglass cloth tape, hardener, compound and specific step-by-step instructions in plain language.

Once you open the kit, you'll be ready to sand and paint or stain in 30 minutes or less (epoxy takes about 24 hours).



Wall Repair Kit

Use on holes, cracks, scratches in interior Sheetrock®, drywall or plaster walls. The white repair compound dries / "cures" and is ready to sand and paint in about 30 minutes, even if you put on a thick layer. Try that with spackling and you will end up with cracks, splits and a project that might take several days.



Tub & Shower Repair Kit

Repair cracks and chips in bathtubs, shower stalls, bathroom sinks and counters, toilets, marble, tile, porcelain and fiberglass. Can even be color matched and used on some pool materials to make a less noticeable repair.



Fiberglass Reinforced Repair Kit

Fix any shattered or damaged fiberglass item around the home or business: Boat hulls, trailer caps, water tanks, laundry tub, shower surrounds, storage units, outdoor furniture, central air shrouds. Can also be used on metal surfaces.

Rotted Wood Repair Kit

Mend wood trim or facings (interior or exterior), window sills, window sashes, columns, railings, landscaping timbers, decks, wood fences and sheds. Contains wood stabilizer that soaks into damaged portions of wood and then hardens, creating a long-lasting surface you can repair, paint and protect. Use the wood filler wherever wood has water or insect damage.



Metal Repair Kit

Repair holes, dents, scratches, punctured, broken or rusted areas in metal: downspouts, gutters, flashing, mailboxes, lawnmower decks, appliances, sheds, wheelbarrows, garage and entry doors, windows and metal siding.



Boat & Pool Repair Kit

Fill even small scratches, cuts and nicks in the gel-coat of your personal pleasure craft that expose the fiberglass. The fiberglass absorbs or "wicks" moisture and weakens the entire structure. This kit guides you step-by-step on restoring the gel-coat to its original watertight

function. Note: If your fiberglass is already weakened, you will need to repair it first, using the Fiberglass Repair Kit described above.

Deluxe Tub & Shower Repair Kit


Fill even small scratches, cuts and nicks in the gel-coat of your personal pleasure craft that expose the fiberglass. The fiberglass absorbs or "wicks" moisture and weakens the entire structure. This kit guides you step-by-step on restoring the gel-coat to its original watertight function. Note: If your fiberglass is already weakened, you will need to repair it first, using the Fiberglass Repair Kit described above.



Aqua Jet & Snowmobile Repair Kit

Fill even small scratches, cuts and nicks in the gel-coat of your personal pleasure craft that expose the fiberglass. The fiberglass absorbs or "wicks" moisture and weakens the entire structure. This kit guides you step-by-step on restoring the gel-coat to its original watertight

function. Note: If your fiberglass is already weakened, you will need to repair it first, using the Fiberglass Repair Kit described above.



REPAIRING SPECIFIC MATERIALS

Look for the blue label on packages sized from half pints to gallons to help you with any size repair project. Unlike competing products, storing **Bondo® Home Solutions™** for future use is never a problem. Our compounds will not "dry" out in the can, and can be kept (and used) in cold or warm areas. Our 30-minute drying, easy sanding and strong bonding is why Bondo® brand products have been used in the home by professionals for decades.



Drywall Repair Compound

Available in quarts or gallons, **Bondo® Home Solutions™** Sheetrock Repair Compound should be used anytime you don't want to wait for spackling to dry, shrink, crack and recoat. This compound "cures" in 30 minutes without shrinking. One coat and you are ready to sand!



Concrete, Brick & Stucco Repair Compound

For fixing and filling knot holes in shingles, holes or cracks in brick, stucco and concrete walls, driveways, holes around water pipe outlets, seal around sinks, shower stalls, tubs, toilets, and the area around shower heads. Quarts and gallons.



Wood Filler

Half pint, quart and gallon sizes let you purchase the right amount for your projects. Restores and fills cracks, holes, splits and scratches in wood. Can be stained, varnished, primed, painted, drilled, sanded, routed, carved, planed, shaped or filed in only 20–30 minutes.



Scratch & Nail Hole Repair Putty

No mess or mixing is needed for you to make quick repairs to nail holes, other small holes or scratches in wood trim, sheetrock, plaster, paneling or exterior surfaces. Comes in handy 1.5 oz. or 4.5 oz. tubes.

Rotted Wood Stabilizer



Water leaks, contact with the ground, leaves, compost or even constant shade can rot large sections of wood outdoors and indoors. Rotted Wood Stabilizer (pints or quarts) penetrates deeply into rotted wood fibers and hardens them. Then use **Bondo® Home Solutions™** Wood Filler to replace the missing sections.



Metal Repair Compound

Few jobs are too large for **Bondo® Home Solutions™** Metal Repair Compound. Simple, specific directions help you prepare the surface and make permanent repairs to damaged metals of all types, including aluminum and galvanized. Quarts and gallons available.

Multi-Purpose Reinforced Filler

Few jobs are too large for **Bondo® Home Solutions™** Metal Repair Compound. Simple, specific directions help you prepare the surface and make permanent repairs to damaged metals of all types, including aluminum and galvanized. Quarts and gallons available.



Easy Patch

The best bet for broken bolts, hinges, seams, anchors; wherever permanent strong bonds need to be established or restored. Bonds and fills gaps.



Self-Adhesive Metal Patch

The best bet for broken bolts, hinges, seams, anchors; wherever permanent strong bonds need to be established or restored. Bonds and fills gaps.

