

CONTENTS

PLASTIC / BUMPER REPAIR	
FINISHING & TRIM	
UNDERCOATINGS	2
GENERAL TRIM ADHESIVE	
HARDENERS	
PRIMER SURFACERS	
PRIMER SURFACERS	
PRIMER SURFACERS	
TOTAL-PREP® CLEANER	
TRUCK GUARD PRO™	
ONE-STEP® RUST CONVERTER	
TAL-STRIP® PAINT REMOVER	

3M

3M Automotive Aftermarket Division
3M Center/Bldg. 223-6N-01
St. Paul, MN 55144-1000
1-877-MMM-CARS (666-2277)
www.3m.com/automotive
Made in U.S.A.

③ 3M 2009
3M, Bondo, MarHyde, BlackSatin,
One-Step, QuikSand, SingleStage,
Tal-Strip, Total-Prep and Truck Guard
Pro are trademarks of 3M.
60-4402-4640-7



PLASTIC / BUMPER REPAIR



Nar-Hyde® Plastic and Bumper Repair products feature everything you need from start to finish.

Mar-Hyde® FLEXIBLE PRIMER SURFACER – Satin Black fills small scratches and pinholes, and may be used as a satin black finish coat.

Mar-Hyde® ADHESION PROMOTER improves adhesion of all paints so that it eliminates the need to identify the type of plastic to be refinished or repaired.

Mar-Hyde® FLEXIBLE BUMPER & PLASTIC PATCH KIT repairs tears, punctures and gouges in most automotive plastics. The two-part system sets up in 6-8 minutes, and will not shrink, pop out or pinhole under extremes of hot or cold.

Mar-Hyde® BUMPER BLACK renew and recolor automotive plastics. These durable, flexible coatings are especially designed for all flexible and rigid automotive parts.

Part #	Product Description	Size	Case Oty.
3310	Mar-Hyde® Flexible Bumper & Plastic Patch Kit	12 oz.	6
3611	Mar-Hyde® Flexible Primer Surfacer (Satin Black) – Aerosol	12 oz.	12
4911	Mar-Hyde® Bumper Black – Aerosol	12 oz.	12
4912	Mar-Hyde® Bumper Black	Quart	6

FINISHING & TRIM



Mar-Hyde® BLACK SATIN™ is an extremely durable, black coating for use on exterior automotive trim, such as aluminum, stainless steel and steel, as found on fascias, window trim, door locks and lower body panels. Try it for yourself — spray Mar-Hyde® BLACK SATIN™ on aluminum foil, let it dry, crumple the foil and see the adhesion! Also provides excellent adhesion to brass, galvanized steel and plastics.

Mar-Hyde® GRAY SATIN is an extremely durable gray coating for use on exterior automotive trim, such as aluminum, plastic, stainless steel and steel, as found on fascias, window trim, door locks and lower body panels.

Part #	Product Description	Size	Case Oty.
3811	Mar-Hyde® Black Satin Aerosol	12 oz.	12
3812	Mar-Hyde® Black Satin	Quart	6
3821	Mar-Hyde® Gray Satin Aerosol	12 oz.	12

UNDERCOATINGS



Mar-Hyde® UNDERCOATINGS provide a complete line of products for every undercoating need. Top-quality, competitively-priced undercoatings are available in the following formulations: Mar-Hyde® UNDERCOATING inhibits the effects of rust, corrosion, moisture, furnes, dust, heat and cold. Also provides an effective sound barrier by reducing vibration and road noise. Asphalt-based. Mar-Hyde® RUBBERIZED UNDERCOATING is a durable, protective coating designed to inhibit the effects of rust, corrosion, moisture, heat and cold. This fast-drying formula remains flexible and repels water. Rubber/Asphalt-based.

Mar-Hyde® PAINTABLE RUBBERIZED UNDERCOATING is a durable, professional-quality undercoating that is fast drying, water-repellent and flexible. Highly resistant to abrasion and protects against rust, corrosion, moisture, heat and cold. This tack-free formula provides the perfect foundation for paint without any bleed-thru. Rubber/Solvent-based.

Part #	Product Description	Size	Case Oty.
4111	Mar-Hyde® Undercoating – Aerosol	16 oz.	12
4211	Mar-Hyde® Rubberized Undercoating – Aerosol	18 oz.	12
4311	Mar-Hyde® Paintable Rubber Undercoat – Aerosol	18 oz.	12



GENERAL TRIM ADHESIVE

Mar-Hyde® GENERAL TRIM ADHESIVE is a strong, fast-drying, waterproof adhesive for attaching lightweight materials, foams, fabrics, carpet, jute, kick pads, insulation materials, canvas, felt, rubber, leather and types of supported vinyl to metal, plastic and other surfaces.

Part #	Product Description	Size	Case Oty.
3411	Mar-Hyde® General Trim Adhesive	19 oz. Aerosol	6



HARDENERS

Mar-Hyde® UNIVERSAL URETHANE ACTIVATOR is compatible with all polyurethanes except where a one-to-one mixing ratio is specified.

Mar-Hyde® ULTRA WET LOOK HARDENER – High Solids produces a high distinctness of Image and has outstanding exterior durability.

Mar-Hyde® WET LOOK HARDENER produces a super high-gloss finish.

Part #	Product Description	Size	Case Qty.
2600	Ultra Wet Look Hardener – High Solids	Pint	12
2610	Wet Look Hardener	Quart	12
2612	Wet Look Hardener	Pint	12
2643	Universal Urethane Activator	Quart	12



PRIMER SURFACERS

Ultimate 2K Urethane Primer Surfacer

Mar-Hyde® ULTIMATE 2K PRIMER SURFACER brings the "ultimate" performance characteristics to the repair process with its fast drying, high build, excellent adhesion, and easy sanding properties. Designed for any size repair, this high quality primer-surfacer can be applied over properly prepared steel, aluminum, iron, fiberglass and previously painted surfaces and can be topcoated with any automotive paint system. Mixing ratio of 4:1:1 results in ready-to-spray VOC of 4.3 lb/gal. USEPA National Rule compliant.

Part #	Product Description	Size	Case Qty.
5553	Ultimate 2K Urethane Primer Surfacer-Buff	Gallon	4
5563	Ultimate 2K Urethane Tintable Primer Surfacer- Gray	Gallon	4
5556	Ultimate 2K Urethane Primer Surfacer 4:1 Catalyst	Pint	12
5557	Ultimate 2K Urethane Primer Surfacer 4:1 Catalyst	Quart	12





PRIMER SURFACERS

Premium High Build Primer



Mar-Hyde® PREMIUM HIGH BUILD PRIMER is a high-speed, easy-sanding, lacquer-type primer which exhibits very good holdout of color coats. It is solvent resistant, has excellent adhesion to previously painted surfaces and bare steel, and can be topcoated with any automotive paint system. Ready-to-spray VOC of 4.4 lb/gal. USEPA National Rule compliant.

Part #	Product Description	Size	Case Qty.
5512	4.4 Premium High Build Primer Surfacer - Gray	Quart	6
5513	4.4 Premium High Build Primer Surfacer - Gray	Gallon	4
5523	4.4 Premium High Build Primer Surfacer-Red Oxide	Gallon	4

PRIMER SURFACERS

Single Stage® Self-Etching Primer



Mar-Hyde® SINGLE STAGE® SELF-ETCHING PRIMER is a ready-to-spray, pretreatment/primer that provides excellent corrosion protection and creates a superior bond to most metals by chemically etching the surface of the panel. It is solvent resistant, has excellent adhesion to aluminum, bare steel, galvanized steel and fiberglass and can be topcoated with all automotive primers and paint systems. Ready-to-spray VOC of 6.4 lb/qal. USEPA National Rule and California Rule 1151 compliant.



Part #	Product Description	Size	Case Qty.
5111	Single Stage® Self-Etching Primer Aerosol	19 oz.	6
5112	Single Stage® Self-Etching Primer	Quart	6
5113	Single Stage® Self-Etching Primer	Gallon	4

PRIMER SURFACERS

QuikSand® 2K Polyester Primer Surfacer



Mar-Hyde® QUIKSAND® 2K POLYESTER PRIMER SURFACER offers 2K performance at a fraction of the price of urethanes! New sprayable polyester technology was used to develop this fast-drying, high-build, easy-sanding primer-surfacer for easy filling of checks, gravel chips, and other surface defects. QuikSand® was designed to work with all automotive paint systems and to excel as a surfacer for basecoat/clearcoat systems. Ready-to-spray VOC of 2.0 lb/gal. USEPA National Rule and California Rule 1151 compliant.



Part #	Product Description	Size	Case Oty.
5405	MEKP Hardener for QuikSand®	4 oz.	?
5433	QuikSand® 2K Polyester Primer Surfacer - Gray	Gallon	4
5463	QuikSand® 2K Polyester Primer Surfacer-Buff	Gallon	4



2.1 Ultimate 2K Urethane Primer Surfacer

PRIMER SURFACERS

Mar-Hyde® 2.1 ULTIMATE 2K URETHANE PRIMER SURFACER SURFACER brings the "ultimate" performance characteristics to the repair process with its fast drying, high build, excellent adhesion, and easy sanding properties. Designed for any size repair, this high quality primer surfacer can be applied over properly prepared steel, aluminum, iron, fiberglass and previously painted surfaces and can be topcoated with any automotive paint system. Mixing ratio of 4:1:1 results in ready-to-spray VOC of 2.1 lb/gal. California Rule 1151 compliant.



Part #	Product Description	Size	Case Qty.
5577	2.1 Ultimate 2K Urethane Primer Surfacer Catalyst	Quart	12



TOTAL PREP® CLEANER

Mar-Hyde® TOTAL PREP® CLEANER is especially formulated to remove oil, wax, grease, poly-silicone products, polyglycoat, road film and other contaminants from painted surfaces, metal, vinyl, leather and rigid and non-rigid plastics. Developed to prepare a car for automotive paint or Mar-Hyde® VINYL COLOR. A MUST PRIOR TO PAINTING OR BODYWORK!





TRUCK GUARD PRO™

Mar-Hyde® Truck Guard Pro™ is a high-quality, professional spray-on coating for truck beds and other surfaces that require a tough, durable finish. Designed for application with a standard undercoating spraygun, Truck Guard Pro represents a significant new money-making opportunity for every bodyshop.

Features:

- Easy to mix and use in pre-measured Schutz cans
- No primer required
- Not temperature or humidity sensitive
- 100% Isocyanate-free



Part #	Product Description	Size	Case Oty.
7277	Truck Guard Pro™ Kit	6 Liter	1
120	Undercoating Spray		1



ONE-STEP®



Mar-Hyde® ONE-STEP® RUST CONVERTER PRIMER SEALER chemically reacts to convert rust into a hard, black primer sealer. Apply ONE-STEP® on rusted surfaces and rust is permanently converted and ready for primer and topcoat. ONE-STEP® RUST CONVERTER PRIMER SEALER is a water-based latex containing rust modifiers, which is designed for application directly over tightly bonded rust on iron or steel. Also proven effective on new degreased or mild steel where flash-rusting has occurred. Shortly after application, the rusted surface will change from white to purple to a stable, black coating. A uniform black coating indicates the complete conversion of the rust; white streaks or remaining rust indicates that an additional coat is required.

Part #	Product Description	Size	Case Qty.	
3509	One-Step® Rust Converter Primer Sealer Aerosol	10 oz.	12	
3512	One-Step® Rust Converter Primer Sealer	Pint	12	
3513	One-Step® Rust Converter Primer Sealer	Quart	6	
3514	One-Step® Rust Converter Primer Sealer	Gallon	4	



TAL-STRIP® PAINT REMOVER



Mar-Hyde® TAL-STRIP® EXTRA STRENGTH PAINT REMOVER is a fast-acting, non-caustic paint and coating remover. Removes enamel, lacquer, epoxy, urethane, varnish, shellac, decals, and gaskets from metal, wood, glass, concrete, stone, brick and ceramic tile.

Mar-Hyde® TAL-STRIP® II AIRCRAFT COATING REMOVER is especially designed to remove basecoat/clearcoat systems from today's automobiles. Also removes polyurethanes,

enamels, lacquers, primers and most other paints and coatings from aluminum and other metals.

Mar-Hyde® TAL-STRIP® IV URETHANE PARTS PAINT REMOVER specifically designed to strip paints and coatings from urethane automotive parts without attacking and damaging the urethane substrate. Only available as an aerosol.

Part #	Product Description	Size	Case Qty.
2811	Tal-Strip® Extra Strength Paint Remover Aerosol	15 oz.	12
2812	Tal-Strip® Extra Strength Paint Remover	Quart	6
2813	Tal-Strip® Extra Strength Paint Remover Gallon	Plastic Jug	4
3711	Tal-Strip® II Aircraft Coating Remover Aerosol	12 oz.	12
3712	Tal-Strip® II Aircraft Coating Remover	Quart	6
3713	Tal-Strip® II Aircraft Coating Remover	Gallon	4
5611	Tal-Strip® IV Urethane Parts Paint Remover Aero.	17 oz.	12