



Quick Links
[Resource Library](#)
[Safety Data Sheets \(SDS\)](#)
[Video Library](#)

Some of these links lead to web-based resources that are not product-specific.

Product Description

3M™ Speed Stripper Concentrate 6A is a concentrated product to be diluted and dispensed using only the 3M™ Flow Control System Wall Mount Dispenser or 3M™ Flow Control System Portable Dispenser.

3M™ Speed Stripper Concentrate 6H is a concentrated product to be diluted and dispensed using only the 3M™ Twist 'n Fill™ Cleaning Chemical Management System.

Ready-to-use 3M™ Speed Stripper is formulated to quickly and effectively soften and remove floor finishes and sealers.

Special Features

- Automatic dispensing eliminates measuring and mixing and ensures accurate dilutions
- Excellent performance in removing multiple layers of finishes hardened from frequent burnishing
- Five-minute dwell time
- Low-foaming
- Mild fragrance
- Non-damaging to vinyl
- Non-ammoniated

Applications

Remove sealers, floor finish buildup and finishes from resilient floors.

Note: Do not use on wood floors or floorings (such as linoleum) that may be affected by highly alkaline cleaners.

Packaging

3M™ Speed Stripper Concentrate 6A

- 0.5-gallon bottle
- 4 bottles per case

Each 0.5-gallon bottle yields 10 ready-to-use gallons.

3M™ Speed Stripper Concentrate 6H

- 0.528-gallon bottle
- 6 bottles per case

Each 0.528-gallon bottle yields 8.2 ready-to-use gallons.

General Use Directions

Refer to ready-to-use SDS for personal protective equipment (PPE) recommendations.

1. Dispense 3M™ Speed Stripper 6A using the 3M™ Flow Control System Dispenser or dispense 3M™ Speed Stripper 6H using the 3M™ Twist 'n Fill™ Cleaning Chemical Management System.
2. Sweep or dust mop the floor.
3. Properly locate caution signs for wet floor conditions.
4. Liberally apply the diluted stripper solution with a mop (100 sq. ft./gallon), leaving the floor uniformly wet.

Note: Floors become very slippery when stripper softens finish.

5. Allow 5-10 minutes for the stripper to penetrate and soften the finish. Observe the floor and apply additional diluted stripper to areas that may be drying out.
6. Use a low-speed floor machine (175 rpm) with the appropriate 3M stripping pad to thoroughly remove the old finish from the floor.
7. Pick up the soiled solution with a wet vacuum.
8. Flood rinse the floor with clean water and remove with wet vacuum.
9. Check dry floor for residue by wiping with dry hand. If residue is observed, repeat step 8 to ensure full removal.
10. Inspect floor for any remaining finish and repeat steps 4-9 as necessary to remove fully.
11. Mop the floor with a tightly wrung mop of clean water.
12. Let the floor dry completely before applying new finish.

3M™ Speed Stripper Concentrate 6A and 6H

Note: If more than 10 coats, contact 3M Rep for ideas on how to quickly remove.

Note: When using an automatic scrubber equipped with the appropriate 3M pad, remember to allow the stripping solution to remain wet on the floor for at least five minutes before agitation and pickup.

Note: Refer to product Safety Data Sheets or specific health hazard, first aid and precautionary information.

- 11-9287-1 (Concentrate)
- 11-9288-9 (RTU)

Precautionary Summary

Do not use on soft metal and plastic surfaces, painted surfaces or other surfaces that are easily scratched.

Health and Safety

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products, go to 3M.com/SDS, or by mail; or in case of an emergency, call 1-888-364-3577 or 1-651-737-6501. When using any equipment, always follow the manufacturers' instructions for safe operation.

Technical Information

Technical information and data, recommendations, and other statements provided by 3M are based on information, tests, or experience which 3M believes to be reliable, but the accuracy or completeness of such information is not guaranteed. Such technical information and data are intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. The typical values shown

should not be used for the purpose of specification limits. If you have questions about this Product, contact the **Customer Service Department at 1-800-852-9722**.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty

3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

Limited Remedy

If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

No Extension of Warranty

In the case of an approved warranty claim, the replacement Product will carry only the remaining term of the original warranty period.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.

Anchorage

11151 Calaska Circle
Anchorage, AK 99515
Telephone: 907-522-5200
Facsimile 907-522-1645

Honolulu

4443 Malaai Street
Honolulu, HI 96818
Mail to: P.O. Box 30048
Honolulu, HI 96820
Telephone: 808-422-2721
Facsimile 808-422-9557

Continental United States

Customer Service Department
3M Center Building 223-5S-07
St. Paul, MN 55144-1000
Order Entry 1-800-852-9722
Facsimile 1-800-447-0408

3M Canada

1840 Oxford Street East
London, Ontario, Canada
N5V 3G2
Mail to: P.O. Box 5757
London, Ontario, Canada
N6A 4T1
Telephone: 800-364-3577
Facsimile: 800-479-4453

Commercial Solutions Division

3M Center, Building 220-12E-04
St. Paul, MN 55144

1-800-328-0033
3M.com/Facility

© 3M 2018. All rights reserved.
3M and Twist 'n Fill are trademarks of 3M Company.
Used under license in Canada.
All other trademarks are property of their respective owners.
Revision A, June 2018. Please recycle.
60041

