

3M Commercial Graphics

3M™ Controltac™ Graphic Film with Comply™ v3 Adhesive IJ180Cv3-10



Smooth, fast and
comfortable

Non-visible air release channels.
Easy and fast application.

Product range includes: IJ180Cv3-10

- Pressure-activated adhesive allows you to slide and reposition the film until firm pressure is applied
- No adhesive curing time minimizes vehicle off road time
- Great-looking graphics with no 'show through'
- Excellent finish, no edge lifting, shrinking or cracking and conformable on many difficult surfaces
- Glossy appearance

3M



3M™ Controltac™ Graphic Film with Comply™ v3 Adhesive IJ180Cv3-10


Uses

- Short to long-term removable film for fleet and vehicle graphics as well as interior and exterior signs, including applications to moderate compound curved, corrugated and riveted surfaces.

Designed for: Piezo ink jet printing

Key Features and Advantages

- 3M's pressure-activated adhesive, available only on Controltac films
- Comply v3 adhesive offers the ultimate in air release technology
- Good initial adhesion assists on compound curves and rivets
- Pigmented adhesive provides excellent hiding power
- Fast, clean removal from automotive clearcoats with heat
- Cast film for conformability and dimensional stability



Peace of mind using products that are tested and backed by 3M

- 3M™ MCS™ Warranty – the first finished graphics warranty in the industry and still going strong – gives peace of mind to discriminating users that require optimum performance for the intended life of the graphic.
- 3M Performance Guarantee – adding confidence to your choice when you use selected 3M media imaged with an expanding range of 3M-qualified OEM printers and inks.

For more details please see our product information at www.3M.eu/graphicsolutions or contact your 3M distributor.



3M Europe S.A./N.V.
Commercial Graphics
Hermeslaan 7
1831 Diegem, Belgium
www.3M.eu/graphicsolutions

Please recycle. Printed in Germany
© 3M 2010. All rights reserved.