

# 3M™ Scotchkote™ Fusion Bonded Epoxy Coating 135

## Data Sheet

### Product Description

3M™ Scotchkote™ Fusion Bonded Epoxy Coating 135 is a one-part, heat curable, thermosetting powdered epoxy coating designed for application over phenolic primers to provide maximum corrosion protection of primary production tubing and gathering lines. It is specifically formulated for operation at elevated temperatures and pressures in the presence of H<sub>2</sub>S, CO<sub>2</sub>, CH<sub>4</sub>, crude oil and brine. Scotchkote 135 FBEC can be used without a primer on nonproduction tubing applications such as valves, pumps, pipe drains, hydrants and porous castings. Scotchkote 135 coating is resistant to wastewater, corrosive soils, hydrocarbons, and sea water. Powder properties allow easy manual or automatic application by electrostatic or air-spray equipment.

### Temperature Operating Range


Scotchkote 135 coating, when properly applied to a nominal thickness of 15 mils, should perform in a satisfactory manner on pipelines operating between -100°F/-73°C to 203°F/95°C. For temperatures reaching 230°F/110°C thicker coatings, greater than 30 mils, may improve the service capability. However, it is difficult to accurately predict field performance from the laboratory data due to the wide variations in actual field conditions. Soil types, moisture content, temperatures, coating thickness, and other factors specific to the area all influence the coating performance and upper temperature operating limits.

### Product Features

- Meets Mil Spec 23236C
- Excellent chemical resistance
- Protects over a wide temperature range
- Resistant to cracking during pipe coupler installation and splitting on upset ends from tubing string weight stress
- Resists cathodic disbondment
- Resists soil stress and backfill compaction
- Long-term storage under most climatic conditions
- High adhesion and toughness
- Will not sag, cold flow or become soft in storage
- Lightweight for lower shipping costs
- Particularly suitable for electrostatic, air-spray or blow application on production tubing
- Compatible with most phenolic primers
- Long gel time allows application without runs, sags, laminations, or overspray
- Can be machined by grinding or cutting to meet close tolerance requirements
- Allows easy inspection of coated articles

### General Application Steps - Internal Pipe

1. Remove oil, grease and loosely adhering deposits
2. Abrasive blast-clean the surface to NACE No. 2 / SSPC-SP10 or white metal with a 1.5 mil (38 μ) surface profile
3. Apply mechanical masks, release agents or mask with Scotch® Glass Cloth Tape 361 or Scotch Aluminum Foil Tape 425 as required
4. Apply liquid phenolic primer to dry film thickness of 1 mil (25 μm), if specified
5. Preheat cleaned, primed pipe to 325° to 375°F (163° to 191°C) for 30 minutes
6. Deposit Scotchkote 135 FBEC by blow coating, lance or electrostatic spray to a minimum thickness of 12 mils (304 μm)
7. Post cure at 450°F (232°C) for 30 minutes
8. Electrically inspect for holidays after the coating has air cooled. Repair all defects.



### Cure Specifications

Scotchkote 135 FBEC may be applied to metal articles which have been preheated to a temperature of 300° to 450°F (149° to 232°C). After application, Scotchkote 135 coating must be cured according to the times and temperatures listed in the cure guide to achieve maximum performance properties.

If Scotchkote 135 coating is electrostatically applied to unheated parts, the cure time should be measured from the time the coated part reaches the cure temperature. After cure, the coating may be force cooled using air or water to facilitate inspection and handling.

#### 3M™ Scotchkote™ Fusion Bonded Epoxy Coating 135 Cure Guide

Temperature of the Article at Time of Powder Application	Typical Gel Time	Cure Time
475°F (246°C)	40 seconds	7 minutes
450°F (232°C)	60 seconds	10 minutes
400°F (204°C)	120 seconds	15 minutes
350°F (177°C)	330 seconds	25 minutes



## Typical Properties

Property	Value
Color	Gray
Specific Gravity - Powder (Air Pycnometer)	1.51
Coverage	127 ft <sup>2</sup> /lb/mil (0,66 m <sup>2</sup> /kg/mm)
Fluidized Bed Density	33 lbs/ft <sup>3</sup> (530 kg/m <sup>3</sup> )
Shelf Life at 80°F (27°C)	18 months
Average Gel Time at 400°F (204°C)	134/70 seconds    135/45 seconds
Pill Flow	75 - 100 mm
Edge Coverage	12% - 18%
Minimum Explosive Concentration	0.03 oz/ft <sup>3</sup> (30,6 g/m <sup>3</sup> )
Ignition Temperature	986°F (530°C)

## 3M™ Scotchkote™ Fusion Bonded Epoxy Coating 135 Test Data - without Primer

Property	Test Description	Results
<b>Adhesion</b>	Elcometer	< 3000 psi (210 kg/cm <sup>2</sup> )
<b>Adhesion to Steel (Shear)</b>	ASTM D 1002 10 mil (254 micron) glue line	4300 psi (302 kg/cm <sup>2</sup> )
<b>Impact</b>	Gardner 5/8 in (1,6 cm) diameter tup 1/8" x 3" x 3" (0,32 cm x 7,6 cm x 7,6 cm) steel panel	160 in•lbs 1,8 kg•m
<b>Hardness</b>	Barcol ASTM D 2583	23
<b>Abrasion Resistance</b>	ASTM D 1044 CS-17 1000 g weight / 5000 cycles	0,07 g loss
<b>Thermal Shock</b>	310° to -100°F (154° to -73°C) 4" x 4" (10,2 cm x 10,2 cm) coated panel	10 cycles, no effect
<b>Penetration</b>	ASTM G 17 -40° to 240°F (-40° to 116°C)	0.0
<b>Tensile Strength</b>	ASTM D 2370	7300 psi (512 kg/cm <sup>2</sup> )
<b>Elongation</b>	ASTM D 2370	4.2%
<b>Compressive Strength</b>	ASTM D 695	12800 psi (900 kg/cm <sup>2</sup> )
<b>Coefficient of Friction</b>	API RP5L2-1968, App 8	23°
<b>Electric Strength</b>	ASTM D 149	1000 volts/mil (39,4 kv/mm)
<b>Hot Water Resistance</b>	160°F (71°C) immersion / 120 days	Good adhesion, no blistering
<b>Electrical Resistivity</b>	ASTM D 257	1.2 x 10 <sup>15</sup> ohm•cm
<b>Thermal Conductivity</b>	MIL-I-16923E	7 x 10 <sup>-4</sup> cal/sec/cm <sup>2</sup> /C°/cm
<b>Water Absorption</b>	3M 10 mil (254 micron) free film 30 days	6,5 g/m <sup>2</sup>
<b>Fungus Resistance</b>	MIL-STD 810-B Method 508	Funginert
<b>Salt Fog</b>	MIL-E-5272C	No effect
<b>Weatherometer</b>	ASTM G 23 5000 hours	Surface chalk
<b>Soil Stress - Burial</b>	Bureau of Reclamation 25 cycles	No effect
<b>Salt Crock</b>	30 day, 5 volt, 5% NaCl sand crock 230°F (110°C)	10 mmm
<b>Bendability</b>	3/8" (9,5 mm) coupon four point bender at 73°F (23°C)	30 pipe diameters 1.90°/diameter length

**Chemical Resistance Exposure at 73°F (23°C)\***

Acetic Acid up to 25%	Ferric Nitrate	Potassium Borate
Acetone (softened)	Ferric Sulfate	Potassium Carbonate
Aluminum Chloride	Ferrous Nitrate	Potassium Chloride
Aluminum Hydroxide	Ferrous Sulfate	Potassium Dichromate up to 10%
Aluminum Nitrate	Formaldehyde up to 100%	Potassium Hydroxide
Aluminum Sulfate	Formic Acid up to 10%	Potassium Nitrate
Ammonium Carbonate	Freon; Gas and Liquid	Potassium Sulfate
Ammonium Chloride	Gas (Mfg)	Propylene Glycol
Ammonium Hydroxide up to 100%	Gas (Natural)	Sewage
Ammonium Nitrate	Gasoline Leaded	Silver Nitrate
Ammonium Phosphate	Gasoline Unleaded	Soap Solution
Ammonium Sulfate	Glycerine	Soaps
Amyl Alcohol	Heptane	Sodium Bicarbonate
Barium Carbonate	Hexane	Sodium Bisulfate
Barium Chloride	Hexylene Glycol	Sodium Carbonate
Barium Hydroxide	Hydrochloric Acid up to 25%	Sodium Chlorate
Barium Nitrate	Hydrofluoric Acid up to 40%	Sodium Chloride
Barium Sulfate	Hydrogen Sulfide	Sodium Hydroxide
Benzene	Isopropyl Alcohol	Sodium Meta Silicate up to 5%
Boric Acid	Jet Fuel	Sodium Nitrate
Borax	Kerosene	Sodium Sulfate
Butyl Alcohol	Linseed Oil	Sodium Thiosulfate up to 5%
Cadmium Chloride	Lubricating Oil	Stannic Chloride
Cadmium Nitrate	Magnesium Carbonate	Sulfur
Cadmium Sulfate	Magnesium Chloride	Sulfuric Acid up to 60%
Calcium Carbonate	Magnesium Hydroxide	Synthetic Sea Fuel (60% Naphtha, 20% Toluene, 15% Xylene, 5% Benzene)
Calcium Chloride	Magnesium Nitrate	
Calcium Hydroxide	Magnesium Sulfate	
Calcium Nitrate	MEK (softened)	Synthetic Silage
Calcium Sulfate	Mercuric Chloride	Tetrapropylene
Calcium Disulfide	Methanol (softened)	Toluene
Carbon Tetrachloride	MIBK (Methyl Isobutyl Ketone)	Triethylene Glycol
Caustic Potash	Mineral Oil	Trisodium Phosphate
Caustic Soda	Mineral Spirits	Turpentine
Chlorine 2%	Molasses	Undecanol
Citric Acid up to 25%	Motor Oil	Urea
Copper Chloride	Muriatic Acid	Urine
Copper Nitrate	Naphtha	Vinegar
Copper Sulfate	Nickel Chloride	Water
Crude Oil	Nickel Nitrate	Chlorinated
Cyclohexane	Nickel Sulfate	Demineralized
Cyclohexene	Nitric Acid up to 30%	Distilled
Cyclopentane	Nonane	Salt
Detergent	Octane	Sea
Diesel Fuel	Oxalic Acid	Xylol
Diethylene Glycol	Pentane	Zinc Chloride
Dipropylene Glycol	Perchloroethylene	Zinc Nitrate
Ethanol (softened)	Phosphoric Acid up to 50%	Zinc Sulfate
Ethylbenzene	Phosphorous Trichloride	10-10-10 Fertilizer, Saturated
Ethylene Glycol	Potassium Aluminum Sulfate	
Ferric Chloride up to 50%	Potassium Bicarbonate	

\*Tests conducted for two years on similar products. No effect unless otherwise stated.

## Chemical/Pressure/Temperature Resistance

All tests performed on Scotchkote™ Fusion Bonded Epoxy Coating 135 applied over a 1 mil (25,4 microns) phenolic primer. Liquid phase for all test conditions: 33% kerosene, 33% toluene, 34% brine solution 5% NaCl.

Operating Results		
Test Conditions	Gas Phase	Results
Autoclave, 120°F (49°C) 48 hours, 1500 psi (10.3 MPa)	99.5% CO <sub>2</sub> 0.5% H <sub>2</sub> S	Excellent adhesion, no coating loss or blisters in aqueous, hydrocarbon, or gas phase
Autoclave, 150°F (66°C) 24 hours, 2200 psi (15.2 MPa)	80% CH <sub>4</sub> 12% CO <sub>2</sub> 8% H <sub>2</sub> S	
Autoclave, 200°F (93°C) 24 hours, 3300 psi (22.8 MPa)	86% CH <sub>4</sub> 8% CO <sub>2</sub> 6% H <sub>2</sub> S	Excellent adhesion, no coating loss or blisters in aqueous, hydrocarbon, or gas phase
Autoclave, 300°F (149°C) 24 hours, 3000 psi (20.7 MPa)	90% CH <sub>4</sub> 10% CO <sub>2</sub> Trace H <sub>2</sub> S	

## Handling and Safety Precautions

Read all Health Hazard, Precautionary and First Aid, Material Safety Data Sheet, and/or product label prior to handling or use.

3M, Scotchkote, and Scotchtrak are trademarks of 3M Company.

## Ordering Information/Customer Service

For ordering technical or product information, or a copy of the Material Safety Data Sheet, call:  
Phone: 800/722-6721  
Fax: 877/601-1305

## Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

## Warranty; Limited Remedy; Limited Liability.

Because conditions of product use are outside of our control and vary widely, the following is made in lieu of all express or implied warranties: this product will conform to 3M's published product specifications and be free from defects in material and manufacture on the date of your purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether indirect, special, incidental or consequential regardless of the legal theory asserted.**



## Electrical Markets Division

6801 River Place Blvd.  
Austin, TX 78726-9000  
www.3M.com/corrosion

Please recycle. Printed in USA.  
© 3M 2015. All rights reserved.  
80-6111-8495-5 Rev B