


## Specifications and Ordering Information for 3M CI-A Series Connectors up to 35 kV



Product Number	Description	UPC (054007-)	Conductor Size Cu or Al Stranded	Cu or Al Solid	Connector O.D.	Min. Order Case Qty.
CI-1/0A	Used with molded rubber splices 3M 5420 Series, 5461 splice kit and 5450 Series	14176	1/0 AWG	—	0.91" (23 mm)	10 each
CI-1A	Used with molded rubber splices 3M 5420 Series, 5461 splice kit and 5450 Series	00722	1 AWG	1/0 AWG	0.91" (23 mm)	10 each
CI-2A	Used with molded rubber splices 3M 5420 Series, 5461 splice kit and 5450 Series	00721	2 AWG	1 AWG	0.91" (23 mm)	10 each
CI-22A	Used with molded rubber splices 3M 5420 and 3M 5450 Series	15868	—	2 AWG	0.91" (23 mm)	10 each