

3M 5730-5731 Cold Shrink Series Selection

Kit Number	Cable Sizes (AWG)	Overall Jacket Diameter	Amount of Sheath Wrap Required*
5730	14 - 10	0.62 - 1.0" (16 - 25 mm)	1 roll
5731	8 - 4	0.95 - 1.4" (24 - 36 mm)	1 roll

Note: Connectors are not included in the kit. Use only CSA Certified compression connectors. Vinyl or nylon butt connectors are preferable.

*Amount of Amount Sheath Cast needed based on two half lapped layers.

Order the 15 ft. rolls.