

## Cold Shrink QT-III Outdoor Skirted Termination

Kit Number	BIL	Cable Insulation		Conductor Size Range				UPC (054007-)
		O.D. Range in. (mm)	5 kV	8.7 kV	AWG and kcmil (mm <sup>2</sup> )	15 kV	25/28 kV	
<b>Concentric and Jacketed Concentric Cable Kits with Top Insulator</b> (Each kit makes one termination)								
7652-S-4-TI	150 kV	0.64 – 1.08 (16,3 – 27,4)	4/0 – 400	3/0 – 300	2 – 4/0 (35 – 120)	2 – 1/0 (35 – 50)	—	43409
7653-S-4-TI	150 kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250 – 500	2/0 – 300 (70 – 150)	2 – 4/0 (35 – 120)	—	43410
7654-S-4-TI	150 kV	0.83 – 1.53 (21,1 – 38,9)	500 – 750	350 – 700	4/0 – 500 (120 – 240)	2/0 – 250 (70 – 150)	—	43411
7655-S-4-TI	150 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600 – 1250	500 – 1000 (240 – 500)	250 – 800 (150 – 400)	—	43412
7656-S-4-TI	150 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500 – 2000	1250 – 2000 (625 – 1000)	900 – 1750 (500 – 800)	—	43413