

Cold Shrink QT-III Outdoor Skirted Termination

Kit Number	BIL	Cable Insulation		Conductor Size Range			25/28 kV	35 kV	UPC (054007-)
		O.D. Range in. (mm)	5 kV	8.7 kV	AWG and kcmil (mm ²)	15 kV			
Inverted Kits for Concentric and Jacketed Concentric Cable (Each kit makes one termination)									
7642-S-INV-2	110 kV	0.64 – 1.08 (16,3 – 27,4)	4/0 – 400	3/0 – 300	2 – 4/0 (35 – 120)	—	—	04622	
7653-S-INV-4	150 kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250 – 500	2/0 – 300 (70 – 150)	2 – 4/0 (35 – 120)	—	04625	
7655-S-INV-4	150 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600 – 1250	500 – 1000 (240 – 500)	250 – 800 (150 – 400)	—	04623	
7656-S-INV-4	150 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500 – 2000	1250 – 2000 (625 – 1000)	900 – 1750 (500 – 800)	—	04624	