

Cold Shrink QT-III Outdoor Skirted Termination

Kit Number	BIL	Cable Insulation		Conductor Size Range					UPC (054007-)
		O.D. Range in. (mm)	5 kV	8.7 kV	AWG and kcmil (mm ²)	15 kV	25/28 kV	35 kV	
Concentric and Jacketed Concentric Cable Kits (Each kit makes one termination)									
7642-S-2	110 kV	0.64 – 1.08 (16,3 – 27,4)	4/0 – 400	3/0–300	2–4/0 (35–120)	—	—	42011	
7652-S-4	150 kV	0.64 – 1.08 (16,3 – 27,4)	4/0 – 400	3/0–300	2–4/0 (35–120)	2 – 1/0 (35 – 120)	—	42178	
7653-S-4	150 kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250–500	2/0–300 (70–150)	2 – 4/0 (35 – 120)	—	42192	
7654-S-4	150 kV	0.83 – 1.53 (21,1 – 38,9)	500 – 750	350–700	4/0–500 (120–240)	2/0 – 250 (70 – 150)	—	42203	
7655-S-4	150 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600–1250	500–1000 (240–500)	250 – 800 (150 – 400)	—	42208	
7656-S-4	150 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500–2000	1250–2000 (625–1000)	900 – 1750 (500 – 800)	—	42210	
7663-S-8	200 kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250–500	2/0–300 (70–150)	2 – 4/0 (35 – 120)	2 – 2/0 (35 – 70)	42433	
7664-S-8	200 kV	0.83 – 1.53 (21,1 – 38,9)	500 – 750	350–700	4/0–500 (120–240)	2/0 – 250 (70 – 150)	2 – 4/0 (35 – 120)	42447	
7665-S-8	200 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600–1250	500–1000 (240–500)	250 – 800 (150 – 400)	3/0 – 600 (95 – 325)	42461	
7666-S-8	200 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500–2000	1250–2000 (625–1000)	900 – 1750 (500 – 800)	700 – 1500 (400 – 725)	42463	