

## 7600-S-INV-3W Series — Kit Selection Guide

<b>Kit Number</b>	<b>Cable Insulation Range mm (in.)</b>	<b>3.3 kV (mm<sup>2</sup>) JIS</b>	<b>3.3 kV (mm<sup>2</sup>) AEIC</b>	<b>5.0 kV (AWG) JISIEC</b>	<b>6.6 kV (mm<sup>2</sup>) AEIC</b>	<b>6.6 kV (mm<sup>2</sup>) IEC</b>	<b>8.7 kV (AWG) IEC</b>	<b>10 kV (mm<sup>2</sup>) AEIC</b>	<b>UPC (051131-)</b>
7693-S-4-INV-3W	23.4-30.0 (0.92-1.18)	240-300	200-250	500-750	150-250	185-300	400-600	185-300	04746
7695-S-4-INV-3W	30.0-38.6 (1.18-1.52)	—	300-325	800-1000	300-325	—	750-1000	—	04747

(Final determining factor is cable insulation diameter. Listed insulation ranges allow +2.54 mm (0.10") for shielding.)

<b>Kit Number</b>	<b>Cable Insulation Range mm (in.)</b>	<b>15 kV (mm<sup>2</sup>) IEC</b>	<b>15 kV (AWG) AEIC</b>	<b>20 kV (mm<sup>2</sup>) IEC</b>	<b>25/28 kV (AWG) AEIC</b>	<b>UPC (051131-)</b>
7693-S-4-INV-3W	23.4-30.0 (0.92-1.18)	120-185	250-450	95-185	2/0-250	04746
7695-S-4-INV-3W	30.0-38.6 (1.18-1.52)	200-325	500-750	240-300	300-500	04747