

## 7690-S-INV-3 RJS Series — Kit Selection Guide

Kit Number	Cable Insulation Range mm (in.)	3.3 kV	3.3 kV	5.0 kV	6.6 kV	6.6 kV	8.7 kV	10 kV	UPC (054007-)
		(mm <sup>2</sup> ) IEC	(mm <sup>2</sup> ) JIS	(AWG) AEIC	(mm <sup>2</sup> ) JIS	(mm <sup>2</sup> ) IEC	(AWG) AEIC	(mm <sup>2</sup> ) IEC	
7693-S-4-INV-3-RJS	23.4-30.0 (0.92-1.18)	240-300	200-250	500-750	150-250	185-300	400-600	185-300	04720
7695-S-4-INV-3-RJS	30.0-38.6 (1.18-1.52)	—	300-325	800-1000	300-325	—	750-1000	—	04721

(Final determining factor is cable insulation diameter. Listed insulation ranges allow +2.54 mm (0.10") for shielding.)

Kit Number	Cable Insulation Range mm (in.)	15 kV	15 kV	20 kV	25/28 kV	UPC (054007-)
		(mm <sup>2</sup> ) IEC	(AWG) AEIC	(mm <sup>2</sup> ) IEC	(AWG) AEIC	
7693-S-4-INV-3-RJS	23.4-30.0 (0.92-1.18)	120-185	250-450	95-185	2/0-250	04720
7695-S-4-INV-3-RJS	30.0-38.6 (1.18-1.52)	200-325	500-750	240-300	300-500	04721