

## Rejacketing Sleeve Selection Guide—Based on Diameter Range and Cable Conductor Size

Product Number	UPC (054007-)	Size feet	Metallic Shield Diameter Range mm (in.)	3.3 kV (mm) IEC	3.3 kV (mm) JIS	5.0 kV (AWG) AEIC	6.6 kV (mm) IEC	6.6 kV (mm) JIS	8.0 kV (AWG) AEIC	Inner Unit Pack	Case Qty.
RJS-1	43098	4	10.9-15.2 (0.43-0.60)	16-35	8-22	8-2	16--25	8-10	6-4	10 bags/bx.	10
RJS-1	43099	10	10.9-15.2 (0.43-0.60)	16-35	8-22	8-2	16--25	8-10	6-4	1 bag/bx.	1
RJS-2	43100	4	15.2-20.3 (0.60-0.80)	50-95	38-60	1-3/0	35-70	14-38	2-2/0	10 bags/bx.	10
RJS-2	43101	10	15.2-20.3 (0.60-0.80)	50-95	38-60	1-3/0	35-70	14-38	2-2/0	1 bag/bx.	1
RJS-3	43102	4	20.3-26.0 (0.80-1.02)	120-185	100-150	4/0-400	95-150	60-100	3/0-350	10 bags/bx.	10
RJS-3	43103	10	20.3-26.0 (0.80-1.02)	120-185	100-150	4/0-400	95-150	60-100	3/0-350	1 bag/bx.	1
RJS-4	43104	4	25.9-32.4 (1.02-1.28)	240-300	200-250	500-750	185-300	150-250	400-600	10 bags/bx.	10
RJS-4	43105	10	25.9-32.4 (1.02-1.28)	240-300	200-250	500-750	185-300	150-250	400-600	1 bag/bx.	1
RJS-5	43106	4	32.5-41.1 (1.28-1.62)	—	300-325	800-1000	—	300-325	750-1000	10 bags/bx.	10
RJS-5	43107	10	32.5-41.1 (1.28-1.62)	—	300-325	800-1000	—	300-325	750-1000	1 bag/bx.	1

## Rejacketing Sleeve Selection Guide—Based on Diameter Range and Cable Conductor Size

Product Number	UPC (054007-)	Size feet	Metallic Shield Diameter Range mm (in.)	10 kV (mm) IEC	15 kV (AWG) AEIC	20 kV (mm) IEC	25 kV (AWG) AEIC	30 kV (mm) IEC	35 kV (AWG) AEIC	Inner Unit Pack	Case Qty.
RJS-1	43098	4	10.9-15.2 (0.43-0.60)	—	—	—	—	—	—	10 bags/bx.	10
RJS-1	43099	10	10.9-15.2 (0.43-0.60)	—	—	—	—	—	—	1 bag/bx.	1
RJS-2	43100	4	15.2-20.3 (0.60-0.80)	10-50	2-1	—	—	—	—	10 bags/bx.	10
RJS-2	43101	10	15.2-20.3 (0.60-0.80)	10-50	2-1	—	—	—	—	1 bag/bx.	1
RJS-3	43102	4	20.3-26.0 (0.80-1.02)	70-150	1/0-4/0	25-70	2-1/0	—	—	10 bags/bx.	10
RJS-3	43103	10	20.3-26.0 (0.80-1.02)	70-150	1/0-4/0	25-70	2-1/0	—	—	1 bag/bx.	1
RJS-4	43104	4	25.9-32.4 (1.02-1.28)	185-300	250-450	95-185	2/0-250	35-70	1/0-3/0	10 bags/bx.	10
RJS-4	43105	10	25.9-32.4 (1.02-1.28)	185-300	250-450	95-185	2/0-250	35-70	1/0-3/0	1 bag/bx.	1
RJS-5	43106	4	32.5-41.1 (1.28-1.62)	—	500-750	240-300	300-500	95-240	4/0-500	10 bags/bx.	10
RJS-5	43107	10	32.5-41.1 (1.28-1.62)	—	500-750	240-300	300-500	95-240	4/0-500	1 bag/bx.	1