


Specifications and Ordering Information for Silicone Rubber Termination Kits 5610-A Series for 5 and 8 kV

Part Number		UPC (054007-)	Conductor Range	Cable Insulation O.D. Range	Terminations per Kit	Case Qty.
5610A Series Silicone Rubber Termination Kits 5 kV and 8 kV			Nonshielded (Dry) Cable, Nonshielded (Wet or Dry) Cable			
	5611A	49549	8-4 AWG (10-16 mm ²)	0.31 - 0.72" (7,9-18,3 mm)	3	1
	5612A	49550	2-2/0 AWG (35-60 mm ²)	0.44 - 0.95" (11,2-24,1 mm)	3	1
	5613A	49551	3/0 AWG-300 kcmil (95-150 mm ²)	0.56 - 1.18" (14,2-30,0 mm)	3	1
	5614A	49552	350-1000 kcmil (180-500 mm ²)	0.95 - 1.94" (24,1-49,3 mm)	3	1

Note: Because of the various factors which affect cable primary insulation O.D. and cable jacket O.D. (e.g., type of conductor, insulation thickness), the cable sizes in the chart above are guidelines. Confirm that cable insulation O.D. fits range specified above for the termination.