



# Scotch-Seal™ Metal Sealant

## 2084

**Technical Data**

**July 2014**

### Features

- 3M™ Scotch-Seal™ Metal Sealant 2084 is a one-part aluminum colored sealant which air dries to a tough, flexible film that resists water, oils and fuel.
- Retains sealing properties after extended aging when painted.
- Can be used to bond and seal aluminum to glass; also adheres well to many other metals and woods. Painting after curing is recommended, especially if sealed area will be subjected to UV exposure.

### Typical Physical Properties and Performance Characteristics

**Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

|   |  |
|---|--|
| <b>Color:</b>   | Aluminum   |
| <b>Viscosity: (approx.)<br/>Brookfield Viscometer:</b>                  | 7,000 - 22,50 cps<br>RVF #6 sp. @ 20 rpm @ 80°F (26.7°C) |
| <b>Solids Content: (by wt.) (approx.)</b>                               | 40 - 47%   |
| <b>Net Wt.: (approx.)</b>   | 7.7 - 8.1 lbs./gal.                                      |
| <b>Flash Point: (c.c)</b>   | 0°F (-18°C)  |
| <b>Coverage: (1/8" diam. wet bead)</b>                                  | 1500 lineal ft./gal.                                     |
| <b>Solvent:</b>   | Acetone  |
| <b>Tack Free Time: (approx.)</b>  | 5 minutes  |
| <b>Dry Time: (approx.)</b>  | 24 hours   |
| <b>Gap Filling Capability:</b>  | 1/16 inch  |
| <b>Adhesion, Canvas to aluminum<br/>180° peel, pulled at 2"/minute:</b> | 25 lbs./inch width                                       |

# 3M™ Scotch-Seal™

## Metal Sealant

### 2084

#### Application Equipment Suggestions

**Note:** Appropriate application equipment can enhance adhesive performance. We suggest the following application equipment for the user's evaluation in light of the user's particular purpose and method of application.

**Pump** – 9 to 1 ratio double acting ball check type pump, 11.0 cu. inch per cycle with 4 1/4" air motor with single wiper follower plate. Packings, hoses and pail wiper must be compatible with acetone.

**Hose** – Nylon lined, 500 psi working pressure.

#### Reference Information

Material Temperature – 58°F (14°C)

| Hose Assembly                    | Material Pressure psi | Output Lb./Min. | Material Pressure psi | Output Lb./Min. |
|----------------------------------|-----------------------|-----------------|-----------------------|-----------------|
| Ten Foot Length 3/4 I.D. Hose    | 324                   | 5.7             | 180                   | 2.4             |
| Twenty Foot Length 3/4 I.D. Hose | 405                   | 4.6             | 180                   | 1.1             |
| Twenty Foot Length 1/2 I.D. Hose | 675                   | 6.2             | 180                   | .48             |
| Ten Foot Length 1/2 I.D. Hose    | 810                   | 1.0             | —                     | —               |

**Note:** Material pressure = operating air pressure x pump ratio.

**Flow Gun** – Tip seal type.

**Manual Caulking Gun Filling** – Kenmar® caulking gun loader with acetone resistant wiper; Graco® Model 225-975 gun loader with acetone resistant wiper; Pyles® Vaculoder.

**Chemical Resistance Requirements** – Synthetic materials in contact with 3M™ Scotch-Seal™ Metal Sealant 2084 must be resistant to acetone. Polysulfide, butyl, nylon and PTFE are compatible.

#### Handling/Application Information

##### Directions for use:

**Surface Preparation:** Best results are obtained on clean, dry surface. Oil, grease and other contaminants may be removed by wiping with a solvent such as isopropyl alcohol, MEK, acetone, or other locally compliant solvent.\*

**Application:** Production dispensing is best achieved with pressure-flow equipment. Hand caulking guns may also be used.

**Cleanup:** Equipment and excess sealer may be cleaned with solvent such as isopropyl alcohol, MEK, acetone, or other locally compliant solvent.\*

**\*Note:** When using solvents for clean-up, extinguish all ignition sources and follow manufacturer's precautions and directions for use when handling such materials.

# 3M™ Scotch-Seal™

## Metal Sealant

### 2084

---

#### Storage and Handling

**Storage:** For optimum storage 3M™ Scotch-Seal™ Metal Sealant 2084 should be stored at 60-80°F (15-26°C). Higher temperatures reduce normal storage life. Lower temperatures cause increased viscosity of a temporary nature. Rotate stock on a “first in-first out” basis.

**Shelf Life:** When stored at recommended temperature in original, unopened container, this product has a shelf life of 15 months from the date 3M ships the product.

---

#### Precautionary Information

Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

---

#### Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

---

#### Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

---

#### Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

---

#### Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



#### Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06  
St. Paul, MN 55144-1000  
800-362-3550 • 877-369-2923 (Fax)  
www.3M.com/sealant