



Features — Advantages — Benefits

Wire Pulling Lubricant Wintergrade

Temperature stable*	Lube is not wasted	Saves money
Thick, non-runny gel	Faster and neater application. Less waste	Saves money
Non-staining	Faster and easier clean-up	Saves time
Low coefficient of friction	Less wire damage and equipment wear	Safety
Low residue (<3.5% solids)	Easier cable replacement during refurbishment	Saves time
Broadly compatible with wire and cable jackets inventory	Lubricant suitable for multiple uses — electrical, co-ax, high voltage. Minimizes investment	Saves money

*Useable from 10°F to 110°F (-12°C to 43°C)