

# 3M™ High Routability Internal Serial Attached SCSI (SAS) Cable Assemblies

## 8U, 8F36 and 8F68 Series

**Your system should be built around performance, not around your cables.**

The 3M High Routability Internal miniSAS Cable Assemblies utilize 3M's new ultra low profile, high speed, high signal density 3M™ Twin Axial Cable SL8800 Series. Available with and without sidebands, these cable assemblies are ideal for space constrained systems. Cable assemblies are typically available unjacketed. MiniSAS has an optional ultra-thin jacket (UTJ) applied over each strip, and miniSAS HD assemblies are available with a mesh sleeve. The cable can be folded with minimal loss or performance impact. These assemblies can route along the sides of cabinets and through narrow openings between fans or heat sinks. Right angle terminations or sharp turns are easy to navigate, due to the foldability of this unique cable.

## No compromises

The High Routability Internal miniSAS Cable Assemblies are not just for tightly packaged systems. The high performance SL8800 Series Cable used in the construction of these assemblies also provides excellent transmission properties, allowing your signals to go the distance. The excellent performance of the cable may allow an even longer cable to be used. This performance benefit will stretch your loss budget, allowing you to use extra length to route the cable through a more convenient location, out of the way of airflow, or around difficult obstructions.

High Routability Internal Assemblies are available for 36- and 68-position SFF 8087 styles (miniSAS), for SFF-8643 (miniSAS HD) and for hybrids of the two. Whether or not you need the routability of these cables, they have the performance to help keep your system running at top speed. If you need a little extra “edge” in your SAS environment or you have a challenging packaging situation, look at the 3M High Routability miniSAS Cable Assemblies.

3M has tested these assemblies in folded configurations, and each fold impacts the impedance at that location by approximately only one ohm, well within the tightest impedance specifications (and note that the impedance at each fold is not cumulative, but is only a variation at that point). Similarly, S-parameter performance metrics are not degraded, even with multiple folds. Should your design require any folding, be sure to restrain the cable with the appropriate cable clamps to prevent repeated flexure at the folds.



3M™ High Routability Internal MiniSAS HD Cable Assembly

3M™ High Routability Internal miniSAS Assembly using 3M™ Twin Axial Cable wSL8800 Series low profile cable



36-position, 8F36 Series

68-position, 8F68 Series



3M™ Internal MiniSAS HD to Internal MiniSAS 36-Position Hybrid Cable Assembly



# 3M™ High Routability Internal Serial Attached SCSI (SAS) Cable Assemblies

Configuration	Drawing #	Spec #
miniSAS, High Routability Cable Assemblies, 8F36 Series	78-5100-2363-9	PDS-0082
miniSAS, High Routability Cable Assemblies, 8F68 Series	78-5100-2450-9	PDS-0082
miniSAS HD High Routability Cable Assemblies, 8U Series	78-5100-2555-0	PDS-0147
miniSAS HD to miniSAS High Routability Cable Assemblies, 8UH Series	78-5100-2622-8	PDS-0195


## Technical Information

- 100 Ohm differential pairs
- Bi-directional SAS channels with or without sidebands
- SAS 2.1 and SAS 3.0 performance compliant
- Solid insulation
- RoHS compliant\*
- The cable used in this assembly is UL AWM 21008 (150V, 80C)
- The connector materials (resin/PCB) are rated 94 V-0

## Ordering Information

### MiniSAS, 68-position, 8F68 Series

#### 8F68 – AAXX05 – X.XX




#### Cable Used

G = 4-lane with sidebands, SN-plated signal, cable P/N SL8801/12-21DA5-00  
 J = 4-lane with sidebands, AG-plated signal, cable P/N SL8801/12/20DA5-00

\*For cables without sidebands or other configurations, contact a 3M sales representative

### MiniSAS, 36-position, 8F36 Series

#### 8F36 – AAXX05 – X.XX




#### Cable Used

A = 4-lane with sidebands, SN-plated signal, cable P/N SL8801/12-11DA5-00  
 B = 4-lane with sidebands, AG-plated signal, cable P/N SL8801/12/10DA5-00  
 C = 4-lane no sidebands, SN-plated signal, cable P/N SL8802/08-21DN5-00  
 D = 4-lane no sidebands, AG-plated signal, cable P/N SL8802/08-20DN5-00

### MiniSAS HD, 8U Series


#### 8US4 – XXX 19 – 00 – X.XX



AA1 = Std MiniSAS HD 4i with sidebands (see Table 2 on customer drawing)  
 CB1 = MiniSAS HD 4 I without sidebands (see Table 3 on customer drawing)

### MiniSAS HD to MiniSAS, 8UH Series

#### 8UH4 – XXX13 – 00 – X.XX



BA1 = Std MiniSAS 4i to Std MiniSAS HD 4i, with sidebands (see Table 2 on customer drawing)  
 BA2 = Std MiniSAS 4i to Std MiniSAS HD 4i, with sidebands (see Table 2 on customer drawing)  
 DB1 = MiniSAS 4i to MiniSAS HD 4i, without sidebands (see Table 3 on customer drawing)  
 DB2 = MiniSAS 4i to MiniSAS HD 4i, without sidebands (see Table 3 on customer drawing)

\*"RoHS 2011/65/EU" means that the product or part does not contain any of the substances in excess of the maximum concentration values ("MCVs") in EU RoHS Directive 2011/65/EU. The MCVs are by weight in homogeneous materials. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

3M is a trademark of 3M Company.

## Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

## Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



## Electronic Solutions Division Interconnect Products

6801 River Place Blvd.  
 Austin, TX 78726-9000  
 1-800-225-5373  
 www.3Mtwinx.com

Please recycle. Printed in USA  
 © 3M 2014. All rights reserved.  
 80-4000-1997-4