3M[™] Dyneon[™] PTFE Fine Powder TF 2073Z

Product Description

3M™ Dyneon™ PTFE Fine Powder TF 2073Z is recommended for the manufacture of micro tubing, wire and cable insulations.

Special Features

- Meets ASTM D 4895 Type I, Grade 1, Class C classification
- High molecular weight PTFE powder produced by emulsion polymerisation
- Reduces lubricant consumption (1 part by weight per 100 parts by weight PTFE, compared with TF 2072Z)
- Wide processing window due to large reduction ratio (RR) range
- Reduced extruder load because of lower extrusion pressure
- Far more cost-effective processing because of the possible use of larger pre-forms

- Processing by standard paste extrusion methods
- Excellent chemical inertness
- Low friction behaviour
- High flame retardance
- Exceptional temperature resistance
- Very good electrical properties

Properties	Test method	Unit	Value*
Bulk Density	DIN EN ISO 60	g/l	490
Average Particle Size	ISO 13320	μm	400
Powder Flow Properties			free-flowing
Extrusion Pressure (Reduction Ratio 1600)	ASTM D 4895	MPa	26
Reduction Ratio (RR) Range	Internal Dyneon method	-	50 - 4400:1
Tensile Strength	DIN EN ISO 527-3	MPa	35
Elongation at Break	DIN EN ISO 527-3	%	460
Specific Gravity	DIN EN ISO 12086	g/cm³	2.17



^{*} average values

3M[™] Dyneon[™] PTFE Fine Powder TF 2073Z

Typical Properties

3M™ Dyneon™ PTFE Fine Powder TF 2073Z is the fine powder product grade with the lowest extrusion pressure value, resulting in the possibility of higher reduction ratio applications compared to TF 2072Z.

Typical Applications

 $3M^{TM}$ Dyneon TM PTFE Fine Powder TF 2073Z is a valuable addition to TF 2072Z for very thin wall, smallest diameter tubing and wire and cable insulation with a maximum reduction ratio of up to 4400:1

Processing Recommendations

3M™ Dyneon™ PTFE Fine Powder TF 2073Z can be processed by standard paste extrusion methods, which means the processing of the fine powder together with a suitable lubricant to prevent excessive shearing of sensitive PTFE particles during extrusion. To achieve optimum extrudate quality, all processing parameters such as temperature settings, extrusion pressure, lubricant content, extrusion rate and extrudate dimensions must be carefully balanced.

The fine powder should be mixed with a suitable lubricant, stored for at least 24 hours at a minimum temperature of 25 °C and compacted into a preform, which is then extruded through a die on a ram-type extruder to produce either tubing or wire insulation. The lubricant is usually evaporated in a suitable drying oven and in the next step the tubing or wire insulation is sintered inline in a suitable sintering oven.

During paste extrusion the round fine powder particles get fibrillated and the extrudate builds up its mechanical green strength. In the following sintering step the particles fuse together and the voids are closed.

The reduction ratio (RR) is defined as the result of the cross-section of the extrusion cylinder divided by the cross-section of the extrusion die. It is an important processing parameter for paste extrusion, which influences the extrudate quality.

Storage and Handling

3M™ Dyneon™ PTFE Fine Powder TF 2073Z can be stored for a relatively long period of time provided it is kept in a clean, dry place at a temperature of less than 19 °C to safeguard free-flowing properties. Careful handling of fine powder is recommended because it is relatively shear-sensitive. Excessively sheared particles usually result in extrudate defects.

Safety Instructions

Follow the normal precautions observed with all fluoropolymer materials.

Please consult the Material Safety Data Sheet and Product Label for information regarding the safe handling of the material. By following all precautions and safety measures, processing these products poses no known health risks. General handling/processing precautions include: 1) Process only in well-ventilated areas. 2) Do not smoke in areas contaminated with powder/residue from these products. 3) Avoid eye contact. 4) If skin comes into contact with these products during handling, wash with soap and water afterwards. 5) Avoid contact with hot fluoropolymer.

Potential hazards, including release of toxic vapours, can arise if processing occurs under excessively high temperature conditions. Vapour extractor units should be installed above processing equipment. When cleaning processing equipment, do not burn off any of this product with a naked flame or in a furnace.

Delivery Form

3M™ Dyneon™ PTFE Fine Powder TF 2073Z is delivered in powder form.

Packaging size is:

25 kg plastic drum



Product Data Sheet

3M[™] Dyneon[™] PTFE Fine Powder TF 2073Z

Important Notice

All information set forth herein is based on our present state of knowledge and is intended to provide general notes regarding products and their uses. It should not therefore be construed as a guarantee of specific properties of the products described or their suitability for a particular application. Because conditions of product use are outside Dyneon's control and vary widely, user must evaluate and determine whether a Dyneon product will be suitable for user's intended application before using it.

The quality of our products is warranted under our General Terms and Conditions of Sale as now are or hereafter may be in force.

Technical information, test data, and advice provided by Dyneon personnel are based on information and tests we believe are reliable and are intended for persons with knowledge and technical skills sufficient to analyze test types and conditions, and to handle and use raw polymers and related compounding ingredients.

No license under any Dyneon or third party intellectual rights is granted or implied by virtue of this information.

General recommendations on health and safety in processing, on work hygiene and on measures to be taken in the event of accident are detailed in our material safety data sheets.

You will find further notes on the safe handling of fluoropolymers in the brochure "Guide for the safe handling of Fluoropolymers Resins" (download link) by PlasticsEurope, Box 3, B-1160 Brussels, Tel. +32 (2) 676 17 32.

You can also download it with your smartphone using the QR code below.



Customer Service

Europe

Phone: 00 800 396 366 27 Fax: 00 800 396 366 39

Italy

Phone: 800 7 910 18 Fax: 800 7 810 19

USA

Phone: +1 800 810 8499 Fax: +1 800 635 8061

Technical Service Fluoroplastics

Dyneon GmbH

3M Advanced Materials Division Industrieparkstraße 1 84508 Burgkirchen

Germany

Phone: +49 8679 7 4709 Fax: +49 8679 7 5037

Technical Service Fluoroelastomers & Polymer Processing Additives

3M Belgium N.V.

3M Advanced Materials Division Canadastraat 11, Haven 1005 2070 Zwijndrecht

Belgium

Phone: +32 3 250 7868 Fax: +32 3 250 7905

Technical Service PTFE Compounds

Dyneon B.V.

The Netherlands

3M Advanced Materials Division Tunnelweg 95 6468 EJ Kerkrade

Phone: +31 45 567 9600 Fax: +31 45 567 9619

We will gladly supply further contact details for our full network of global sales offices. Alternatively, find them here.