



November 30, 2010

Product Discontinuation Notice – Effective December 31, 2010
3M™ Macurco™ Fixed Gas Carbon Monoxide (CO) Detectors
CM-1B, CM-2B, CM-3 and CS102A

Dear Valued 3M Distributor,

The 3M™ Macurco™ Carbon Monoxide (CO) Detectors CM-1B, CM-2B, CM-3 and CS102A are being discontinued effective December 31, 2010.

Discontinued Product Description	3M ID	UPC
3M™ Macurco™ Fixed Gas Carbon Monoxide Detector CM-1B	70 0714 8486 2	0 00 51135 89052 3
3M™ Macurco™ Fixed Gas Carbon Monoxide Detector CM-2B	70 0714 0324 3	0 07 83748 81230 1
3M™ Macurco™ Fixed Gas Carbon Monoxide Detector CM-3	70 0714 0323 5	0 07 83748 81130 4
3M™ Macurco™ Fixed Gas Carbon Monoxide Sensor Transducer CS102A	70 0714 0329 2	0 07 83748 81635 4

- These 3M™ Macurco Fixed Gas products are being discontinued effective December 31, 2010.
- All valid warranty claims for the CM-1B, CM-2B, CM-3 and CS102A will be honored.
- Ongoing technical support to our existing customer base, along with repair and service as needed, will continue to be provided.
- Subject to availability, service will continue to be supported as follows:
Electronics: 3 years

The newly released 3M™ Macurco™ Carbon Monoxide (CO) Detector, Controller and Transducer **CM-6 is the replacement product for the 3M™ Macurco™ CM-1B, CM2B and CM-3 Fixed Gas Carbon Monoxide Detectors.** The low-voltage, dual relay CM-6 helps to monitor carbon monoxide levels in enclosed parking garages, automotive maintenance facilities and other commercial applications by measuring the concentration of carbon monoxide (CO), providing feedback and automatically controlling exhaust fans. The CM-6 is ETL Listed to UL 61010-1, and guaranteed for a full two-year period from the date of manufacture.

Replacement Product Description	3M ID	UPC
3M™ Macurco™ Carbon Monoxide Detector CM-6	70 0715 6500 9	0 00 51131 49580 7

The replacement for the CS102 is the 3M™ Macurco™ CM-4. The CM-4 has a 1-3 volt analog output as was available with the CS102A.

Replacement Product Description	3M ID.	UPC
3M™ Macurco™ Carbon Monoxide Sensor Trans, 24V, 4-20MA CM-4	70-0714-0318-5	0 07 83748 81540 1

November 30, 2010

Page Two

Thank you for your continued support of 3M detection products. Should you have any questions or concerns regarding this discontinuation notice, please contact your local 3M sales representative, or 3M Customer Service at 800.328.1667.

Best regards,

A handwritten signature in black ink, appearing to read 'Shawn Lowry', with a long horizontal line extending to the right.

Shawn Lowry
Global Business Manager – Detection Portfolio