

Description:

3M™ Easy Trap Duster System is a unique floor and surface dusting material that captures and holds dust and dirt. The 3M™ Easy Trap Duster System is comprised of the 3M™ Easy Trap Duster and 3M™ Easy II Holder.

Special Features:

3M™ Easy Trap Duster

- The dusting cloth can be used on both sides to increase your effective floor and surface dusting area.
- The open construction of the cloth provides space for dirt and dust to be captured up in the cloth.
- The proprietary fiber technology helps capture and hold the dirt and dust in the cloth.
- The open construction helps to reduce drag when floor and surface dusting.
- The proprietary fiber technology pick-up even when wet.
- Perforated cloth allows you to customize the size cloth by every 6" (15 cm).

3M™ Easy II Holder

- The holder works with a standard threaded broom handle.
- Allows you to easily use both sides of the 3M™ Easy Trap Duster cloth with out bending over.
- The "A" shape allows you to plow large debris (i.e. cups, paper or wrappers) without them tumbling over the holder.
- The extruded "A" shape is light weight yet very durable.
- The 3M™ Easy Trap Duster cloth easily attaches to the holder.
- The holder is available in three sizes.

Packaging:

3M™ Easy Trap Duster Standard

2 rolls/box

3M™ Easy Trap Duster Large

1 roll/box

3M™ Easy Trap Duster Cart

30 ft (9 m) /box/8 boxes per case

3M™ Easy II Holder (bulk package)

1/bag


3M™ Easy II Holder (Individual package)

1/box

General Use Directions:

Preparation:

1. Tear off the needed amount of dusting media to cover the width of the 3M™ Easy II Holder.
2. Lean the 3M™ Easy II Holder with stick up against the wall so that the top of the "A" is facing you (Figure 1).



3. Start by applying the duster cloth to the black brush surface of the 3M™ Easy II Holder on one side and work your way across the 3M™ Easy II Holder. Make sure to align the edge of the duster with the edge of the black brush attachment surface (Figure 2).
4. Once applied all the way across the 3M™ Easy II Holder, rub hand over surface to set in place.
5. You are now ready to dust the floor.

When to Replace Duster Cloth



Dust and debris will begin loading from the leading edge of the cloth.



Continue to use the cloth until it is fully loaded.



The cloth is fully loaded when you begin to see debris or dust particles exiting from the trailing edge of the cloth.



When cloth no longer picks up dirt, flip the cloth over and use the opposite side. When both sides of the cloth are completely soiled, replace cloth.

Clean-up

- Remove dirty duster cloth from the holder and place in trash.

Product Specifications:

3M™ Easy Trap Duster Standard

5" (13 cm) by 125 ft (38 m) per roll (2 rolls per box) – perforated every 6 inches (15 cm)

3M™ Easy Trap Duster Large

8" (20 cm) by 125 ft (38 m) per roll (one roll per box) – perforated every 6 inches (15 cm)

3M™ Easy Trap Duster Cart

5" (13 cm) by 30 ft (9 m) per box, 8 boxes per case – perforated every 6 inches (15 cm)

3M™ Easy II Holder

3 1/2" x 1 5/8" X 17" (9 cm x 4 cm x 43 cm)

3 1/2" x 1 5/8" X 46" (9 cm x 4 cm x 119 cm)

3 1/2" x 1 5/8" X 59" (9 cm x 4 cm x 150 cm)

Important:

The information provided in this report is believed to be reliable; however, due to the wide variety of intervening factors, 3M does not warrant that the results will necessarily be obtained. All details concerning product specifications and terms of sale are available from 3M.



3M Commercial Solutions Division
PO Box 5757
1840 Oxford Street East
London, ON N6A 4T1
Phone 1-800-364-3577
Web: 3M.ca