

Enhanced Visibility with Excellent Color Durability

3M™ Scotchlite™ Reflective Material – Silver Home Wash Transfer Films

3M™ Scotchlite™ Reflective Material – Silver Home Wash Transfer Films will not only wear well, but will stay bright and continue to reflect light, even through the rigors of typical use. See how the 3M™ Scotchlite™ Reflective Material product line offers a solution for visibility and comfort, with home wash performance advantages you'll appreciate.

Wears well, stays bright

These 3M™ Scotchlite™ Reflective Material – Silver Home Wash Transfer Films now have excellent color after washing. They feature wide angle, retroreflective lenses to reflect light directly back to a light source. They are home washable with an initial average coefficient of reflection (R_A) of up to 500 cd/lux/m² and a minimum of 100 cd/lux/m² after the prescribed number of washings.

3M™ Scotchlite™ Reflective Material			
	Recommended Garment Applications	Key Features	Authenticity Verification
5510	Ideal for light to heavy weight fabrics, such as knit T-shirts, sweatshirts, outerwear	Segmented for increased comfort and increased wash durability	None
5807	Ideal for light to heavy weight fabrics, such as knit T-shirts, sweatshirts, outerwear	Plotter cuttable for graphics and lettering	None
8711	Ideal for light to medium weight, polyester and polyester blend fabrics, such as vests and limited use garments.*	Ideal for screen printing	None
8712	Ideal for light to medium weight, polyester and polyester blend fabrics, such as vests and limited use garments.*	Excellent color after wash	3M logo on front of product
8725	Ideal for light to heavy weight fabrics, such as knit T-shirts, sweatshirts, outerwear, vests	Versatility with additional durability	3M logo on front of product
8725LL	Ideal for light to heavy weight fabrics, such as knit T-shirts, sweatshirts, outerwear, vests	Versatility with additional durability and linerless construction	3M logo on front of product
8726	Ideal for light to heavy weight fabrics, such as knit T-shirts, sweatshirts, outerwear, vests	More resilient during handling	None
8726LL	Ideal for light to heavy weight fabrics, such as knit T-shirts, sweatshirts, outerwear, vests	More resilient during handling and linerless construction	None

*Performs best when laminated to polyester and polyester blend fabrics. It should not be used on knitted T-shirts or 100% cotton fabrics where good adhesion is required for extended use.

Why 3M?

From a trusted leader in reflective technology

3M invented reflective technology. Using more than 70 years of reflective technology experience, we are helping to enhance the visibility of workers by providing reliable reflective material components for garments. And you can count on 3M™ Scotchlite™ Reflective Material products to last through multiple laundry cycles and to meet or exceed many global high visibility standards. Scotchlite reflective material has a broad portfolio of more than 35 wash-durable products designed to comply with high visibility standards, including ANSI 107 Level 2, EN 471 Level 2 and CSA Z96 Level 2.

For more information on 3M™ Scotchlite™ Reflective Material – Silver Home Wash Transfer Films, see your 3M representative or go to Scotchlite.com.

Important Notice

WARRANTY, LIMITED REMEDY AND DISCLAIMER: 3M warrants that 3M™ Scotchlite™ Reflective Material that is stored, maintained and used in accordance with 3M's written instructions will meet the applicable 3M product specifications. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If any Scotchlite reflective material does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

LIMITATION OF LIABILITY: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract or strict liability.

PRODUCT USE: Because of the variety of factors that can affect the use and performance of Scotchlite reflective material, user is solely responsible for evaluating the product and determining whether it is fit for a particular purpose and suitable for user's method of application. User is solely responsible for determining the proper amount and placement of the product. While reflective products enhance visibility, no reflective product can ensure visibility or safety under all possible conditions. 3M may change the product, specification and availability of the product as improvements are made; therefore, user should contact 3M for latest information before specifying the product.



**Occupational Health and Environmental Safety Division
3M Performance Safety Materials**
3M Center, Building 0235-02-F-06
St. Paul, MN 55144-1000
800-328-7098
Scotchlite.com

3M Canada
P.O. Box 5757
London, Ontario N6A 4T1
800-267-4414 Technical Service
800-364-3577 3M HELPS
3M.ca/Scotchlite

3M and Scotchlite are trademarks of 3M, used under license in Canada. Please recycle. Printed in U.S.A.
© 3M 2012. All rights reserved.
75-0501-0468-8