
















The Height of Confidence



3M™ Fall Protection

It is our mission at 3M to provide those responsible for the safety of workers at height with reliable fall arrest equipment. We offer the knowledge and support to help take the fear out of height. To see the full line of 3M Fall Protection products, visit www.3M.com/FallProtection.

	Price	Product	Description	Key Features and Benefits	Image
Harnesses	\$\$\$	Elevation™	The premium 3M™ Fall Arrest Harness	<ul style="list-style-type: none"> -Premium padding -Intuitive adjustment hardware -Web designed for additional abrasion resistance -Rubber protective shield for label pack 	
	\$\$	Ameba	Features comfort forming webbing	<ul style="list-style-type: none"> -Non-elastic helical yarn moves with wearers to assist comfort and mobility -Value padding for added comfort and moisture wicking -Laminated sleeve helps protect label 	
	\$	SafeLight	The economical choice in fall arrest harnesses	<ul style="list-style-type: none"> -Quality construction at a value price -Bright color web assists worker visibility on a jobsite 	
Self-Retracting Lanyards	\$\$\$	ReLoad™	The field serviceable self-retracting lanyard	<ul style="list-style-type: none"> -Can be inspected and serviced onsite by authorized technicians for lower maintenance costs -Clicking sound provides audible indication that pawls are functioning correctly -400 lbs. max capacity for cable units, 310 lbs. for web units -Cable units range from 23'-50', available in galvanized or stainless steel -Web units range from 7'-23' 	
	\$\$	Thor	Classic design with swivel top housing and spring	<ul style="list-style-type: none"> -Durable aluminum housing -Spring cushion cable guide helps reduce cable rewind damage -Swivel top housing for enhanced mobility -310 lbs. max capacity -Cable units range from 10'-130', available in galvanized or stainless steel -Web units range from 7'-50' 	
	\$	G-Series	Versatile product suitable for multiple industries	<ul style="list-style-type: none"> -Assembled in the U.S.A. from high quality materials -Rugged durability and lightweight design -310 lbs. max capacity -Cable units range from 20'-50', available in galvanized or stainless steel -Web units range from 7' to 20' 	

	Price	Product	Description	Key Features and Benefits	Image
Lanyards	\$\$\$	SafeAbsorb Xtra	Stretches from 4'-6' to help reduce trip hazards	-310 lbs. rated -3600 lbs. gate rated hardware -Integrated shock absorber	
	\$\$	SafeAbsorb	Versatile offering of lengths and hardware for general use	-310 lbs. rated -3600 lbs. gate rated hardware -Meets requirements of latest ANSI Z359.13-2009 standards -Includes an external shock pack	
	\$	SafeLight	The economical choice in fall arrest lanyards	-310 lbs. rated -3600 lbs. gate rated hardware -Meets requirements of ANSI Z359.1-2007 standards -Available in low-profile or external shock pack designs	

	Type	Product	Description	Key Features and Benefits	Image
Anchorage Devices	Concrete	4075 5,000lbs 4077 10,000lbs	vSafeClaw reusable concrete anchorage device	-Trigger mechanism allows unit to be easily inserted and removed from pre-drilled poured concrete -Available in 5000 lbs. and 10,000 lbs. rated designs	
	Roofing	4000 Reusable Roof Anchor	Hinged anchor for wood and metal decking	-Steel design -Fits most pitch angles -Appropriate for Horizontal Lifeline Applications	
	I-Beam	4650-3 Beam Anchor	Sliding beam anchor	-Lightweight aluminum construction -Dual axis swivel D-ring helps prevent entanglement -Smooth, non-chattering mobility across exposed I and H beams	
	Steel	4005 Permanent D-Bolt Anchor	Designed for permanent installation	-Permanent D-Bolt Anchor -Includes nut, bolt and washer hardware	

	Type	Product	Description	Key Features and Benefits	Image
Kits	Aerial Lift	30500	Designed for use with rental lifts	-Includes a 10910 SafeLight Harness and a 209512 6' SafeLight Lanyard -Includes a tool bag for equipment storage -Can be personalized with a customer logo	
	Roofing	20058	A complete Personal Fall Arrest System in a bucket	-Includes a 10910 SafeLight Harness, 209512 6' SafeLight Lanyard, 4000 Roof Anchor, 0221-50RG 50' Lifeline with attached Rope Grab -Includes 5-gallon storage bucket	

WARNING!

Compliant fall protection and emergency rescue systems help prevent serious injury during fall arrest. Users must read and understand the *User Instructions* provided with the product and be properly trained by their employer prior to use per OSHA 1910.66 and 1926.503 or applicable local standards. **Misuse or failure to follow warnings and instructions may result in serious personal injury or death.** For proper use, see supervisor, User Instructions, or call 3M OH&ESD Technical Service at 1-800-243-4630. In Canada, call 1-800-267-4414.



Corporate Headquarters
3M Center
Saint Paul, MN 55144-1000
U.S.A.

For more information:

Sales Assistance: 1-800-328-1667
Technical Assistance: 1-800-243-4630 in US
1-800-267-4414 in Canada
www.3M.com/FallProtection

© 3M 2011. All rights reserved.
3M, Elavation, and ReLoad are trademarks of 3M Company, used under license in Canada.
70-0715-7479-5