



# Glass Decorative Films

The creative alternative  
to traditional glass decoration

Glass means transparency, brightness, lightness, freshness and elegance. It can be used as communication, it can be decorated. It is an essential element in building design. 3M Decorative Glass films are perfect for privacy and decorative applications on glass and windows.

The ideal solution to give a touch of elegance and originality to the glass surfaces of malls, shops, restaurants, offices, hotels, wellness, spas.

## 3M™ Fasara™ and 3M™ Crystal Glass Decorative Films

3M offers interior designers and contractors a wide range of creative options for decorating glass with surprising effects that can be customised as required, to suit the tastes of each customer. In addition to providing a high-quality end result, these films are easy to adapt and apply. They are designed for indoor or outdoor application, and combine functional characteristics with decorative elements to give strong connotations to different rooms.

**3M™ Fasara™ Glass Decorative Films** is a range of high quality films made of durable polyester with a decorative matte surface, perfect for privacy and decorative applications on glass and windows. They enhance design, provide privacy and shatter resistance at a fraction of the cost of decorative glass. They are available in more than 50 different designs.

With the option of creating dusted and frosted crystal effects on glass windows and partitions, **3M™ Crystal Glass Decorative Films** act as an excellent solution, ensuring both durability and stability. These translucent cast and polymeric films provide the ability to create complex designs or lettering using the electronic cutting technology. **3M™ Scotchcal™ Dusted/Frosted Crystal Film Series 7725-300** and **3M™ Scotchcal™ Haze/Sandblast Crystal Film Series 5525-300** are part of the 3M™ Crystal Glass Decorative Films family.

## Where you should use 3M™ Fasara™ and 3M™ Crystal Glass Decorative Films


Fasara and Crystal Glass films are perfectly suited for glass doors or windows. Use our decorative window films for:

- Conference rooms
- Lobbies
- Retail environments
- Residential settings
- Offices
- Exterior windows
- Partitions
- Verandas

Product	Range	Maximum 3M Warranty (Years-Interior)	Maximum 3M Warranty (Years-Exterior)	Film Type	Electronic Cutting
Fasara	50 patterns	5	3	Polyester	
Scotchcal 7725-314	Dusted clear	15	4	Cast PVC	v
Scotchcal 7725-324	Frosted clear	15	4	Cast PVC	v
Scotchcal 7725-323	Frosted pink	15	4	Cast PVC	v
Scotchcal 7725-326	Frosted green	15	4	Cast PVC	v
Scotchcal 7725-327	Frosted blue	15	4	Cast PVC	v
Scotchcal 7725-331	Frosted gold	15	4	Cast PVC	v
Scotchcal 5525-314	Haze	5	3	Calendered PVC	v
Scotchcal 5525-324	Sandblast	5	3	Calendered PVC	v
Scotchcal 5525C-314	Haze Comply	5	3	Calendered PVC	v*
Scotchcal 5525C-324	Sandblast Comply	5	3	Calendered PVC	v*

\*to be tested before application

# 3M™ Fasara™ Glass Decorative Films



## Elegance and versatility

3M Fasara Decorative Glass Films have been designed to offer innovative new ways to manage space. When applied to glass surfaces, these films create a serene etched-glass appearance, renovating cold plain glazing and lifting the whole building's look. 3M Fasara Decorative Glass films are made of thin, durable polyester with a decorative matte surface - perfect for privacy, decorative and architectural applications. Perfect for indoor or outdoor application. Works on flat or curved surfaces. The material itself is amazingly flexible and easy to apply.

### Key Features:

- Translucent polyester films.
- Permanent transparent adhesive.
- Available in more than 50 textures (dot, line, prism, rice paper designs...).
- Long term applications.
- Low gloss surface.

### Key Benefits:

- Installation on site. No need to remove the glass/window.
- Design flexibility.
- Reduces glare while blocking out 99% of UV light.
- Easy to clean.
- Cost-savings quality graphics.

# 3M™ Crystal Glass Decorative Films

## The art on the glass

3M™ Scotchcal™ Dusted/Frosted Crystal Film Series 7725-300 and 3M™ Scotchcal™ Haze/Sandblast Crystal Film Series 5525-300 are intended for use in creating window graphics and internally-illuminated displays. These films are designed for interior and exterior applications. They increase the visual impact of your windows, doors and partitions while providing privacy. These films provide the ability to create complex designs or lettering using the electronic cutting technology. Use SC5525C, with Comply adhesive, for fast, dry and bubble-free application.



### Key Features:

- Translucent PVC films.
- Permanent transparent adhesive.
- Available in different finishes.
- Electronic/computer plot.
- Long term applications (7725) or medium term applications (5525).

### Key Benefits:

- Installation on site. No need to remove the glass/window.
- Unlimited design options, durable, will not peel or curl.
- Can be applied on either side of the transparent substrate.
- Easy to clean, eliminate glare.
- Ability to create complex designs in small designs or simple lettering.
- Cost-savings quality graphics.







Visit [www.3M.eu/ArchitecturalMarkets](http://www.3M.eu/ArchitecturalMarkets) for the most current, up-to-date information.



**Architectural Markets**  
**3M Europe**  
Hermeslaan 7  
1831 Diegem  
Belgium