

3M™ Dyneon™

Fluoroelastomer FG 5630Q

Product Description

3M™ Dyneon™ Fluoroelastomer FG 5630Q is a dipolymer made from hexafluoropropylene and vinylidene fluoride. FG 5630Q has an incorporated bisphenol cure system. It has been especially designed for finished parts which are compliant with the regulations of the U.S. Food and Drug Administration (FDA) 21 CFR 177.2600(c)(4)(i).

Special Features

- Composition: dipolymer of vinylidene fluoride and hexafluoropropylene
- Excellent mould release
- Superior compression set resistance compared to diamine cured compounds
- Proprietary incorporated cure technology
- In compliance with U.S. Food and Drug Administration (FDA) 21 CFR 177.2600(c)(4)(i)
- Better mould flow compared to diamine cured compounds
- Superior water resistance at elevated temperatures compared to diamine cured compounds

Typical Applications

3M™ Dyneon™ Fluoroelastomer FG 5630Q is recommended for O-rings with direct food contact. FG 5630Q can be blended with 3M™ Dyneon™ Fluoroelastomer FC 2230 and 3M™ Dyneon™ Fluoroelastomer FC 2178 to adjust crosslink density.

Typical Polymer Properties

| Property | Test method | Unit | Value |
|-------------------------------------|---------------|-------------------|--------------------|
| Fluorine Content | QCM 50.18.3.C | % | 65.9 |
| Specific Gravity | QCM 14.10 | g/cm ³ | 1.80 |
| Colour | - | - | opaque off-white |
| Solubility | - | - | Ketones and Esters |
| Mooney Viscosity ML 1 + 10 @ 121 °C | QCM 2.14.4.C | MU | approx. 30 |

Storage and Handling

Store and use all Dyneon Fluoroelastomers only in well ventilated areas under cool and dry conditions.
The shelf life of FG 5630Q is 3 years from date of manufacturing.

Delivery Form

3M™ Dyneon™ Fluoroelastomer FG 5630Q is delivered in slab form.

Packaging sizes are:

- 25 kg cardboard box, containing two PE-bags with 12.5 kg content each
- 600 kg bulk container, containing 48 PE-bags with 12.5 kg content each

Processing Recommendations

Dyneon FG 5630Q can be compounded using standard water cooled internal mixers or two-roll mills with standard fillers and ingredients utilized in typical fluoroelastomer formulations. The “dry” ingredients should be blended before adding to the masticated gum. For best results, FG 5630Q should be banded on the mill several minutes prior to adding the blended dry ingredients. Once mixed, the compounded stocks have good scorch resistance and storage stability.

Typical Properties (Formulation for comparison purposes only)

| Compound | Amount (in Parts/100) |
|---------------------|-----------------------|
| FG 5630Q | 100 |
| N-990 MT Black | 30 |
| MgO | 3 |
| Ca(OH) ₂ | 6 |

Typical Rheological Properties (ASTM D 5289)

Moving Die Rheometer (MDR 2000®)
100 cpm, 0.5° Arc, 6 minutes , 177 °C

| Property | Unit | Value |
|--|---------|-------|
| ML, Minimum Torque | dNm | 1.0 |
| Ts2, Time to 2 inch-lb rise from minimum | Minutes | 1.2 |
| t'50, Time to 50 % cure | Minutes | 1.4 |
| t'90, Time to 90 % cure | Minutes | 1.9 |
| MH, Maximum Torque | dNm | 23.8 |

Typical Physical Properties (ASTM D 412 Method A, Die D)

Press Cure 7 minutes @ 177 °C
Post Cure 16 hours @ 230 °C

| Property | Unit | Value |
|------------------------|---------|-------|
| Tensile | MPa | 15.5 |
| 100 % Modulus | MPa | 8.5 |
| Elongation at Break | % | 170 |
| Hardness (ASTM D 2240) | Shore A | 80 |

Compression Set on O-rings (ASTM D 1414)

| | | |
|------------------------------|---|----|
| Air aged 70 hours @ 200 °C | | |
| Post cured 16 hours @ 230 °C | % | 27 |
| Post cured 24 hours @ 260 °C | % | 22 |

Retraction at Lower Temperatures (ASTM D 1329)

| | | |
|-------|----|-----|
| TR 10 | °C | -18 |
|-------|----|-----|

3M™ Dyneon™ Fluoroelastomer FG 5630Q

Safety Instructions

Follow the normal precautions observed with all fluoropolymer materials.

Please consult the Material Safety Data Sheet and Product Label for information regarding the safe handling of the material. By following all precautions and safety measures, processing these products poses no known health risks. General handling/processing precautions include: 1) Process only in well-ventilated areas. 2) Do not smoke in areas contaminated with powder/residue from these products. 3) Avoid eye contact. 4) If skin comes into contact with these products during handling, wash with soap and water afterwards. 5) Avoid contact with hot fluoropolymer.

Potential hazards, including release of toxic vapours, can arise if processing occurs under excessively high temperature conditions. Vapour extractor units should be installed above processing equipment. When cleaning processing equipment, do not burn off any of this product with a naked flame or in a furnace.

Important Notice

All information set forth herein is based on our present state of knowledge and is intended to provide general notes regarding products and their uses. It should not therefore be construed as a guarantee of specific properties of the products described or their suitability for a particular application. Because conditions of product use are outside Dyneon's control and vary widely, user must evaluate and determine whether a Dyneon product will be suitable for user's intended application before using it.

The quality of our products is warranted under our General Terms and Conditions of Sale as now are or hereafter may be in force.

Technical information, test data, and advice provided by Dyneon personnel are based on information and tests we believe are reliable and are intended for persons with knowledge and technical skills sufficient to analyze test types and conditions, and to handle and use raw polymers and related compounding ingredients.

No license under any Dyneon or third party intellectual rights is granted or implied by virtue of this information.

General recommendations on health and safety in processing, on work hygiene and on measures to be taken in the event of accident are detailed in our material safety data sheets.

You will find further notes on the safe handling of fluoropolymers in the brochure "[Guide for the safe handling of Fluoropolymers Resins](#)" (download link) by PlasticsEurope, Box 3, B-1160 Brussels, Tel. +32 (2) 676 17 32.

You can also download it with your smartphone using the QR code below.



Customer Service

Europe
Phone: 00 800 396 366 27
Fax: 00 800 396 366 39
Italy
Phone: 800 7 910 18
Fax: 800 7 810 19
USA
Phone: +1 800 810 8499
Fax: +1 800 635 8061

Technical Service Fluoroplastics

Dyneon GmbH
3M Advanced Materials Division
Industrieparkstraße 1
84508 Burgkirchen
Germany
Phone: +49 8679 7 4709
Fax: +49 8679 7 5037

Technical Service Fluoroelastomers & Polymer Processing Additives

3M Belgium BVBA / SPRL
3M Advanced Materials Division
Canadastraat 11,
Haven 1005
2070 Zwijndrecht
Belgium
Phone: +32 3 250 7868
Fax: +32 3 250 7905

Technical Service PTFE Compounds

Dyneon B.V.
3M Advanced Materials Division
Tunnelweg 95
6468 EJ Kerkrade
The Netherlands
Phone: +31 45 567 9600
Fax: +31 45 567 9619

We will gladly supply further contact details for our full network of global sales offices. Alternatively, find them [here](#).

