

# 3M™ Dyneon™ Fluoroelastomer FE 5642

## Product Description

3M™ Dyneon™ Fluoroelastomer FE 5642 is a dipolymer made from hexafluoropropylene and vinylidene fluoride. FE 5642 has an incorporated bisphenol cure system.

## Special Features

- Composition: dipolymer of vinylidene fluoride and hexafluoropropylene
- Improved scorch resistance at high moulding temperatures
- Excellent mould release
- Process targets: transfer and compression moulding, bonding and calendering
- Proprietary incorporated cure technology
- Clean running

## Typical Applications

The development of 3M™ Dyneon™ Fluoroelastomer FE 5642 targeted bonded shaft seal applications.

## Typical Polymer Properties

Property	Test method	Unit	Value
Fluorine Content	QCM 50.18.3.C	%	65.9
Specific Gravity	QCM 14.10	g/cm <sup>3</sup>	1.80
Colour	-	-	opaque off-white
Solubility	-	-	Ketones and Esters
Mooney Viscosity ML 1 + 10 @ 121 °C	QCM 2.14.4.C	MU	approx. 42

## Storage and Handling

Store and use all Dyneon Fluoroelastomers only in well ventilated areas under cool and dry conditions.

The shelf life of FE 5642 is 3 years from date of manufacturing.

## Delivery Form

3M™ Dyneon™ Fluoroelastomer FE 5642 is delivered in slab form.

Packaging sizes are:

- 25 kg cardboard box, containing two PE-bags with 12.5 kg content each
- 600 kg bulk container, containing 48 PE-bags with 12.5 kg content each

## Processing Recommendations

Dyneon FE 5642 can be compounded using standard water cooled internal mixers or two-roll mills with standard fillers and ingredients utilized in typical fluoroelastomer formulations. The “dry” ingredients should be blended before adding to the masticated gum. For best results, FE 5642 should be banded on the mill several minutes prior to adding the blended dry ingredients. Once mixed, the compounded stocks have good scorch resistance and storage stability.

## Typical Properties

Compound	Amount (in Parts/100)
FE 5642	100
N-990 MT Black	30
MgO	3
Ca(OH) <sub>2</sub>	6

## Typical Rheological Properties (ASTM D 5289)

Moving Die Rheometer (MDR 2000®)  
100 cpm, 0.5° Arc, 6 minutes, 177 °C

Property	Unit	Value
ML, Minimum Torque	dNm	1.5
Ts2, Time to 2 inch-lb rise from minimum	Minutes	1.5
t'50, Time to 50 % cure	Minutes	1.9
t'90, Time to 90 % cure	Minutes	3.0
MH, Maximum Torque	dNm	18.0

## Typical Physical Properties (ASTM D 412 Method A, Die D)

Press Cure 7 minutes @ 177 °C  
Post Cure 16 hours @ 230 °C

Property	Unit	Value
Tensile	MPa	17.8
100 % Modulus	MPa	4.2
Elongation at Break	%	290
Hardness (ASTM D 2240)	Shore A	71

## Compression Set on O-rings (ASTM D 1414)

Air aged 70 hours @ 200 °C

Post cured 16 hours @ 230 °C	%	15
Post cured 24 hours @ 260 °C	%	15

## Retraction at Lower Temperatures (ASTM D 1329)

TR 10	°C	-18
-------	----	-----

### 3M™ Dyneon™ Fluoroelastomer FE 5642

#### Safety Instructions

Follow the normal precautions observed with all fluoropolymer materials.

Please consult the Material Safety Data Sheet and Product Label for information regarding the safe handling of the material. By following all precautions and safety measures, processing these products poses no known health risks. General handling/processing precautions include: 1) Process only in well-ventilated areas. 2) Do not smoke in areas contaminated with powder/residue from these products. 3) Avoid eye contact. 4) If skin comes into contact with these products during handling, wash with soap and water afterwards. 5) Avoid contact with hot fluoropolymer.

Potential hazards, including release of toxic vapours, can arise if processing occurs under excessively high temperature conditions. Vapour extractor units should be installed above processing equipment. When cleaning processing equipment, do not burn off any of this product with a naked flame or in a furnace.

#### Important Notice

All information set forth herein is based on our present state of knowledge and is intended to provide general notes regarding products and their uses. It should not therefore be construed as a guarantee of specific properties of the products described or their suitability for a particular application. Because conditions of product use are outside Dyneon's control and vary widely, user must evaluate and determine whether a Dyneon product will be suitable for user's intended application before using it.

The quality of our products is warranted under our General Terms and Conditions of Sale as now are or hereafter may be in force.

Technical information, test data, and advice provided by Dyneon personnel are based on information and tests we believe are reliable and are intended for persons with knowledge and technical skills sufficient to analyze test types and conditions, and to handle and use raw polymers and related compounding ingredients.

No license under any Dyneon or third party intellectual rights is granted or implied by virtue of this information.

General recommendations on health and safety in processing, on work hygiene and on measures to be taken in the event of accident are detailed in our material safety data sheets.

You will find further notes on the safe handling of fluoropolymers in the brochure "[Guide for the safe handling of Fluoropolymers Resins](#)" (download link) by PlasticsEurope, Box 3, B-1160 Brussels, Tel. +32 (2) 676 17 32.

You can also download it with your smartphone using the QR code below.



#### Customer Service

Europe  
Phone: 00 800 396 366 27  
Fax: 00 800 396 366 39  
Italy  
Phone: 800 7 910 18  
Fax: 800 7 810 19  
USA  
Phone: +1 800 810 8499  
Fax: +1 800 635 8061

#### Technical Service Fluoroplastics

Dyneon GmbH  
3M Advanced Materials Division  
Industrieparkstraße 1  
84508 Burgkirchen  
Germany  
Phone: +49 8679 7 4709  
Fax: +49 8679 7 5037

#### Technical Service Fluoroelastomers & Polymer Processing Additives

3M Belgium BVBA / SPRL  
3M Advanced Materials Division  
Canadastraat 11,  
Haven 1005  
2070 Zwijndrecht  
Belgium  
Phone: +32 3 250 7868  
Fax: +32 3 250 7905

#### Technical Service PTFE Compounds

Dyneon B.V.  
3M Advanced Materials Division  
Tunnelweg 95  
6468 EJ Kerkrade  
The Netherlands  
Phone: +31 45 567 9600  
Fax: +31 45 567 9619

We will gladly supply further contact details for our full network of global sales offices. Alternatively, find them [here](#).

