

Available
November 1, 2010

3M™ Hookit™ Purple Clean Sanding Sheet Rolls (70 mm)

P.N.	Description	Grade	Dimension	Case Qty
30716	3M™ Hookit™ Purple Clean Sanding Sheet Roll	36E	70 mm (2.75 in) x 8 m (8.75 yd)	5
30715	3M™ Hookit™ Purple Clean Sanding Sheet Roll	40E	70 mm (2.75 in) x 8 m (8.75 yd)	5
30714	3M™ Hookit™ Purple Clean Sanding Sheet Roll	60E	70 mm (2.75 in) x 12 m (13.12 yd)	5
30713	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P80E	70 mm (2.75 in) x 12 m (13.12 yd)	5
30712	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P100	70 mm (2.75 in) x 12 m (13.12 yd)	5
30711	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P120	70 mm (2.75 in) x 12 m (13.12 yd)	5
30710	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P150	70 mm (2.75 in) x 12 m (13.12 yd)	5
30709	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P180	70 mm (2.75 in) x 12 m (13.12 yd)	5
30708	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P220	70 mm (2.75 in) x 12 m (13.12 yd)	5
30707	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P240	70 mm (2.75 in) x 12 m (13.12 yd)	5
30706	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P280	70 mm (2.75 in) x 12 m (13.12 yd)	5
30705	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P320	70 mm (2.75 in) x 12 m (13.12 yd)	5
30703	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P400	70 mm (2.75 in) x 12 m (13.12 yd)	5
30702	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P500	70 mm (2.75 in) x 12 m (13.12 yd)	5
30701	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P600	70 mm (2.75 in) x 12 m (13.12 yd)	5
30700	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P800	70 mm (2.75 in) x 12 m (13.12 yd)	5

New!

Standard Operating Procedures

Check it out at www.3M.com/automotive

- Click on Learning Center
- Instructional videos and procedures
- Step-by-step training modules
- Metal and plastic repair
- Dry primer sanding and clear blending
- Spot repair and denib procedures
- Paint finishing, car clean up and more...



Please recycle. Printed in U.S.A.
3M, Triact and Hookit are trademarks of 3M Company.
© 2010, 3M. All rights reserved.
60-4402-7734-5



Automotive Aftermarket Division

3M Center
Building 223-6N-01
St. Paul, MN 55144-1000
U.S.A.

Call 1-877-MMM-CARS (877-666-2277)
www.3M.com/automotive



Paper,
Sand.

Clean Sanding Sheet Rolls

- Long lasting cut and performance
- Kiss-cut design
- Unique chevron hole design
- New range of handblocks

3M™ Hookit™ Blocks

P.N.	Description	Grade	Dimension	Case Qty
05207	3M™ Hookit™ Dust Free Sanding Block	NA	70 mm (2.75 in) x 127 mm (5 in)	5
05208	3M™ Hookit™ Dust Free Sanding Block	NA	70 mm (2.75 in) x 198 mm (7.5 in)	5
05209	3M™ Hookit™ Dust Free Sanding Block	NA	70 mm (2.75 in) x 396 mm (16 in)	1
05216*	3M™ Hookit™ Dust Free Sanding Block	NA	115 mm (4.53 in) x 225 mm (8.86 in)	3
05742	3M™ Hookit™ 5" Soft Hand Block	NA	70 mm (2.75 in) x 127 mm (5 in)	10
05740	3M™ Hookit™ 5" Hand Block	NA	70 mm (2.75 in) x 127 mm (5 in)	10
05741	3M™ Hookit™ 7 3/4" Hand Block	NA	70 mm (2.75 in) x 196.8 mm (7.75 in)	10
05744	3M™ Hookit™ 16" Hand File Board	NA	70 mm (2.75 in) x 396 mm (16 in)	1

*Coming Soon in 2011.

3M™ Hookit™ Accessories

P.N.	Description	Grade	Dimension	Case Qty
05215	3M™ Hookit™ Dust Free Block Hose Extension Kit	NA	6 m (6.56 yd)	1
05848	3M™ Hookit™ 16" Dust Free Air File Board	NA	70 mm (2.75 in)	5
05748	3M™ Hookit™ 16" Air File Board	NA	70 mm (2.75 in)	5
05899	3M™ Hookit™ 16" Dust Free Orbital Air File Shoe	NA	70 mm (2.75 in)	5
05746	3M™ Hookit™ 16" Orbital Air File Shoe	NA	70 mm (2.75 in)	5
05898	3M™ Hookit™ 16" Orbital File Shoe Base Plate	NA	70 mm (2.75 in)	5
05750	3M™ Hookit™ 11" Straight Line Air File Shoe	NA	70 mm (2.75 in)	5

Coming Soon
in **2011**

3M™ Hookit™ Purple Clean Sanding Sheet Rolls (115 mm)

P.N.	Description	Grade	Dimension	Rolls per case
30740	3M™ Hookit™ Purple Clean Sanding Sheet Roll	36E	115 mm (4.53 in) x 8 m (8.75 yd)	3
30739	3M™ Hookit™ Purple Clean Sanding Sheet Roll	40E	115 mm (4.53 in) x 8 m (8.75 yd)	3
30738	3M™ Hookit™ Purple Clean Sanding Sheet Roll	60E	115 mm (4.53 in) x 12 m (13.12 yd)	3
30737	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P80E	115 mm (4.53 in) x 12 m (13.12 yd)	3
30736	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P100	115 mm (4.53 in) x 12 m (13.12 yd)	3
30735	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P120	115 mm (4.53 in) x 12 m (13.12 yd)	3
30734	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P150	115 mm (4.53 in) x 12 m (13.12 yd)	3
30733	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P180	115 mm (4.53 in) x 12 m (13.12 yd)	3
30732	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P220	115 mm (4.53 in) x 12 m (13.12 yd)	3
30731	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P240	115 mm (4.53 in) x 12 m (13.12 yd)	3
30730	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P280	115 mm (4.53 in) x 12 m (13.12 yd)	3
30729	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P320	115 mm (4.53 in) x 12 m (13.12 yd)	3
30727	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P400	115 mm (4.53 in) x 12 m (13.12 yd)	3
30726	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P500	115 mm (4.53 in) x 12 m (13.12 yd)	3
30725	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P600	115 mm (4.53 in) x 12 m (13.12 yd)	3
30724	3M™ Hookit™ Purple Clean Sanding Sheet Roll	P800	115 mm (4.53 in) x 12 m (13.12 yd)	3



NEW!

Kiss-cut Underscore Technology

The unique kiss-cut underscore technology enables purple abrasive sheet rolls to be easily converted into multiple sheet-length configurations.



Hookit™ Purple Clean Sanding Sheet Rolls use proven abrasive technology that enables bodyshops to increase profitability by:

- Increasing vehicle repair throughput
- Working to an efficient process
- Reducing material consumption

Fast cutting abrasive is combined with unique face-side construction to:

- Increase cutting power whether the product is used with or without a dust extraction system.
- Reduce loading, allowing the technician to work faster for longer!



Stronger. Faster. Cleaner.


Innovative abrasive construction with clean sanding chevron design combines with a new range of accessories to offer the very best solution for efficient sanding.

To achieve maximum performance, 3M has added hundreds of small holes that have been purposely arranged on the sheet in a chevron formation. This configuration of holes allows for optimal particulate removal from the face of the sheet, improving performance when used with or without dust extraction.

When using a dust extraction system, sheet alignment is not necessary to achieve direct air flow from the panel through the abrasive sheet.



Unique hole pattern.
better dust removal = improved performance!




New Range of Tools



The new range of accessories has been ergonomically designed to offer the most comfortable lightweight solution for every application.



Adjustable air management valve with every tool



Kiss-cut technology allows for easy tearing of sheets.