



## Technical Data

# 3M™ Glass Cleaner Concentrate 1A and 1L

### Description

3M™ Glass Cleaner Concentrate 1A is diluted and dispensed using the 3M™ Flow Control System Wall Mount Dispenser or the 3M™ Flow Control System Portable Dispenser.

3M™ Glass Cleaner Concentrate 1L is dispensed using the 3M™ Twist 'n Fill™ Cleaning Chemical Management System.

Improper use or dilution may result in altered product performance and may increase the risk of health effects.

3M™ Glass Cleaners are fast-drying, non-streaking glass cleaners formulated to effectively clean soil, water spots, oil, lipstick, and hairspray from a variety of glass and mirrored surfaces.

### Special Features

- Automatic dispensing eliminates measuring and mixing and helps ensure accurate dilutions
- Green Seal™ GS-37 Certification
- Pleasant fragrance
- Hard water tolerant
- Non-ammoniated formula

### Applications

- Windows
- Mirrors and other mirrored surfaces
- Glass

### Packaging

#### 3M™ Glass Cleaner Concentrate 1A

- 0.5-gallon bottle
- 4 bottles per case

Each 0.5 gallon bottle typically yields 35 ready-to-use gallons (dilution ratio 1:70).

#### 3M™ Glass Cleaner Concentrate 1L

- 0.528 gallon bottle
- 6 bottles per case

Each 0.528 gallon bottle typically yields 37 ready-to-use gallons (dilution ratio 1:69).

### General Use Directions

Dispense 3M™ Glass Cleaner Concentrate 1A using the 3M™ Flow Control System Wall Mount Dispenser or 3M™ Flow Control System Portable Dispenser. Dispense the 3M™ Glass Cleaner Concentrate 1L using the 3M™ Twist 'n Fill™ Cleaning Chemical Management System.

1. Spray the ready-to-use glass cleaner into a clean cloth or onto the surface.
2. Wipe the surface with a clean cloth or paper towel until clean and dry.
3. When using a squeegee, apply cleaner, scrub to loosen soil, then squeegee.

### Personal Protective Equipment (PPE)

**Recommendation:** Refer to SDS for specific PPE guidance.

### Ready-To-Use:

When used as directed and diluted with a 3M chemical dispensing system, eye or skin exposure is not significant enough to require protection.

### Waste Disposal Method:

Dispose of contents/container in accordance with applicable local/regional/national/international regulations. Rinse empty container with water and recycle (No.2 HDPE).

#### NOTE:

Refer to product Safety Data Sheet for specific physical properties, health hazard, first aid and precautionary information.

▪ 28-9276-8  
(Concentrate)

▪ 28-9283-4  
(RTU)



This product meets Green Seal™ Standard GS-37 based on effective performance, concentrated volume, minimized/recycled packaging, and protective limits on: VOCs and human & environmental toxicity. GreenSeal.org.



## 3M Branch Sales Offices

### ANCHORAGE

11151 Calaska Circle  
Anchorage, AK 99515

Telephone: 907/522-5200  
Facsimile 907/522-1645

### HONOLULU

4443 Malaai Street  
Honolulu, HI 96818  
Mail to: P.O. Box 30048  
Honolulu, HI 96820

Telephone: 808/422-2721  
Facsimile 808/422-9557

### CONTINENTAL UNITED STATES

Customer Service Department  
3M Center Building 223-5S-07  
St. Paul, MN 55144-1000

Order Entry 1-800-852-9722  
Facsimile 1-800-447-0408

### CANADA

1840 Oxford Street East  
London, Ontario, Canada  
N5V 3G2  
Mail to: P.O. Box 5757  
London, Ontario, Canada  
N6A 4T1

Telephone: 800/364-3577  
Facsimile: 800/479-4453

## Important Notice to User

**Technical Information:** The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

**Product Use:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

**Warranty and Limited Remedy:** 3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.



### Commercial Solutions Division

St. Paul, MN 55144-1000  
1-800-852-9722  
[www.3M.com/facility](http://www.3M.com/facility)

3M is a trademark of 3M Company.  
Green Seal and Twist 'n Fill are trademarks of Green Seal.  
Used under license in Canada.  
© 3M 2015. All rights reserved.  
Asset ID 741501