



Automotive Attachment Tape 06394 (Gray)

Technical Data Sheet

January 2006

General Description


3M Automotive Attachment Tape 06394 is a .090-inch-thick, gray, high-performance, double-coated acrylic foam tape. This OEM-approved tape is designed for reliable attachment of a wide variety of automotive exterior and interior trim including running boards, ground effects, claddings, rocker panel moldings, spoilers, wheel flares, bumper trim and other larger or heavier automotive trim components.

3M tape 06394 is OEM approved for the most demanding trim attachment applications where bonding surface contours may be poorly matched and/or a thick foam is required. Its thick, gray, high-strength core offers unique viscoelastic properties that allow it to elongate and relax when put under load, thereby minimizing stress at the adhesive bond line. This thick tape offers the following key performance features:


- Superior adhesion to automotive substrates
- Conformable core gives excellent wet-out (tape contact) on mismatched surfaces
- High-strength core absorbs and dissipates stress on bond line

3M™ Automotive Adhesion Promoter 06396 is recommended for use on all plastic parts such as RIM, TPO, PPO, PP, PC, PC+ABS, etc., for tape-to-part adhesion when used with 3M tape 06394.

Typical Applications



Product Construction



Technical Data Sheet 06394

Page 2

Physical Properties

Foam	Gray acrylic
Liner color	Red
Thickness	.090 in. (2,29 mm)
Package	Clam shell

Ordering Information	Part Number	Color	Size	Rolls Per Box	Boxes Per Case
	06394	Gray	1/2" x 10 yds (12,7 mm x 9,1 m)	1	12

Other Trim Attachment And Repair Products

Please see your 3M catalog or consult your 3M representative for information about our complete line of automotive attachment tapes and adhesion promoter. Or you may visit us at www.3M.com/automotive, then click on "Product Catalog," then "3M™ Tapes and Scotch® Tapes," and then "3M™ Automotive Attachment Tapes."

3M™ Automotive Adhesion Promoter 06396 is recommended for tape bonding to all plastic substrates. Please contact your 3M sales representative with application or performance questions.

Note: All statements, technical information and recommendations herein are based on tests 3M believes are reliable. 3M does not warrant or guarantee the accuracy or completeness of this information.

Warranty and Limited Remedy: This product will be free from defects in material and workmanship at the time of shipment. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If this product is defective, your exclusive remedy and 3M's and seller's sole obligation shall be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability: Except as provided above, 3M and seller will not be liable.

3M and Scotch are trademarks of 3M.

NASCAR™ and NASCAR Performance™ are registered trademarks of the National Association for Stock Car Auto Racing, Inc.



Automotive Aftermarket Division
3M Center, Building 223-6N-01
St. Paul, MN 55144-1000
www.3M.com/automotive



Minimum 30% Post-Consumer Fiber
Printed in U.S.A.
© 3M 2006 75-3469-7671-7



ISO 9001:2000
File No. A2109