

A decorative graphic consisting of a grid of orange squares of varying shades, arranged in a pattern that tapers to the right. The text is overlaid on this graphic.

# Sound Deadenening &









NVH

<b>Section</b>	<b>Page</b>
Sound Deadening & NVH .....	5-9
Accessories .....	5
Coatings .....	6-7
Expandable Foams .....	8
Vibration Isolation .....	8-9






## Accessories

### Accessories/Applicators

	02576	08188	08190	08193
Description	 Rack for holding dispense box of 3M™ Dynamic Mixing Nozzles, PN05847.	 Conical tapered nozzle for use with Flex Pack packaged products.	 A manual applicator gun designed for use with 3M's 1:1 50mL and 2:1 37.5mL cartridges	 3M™ Static Mixing Nozzle for use with all 3M 200mL and 400mL two-component cartridges.
Part Number	02576	08188	08190	08193
UPC	0-00-51131-02576-9	0-00-51135-08188-4	0-00-51135-08190-7	0-00-51131-08193-2
Product Name	3M™ Bulk Nozzle Rack	3M™ Flex Pack Nozzle	3M™ Performance Manual Applicator	3M™ Mixing Nozzle
Color	Red	Opaque	Black/Grey	Opaque/Gold
Packaging	1 per case	6 per case	1 per Case	6 nozzles per bag 6 bags per case
Container Volume		-	50 Millilitre	
	08194	08801	08966	08991
Description	 3M™ Static Mixing Nozzle for use with all 3M 200mL and 400mL two-component cartridges.	 One piece metal applicator gun designed for use with all No Cleanup products. Requires no cleaning. Refer to individual No Cleanup products for proper air pressures. Requires the use of No Cleanup Replacement Nozzle 08966.	 Designed for use with 3M™ No Cleanup Coatings, part numbers 08804, 08949 and 08964.	 Fully enclosed all metal, rod driven, friction feed applicator gun for use with 450 mL 3M™ Windshield Urethanes. This tool has an 18:1 ratio.
Part Number	08194	08801	08966	08991
UPC	0-00-51131-08194-5	0-00-51135-08801-2	0-00-51135-08966-8	0-00-51135-08991-0
Product Name	3M™ Static Mixing Nozzle	3M™ No Cleanup Applicator Gun	3M™ No Cleanup Replacement Nozzles	3M™ Flex Pack Heavy Duty Applicator Gun
Color	Opaque	Black	Opaque	Metallic/Black
Packaging	50 nozzles per box 6 boxes per case	8 per case	8 per bag 4 bags per case	1 per case
Container Volume				450 Millilitre




## Accessories

### Accessories/Applicators (continued)

	08997	38191	38193
Description	 <p>Developed to provide a unique, convenient and inexpensive means for spraying 3M™ Rubberized Body Schutz, part number 08864, 3M™ Rocker Schutz, part number 08874 and 3M™ Rust Fighter-I, part number 08991.</p>	 <p>3M™ Static Mixing Nozzle is a cascade mix/meter nozzle for an easy squeeze of adhesive right on target. Engineered for use with 3M 50mL cartridges.</p>	 <p>3M™ Static Mixing Nozzle is a cascade mix/meter nozzle for an easy squeeze of adhesive right on target. Engineered for use with 3M 50mL cartridges.</p>
Part Number	08997	38191	38193
UPC	0-00-51135-08997-2	0-00-51131-38191-9	0-00-51131-38193-3
Product Name	3M™ Body Schutz™ Applicator Gun	3M™ Static Mixing Nozzle - 50mL	3M™ Static Mixing Nozzle
Color	Silver	Opaque/Gold	Opaque/Gold
Packaging	1 per case	12 nozzles per bag 6 bags per case	50 nozzles per bag 6 bags per case
Container Volume			50 Millilitre







## Coatings

### Coatings

	08374	08804	08864
Description	 <p>Gray high-performance, general-purpose seam sealer that can be caulked or sprayed. Adheres well to all primed surfaces except acrylic lacquer.</p>	 <p>Superior performing, paintable, rubberized undercoating with excellent coverage and corrosion protection, while also meeting the low VOC requirements in most areas. Use with 3M™ No Cleanup Applicator Gun 08801.</p>	 <p>Black, rubberized, protective coating developed primarily for use as a sound deadener, protective coating, and underseal. Bonds to a wide variety of surfaces. Use with applicator gun, part number 08997.</p>
Part Number	08374	08804	08864
UPC	0-00-51135-08374-1	0-00-51135-08804-3	0-00-51135-08864-7
Product Name	3M™ MSP Sprayable Seam Sealer	3M™ No Cleanup Waterbased Undercoating	3M™ Body Schutz™ Rubberized Coating Black
Container Volume	0.1 Gallon (US)	18.5 fl oz	1 Quart (US)
Color	Gray	Black	Black
Packaging	6 per case	6 per case	6 per case

## Coatings

### Coatings (continued)



	08874	08881	08882
Description	 <p>Fast drying, tintable, paintable, chip resistant coating for use on motor vehicles; resists weathering, salt spray, and abrasion. Texture is coarse. Use with applicator gun, part number 08997.</p>	 <p>Black, multi-purpose, low cost, aerosol undercoating. Specifically used for undercarriages, wheel wells, frame rails, and fenders. Designed to protect metal from corrosion and abrasion. Can also be used as a sound dampening coating.</p>	 <p>Paintable aerosol undercoating designed to protect surfaces from corrosion and provide sound deadening. Can be applied to bare or primed metal. For painting, let dry for 30 minutes at room temperature or greater than 60 degrees.</p>
Part Number	08874	08881	08882
UPC	0-00-51135-08874-6	0-00-51135-08881-4	0-00-51131-08882-5
Product Name	3M™ Rucker Schutz™ Coating	3M™ Undercoating	3M™ Undercoating
Container Volume	1 Quart	16 oz	17 oz
Color	Beige	Black	Black
Packaging	6 per case	6 per case	6 per case
	08883	08949	08964
Description	 <p>A tough, high-performance rubberized aerosol undercoating. Provides rust-proofing and sound deadening for a variety of applications, including fenders, quarter panels, door panels, repaired sections, welded joints, hoods, and decklids.</p>	 <p>Paintable, tough, beige-colored coating designed for use as a rocker panel chip-resistant protective surface. Use wherever stone chip protection is needed. Must be applied over a 2K epoxy primer. Use with 08801 applicator gun.</p>	 <p>Tough, fast drying, paintable, rubberized undercoating material that effectively protects and sound deadens door skins, quarter panels, wheel wells, frame rails, trunks and fenders. Use with 08801 applicator gun.</p>
Part Number	08883	08949	08964
UPC	0-00-51131-08883-2	0-00-51135-08949-1	0-00-51135-08964-4
Product Name	3M™ Rubberized Undercoating	3M™ No Cleanup Rocker Gard™ Coating	3M™ No Cleanup High Coverage Body Schutz™ Coating
Container Volume	19.7 Fluid Ounce (US)	22 fl oz	22 Fluid Ounce (US)
Color	Black	Tan	Black
Packaging	6 per case	6 per case	6 per case

## Expandable Foams

### Expandable Foams




Container Volume 200 Millilitre

Packaging 6 per case

	08458	08463
Description	 Two part urethane which foams in place to fill posts, pillars, and automotive body cavities. Use with the 08117 applicator	 Two part urethane which foams in place; designed to replace flexible foams found in OEM applications such as trunks, door cavities, door skins, roof beams, etc.
Part Number	08458	08463
UPC	0-00-51135-08458-8	0-00-51131-08463-6
Product Name	3M™ Rigid Pillar Foam	3M™ Flexible Foam
Color	Yellow/Brown	Black/Brown







## Vibration Isolation

### Vibration Isolation

	04274	08360	08361
Description	 Ideal 2-part urethane product for replacing factory NVH (Noise, Vibration & Harshness) sealants and foams. Can be used for large installations. Remains very soft, yet sturdy and will not degrade. 60 minute work time.	 High solids seam sealer ideal for sealing interior and exterior automotive and RV seams and joints. Adheres well to primed metal and painted surfaces. Can be smoothed to a featheredge and/or brushed. Tack free and paintable in 30 minutes.	 High solids seam sealer ideal for sealing interior and exterior automotive and RV seams and joints. Adheres well to primed metal and painted surfaces. Can be smoothed to a featheredge and/or brushed. Tack free and paintable in 30 minutes.
Part Number	04274	08360	08361
UPC	0-00-51131-04274-2	0-00-51131-16830-5	0-00-51131-16831-2
Product Name	3M™ NVH Dampening Material	3M™ Urethane Seam Sealer	3M™ Urethane Seam Sealer
Container Volume	200 Millilitre	310 Millilitre	310 Millilitre
Color	Black/Clear	White	Gray
Packaging	6 per case	6 per case	6 per case

## Vibration Isolation

### Vibration Isolation (continued)

	08364	08369	08370
Description	 <p>High solids seam sealer ideal for sealing interior and exterior automotive and RV seams and joints. Adheres well to primed metal and painted surfaces. Can be smoothed to a featheredge and/or brushed. Tack free and paintable in 30 minutes. Beige in color.</p>	 <p>High quality, heavy-bodied, general purpose, moisture-curing seam sealers that are designed for interior and exterior body joints. Adheres well to primed surfaces except acrylic lacquer. Tack free in 30 minutes and immediately paintable up to 72 hours. Use with 3M™ Flexible Package Applicator Gun, PN08398.</p>	 <p>High quality, heavy-bodied, general purpose, moisture-curing seam sealers that are designed for interior and exterior body joints. Adheres well to primed surfaces except acrylic lacquer. Tack free in 30 minutes and immediately paintable up to 72 hours. Use with 3M™ Flexible Package Applicator Gun, PN08398.</p>
Part Number	08364	08369	08370
UPC	0-00-51135-08364-2	0-00-51135-08369-7	0-00-51135-08370-3
Product Name	3M™ Urethane Seam Sealer	3M™ MSP Seam Sealer	3M™ MSP Seam Sealer
Container Volume	310 Millilitre	310 Millilitre	310 Millilitre
Color	Beige	White	Gray
Packaging	6 per case	6 per case	6 per case
	08578	08840	34274
Description	 <p>Soft non-hardening caulking material in one foot lengths for use in all types of seams, joints and openings. This product is easily thumbed into place and smoothed with a finger. It may be painted immediately.</p>	 <p>3M™ Sound Deadening Pads suppress noise and vibration</p>	 <p>Ideal 2-part urethane product for replacing factory NVH (Noise, Vibration &amp; Harshness) sealants and foams. Can be used for large installations. Remains very soft, yet sturdy and will not degrade. 60 minute work time.</p>
Part Number	08578	08840	34274
UPC	0-00-51135-08578-3	0-31-34375-38543-5	0-00-51131-34274-3
Product Name	3M™ Strip Calk	3M™ Sound Deadening Pads	3M™ NVH Dampening Material
Container Volume			47.3 Millilitre
Color	Black		
Packaging	60-1 ft Strips per box 12 boxes per case	10 per case	6 per case



## Index by Product Number

Product Number	Page
02576 .....	5
04274 .....	8
08188 .....	5
08190 .....	5
08193 .....	5
08194 .....	5
08360 .....	8
08361 .....	8
08364 .....	9
08369 .....	9
08370 .....	9
08374 .....	6
08458 .....	8
08463 .....	8
08578 .....	9
08801 .....	5
08804 .....	6
08840 .....	9
08864 .....	6
08874 .....	7
08881 .....	7
08882 .....	7
08883 .....	7
08949 .....	7
08964 .....	7
08966 .....	5
08991 .....	5
08997 .....	6
34274 .....	9
38191 .....	6
38193 .....	6