



Dual Lock™ Reclosable Fastener SJ3872

Product Data Sheet

August 2018
Supersedes: July 2010

Product Description

3M™ Dual Lock™ Reclosable Fastener SJ3872 has a high strength modified acrylic adhesive.

Key Features

- Stem density: 170 stems/in² = 26 stems/cm²
- Closure cycle life > 1 000
- Mushroom shaped stems snap in place to ensure fastener is engaged
- Good initial adhesion
- Quick and easy to install
- Durable

Physical Properties

Type	SJ3872
Adhesive Type	Modified Acrylic Foam Adhesive
Tape Colour	Black
Backing	Black polypropylene
Stems	Black polypropylene
Release Liner	Red Polyolefin
Engaged Thickness <small>acc ASTM D3652-01</small>	6 mm

Performance Characteristics

Type	SJ3872
90 ° Peel adhesion to Stainless Steel acc. to ASTM D3330-04, 90 ° peel angle @ RT, after 72h @ RT dwell	43 N/cm
90 ° Peel adhesion to Stainless Steel acc. to ISO ASTM D3330-04, 90 ° peel angle @ RT, after 72h @ RT dwell and after 10d @ 38 °C & 98 % rH	27 N/cm
Dyn. Tensile Engagement Strength acc. to ASTM D897-08, tested @ RT	19 N/cm ²
Dyn. Tensile Disengagement Strength acc. to ASTM D897-08, tested @ RT	42 N/cm ²
Dynamic Shear – Max. Force Acc. to ASTM D3654-06 to stainless steel	7 N/cm ²
Static Shear Strength Stainless Steel acc. to ASTM D3654-06, after 72h @ RT dwell (Holds minimum 155 g/cm ² for 10.000 minutes)	23°C – 1000 g
Static Shear Strength Stainless Steel acc. to ASTM D3654-06, after 72h @ RT dwell (Holds minimum 77.5 g/cm ² for 10.000 minutes)	85°C – 500 g
Permanent static load Dead load has to be supported accordingly in order to prevent excessive creep.	10 N/60 cm ²

Application Ideas

- Access panels on exercise equipment
- Attaching accessories to computer monitors
- Decorative trim attachment
- Kick plates on office partitions
- Fastening of headliner, instrument panel, control boxes and door panels

Additional Performance Characteristics

Washing and Dry Cleaning:

The adhesive present on these Dual Lock products typically makes them unsuitable to washing or dry cleaning processes

Attachment Techniques

Pressure Sensitive Adhesive attachment:

The fasteners and substrate surfaces should have equilibrated for a minimum of 1 hour at temperatures of 20 °C or greater before application. Generally, this adhesive backed fastener should be applied to surfaces that are smooth, dry and free of oils, mould release agents or other surface contaminants.

The substrate surface should be cleaned to remove any surface contaminants with an appropriate cleaning method for the customer's substrate, type and quantity of surface contaminants that need to be removed.

Note: Be sure to follow all government regulations and the manufacturer's precautions and directions for use when using solvents or other cleaning methods.

After the substrate has been cleaned and dried, the liner is removed from the fastener's adhesive and without touching the adhesive, the fastener's adhesive is applied to the surface using light finger pressure. The fastener can then be rolled down, to increase contact of the adhesive with the substrate's surface, by one of two methods. Extra care must be exercised when rolling down 3M™ Dual Lock™ Reclosable Fasteners to prevent bending of the stems which can compromise the closure strength.

The pressure-sensitive adhesive bonds to the substrate on contact and parts can be handled immediately. Adhesive bond strength increases with time, pressure and temperature.

A minimum of one hour dwell is recommended before applying a load or disengaging assembled parts. Recommended time to achieve maximum bond strength is 24 hours.

Storage & Shelf Life

Store at 16 °C – 25 °C and 40 – 65 % relative humidity in its original box. The product can be stored up to 24 months after production.

Note: The shelf life may be shortened if the original packaging is not properly sealed or stored in an environment with high temperatures or humidity.

For Additional Information

To request additional product information or to arrange for sales assistance, call.....

Address correspondence to: 3M

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark of the 3M Company.

3M United Kingdom PLC

2M Centre, Cain Road,
Bracknell
RG12 8HT
United Kingdom

3M Svenska AB

Herrjärva torg 4
170 67 Solna
Sweden

3M Eesti OÜ

Pärnu mnt. 158
11317 Tallinn
Estonia

3M Ireland Ltd

The Iveagh Building, 3rd Floor
The Park, Carrickmines 18
Ireland

3M a/s

Hannemanns Allé 53
DK-2300 Copenhagen S.
Denmark

3M Latvia SIA

K.Ulmaņa gatve 5
Rīga, LV-1004
Latvia

3M Belgium bvba/sprl

Hermeslaan 7
1831 Diegem
Belgium

3M Norge AS

Tærudgata 16
2004 Lillestrøm
Norway

3M Lietuva UAB

A.Goštauto g. 40
Vilnius LT- 03163
Lithuania

3M Nederland B.V.

Molengraaffsingel 29
2629 JD Delft
The Netherlands

Suomen 3M Oy

Keilaranta 6
02150 Espoo
Finland