

IJ8150

Product Description

- For Solvent, UV and Latex Inkjet Printing and Screen Printing
- 2-mil optically clear, vinyl film

Product Features

- Pressure-sensitive adhesive
- Conforms to simple curves and mild compound curves (as found on vehicle windows)
- Removable without heat from most surfaces (within the Warranty Period)
- Expected Performance Life of 7 years (unwarranted period for unprinted film with no graphic protection, applied to a flat, vertical, outdoor surface)

Recommended Types of Graphics and End Uses

- Building windows and dividers, interior and exterior
- Non-regulated vehicle and bus windows

Recommended Compatible Products

See [3M.com/graphicswarranties](https://www.3m.com/graphicswarranties) for a complete list of compatible products that are approved by 3M for use with the base film covered in this Bulletin and used for the creation of a graphic that may be eligible for the 3M™ MCS™ Warranty or 3M Performance Guarantee.

Graphic Protection

- [3M™ Scotchcal™ Gloss Overlamine 8518](#)
- [3M™ Scotchcal™ Gloss Overlamine 8528](#) with horizontal vehicle warranty
- [3M™ Envision™ Gloss Wrap Overlamine 8548G](#) with horizontal vehicle warranty
- [3M™ Wrap Overlamine Series 8900](#)
- [3M™ Scotchcal™ Gloss Optically-Clear Overlamine 8914](#)
- [3M™ Screen Print Gloss Clear 1920DR](#)
- [3M™ Screen Print UV Gloss Clear 9740i](#)
- [3M™ Screen Print Low Gloss Clear 9730UV](#)
- [3M™ Screen Print UV Gloss Clear 9800CL](#)

Application Tapes

See [3M Instruction Bulletin AT-1](#) to determine what application tape is recommended for the film or finished graphic.

Other Products

- [3M™ Edge Sealer 3950](#)
- [3M™ Edge Sealer Tape 8914](#)

Certificate of 3M™ MCS™ Warranty

Graphic manufacturers who produce digitally printed graphics made with all 3M Graphics Products, including 3M Ink purchased through a qualified 3M Distributor or 3M Printing Partner, may register to be recognized with a Certificate of 3M™ MCS™ Warranty. Only graphic manufacturers having a current Certificate of 3M™ MCS™ Warranty are eligible to extend this warranty to their customers.

Quick Links

- [3M Graphics Warranties](#)
- [Technical Information Selector](#)
- [Safety Data Sheets \(SDS\)](#)
- [Flammability \(ASTM E84 Reports\)](#)
- [Videos](#)

Some of these links lead to web-based resources that are not product-specific.



Characteristics

These are typical values for unprocessed product. Processing may change the values.

Physical Characteristics

Characteristic	Value
Material	Cast vinyl
Film Color	Optically-clear
Thickness	Without Adhesive: 2 mil (0.05 mm) With Adhesive: 3-4 mil (0.08-0.10 mm)
Adhesive	Pressure-sensitive
Adhesive Color	Clear
Liner	Transparent synthetic
Adhesion, Typical 24 hours after application	ABS 4–5 pounds/inch (0.72–0.89 kg/cm) Acrylic enamel 3–4 pounds/inch (0.54–0.72 kg/cm) Aluminum, anodized 7–8 pounds/inch (1.26–1.43 kg/cm) Aluminum, etched 5–6 pounds/inch (0.89–1.08 kg/cm) Chrome 4–5 pounds/inch (0.72–0.89 kg/cm) Fruehauf pre-painted panels 3–5 pounds/inch (0.54–0.89 kg/cm)
Tensile Strength	5 pounds/inch at 73 °F (0.9 kg/cm at 23 °C)
Chemical Resistance	Resists mild alkalis, mild acids, and salt Excellent resistance to water (does not include immersion) Resists occasional fuel spills
Flammability	Go to the online Product Catalog at 3M.com/graphics or Call 3M at 1-800-328-3908

Application Characteristics

Characteristic	Value
Finished Graphic Application Recommendation	Surface type: Flat, simple curves, mild compound curves Substrate type: Transparent substrates such as acrylic, glass, and polycarbonate Application method: Wet (preferred) Application temperature (air and substrate): 50 °F - 100 °F (10 °C - 38 °C)
Applied Shrinkage	0.015 inches (0.4 mm)
Temperature Range After Application	-65 to +150 °F (-51 to +66 °C) (not for extended periods of time at the extremes)
Graphic Removal	Removable without heat from most substrates within the Warranty Period at 50 °F (10 °C) minimum (air and substrate). 3M makes no claims as to the ease or speed of removal. See 3M Instruction Bulletin 6.5 for removal techniques.

Warranty Information

Warranty Coverage Overview

The warranty coverage for eligible graphics is based on the user both reading and following all applicable and current 3M Graphics Product and Instruction Bulletins. The warranty period for eligible graphics is as stated in the 3M Graphics Warranties Matrices at the time that the film was purchased. Information found at [3M.com/graphicswarranties](https://www.3m.com/graphicswarranties) includes:

- [3M Graphics Warranties Bulletin](#)
 - This bulletin contains information on limitations and exceptions, and warranty period reductions for 3M Graphics Warranties. The warranty period may be reduced and stipulations may apply for certain constructions, applications, and graphic exposures as covered in this Bulletin.
- [3M Graphics Warranties Selector](#)
 - Use this selector to search for your vertical warranty period by product type, ink type, film name, and/or ink/printer platform.
- [U.S. Desert Southwest Region Map](#)
 - Use this map of hot, arid desert areas to determine if you are subject to reduced warranted durabilities.

The warranties set forth in this Bulletin are made in lieu of all other express or implied warranties, including any implied warranty of merchantability, fitness for a particular purpose, or arising out of a course of dealing, custom, or usage of trade.

3M Basic Product Warranty

3M Graphics Products are warranted to be free of defects in materials and manufacture at the time of shipment and to meet the specifications stated in its applicable 3M Graphics Product Bulletin and as further set forth in the [3M Graphics Warranties Bulletin](#).

Limited Remedy

The limited remedy applicable to each warranty is addressed in the 3M Graphics Warranties Bulletin found at [3M.com/graphicswarranties](https://www.3m.com/graphicswarranties).

Limitation of Liability

Except where prohibited by law, 3M SHALL NOT UNDER ANY CIRCUMSTANCES BE LIABLE TO PURCHASER OR USER FOR ANY DIRECT (EXCEPT FOR THE LIMITED REMEDY PROVIDED IN THE 3M GRAPHICS WARRANTIES BULLETIN), INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES (INCLUDING, BUT NOT LIMITED TO, LABOR, NON-3M MATERIAL CHARGES, LOSS OF PROFITS, REVENUE, BUSINESS, OPPORTUNITY, OR GOODWILL) RESULTING FROM OR IN ANY WAY RELATED TO 3M'S GRAPHICS PRODUCTS, SERVICES, or THIS BULLETIN. This limitation of liability applies regardless of the legal or equitable theory under which such losses or damages are sought.

Additional Limitations

Additional warranty limitations may apply. Please see the 3M Graphics Warranties Bulletin at [3M.com/graphicswarranties](https://www.3m.com/graphicswarranties) for information on reduced warranties for other exposures, limitations of liability, and additional warranty terms and limitations.

Factors that Affect Graphic Performance Life

The actual performance life of a graphic is affected by:

- the combinations of graphics materials used.
- complete ink drying or curing.
- selection, condition and preparation of the substrate.
- surface texture.
- application methods.
- angle and direction of sun exposure.
- environmental conditions.
- cleaning or maintenance methods.

Graphics Manufacturing

CAUTION

Before using any equipment, always read the manufacturer's instructions for safe operation.

Inkjet Printing

Always read and follow the ink manufacturer's written instructions on usage.

IMPORTANT NOTE

3M recommends that all print jobs be preceded by a one-panel test installation and inspection, at the final customer location, to ensure customer acceptance. Optically-clear films can highlight minor imperfections, created during manufacture or installation of the graphic, which may not be visually apparent with the film on its original liner.

Total Ink Coverage

The maximum recommended total ink coverage for this film is:

- **270%** when printed with all approved 3M solvent inkjet inks.
- **280%** when printed with all approved 3M UV inkjet inks.
- **280%** when printed with all approved 3M latex inkjet inks.

Do not exceed the recommended total ink coverage for the ink series used on this product. Having too high a total physical ink amount on the product results in media characteristic changes, incomplete drying, overlamine lifting, and/or poor graphic performance. For additional details about total ink coverage, refer to the 3M Product and Instruction Bulletin for 3M inks or the [3M Performance Guarantee Matrix](#) for OEM inks.

Completely Dry Graphics

IMPORTANT NOTE

Incomplete drying or curing can result in graphic failure including curling, increased shrinkage and adhesion failure, which are not covered under any 3M Graphic Warranty.

See the specific ink's 3M Product and Instruction Bulletin for more details.

Cutting

See [3M Instruction Bulletin 4.1](#) for Sheeting, Scoring and Film Cutting details.

Graphic Protection

Graphic protection may improve the appearance, performance and durability of the graphic. Click on the graphic protection options listed in Product Bulletin for more information.

IMPORTANT NOTE

During installation, scratches may occur on films without graphic protection.

Application Tapes

There are two types of application tapes. See [3M Instruction Bulletin AT-1](#) to determine what application tape is recommended for the film or finished graphic.

Premasking Tape

Increases stiffness during application while preventing stretching and damage. Use when little or no liner is exposed. See [3M Instruction Bulletin 4.3](#) for complete details.

Prespacing Tape

Holds cut and weeded letters or graphics in place during application and after removing the film liner, while preventing stretching and damage. Use when large amounts of liner are exposed. See [3M Instruction Bulletin 4.3](#) for complete details.

Application and Installation

In addition to other 3M Bulletins specified in this document, the following Bulletins provide details that you may need to successfully apply a graphic.

- [3M Instruction Bulletin 4.22](#) Lamination Basics for Inkjet Printed Graphics
- [3M Instruction Bulletin 5.36](#). Application Techniques for Automobiles, Vans and Buses. Complete the 3M Pre-Installation Inspection Record found in this Instruction Bulletin prior to manufacturing or applying a graphic to an automobile, van, or bus.
- [3M Instruction Bulletin 5.37](#) A Guide to Understanding and Applying Graphics to Common Smooth and Textured Wall Surfaces
- [3M Instruction Bulletin 5.42](#). Application, Special Considerations for Watercraft. Complete the 3M Pre-Installation Inspection Record found in this Instruction Bulletin prior to manufacturing or applying a graphic to a watercraft.
- [3M Instruction Bulletin 5.5](#) Application, General Procedures for Interior and Exterior Dry Application
- [3M Instruction Bulletin 6.5](#) Storage, Handling, Maintenance, and Removal of Films and Sheetings

Stretchability

Many finished graphic constructions can be stretched without primer or relief cuts and maintain lift resistance.

- For Automobiles, Vans and Buses, see [3M Instruction Bulletin 5.36](#) for details and exceptions.
- For Straight trucks, semi-trucks and semi-trailers, see [3M Instruction Bulletin 5.4](#) for details and exceptions.

3M™ Tape Primer 94

3M recommends that where the film will be stretched, particularly on the edges of the film, use primer to maximize a graphic's bond to its substrate.

Maintenance and Cleaning

Use a cleaner designed for high-quality painted surfaces. The cleaner must be wet, non-abrasive, without solvents, and have a pH value between 3 and 11 (neither strongly acidic nor strongly alkaline). See [3M Instruction Bulletin 6.5](#) for details.

Removal

Removal may require heat. 3M makes no claims as to the ease or speed of removal. See [3M Instruction Bulletin 6.5](#) for details.

Shelf Life, Storage and Shipping

Shelf Life

The shelf life is **never more than 3 years** from the date of manufacture on the original box.

If you process the film, the shelf life is changed to **1 year** from the processing date, but not later than the 3 year maximum from the manufacturing date.

Storage Conditions

- 40° to 100 °F (4° to 38 °C)
- Out of sunlight
- Clean, dry area
- Original container
- Bring the film to room temperature before use

Shipping Finished Graphics

Flat, or rolled printed-side-out on 6 inch (15 cm) or larger core. This helps prevent the application tape, if used, from popping off.

Health and Safety

CAUTION

When handling any chemical products, read the manufacturers' container labels and the Safety Data Sheets (SDS) for important health, safety and environmental information. To obtain SDS sheets for 3M products go to [3M.com/SDS](https://www.3m.com/SDS), or by mail or in case of an emergency, call 1-800-364-3577 or 1-651-737-6501.

When using any equipment, always follow the manufacturer's instructions for safe operation.

Commercial Solutions

3M Center, Building 220-12E-04
St. Paul, MN 55144

1-800-328-3908
[3M.com/Graphics](https://www.3m.com/Graphics)

© 3M 2020. All rights reserved.
3M, MCS, Envision, Scotchcal, and Scotchgard are trademarks of 3M. Used under license in Canada.
All other trademarks are property of their respective owners.
Revision C, March 2020 Please recycle.

