



Scotch-Weld™

Super 77™ Cylinder Spray Adhesive

Technical Data

June, 2008

Product Description

3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive is an industrial grade, versatile bulk mist spray adhesive designed for lightweight applications. Formulated with high tack, high coverage, fast drying and long bonding range. The adhesive is packaged in convenient, portable, no maintenance aerosol cylinders.

Features

- High solids, high coverage adhesive.
- Fast drying formulas with aggressive tack to help speed assembly.
- Uniform mist spray pattern, very low soak in.
- Good heat and moisture resistance to help protect bonds.
- Temporary and permanent lightweight bonds on substrates like papers, cardboard, fabrics, foams, wood, metal, glass and most plastics.
- One or two surface bonding capabilities.

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Base:	Synthetic Elastomer	
Solids Content of Adhesive – propellant removed (by wt.):	36.5%	
Solids Content – aerosol (by wt.):	27.4%	
Color(s):	Clear, Red	
Volatile Organic Compounds (VOC):	534 g/L	
Hazardous Air Pollutants (HAPS) % wt. (calculated):	4-5%	
MACT Compliant:	Yes	
Flammability:	Solvent	Propellant
	Yes	Yes

3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive

Available Sizes and Expected Coverage

Cylinder Size Availability	Cylinder Adhesive Net. Wt. (lbs.):	Sq. Ft. Coverage per Wet lb. of Adh @ 0.5 gm./sq. ft. (dry wt.):	Sq. Ft. Coverage @ 0.5 gm./sq. ft. (dry wt.):	Sq. Ft. Coverage @ 1 gms./sq. ft. (dry wt.):
Large - Disposable	29.3	249	7,290	3,645

Handling/Application Information

Surface Preparation:

For best results, all surfaces to be bonded must be clean, dry and free from dirt, dust, oil, loose paint, wax or grease, etc.

Application Temperature:

For best results, the temperature of the adhesive and the surfaces being bonded should be between 60°-80°F (16°-27°C). Temperatures outside this range may affect the bonding range and sprayability.

Equipment Setup:

Attach the larger flare fitting end to the spray applicator and tighten the nut securely. Check to see that the applicator gun trigger stop/adjusting nut is fully locked against the trigger. Attach the other end of the hose, a smaller flare fitting, to the cylinder valve and tighten securely.

Directions For Use:

- 1.) Shake well before use.
- 2.) Slowly open the cylinder valve and inspect the connections for any leaks. Tighten if needed.
- 3.) Fully open the valve.
- 4.) Unscrew the trigger stop/adjusting nut away from the trigger 3-4 turns and spray a test pattern. For more adhesive output, continue to screw the nut away from the trigger. For less adhesive output, screw the nut back towards the trigger.
- 5.) Hold the applicator 6-12 inches away from the surfaces to be sprayed and apply a uniform coat of adhesive. (The smaller the spray pattern chosen in step 3, the closer the applicator gun will need to be to the surface and vice versa for larger patterns.)
- 6.) Apply 1-3 even coats of adhesive. (This will depend on the needed coverage for the bonding application.)
- 7.) Allow adhesive to dry until tacky and then apply sufficient pressure to ensure complete contact.

Note: Test for tackiness by gently touching the adhesive with your knuckle. If the adhesive transfers to your skin, it is too wet. If the adhesive is aggressively tacky and does not transfer to your skin, it is ready to bond. If the adhesive is too dry or only has a very light tack, it is too dry and another coat of adhesive should be applied to at least one of the surfaces.

3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive

Handling/Application Information (continued)

Dry Time (minutes):	< 1
Open Time (minutes):	10 seconds to 15 seconds (one surface bonding) 1-30 minutes (two surface bonding)

One Surface Bonding: Less demanding applications. Spray the more non-porous surface and bond within Open Time (see Open Times in above table).

Two Surface Bonding: Permanent, more demanding applications. Spray both surfaces and bond within Open Time (see Open Times in above table).

Equipment Shut Down: For storage – screw the trigger stop/adjusting nut all the way to the trigger lock position. Turn the valve on the cylinder to the closed position. Replace nozzle.

Application Equipment Suggestions for Cylinder

Description	3M ID Number
3M™ Scotch-Weld™ Cylinder Adhesive Applicator (includes 9501 tip)	62-9880-9930-5
Scotch-Weld Cylinder Adhesive Applicator H (includes 4001 tip) – this applicator is for use with 3M™ Scotch-Weld™ Cylinder 94 CA	62-9880-9950-3
Scotch-Weld Cylinder Adhesive Applicator EX (with 18" Extension and 9501 Tip)	62-9880-9940-4
Scotch-Weld Cylinder Adhesive 6 Foot Hose	62-9880-0006-3
Scotch-Weld Cylinder Adhesive 12 Foot Hose	62-9880-0012-1
Scotch-Weld Cylinder Adhesive 25 Foot Hose	62-9880-0025-3
Scotch-Weld Cylinder Adhesive 50 Foot Hose	62-9880-0050-1
Scotch-Weld Cylinder Adhesive 250050 Spray Tip	62-9880-8133-7
Scotch-Weld Cylinder Adhesive 4001 Spray Tip	62-9880-4001-0
Scotch-Weld Cylinder Adhesive 650050 Spray Tip – this nozzle has half the output of the 6501 nozzle	62-9880-8173-3
Scotch-Weld Cylinder Adhesive 6501 Spray Tip	62-9880-6501-7
Scotch-Weld Cylinder Adhesive 730154 Spray Tip – this nozzle minimizes dripping on 3M™ Scotch-Weld™ Cylinder 60 CA	62-9880-7301-1
Scotch-Weld Cylinder Adhesive 9501 Spray Tip	62-9880-9501-4
Scotch-Weld Cylinder Adhesive QSS Spray Tip – this nozzle is needed for 3M™ Scotch-Weld™ Cylinder 70	62-9880-8148-5
Scotch-Weld Cylinder Adhesive T-Fitting	62-9880-8348-1
Scotch-Weld Cylinder Adhesive Hose Swivel	62-9880-7948-9

Applicator Suggestion: 3M™ Scotch-Weld™ Cylinder Adhesive Applicator (62-9880-9930-5) is suggested for 3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive.

3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive

Application Equipment Suggestions for Cylinder (continued)

Nozzle Suggestions:

	250050	4001	650050	6501	9501
Spray Pattern (inches): (see *Note below)	1-4	2-6	3-8	3-8	5-12
Applications:	Restricted output (General)	General laminating	Restricted output (General)	General laminating	General laminating

***Note:** Spray pattern widths will vary between products, due to formulation and pressure differences.

Spray Pattern Adjustments: Unscrew the trigger stop/adjusting nut away from the trigger 3-4 turns and spray a test pattern. For more adhesive output and a wider spray pattern, continue to unscrew the nut away from the trigger. For less output and smaller spray pattern, screw the adjusting nut back towards the trigger. Hold the applicator 6-12 inches away from the surfaces to be sprayed and apply a uniform coat of adhesive. (The smaller the spray pattern, the closer the applicator gun will need to be to the surface). The mist spray is a continuous triangular pattern that gets larger as you continue to move the applicator from the surface being sprayed.

Typical Adhesive Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Overlap Shear Strength: 1 square inch bonds tested at 2 inches per minute separation rate at 75°F (24°). Results are reported in PSI - pounds per square inch.

Substrate Bonded	3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive
ABS to ABS (2 surface adhesive bond)	165
ABS to ABS (1 surface adhesive bond)	132
Acrylic to Acrylic (2 surface adhesive bond)	158
Aluminum to Aluminum (2 surface adhesive bond)	142
Birch to Birch (2 surface adhesive bond)	215
Birch to Birch (1 surface adhesive bond)	200
Galvanized to Galvanized (2 surface adhesive bond)	188
Galvanized to Galvanized (1 surface adhesive bond)	140
Polyethylene to Polyethylene (2 surface adhesive bond)	107
Polypropylene to Polypropylene (2 surface adhesive bond)	176
FRP (Fiber Reinforced Plastic) to FRP (2 surface adhesive bond)	114

Tensile Strength Failure Temperature: 2 square inch bonds tested with 30 grams hanging in tensile. Temperature is held for 10 minutes and ramped at 10°F increments, until complete failure.

3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive	Failure Temperature (°F)
77:	190

3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive

Cold Weather Warning

How Cold Weather Affects Cylinders:

- 1.) The bulk adhesive in the cylinder will thicken as temperatures get colder.
- 2.) The propellants used will decrease in pressure and, therefore, effectiveness:
 - a. Liquefied hydrocarbon propellants will condense and reduce the effective amount of available pressure on the cylinder. This will adversely affect the spray pattern and, consequently, the overall performance of the adhesive.
 - b. Compressed gas propellants will shrink dramatically in cold weather causing the system to have much less available force to push a thicker bulk adhesive out. The effect will be improper, less controlled spray properties with longer dry times needed.

How to Eliminate Cold Weather Problems:

- 1.) Store the cylinders in a controlled environment with temperatures between 60°-80°F (16°-27°C).
- 2.) Keep cylinders off of cold concrete floors and away from outside walls.
- 3.) Use heat belts or blankets, approved for use with flammable adhesives, to control the temperature of the cylinders.
- 4.) Allow additional time for solvents and propellants to flash off, when temperatures are below 60°F (16°C).

If Cylinders Get Too Cold:

If cylinders arrive cold or have been exposed to temperatures that are causing poor spray properties, move to an area that is heated above 70°F (21°C). The larger the cylinder, the longer it will take for the temperature to equilibrate. Mini (~11 lb.) and Large (~30 lb.) cylinders can be shaken or submerged in hot water to accelerate the warming process. Once the cylinders equilibrate back to at least 60°F (16°C), the products will perform as normal.

3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive

Trouble Shooting – Applicator/Hose Clog

Applicator – Hose Clog Checklist for 3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive.

If the system sprays poorly or won't spray at all: The sequence below runs through a complete clog into the cylinder valve. If at any time during the sequence the problem is resolved, stop, clean the needed parts, put the system back together, and you are finished.

1. Make sure the cylinder is not empty.
2. Make sure the cylinder valve is open.
3. Close the applicator trigger stop adjusting nut and clean the nozzle tip. (Does it spray now?)
4. Take off the nozzle and try spraying. (Does it spray now?) Clean the nozzle.
5. Shut off the cylinder valve, CAREFULLY and SLOWLY – loosen the applicator gun/hose connection and look for adhesive to squirt out. If adhesive starts to leak out, allow it to slowly continue to do so until it stops. (This will be a little messy, but you will need to bleed off the pressurized adhesive to clean the applicator gun.) The applicator gun has a clog at the valve, stem or inlet area and needs to be cleaned.
6. If nothing leaks out after fully loosening the applicator gun, CAREFULLY remove applicator gun, realizing that the hose may be clogged but could be full of adhesive and pressure depending on where the clog is. (Secure the open end of the hose into a bucket in case the clog releases and the system flushes.)
7. CAREFULLY and SLOWLY loosen the hose connection at the cylinder valve. Look for adhesive to squirt out. If adhesive starts to leak out, allow it to slowly continue to do so until it stops. (This will be a little messy, but you will need to bleed off the pressurized adhesive in the hose). Clean or replace the hose.
8. With everything now isolated from the cylinder, place a bucket in front of the cylinder valve and slowly open it to see if any adhesive comes out. If it does, put the cleaned system parts back together. If it does not, there is something wrong with the cylinder or cylinder valve and it should be returned.

Solvents that can be used for cleaning nozzle, applicator gun and inside of hose:
3M™ Adhesive Remover, Cyclohexane, Toluene, MEK.*

***Note:** When using solvents, extinguish all ignition sources, including pilot lights, and follow the manufacturer's precautions and directions for use.

3M™ Scotch-Weld™ Super 77™ Cylinder Spray Adhesive

Storage Store product at 60°-80°F (16°-27°C) for maximum storage life. Higher temperatures reduce normal storage life. Lower temperatures may cause increased viscosity of a temporary nature. Rotate stock on a “first in-first out” basis.

Shelf Life When stored at the recommended conditions in the original, unopened container, this product has a shelf life of 15 months from date of shipment.

Precautionary Information Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

Product Use All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Industrial Adhesives and Tapes Division

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M, Scotch-Weld and Super 77 are
trademarks of 3M Company.
Printed in U.S.A.
©3M 2008 78-9236-7169-3 (6/08)