

# 3M™ Double-Sided Tapes

## Scotch® ATG Adhesive System

*Quick and easy application of pressure sensitive adhesives*

With Scotch ATG adhesive applicators, a touch of the finger triggers quick, controlled application of a strip of Scotch ATG pressure sensitive adhesive transfer tape at the same time as the liner rewinds into the applicator. With 3M's advanced acrylic adhesive technology, you can bond, join, mount or laminate materials such as paper, plastics, metal, wood, foam and foils.

- Quick and easy to use
- Portable
- Adhesive only where it is required, no mess and no clean-up
- Thin and flexible bond lines



Product Number	Product Name	Features/Applications	Thickness (mm)	Adhesive Type	Temperature Resistance		Relative Adhesion		UV Resistance	Solvent Resistance	Standard Roll Format Equivalent Product
					Minutes/Hours	Days/Weeks	HSE <sup>1</sup>	LSE <sup>2</sup>			
924	General Purpose	Excellent adhesion to most papers and cards.	0.05	400 Acrylic	121°C	82°C	High	Med	Excellent	Good	9665
926	High Performance	High performance, sticks to most substrates. Excellent temperature and solvent resistance.	0.13	350 Acrylic	232°C	149°C	High	High	Excellent	Very Good	9485PC
928	Repositionable	Differential adhesive, removable on one side.	0.05	400/1000 Acrylic	80°C	50°C	Med/Low <sup>3</sup>	Low/Low <sup>3</sup>	Good	Fair	
969	High Tack	Excellent adhesion to most plastics.	0.13	300 Acrylic	121°C	82°C	High	High	Fair	Good	950
976	High Tack	Thinner version of 969.	0.05	300 Acrylic	121°C	82°C	High	High	Fair	Good	
987	General Purpose	Thinner version of 924.	0.04	400 Acrylic	121°C	82°C	High	Med	Excellent	Good	
700	ATG Tape Applicator	For applying ATG Tapes in 6mm <sup>4</sup> , 12.7mm and 19mm widths.									

Notes: 1. HSE - High Surface Energy Material. 2. LSE - Low Surface Energy Material. 3. First value is for side applied with applicator, second value is for side remaining exposed 4. 6mm adaptor available separately.



High tack Scotch® ATG Tape 969 bonds carpet samples to brochure card.



Scotch® ATG Tape 924 helps quickly mount pictures onto frames.



Scotch® ATG Tape is used for fast assembly of merchandising materials.